

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937405

Luminaire Tested: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937405
REPORT IS A COMBINATION OF REPORTS P933496 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 19802.7 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 186
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937405
CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	88	88	88	75	75	75	63	63	63	58			58
1	99	94	90	86	92	88	84	81	76	73	71	65	63	61	55	53	52	47			47
2	89	82	75	69	83	76	70	65	66	61	57	56	53	50	47	45	43	38			38
3	81	71	63	57	75	66	59	54	57	52	47	49	45	41	41	38	36	32			32
4	74	62	54	48	68	58	51	45	50	45	40	43	39	35	36	33	30	27			27
5	68	55	47	40	63	52	44	38	45	39	34	38	34	30	33	29	26	23			23
6	62	49	41	35	57	46	38	33	40	34	29	34	29	26	29	25	22	19			19
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19	17			17
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17	15			15
9	49	36	28	23	46	34	27	22	30	24	20	26	21	17	22	18	15	13			13
10	46	33	26	21	43	31	24	20	27	22	18	24	19	16	20	16	14	12			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4561	4561	4561
5°	4458	5273	6131
10°	4045	7688	10164
15°	3439	10047	12273
20°	2801	11646	12508
25°	2337	12190	12254
30°	1972	12270	12231
35°	1745	12069	12547
40°	1521	11808	12874
45°	1378	11618	12924
50°	1265	11447	12710
55°	1213	11196	12147
60°	1243	10709	11257
65°	1296	9966	10035
70°	1383	8698	8477
75°	1538	7098	6616
80°	1694	4929	4458
85°	1536	2620	2282

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 12924 cd/sqm



TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.8	1.0
10°-20°	845.4	4.3
20°-30°	1478.8	7.5
30°-40°	1903.6	9.6
40°-50°	2126.3	10.7
50°-60°	2036.5	10.3
60°-70°	1613.9	8.1
70°-80°	949.0	4.8
80°-90°	268.6	1.4
90°-100°	630.9	3.2
100°-110°	1658.6	8.4
110°-120°	1719.8	8.7
120°-130°	1379.5	7.0
130°-140°	1082.4	5.5
140°-150°	830.8	4.2
150°-160°	598.3	3.0
160°-170°	366.1	1.8
170°-180°	123.7	0.6
0°-30°	2514.9	12.7
0°-40°	4418.6	22.3
0°-60°	8581.3	43.3
0°-90°	11412.8	57.6
90°-120°	4009.2	20.2
90°-150°	7301.8	36.9
90°-180°	8390.0	42.4
0°-180°	19802.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1475	1475	1475	1475	1475	
5°	1437	1541	1736	1963	2034	133
15°	1076	1987	3348	4059	4187	300
25°	688	2252	3988	4163	4168	317
35°	465	2153	3755	3969	4125	290
45°	318	1716	3319	3803	3974	246
55°	228	1090	2817	3272	3362	207
65°	180	578	2091	2352	2385	179
75°	133	356	1148	1261	1266	139
85°	47	109	284	313	318	50
90°	9	24	66	33	33	10
95°	83	327	1087	560	381	93
105°	299	452	1834	2784	2597	317
115°	531	644	1469	2930	3344	524
125°	738	828	1336	2258	2663	656
135°	880	968	1294	1822	2066	681
145°	1021	1086	1278	1555	1676	639
155°	1154	1186	1278	1403	1444	530
165°	1245	1261	1278	1328	1345	351
175°	1294	1294	1286	1303	1303	123
180°	1294	1294	1294	1294	1294	



TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7	1474.7
2.5°	1474.7	1474.7	1484.1	1488.9	1498.3	1503.1	1512.6	1522.0	1550.5	1555.3	1564.7
5°	1436.7	1455.6	1517.3	1541.0	1607.4	1697.5	1735.5	1797.1	1925.1	1963.1	1986.7
7.5°	1379.8	1422.5	1574.3	1612.2	1778.1	2015.2	2114.8	2247.6	2451.5	2551.0	2631.6
10°	1289.8	1379.8	1650.1	1740.1	2010.4	2370.8	2555.7	2740.6	3048.9	3186.3	3238.6
12.5°	1190.2	1337.1	1730.7	1854.0	2242.8	2769.1	2992.0	3195.9	3546.8	3731.7	3760.1
15°	1076.3	1275.5	1806.5	1986.7	2489.4	3101.1	3347.5	3598.9	3926.1	4058.9	4092.0
17.5°	976.8	1228.1	1877.7	2067.3	2679.0	3399.8	3651.1	3859.7	4125.2	4215.3	4239.1
20°	853.5	1152.2	1925.1	2171.6	2878.2	3617.8	3859.7	4020.9	4201.1	4258.0	4267.4
22.5°	763.4	1071.6	1953.6	2209.6	3010.9	3750.7	3954.6	4082.5	4205.8	4224.8	4229.5
25°	687.5	981.5	1948.8	2252.2	3124.7	3831.3	3987.7	4082.5	4153.7	4163.1	4163.1
27.5°	616.4	882.0	1929.8	2261.8	3210.1	3850.2	3973.5	4039.8	4073.1	4092.0	4092.0
30°	554.8	787.1	1882.4	2242.8	3248.0	3831.3	3930.8	3964.0	3997.2	4025.6	4039.8
32.5°	507.3	697.0	1811.3	2204.9	3252.7	3783.8	3855.0	3874.0	3921.3	3987.7	4011.4
35°	464.7	606.9	1730.7	2152.7	3224.4	3708.0	3755.3	3774.4	3869.2	3968.8	4001.9
37.5°	422.0	540.5	1626.4	2062.6	3181.7	3617.8	3651.1	3684.3	3831.3	3949.8	3987.7
40°	379.3	483.6	1503.1	1963.1	3115.3	3508.9	3537.2	3589.5	3783.8	3921.3	3959.2
42.5°	346.1	436.3	1370.4	1858.8	3029.9	3385.6	3428.2	3504.1	3726.9	3874.0	3916.6
45°	317.7	388.8	1228.1	1716.5	2920.8	3257.5	3319.2	3423.5	3660.5	3802.8	3840.7
47.5°	289.3	355.7	1081.1	1569.5	2802.3	3129.5	3210.1	3328.6	3570.5	3708.0	3741.1
50°	265.5	322.4	934.1	1413.0	2674.3	2992.0	3086.8	3210.1	3456.6	3584.7	3627.4
52.5°	246.6	294.0	796.6	1256.5	2527.3	2849.7	2958.8	3086.8	3319.2	3442.4	3470.8
55°	227.6	270.3	678.1	1090.5	2375.5	2698.0	2816.6	2939.9	3167.4	3271.7	3290.7
57.5°	218.1	251.3	578.5	934.1	2214.3	2527.3	2660.0	2773.9	2987.2	3067.8	3086.8
60°	203.9	237.0	502.6	801.4	2038.9	2366.1	2479.9	2593.7	2773.9	2840.2	2854.5
62.5°	189.7	227.6	445.7	673.3	1858.8	2176.4	2290.2	2394.5	2546.3	2593.7	2612.7
65°	180.2	218.1	403.0	578.5	1673.8	1977.3	2091.0	2181.2	2304.5	2351.8	2361.3
67.5°	170.7	208.7	369.9	497.9	1488.9	1778.1	1863.4	1948.8	2043.7	2091.0	2095.8
70°	156.4	199.1	341.4	440.9	1299.2	1550.5	1621.6	1711.7	1787.6	1811.3	1825.5
72.5°	147.0	184.9	322.4	398.3	1104.8	1332.4	1398.8	1451.0	1517.3	1541.0	1541.0
75°	132.7	166.0	303.5	355.7	905.6	1090.5	1147.5	1199.6	1251.7	1261.3	1247.1
77.5°	118.5	147.0	260.8	298.7	706.5	863.0	910.4	938.9	981.5	991.0	995.7
80°	99.6	128.1	203.9	232.4	512.1	635.4	668.6	692.3	730.2	730.2	739.7
82.5°	75.8	99.6	147.0	166.0	346.1	436.3	464.7	478.9	502.6	502.6	502.6
85°	47.4	61.6	94.8	109.1	208.7	265.5	284.5	289.3	308.2	313.0	313.0
87.5°	23.7	33.2	61.6	66.4	109.1	137.5	137.5	147.0	147.0	142.2	137.5
90°	8.7	15.6	22.5	24.3	38.2	56.8	66.0	58.7	44.0	33.0	33.0
92.5°	34.7	93.8	152.9	167.7	235.6	326.3	371.7	325.8	234.0	165.0	158.5
95°	83.4	191.5	299.6	326.6	579.9	917.7	1086.6	969.7	735.7	560.2	540.3
97.5°	144.2	239.6	334.9	358.7	781.2	1344.4	1626.0	1552.0	1404.2	1293.3	1255.5
100°	191.1	277.6	364.1	385.6	854.4	1479.4	1791.9	1797.3	1808.1	1816.3	1771.1
102.5°	231.1	311.8	392.4	412.5	888.0	1521.9	1838.9	1933.0	2121.4	2262.7	2224.1
105°	298.8	367.2	435.4	452.5	912.9	1526.7	1833.6	2044.8	2467.2	2783.9	2763.1
107.5°	368.3	432.0	495.7	511.6	917.6	1458.8	1729.4	2024.0	2613.1	3054.8	3059.9
110°	415.2	472.7	530.2	544.6	910.6	1398.6	1642.5	1971.9	2630.4	3124.3	3145.9



TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	461.2	516.0	570.9	584.6	910.9	1346.0	1563.5	1900.5	2574.6	3080.1	3113.2
115°	530.7	581.2	631.9	644.5	919.2	1285.7	1468.8	1793.5	2442.8	2929.8	2975.8
117.5°	599.3	645.3	691.2	702.6	936.3	1247.8	1403.6	1696.6	2282.6	2722.1	2773.2
120°	639.3	682.6	725.7	736.6	950.3	1235.1	1377.6	1645.2	2180.7	2582.3	2631.9
122.5°	678.4	722.0	765.6	776.5	970.2	1228.5	1357.6	1598.6	2080.9	2442.5	2491.4
125°	738.3	778.1	817.9	827.8	997.1	1223.0	1335.9	1540.7	1950.3	2257.5	2302.6
127.5°	787.0	827.2	867.3	877.3	1024.1	1219.8	1317.7	1493.6	1845.2	2109.0	2147.0
130°	813.0	856.3	899.4	910.3	1043.7	1221.7	1310.7	1467.2	1780.3	2015.1	2050.2
132.5°	839.9	883.2	926.3	937.2	1059.6	1223.0	1304.6	1444.7	1725.0	1935.2	1966.7
135°	879.9	919.2	958.7	968.5	1077.1	1221.9	1294.2	1411.6	1646.3	1822.3	1849.4
137.5°	920.7	959.7	998.7	1008.4	1103.1	1229.3	1292.5	1391.7	1590.1	1738.9	1761.2
140°	954.5	990.4	1026.4	1035.3	1119.0	1230.6	1286.4	1372.1	1543.5	1672.0	1692.8
142.5°	980.6	1013.9	1047.0	1055.3	1132.4	1235.0	1286.4	1361.7	1512.2	1625.2	1643.0
145°	1020.6	1049.5	1078.5	1085.8	1149.8	1235.0	1277.7	1339.3	1462.5	1554.8	1568.4
147.5°	1060.6	1088.8	1117.0	1124.0	1175.3	1243.5	1277.7	1326.2	1423.0	1495.7	1506.9
150°	1086.6	1112.1	1137.6	1144.0	1188.5	1248.0	1277.7	1318.6	1400.4	1461.8	1470.9
152.5°	1113.5	1132.8	1152.1	1156.9	1197.2	1250.9	1277.7	1312.6	1382.5	1434.9	1441.7
155°	1153.5	1167.8	1182.1	1185.6	1216.3	1257.3	1277.7	1305.5	1361.1	1402.8	1407.4
157.5°	1183.0	1196.9	1210.8	1214.3	1235.4	1263.6	1277.7	1299.3	1342.5	1374.9	1378.1
160°	1203.0	1213.8	1224.7	1227.4	1244.2	1266.5	1277.7	1296.2	1333.3	1361.1	1363.0
162.5°	1223.0	1231.1	1239.1	1241.2	1253.3	1269.6	1277.7	1293.3	1324.6	1348.0	1349.8
165°	1244.7	1252.0	1259.3	1261.2	1266.7	1274.1	1277.7	1288.9	1311.2	1328.1	1329.9
167.5°	1264.6	1268.1	1271.6	1272.5	1277.2	1283.3	1286.4	1293.7	1308.3	1319.4	1320.1
170°	1277.7	1281.2	1284.7	1285.6	1285.8	1286.2	1286.4	1293.7	1308.3	1319.4	1319.4
172.5°	1284.6	1285.4	1286.2	1286.4	1286.4	1286.4	1286.4	1292.2	1303.8	1312.5	1311.8
175°	1294.2	1294.2	1294.2	1294.2	1291.6	1288.2	1286.4	1290.0	1297.4	1302.9	1302.9
177.5°	1294.2	1294.2	1294.2	1294.2	1292.2	1289.5	1288.2	1291.1	1296.9	1301.2	1300.4
180°	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2	1294.2



TEST NUMBER: P937405
CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1474.7	1474.7
2.5°	1574.3	1564.7
5°	2024.7	2034.2
7.5°	2726.4	2721.7
10°	3390.2	3432.9
12.5°	3874.0	3883.4
15°	4167.9	4186.8
17.5°	4281.7	4286.4
20°	4286.4	4277.0
22.5°	4234.3	4224.8
25°	4172.6	4167.9
27.5°	4115.8	4120.5
30°	4092.0	4106.2
32.5°	4092.0	4115.8
35°	4101.5	4125.2
37.5°	4096.8	4125.2
40°	4077.8	4111.0
42.5°	4025.6	4049.4
45°	3945.0	3973.5
47.5°	3840.7	3859.7
50°	3708.0	3726.9
52.5°	3542.0	3546.8
55°	3342.9	3361.8
57.5°	3129.5	3134.2
60°	2892.4	2906.6
62.5°	2641.1	2641.1
65°	2375.5	2385.1
67.5°	2100.6	2124.3
70°	1820.8	1825.5
72.5°	1545.8	1545.8
75°	1261.3	1266.0
77.5°	991.0	991.0
80°	735.0	739.7
82.5°	507.3	516.9
85°	317.7	317.7
87.5°	147.0	132.7
90°	33.0	33.0
92.5°	132.3	106.0
95°	460.8	381.4
97.5°	1104.2	952.9
100°	1590.9	1410.6
102.5°	2069.7	1915.3
105°	2680.1	2597.1
107.5°	3080.0	3100.0
110°	3232.4	3318.9



TEST NUMBER: P937405

CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	3246.0	3378.8
115°	3159.9	3344.1
117.5°	2977.4	3181.7
120°	2830.4	3028.8
122.5°	2687.1	2882.9
125°	2482.9	2663.1
127.5°	2299.1	2451.2
130°	2190.8	2331.4
132.5°	2092.5	2218.4
135°	1957.9	2066.4
137.5°	1849.9	1938.7
140°	1775.8	1858.8
142.5°	1714.5	1785.8
145°	1622.4	1676.3
147.5°	1551.7	1596.5
150°	1507.2	1543.5
152.5°	1469.2	1496.5
155°	1425.5	1443.6
157.5°	1390.9	1403.6
160°	1370.3	1377.6
162.5°	1356.7	1363.7
165°	1337.2	1344.6
167.5°	1323.3	1326.4
170°	1319.4	1319.4
172.5°	1309.1	1306.4
175°	1302.9	1302.9
177.5°	1297.3	1294.2
180°	1294.2	1294.2



TEST NUMBER: P937405
 CATALOG NUMBER: SQ4-FB-075U-125D-B50-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.95	7.93	7.83	8.84	9.99	20.14	21.12	21.02	22.03	23.18
	3H	7.66	8.55	8.56	9.46	10.64	22.00	22.88	22.89	23.79	24.97
	4H	7.97	8.80	8.87	9.73	10.91	22.65	23.48	23.56	24.41	25.60
	6H	8.22	9.00	9.14	9.92	11.13	23.09	23.86	24.01	24.79	25.99
	8H	8.30	9.03	9.22	9.98	11.18	23.22	23.95	24.14	24.90	26.10
	12H	8.32	9.02	9.25	9.96	11.19	23.29	23.99	24.23	24.93	26.16
4H	2H	14.19	15.02	15.10	15.94	17.13	20.43	21.27	21.34	22.19	23.38
	3H	15.77	16.47	16.69	17.42	18.62	22.49	23.19	23.42	24.14	25.35
	4H	15.86	16.51	16.80	17.45	18.68	23.27	23.91	24.20	24.85	26.08
	6H	15.88	16.44	16.83	17.41	18.64	23.82	24.37	24.77	25.34	26.57
	8H	15.86	16.38	16.81	17.35	18.59	23.99	24.50	24.94	25.47	26.71
	12H	15.83	16.29	16.80	17.28	18.53	24.09	24.56	25.06	25.54	26.79
8H	4H	17.32	17.84	18.27	18.81	20.05	23.34	23.86	24.29	24.82	26.06
	6H	17.57	18.00	18.55	19.01	20.25	23.98	24.41	24.95	25.41	26.66
	8H	17.59	17.97	18.58	18.97	20.23	24.20	24.58	25.19	25.58	26.84
	12H	17.57	17.90	18.56	18.89	20.20	24.35	24.69	25.35	25.68	26.99
12H	4H	17.47	17.94	18.45	18.92	20.17	23.30	23.76	24.27	24.75	26.00
	6H	17.83	18.21	18.82	19.21	20.47	23.96	24.34	24.95	25.34	26.60
	8H	17.91	18.24	18.90	19.23	20.54	24.20	24.54	25.19	25.52	26.83