

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938506

Luminaire Tested: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P938506  
REPORT IS A COMBINATION OF REPORTS P933631 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8599.4 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P938506  
CATALOG NUMBER: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P938506

CATALOG NUMBER: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42	35				35
1	94	90	86	82	85	81	78	75	65	63	60	50	49	47	36	35	35	28				28
2	85	78	72	66	77	70	65	61	56	53	49	43	41	39	32	30	29	23				23
3	77	68	61	55	69	61	55	50	49	45	41	38	35	32	28	26	24	19				19
4	71	60	52	46	63	54	47	42	43	38	34	34	30	27	24	22	20	16				16
5	64	53	45	39	58	48	41	36	39	33	29	30	26	23	22	19	17	14				14
6	59	47	39	33	53	43	36	30	34	29	25	27	23	20	19	17	15	12				12
7	54	42	34	29	49	38	31	26	31	26	22	24	20	17	18	15	13	10				10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	15	16	13	11	9				9
9	47	35	27	22	42	31	25	20	26	20	17	20	16	14	15	12	10	8				8
10	43	31	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9	7				7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3561	3561	3561
5°	3476	4113	4788
10°	3149	5991	7936
15°	2673	7822	9583
20°	2173	9058	9766
25°	1812	9472	9568
30°	1525	9524	9551
35°	1347	9358	9797
40°	1171	9145	10052
45°	1059	8987	10092
50°	969	8842	9925
55°	925	8635	9485
60°	945	8245	8790
65°	977	7656	7835
70°	1033	6664	6619
75°	1135	5420	5166
80°	1212	3745	3480
85°	1019	1978	1782

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 10092 cd/sqm



TEST NUMBER: P938506

CATALOG NUMBER: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.6	0.6
10°-20°	220.0	2.6
20°-30°	384.9	4.5
30°-40°	495.5	5.8
40°-50°	553.4	6.4
50°-60°	530.0	6.2
60°-70°	420.1	4.9
70°-80°	247.0	2.9
80°-90°	71.9	0.8
90°-100°	423.1	4.9
100°-110°	1112.4	12.9
110°-120°	1153.4	13.4
120°-130°	925.2	10.8
130°-140°	725.9	8.4
140°-150°	557.2	6.5
150°-160°	401.3	4.7
160°-170°	245.5	2.9
170°-180°	82.9	1.0
0°-30°	654.6	7.6
0°-40°	1150.0	13.4
0°-60°	2233.5	26.0
0°-90°	2972.5	34.6
90°-120°	2688.9	31.3
90°-150°	4897.1	56.9
90°-180°	5627.0	65.4
0°-180°	8599.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	384	384	384	384	384	
5°	374	401	452	511	530	35
15°	280	517	871	1056	1090	78
25°	179	586	1038	1084	1085	82
35°	121	560	977	1033	1074	76
45°	83	447	864	990	1034	64
55°	59	284	733	852	875	54
65°	47	151	544	612	621	47
75°	35	93	299	328	330	36
85°	12	28	74	81	83	13
90°	6	16	44	22	22	6
95°	56	219	729	376	256	62
105°	200	304	1230	1867	1742	212
115°	356	432	985	1965	2243	352
125°	495	555	896	1514	1786	440
135°	590	650	868	1222	1386	457
145°	684	728	857	1043	1124	429
155°	774	795	857	941	968	355
165°	835	846	857	891	902	236
175°	868	868	863	874	874	82
180°	868	868	868	868	868	



TEST NUMBER: P938506

CATALOG NUMBER: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8	383.8
2.5°	383.8	383.8	386.3	387.5	389.9	391.3	393.7	396.1	403.6	404.8	407.2
5°	374.0	378.9	394.9	401.1	418.3	441.8	451.7	467.7	501.1	510.9	517.1
7.5°	359.1	370.2	409.7	419.6	462.8	524.5	550.4	585.0	638.0	664.0	684.9
10°	335.7	359.1	429.5	452.9	523.2	617.1	665.2	713.3	793.5	829.3	842.9
12.5°	309.8	348.0	450.5	482.5	583.8	720.8	778.8	831.8	923.2	971.3	978.6
15°	280.1	331.9	470.2	517.1	647.9	807.2	871.3	936.7	1021.9	1056.4	1065.0
17.5°	254.2	319.6	488.7	538.1	697.3	884.9	950.3	1004.6	1073.7	1097.2	1103.3
20°	222.1	299.9	501.1	565.3	749.2	941.7	1004.6	1046.5	1093.4	1108.3	1110.7
22.5°	198.7	278.9	508.5	575.1	783.6	976.2	1029.3	1062.6	1094.6	1099.6	1100.8
25°	179.0	255.4	507.3	586.2	813.3	997.1	1037.9	1062.6	1081.1	1083.5	1083.5
27.5°	160.5	229.6	502.3	588.7	835.5	1002.1	1034.2	1051.5	1060.1	1065.0	1065.0
30°	144.4	204.8	490.0	583.8	845.4	997.1	1023.1	1031.7	1040.4	1047.8	1051.5
32.5°	132.1	181.4	471.5	573.8	846.6	984.8	1003.3	1008.3	1020.6	1037.9	1044.1
35°	121.0	157.9	450.5	560.3	839.2	965.1	977.4	982.4	1007.0	1033.0	1041.6
37.5°	109.8	140.7	423.3	536.9	828.1	941.7	950.3	958.9	997.1	1028.1	1037.9
40°	98.7	125.9	391.3	510.9	810.8	913.3	920.6	934.3	984.8	1020.6	1030.5
42.5°	90.1	113.6	356.7	483.8	788.6	881.1	892.3	912.1	970.1	1008.3	1019.4
45°	82.7	101.2	319.6	446.7	760.2	847.9	863.9	891.0	952.8	989.8	999.7
47.5°	75.3	92.6	281.4	408.5	729.4	814.5	835.5	866.4	929.3	965.1	973.7
50°	69.1	84.0	243.1	367.8	696.0	778.8	803.4	835.5	899.7	933.0	944.1
52.5°	64.2	76.5	207.3	327.1	657.8	741.7	770.1	803.4	863.9	896.0	903.4
55°	59.2	70.3	176.5	283.8	618.3	702.2	733.1	765.1	824.4	851.5	856.5
57.5°	56.8	65.4	150.6	243.1	576.4	657.8	692.4	722.0	777.5	798.5	803.4
60°	53.1	61.7	130.9	208.6	530.7	615.8	645.5	675.1	722.0	739.3	742.9
62.5°	49.4	59.2	116.0	175.2	483.8	566.5	596.1	623.3	662.8	675.1	680.0
65°	46.9	56.8	104.9	150.6	435.6	514.6	544.2	567.7	599.8	612.1	614.6
67.5°	44.5	54.3	96.3	129.5	387.5	462.8	485.0	507.3	531.9	544.2	545.5
70°	40.7	51.8	88.8	114.8	338.1	403.6	422.1	445.5	465.2	471.5	475.1
72.5°	38.3	48.1	84.0	103.7	287.6	346.8	364.1	377.6	394.9	401.1	401.1
75°	34.6	43.2	79.0	92.6	235.7	283.8	298.7	312.2	325.8	328.3	324.6
77.5°	30.8	38.3	67.9	77.7	183.9	224.6	237.0	244.3	255.4	258.0	259.2
80°	25.9	33.3	53.1	60.4	133.3	165.4	174.0	180.2	190.1	190.1	192.5
82.5°	19.7	25.9	38.3	43.2	90.1	113.6	121.0	124.7	130.9	130.9	130.9
85°	12.3	16.1	24.7	28.4	54.3	69.1	74.1	75.3	80.2	81.4	81.4
87.5°	6.2	8.6	16.1	17.3	28.4	35.8	35.8	38.3	38.3	37.0	35.8
90°	5.8	10.5	15.1	16.3	25.7	38.1	44.3	39.3	29.5	22.1	22.1
92.5°	23.3	62.9	102.6	112.5	158.0	218.8	249.3	218.5	156.9	110.7	106.3
95°	55.9	128.4	200.9	219.0	388.9	615.5	728.8	650.3	493.4	375.7	362.4
97.5°	96.7	160.6	224.6	240.6	523.9	901.7	1090.5	1040.9	941.8	867.4	842.0
100°	128.1	186.1	244.1	258.6	573.0	992.2	1201.8	1205.4	1212.7	1218.1	1187.9
102.5°	155.0	209.1	263.2	276.7	595.6	1020.7	1233.3	1296.4	1422.8	1517.6	1491.7
105°	200.4	246.3	292.1	303.6	612.2	1023.9	1229.7	1371.3	1654.6	1867.1	1853.1
107.5°	247.0	289.7	332.5	343.2	615.4	978.4	1159.8	1357.4	1752.5	2048.8	2052.2
110°	278.4	317.0	355.7	365.3	610.7	937.9	1101.6	1322.5	1764.1	2095.4	2109.9



TEST NUMBER: P938506

CATALOG NUMBER: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	309.3	346.1	382.9	392.1	610.9	902.7	1048.6	1274.6	1726.7	2065.7	2088.0
115°	355.9	389.9	423.8	432.3	616.5	862.3	985.1	1202.8	1638.3	1964.9	1995.9
117.5°	402.0	432.8	463.6	471.3	628.0	837.0	941.4	1137.9	1530.9	1825.7	1860.0
120°	428.7	457.8	486.7	494.0	637.3	828.4	923.9	1103.4	1462.6	1731.9	1765.2
122.5°	455.0	484.2	513.5	520.8	650.7	824.0	910.6	1072.2	1395.6	1638.1	1670.9
125°	495.2	521.8	548.5	555.2	668.7	820.2	896.0	1033.3	1308.0	1514.0	1544.3
127.5°	527.8	554.7	581.6	588.3	686.8	818.1	883.8	1001.7	1237.6	1414.4	1439.9
130°	545.3	574.2	603.2	610.5	700.0	819.4	879.1	984.1	1194.0	1351.5	1375.0
132.5°	563.3	592.3	621.3	628.6	710.7	820.2	875.0	968.9	1156.9	1297.9	1319.0
135°	590.1	616.5	642.9	649.5	722.4	819.4	868.0	946.7	1104.1	1222.1	1240.4
137.5°	617.5	643.6	669.8	676.3	739.8	824.5	866.8	933.3	1066.4	1166.3	1181.1
140°	640.3	664.4	688.5	694.4	750.6	825.4	862.7	920.2	1035.2	1121.4	1135.3
142.5°	657.7	680.0	702.2	707.8	759.4	828.3	862.7	913.3	1014.2	1090.0	1101.9
145°	684.5	704.0	723.3	728.1	771.1	828.4	856.9	898.2	980.8	1042.7	1051.8
147.5°	711.2	730.2	749.1	753.8	788.2	834.1	856.9	889.4	954.4	1003.1	1010.6
150°	728.8	745.9	762.9	767.2	797.1	837.0	856.9	884.4	939.2	980.4	986.5
152.5°	746.8	759.8	772.7	776.0	803.0	838.9	856.9	880.4	927.3	962.4	967.0
155°	773.6	783.3	792.8	795.2	815.8	843.2	856.9	875.6	912.9	940.8	943.9
157.5°	793.4	802.8	812.0	814.4	828.6	847.5	856.9	871.4	900.4	922.1	924.3
160°	806.8	814.1	821.4	823.1	834.4	849.5	856.9	869.4	894.2	912.8	914.0
162.5°	820.2	825.7	831.1	832.5	840.6	851.5	856.9	867.4	888.4	904.1	905.2
165°	834.8	839.7	844.6	845.8	849.6	854.5	856.9	864.4	879.5	890.7	891.9
167.5°	848.2	850.5	852.8	853.4	856.5	860.7	862.7	867.7	877.5	884.9	885.4
170°	856.9	859.3	861.6	862.2	862.4	862.6	862.7	867.7	877.5	884.9	884.9
172.5°	861.6	862.1	862.6	862.7	862.7	862.7	862.7	866.7	874.4	880.2	879.7
175°	868.0	868.0	868.0	868.0	866.2	863.9	862.7	865.2	870.1	873.9	873.9
177.5°	868.0	868.0	868.0	868.0	866.7	864.9	864.0	865.9	869.7	872.6	872.1
180°	868.0	868.0	868.0	868.0	868.0	868.0	868.0	868.0	868.0	868.0	868.0



TEST NUMBER: P938506

CATALOG NUMBER: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	383.8	383.8
2.5°	409.7	407.2
5°	527.0	529.5
7.5°	709.7	708.3
10°	882.4	893.5
12.5°	1008.3	1010.8
15°	1084.8	1089.7
17.5°	1114.4	1115.7
20°	1115.7	1113.1
22.5°	1102.1	1099.6
25°	1086.1	1084.8
27.5°	1071.2	1072.4
30°	1065.0	1068.8
32.5°	1065.0	1071.2
35°	1067.6	1073.7
37.5°	1066.3	1073.7
40°	1061.4	1070.0
42.5°	1047.8	1053.9
45°	1026.8	1034.2
47.5°	999.7	1004.6
50°	965.1	970.1
52.5°	921.9	923.2
55°	870.0	875.0
57.5°	814.5	815.8
60°	752.8	756.5
62.5°	687.4	687.4
65°	618.3	620.7
67.5°	546.8	552.9
70°	473.9	475.1
72.5°	402.4	402.4
75°	328.3	329.5
77.5°	258.0	258.0
80°	191.3	192.5
82.5°	132.1	134.5
85°	82.7	82.7
87.5°	38.3	34.6
90°	22.1	22.1
92.5°	88.6	71.1
95°	309.1	255.7
97.5°	740.6	639.0
100°	1067.0	946.0
102.5°	1388.1	1284.5
105°	1797.5	1741.8
107.5°	2065.6	2079.1
110°	2167.9	2225.9





TEST NUMBER: P938506

CATALOG NUMBER: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	2177.1	2266.1
115°	2119.3	2242.8
117.5°	1996.9	2133.8
120°	1898.3	2031.4
122.5°	1802.2	1933.5
125°	1665.1	1786.1
127.5°	1541.9	1643.9
130°	1469.3	1563.5
132.5°	1403.3	1487.8
135°	1313.1	1385.9
137.5°	1240.7	1300.2
140°	1190.9	1246.6
142.5°	1149.8	1197.7
145°	1088.1	1124.3
147.5°	1040.7	1070.7
150°	1010.9	1035.2
152.5°	985.4	1003.7
155°	956.0	968.2
157.5°	932.8	941.4
160°	919.0	923.9
162.5°	909.9	914.6
165°	896.8	901.8
167.5°	887.5	889.5
170°	884.9	884.9
172.5°	878.0	876.2
175°	873.9	873.9
177.5°	870.0	868.0
180°	868.0	868.0



TEST NUMBER: P938506  
 CATALOG NUMBER: SQ4-FB-150U-100D-B50-1D-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.80	4.56	4.87	5.64	7.11	16.93	17.70	18.01	18.77	20.25
	3H	4.50	5.18	5.58	6.27	7.76	18.75	19.44	19.83	20.52	22.01
	4H	4.79	5.44	5.88	6.53	8.02	19.38	20.03	20.47	21.12	22.62
	6H	5.03	5.63	6.14	6.72	8.23	19.80	20.39	20.90	21.48	22.99
	8H	5.10	5.67	6.21	6.78	8.28	19.91	20.48	21.01	21.58	23.09
	12H	5.11	5.66	6.23	6.76	8.28	19.96	20.51	21.08	21.61	23.13
4H	2H	10.97	11.62	12.07	12.71	14.21	17.20	17.85	18.30	18.94	20.43
	3H	12.53	13.08	13.64	14.19	15.70	19.22	19.76	20.33	20.88	22.39
	4H	12.63	13.12	13.74	14.23	15.76	19.97	20.47	21.08	21.58	23.11
	6H	12.63	13.06	13.75	14.19	15.71	20.49	20.92	21.61	22.05	23.57
	8H	12.61	13.01	13.72	14.13	15.67	20.65	21.05	21.76	22.17	23.71
	12H	12.56	12.92	13.69	14.05	15.60	20.73	21.09	21.86	22.22	23.77
8H	4H	14.05	14.45	15.17	15.57	17.11	20.02	20.43	21.14	21.55	23.08
	6H	14.29	14.62	15.43	15.78	17.32	20.64	20.97	21.78	22.13	23.67
	8H	14.31	14.60	15.45	15.74	17.29	20.85	21.14	21.99	22.28	23.84
	12H	14.27	14.53	15.42	15.66	17.26	20.98	21.23	22.13	22.37	23.96
12H	4H	14.19	14.55	15.32	15.68	17.23	19.97	20.34	21.11	21.47	23.01
	6H	14.54	14.83	15.69	15.98	17.53	20.62	20.91	21.77	22.05	23.61
	8H	14.61	14.86	15.76	16.00	17.59	20.84	21.09	21.99	22.23	23.82