

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938308

Luminaire Tested: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938308
REPORT IS A COMBINATION OF REPORTS P933645 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14274.4 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 111.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938308
CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P938308

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	30	30	30	21
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	26	25	24	26	25	24	17
2	83	75	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	22	21	20	14
3	75	66	59	53	66	59	53	48	45	40	37	32	29	27	20	18	17	20	18	17	12
4	69	58	50	45	60	52	45	40	39	35	31	28	25	23	17	16	14	17	16	14	10
5	63	51	44	38	55	46	39	34	35	30	27	25	22	19	15	14	12	15	14	12	8
6	57	46	38	32	51	41	34	29	31	26	23	22	19	17	14	12	11	14	12	11	7
7	53	41	33	28	47	37	30	25	28	23	20	20	17	14	12	11	9	12	11	9	6
8	49	37	30	24	43	33	27	22	25	21	17	18	15	13	11	9	8	11	9	8	5
9	45	34	26	21	40	30	24	19	23	18	15	16	13	11	10	9	7	10	9	7	5
10	42	31	24	19	37	27	21	17	21	17	14	15	12	10	10	8	6	10	8	6	4

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1808	1808	1808
5°	1766	2089	2430
10°	1602	3046	4028
15°	1361	3979	4864
20°	1108	4611	4957
25°	925	4825	4856
30°	779	4855	4847
35°	689	4775	4973
40°	601	4670	5102
45°	544	4593	5122
50°	499	4525	5037
55°	478	4423	4814
60°	490	4229	4461
65°	509	3934	3977
70°	543	3430	3360
75°	601	2797	2622
80°	656	1939	1766
85°	582	1030	905

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 5122 cd/sqm



TEST NUMBER: P938308

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.4	0.4
10°-20°	223.4	1.6
20°-30°	390.7	2.7
30°-40°	502.9	3.5
40°-50°	561.8	3.9
50°-60°	538.1	3.8
60°-70°	426.4	3.0
70°-80°	250.7	1.8
80°-90°	76.3	0.5
90°-100°	846.2	5.9
100°-110°	2224.7	15.6
110°-120°	2306.8	16.2
120°-130°	1850.3	13.0
130°-140°	1451.9	10.2
140°-150°	1114.3	7.8
150°-160°	802.5	5.6
160°-170°	491.0	3.4
170°-180°	165.9	1.2
0°-30°	664.5	4.7
0°-40°	1167.4	8.2
0°-60°	2267.2	15.9
0°-90°	3020.7	21.2
90°-120°	5377.7	37.7
90°-150°	9794.2	68.6
90°-180°	11254.0	78.8
0°-180°	14274.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	390	390	390	390	390	
5°	380	407	458	519	537	35
15°	284	525	884	1072	1106	79
25°	182	595	1054	1100	1101	84
35°	123	569	992	1049	1090	77
45°	84	454	877	1005	1050	65
55°	60	288	744	864	888	55
65°	48	153	552	621	630	47
75°	35	94	303	333	334	37
85°	12	29	75	83	84	13
90°	12	33	88	44	44	10
95°	112	438	1458	752	512	124
105°	401	607	2460	3734	3484	425
115°	712	864	1970	3930	4486	703
125°	990	1110	1792	3028	3572	879
135°	1180	1299	1736	2444	2772	913
145°	1369	1456	1714	2086	2249	858
155°	1547	1590	1714	1882	1936	711
165°	1670	1692	1714	1781	1804	471
175°	1736	1736	1726	1748	1748	165
180°	1736	1736	1736	1736	1736	



TEST NUMBER: P938308
 CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6	389.6
2.5°	389.6	389.6	392.1	393.4	395.8	397.1	399.7	402.2	409.7	410.9	413.4
5°	379.6	384.6	400.9	407.1	424.7	448.5	458.5	474.8	508.7	518.7	524.9
7.5°	364.5	375.8	415.9	425.9	469.8	532.4	558.7	593.8	647.6	674.0	695.3
10°	340.7	364.5	436.0	459.8	531.2	626.3	675.3	724.1	805.5	841.8	855.6
12.5°	314.5	353.2	457.3	489.8	592.5	731.6	790.5	844.3	937.1	985.9	993.4
15°	284.4	337.0	477.3	524.9	657.7	819.3	884.5	950.8	1037.3	1072.3	1081.1
17.5°	258.1	324.5	496.1	546.2	707.8	898.2	964.6	1019.7	1089.9	1113.7	1120.0
20°	225.5	304.4	508.7	573.8	760.5	955.9	1019.7	1062.3	1110.0	1125.0	1127.5
22.5°	201.7	283.1	516.1	583.8	795.5	991.0	1044.8	1078.7	1111.2	1116.2	1117.4
25°	181.7	259.3	514.9	595.1	825.6	1012.3	1053.6	1078.7	1097.4	1100.0	1100.0
27.5°	162.9	233.0	509.9	597.6	848.2	1017.2	1049.8	1067.4	1076.2	1081.1	1081.1
30°	146.5	208.0	497.4	592.5	858.2	1012.3	1038.5	1047.3	1056.1	1063.6	1067.4
32.5°	134.0	184.2	478.6	582.5	859.4	999.7	1018.5	1023.5	1036.0	1053.6	1059.8
35°	122.7	160.4	457.3	568.7	851.9	979.7	992.2	997.2	1022.3	1048.6	1057.3
37.5°	111.5	142.8	429.7	545.0	840.6	955.9	964.6	973.4	1012.3	1043.6	1053.6
40°	100.2	127.8	397.1	518.7	823.0	927.1	934.6	948.4	999.7	1036.0	1046.1
42.5°	91.4	115.3	362.0	491.1	800.5	894.5	905.8	925.8	984.7	1023.5	1034.8
45°	84.0	102.7	324.5	453.5	771.7	860.7	876.9	904.5	967.2	1004.7	1014.7
47.5°	76.4	94.0	285.6	414.7	740.4	826.9	848.2	879.5	943.3	979.7	988.5
50°	70.1	85.2	246.8	373.3	706.6	790.5	815.6	848.2	913.3	947.1	958.4
52.5°	65.1	77.7	210.4	331.9	667.7	752.9	781.8	815.6	876.9	909.5	917.0
55°	60.1	71.5	179.1	288.1	627.6	712.8	744.1	776.7	836.9	864.4	869.5
57.5°	57.6	66.4	152.8	246.8	585.1	667.7	702.8	732.9	789.2	810.5	815.6
60°	53.9	62.7	132.8	211.7	538.7	625.1	655.2	685.3	732.9	750.4	754.2
62.5°	50.2	60.1	117.8	177.9	491.1	575.1	605.0	632.7	672.8	685.3	690.3
65°	47.6	57.6	106.5	152.8	442.2	522.4	552.5	576.3	608.9	621.4	623.9
67.5°	45.1	55.1	97.7	131.5	393.4	469.8	492.3	514.9	539.9	552.5	553.7
70°	41.4	52.6	90.2	116.5	343.2	409.7	428.4	452.2	472.3	478.6	482.3
72.5°	38.9	48.8	85.2	105.3	291.9	352.0	369.6	383.3	400.9	407.1	407.1
75°	35.1	43.8	80.1	94.0	239.3	288.1	303.2	316.9	330.7	333.3	329.5
77.5°	31.3	38.9	68.9	78.9	186.7	228.0	240.5	248.1	259.3	261.8	263.1
80°	26.3	33.8	53.9	61.4	135.3	167.8	176.6	182.9	193.0	193.0	195.4
82.5°	20.1	26.3	38.9	43.8	91.4	115.3	122.7	126.6	132.8	132.8	132.8
85°	12.5	16.3	25.0	28.8	55.1	70.1	75.2	76.4	81.4	82.7	82.7
87.5°	6.3	8.8	16.3	17.6	28.8	36.3	36.3	38.9	38.9	37.5	36.3
90°	11.7	21.0	30.3	32.6	51.3	76.1	88.5	78.7	59.0	44.3	44.3
92.5°	46.6	125.8	205.1	224.9	316.2	437.9	498.7	437.0	313.8	221.4	212.6
95°	111.9	256.8	401.8	438.0	777.8	1230.9	1457.5	1300.6	986.9	751.5	724.8
97.5°	193.4	321.3	449.3	481.2	1047.9	1803.4	2181.1	2081.9	1883.6	1734.8	1684.1
100°	256.3	372.3	488.3	517.3	1146.1	1984.4	2403.6	2410.8	2425.3	2436.2	2375.7
102.5°	309.9	418.2	526.3	553.4	1191.1	2041.4	2466.5	2592.9	2845.5	3035.0	2983.3
105°	400.8	492.4	584.1	607.0	1224.5	2047.8	2459.5	2742.8	3309.3	3734.1	3706.3
107.5°	494.0	579.5	664.8	686.2	1230.7	1956.7	2319.7	2714.8	3505.0	4097.6	4104.4
110°	556.9	634.1	711.2	730.5	1221.4	1875.9	2203.2	2644.9	3528.3	4190.9	4219.8



TEST NUMBER: P938308

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	618.7	692.2	765.7	784.1	1221.8	1805.3	2097.1	2549.2	3453.3	4131.4	4175.9
115°	711.9	779.7	847.5	864.5	1233.1	1724.4	1970.2	2405.6	3276.6	3929.8	3991.5
117.5°	803.9	865.5	927.2	942.6	1255.9	1673.8	1882.8	2275.8	3061.8	3651.4	3719.8
120°	857.5	915.5	973.5	988.0	1274.6	1656.7	1847.8	2206.9	2925.2	3463.8	3530.3
122.5°	909.9	968.5	1026.9	1041.6	1301.4	1647.9	1821.0	2144.4	2791.2	3276.2	3341.9
125°	990.3	1043.7	1097.0	1110.3	1337.5	1640.4	1791.9	2066.6	2615.9	3028.0	3088.5
127.5°	1055.6	1109.4	1163.3	1176.7	1373.6	1636.2	1767.4	2003.2	2475.0	2828.8	2879.8
130°	1090.5	1148.5	1206.5	1221.0	1400.1	1638.7	1758.1	1968.0	2388.1	2703.0	2750.2
132.5°	1126.7	1184.7	1242.7	1257.2	1421.5	1640.5	1749.9	1937.9	2313.8	2595.8	2638.0
135°	1180.2	1233.1	1285.9	1299.1	1444.7	1638.9	1735.9	1893.4	2208.3	2444.4	2480.7
137.5°	1235.0	1287.3	1339.5	1352.6	1479.6	1649.0	1733.7	1866.8	2132.9	2332.5	2362.3
140°	1280.4	1328.6	1376.7	1388.8	1501.0	1650.7	1725.5	1840.4	2070.4	2242.8	2270.6
142.5°	1315.4	1359.9	1404.5	1415.6	1518.9	1656.6	1725.5	1826.4	2028.4	2179.9	2203.8
145°	1369.0	1407.8	1446.7	1456.4	1542.2	1656.6	1713.8	1796.4	1961.6	2085.5	2103.6
147.5°	1422.6	1460.4	1498.2	1507.7	1576.4	1668.0	1713.8	1778.8	1908.7	2006.2	2021.3
150°	1457.5	1491.7	1525.9	1534.4	1594.2	1673.9	1713.8	1768.7	1878.5	1960.8	1973.0
152.5°	1493.7	1519.5	1545.5	1551.9	1605.9	1677.8	1713.8	1760.7	1854.4	1924.7	1933.8
155°	1547.3	1566.4	1585.6	1590.3	1631.5	1686.3	1713.8	1751.1	1825.7	1881.6	1887.7
157.5°	1586.9	1605.5	1624.1	1628.8	1657.1	1694.9	1713.8	1742.8	1800.8	1844.4	1848.7
160°	1613.7	1628.1	1642.6	1646.3	1668.8	1698.8	1713.8	1738.6	1788.4	1825.7	1828.1
162.5°	1640.5	1651.3	1662.2	1664.9	1681.2	1703.0	1713.8	1734.8	1776.7	1808.2	1810.6
165°	1669.5	1679.3	1689.2	1691.7	1699.0	1708.8	1713.8	1728.8	1758.9	1781.4	1783.8
167.5°	1696.3	1701.0	1705.7	1706.9	1713.0	1721.4	1725.5	1735.3	1755.0	1769.7	1770.8
170°	1713.8	1718.5	1723.1	1724.4	1724.7	1725.2	1725.5	1735.3	1755.0	1769.7	1769.7
172.5°	1723.1	1724.2	1725.2	1725.5	1725.5	1725.5	1725.5	1733.2	1748.7	1760.4	1759.5
175°	1735.9	1735.9	1735.9	1735.9	1732.5	1727.8	1725.5	1730.4	1740.2	1747.6	1747.6
177.5°	1735.9	1735.9	1735.9	1735.9	1733.2	1729.6	1727.8	1731.7	1739.5	1745.3	1744.2
180°	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9	1735.9



TEST NUMBER: P938308

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	389.6	389.6
2.5°	415.9	413.4
5°	534.9	537.4
7.5°	720.3	719.1
10°	895.7	907.0
12.5°	1023.5	1026.0
15°	1101.2	1106.2
17.5°	1131.3	1132.5
20°	1132.5	1130.0
22.5°	1118.7	1116.2
25°	1102.4	1101.2
27.5°	1087.4	1088.7
30°	1081.1	1084.9
32.5°	1081.1	1087.4
35°	1083.6	1089.9
37.5°	1082.4	1089.9
40°	1077.4	1086.1
42.5°	1063.6	1069.9
45°	1042.3	1049.8
47.5°	1014.7	1019.7
50°	979.7	984.7
52.5°	935.8	937.1
55°	883.2	888.2
57.5°	826.9	828.1
60°	764.2	767.9
62.5°	697.8	697.8
65°	627.6	630.2
67.5°	555.0	561.2
70°	481.1	482.3
72.5°	408.4	408.4
75°	333.3	334.5
77.5°	261.8	261.8
80°	194.2	195.4
82.5°	134.0	136.6
85°	84.0	84.0
87.5°	38.9	35.1
90°	44.3	44.3
92.5°	177.4	142.2
95°	618.1	511.5
97.5°	1481.0	1278.1
100°	2133.9	1892.1
102.5°	2776.1	2569.1
105°	3595.0	3483.6
107.5°	4131.3	4158.2
110°	4335.8	4451.8



TEST NUMBER: P938308

CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	4354.0	4532.1
115°	4238.6	4485.5
117.5°	3993.8	4267.7
120°	3796.5	4062.6
122.5°	3604.4	3866.9
125°	3330.4	3572.2
127.5°	3083.9	3287.9
130°	2938.6	3127.1
132.5°	2806.8	2975.6
135°	2626.2	2771.7
137.5°	2481.4	2600.4
140°	2382.0	2493.3
142.5°	2299.6	2395.4
145°	2176.1	2248.6
147.5°	2081.3	2141.4
150°	2021.7	2070.4
152.5°	1970.6	2007.4
155°	1912.1	1936.4
157.5°	1865.7	1882.8
160°	1838.0	1847.8
162.5°	1819.8	1829.1
165°	1793.7	1803.6
167.5°	1775.0	1779.1
170°	1769.7	1769.7
172.5°	1755.9	1752.3
175°	1747.6	1747.6
177.5°	1740.0	1735.9
180°	1735.9	1735.9



TEST NUMBER: P938308
 CATALOG NUMBER: SQ4-FB-150U-050D-B50-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.15	0.65	1.30	2.93	12.67	13.33	13.83	14.48	16.11
	3H	0.18	0.77	1.35	1.93	3.58	14.49	15.09	15.66	16.25	17.89
	4H	0.46	1.03	1.65	2.19	3.84	15.13	15.69	16.31	16.85	18.50
	6H	0.70	1.23	1.89	2.39	4.05	15.55	16.07	16.74	17.23	18.89
	8H	0.77	1.26	1.96	2.44	4.09	15.66	16.16	16.85	17.34	18.99
	12H	0.78	1.25	1.97	2.42	4.09	15.72	16.19	16.92	17.36	19.04
4H	2H	6.68	7.24	7.87	8.41	10.05	12.92	13.48	14.11	14.64	16.29
	3H	8.23	8.70	9.42	9.89	11.55	14.94	15.42	16.14	16.60	18.26
	4H	8.31	8.75	9.51	9.92	11.60	15.70	16.14	16.90	17.31	18.99
	6H	8.31	8.68	9.51	9.88	11.55	16.23	16.60	17.43	17.80	19.47
	8H	8.28	8.63	9.48	9.82	11.50	16.38	16.73	17.58	17.92	19.61
	12H	8.23	8.55	9.44	9.74	11.43	16.47	16.78	17.68	17.98	19.67
8H	4H	9.74	10.09	10.94	11.28	12.96	15.74	16.09	16.94	17.28	18.97
	6H	9.97	10.26	11.19	11.49	13.17	16.36	16.65	17.58	17.88	19.56
	8H	9.99	10.24	11.21	11.45	13.15	16.58	16.83	17.80	18.04	19.74
	12H	9.95	10.17	11.17	11.37	13.10	16.72	16.94	17.94	18.14	19.87
12H	4H	9.87	10.19	11.09	11.39	13.08	15.69	16.00	16.90	17.20	18.89
	6H	10.23	10.48	11.45	11.69	13.39	16.34	16.59	17.57	17.80	19.50
	8H	10.29	10.51	11.51	11.71	13.44	16.56	16.78	17.79	17.99	19.72