

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844912

Luminaire Tested: **SQ4P-F-050U-100D-B50-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P844912
REPORT IS A COMBINATION OF REPORTS P700193 AND P700244
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-F-050U-100D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5343.0 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 47.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844912

CATALOG NUMBER: SQ4P-F-050U-100D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P844912

CATALOG NUMBER: SQ4P-F-050U-100D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69																			
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	65	63	62	58																			
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48																			
3	85	75	67	61	80	71	64	58	63	58	54	57	52	49	50	47	44	41																			
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38	35																			
5	71	59	50	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30																			
6	66	53	44	38	62	50	43	37	45	39	34	41	36	32	37	32	29	26																			
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23																			
8	56	44	35	30	53	42	34	29	38	31	27	34	29	25	31	26	23	21																			
9	53	40	32	27	50	38	31	26	35	28	24	31	26	22	28	24	21	19																			
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12435	12435	12435
5°	12467	12317	12416
10°	12424	12272	12356
15°	12339	12183	12288
20°	12222	12081	12170
25°	12085	11939	12050
30°	11917	11821	11898
35°	11789	11646	11705
40°	11563	11451	11474
45°	11324	11230	11230
50°	11085	10980	10930
55°	10827	10681	10623
60°	10422	10256	10189
65°	9927	9728	9608
70°	9247	9050	8859
75°	8295	8038	7846
80°	6711	6626	6424
85°	3991	4594	4764



TEST NUMBER: P844912

CATALOG NUMBER: SQ4P-F-050U-100D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	2.4
10°-20°	362.1	6.8
20°-30°	543.9	10.2
30°-40°	649.3	12.2
40°-50°	665.4	12.5
50°-60°	593.4	11.1
60°-70°	441.9	8.3
70°-80°	239.9	4.5
80°-90°	56.2	1.1
90°-100°	102.0	1.9
100°-110°	355.0	6.6
110°-120°	343.9	6.4
120°-130°	269.8	5.0
130°-140°	213.5	4.0
140°-150°	164.8	3.1
150°-160°	118.1	2.2
160°-170°	72.3	1.4
170°-180°	24.4	0.5
0°-30°	1033.2	19.3
0°-40°	1682.5	31.5
0°-60°	2941.3	55.0
0°-90°	3679.2	68.9
90°-120°	800.9	15.0
90°-150°	1449.0	27.1
90°-180°	1664.0	31.1
0°-180°	5343.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1348	1348	1348	1348	1348	
5°	1346	1344	1330	1342	1341	128
15°	1292	1288	1276	1286	1286	364
25°	1187	1184	1173	1180	1184	547
35°	1047	1043	1034	1034	1039	653
45°	868	870	861	859	861	670
55°	673	673	664	659	660	600
65°	455	453	446	440	440	450
75°	233	231	226	222	220	246
85°	38	41	43	45	45	53
90°	4	6	6	4	2	3
95°	17	59	172	44	27	18
105°	59	84	373	629	585	62
115°	103	124	277	585	691	102
125°	140	172	258	436	520	125
135°	168	189	256	364	411	130
145°	197	210	254	314	340	123
155°	224	232	251	279	289	103
165°	245	247	253	264	266	69
175°	256	256	254	258	256	24
180°	256	256	256	256	256	



TEST NUMBER: P844912

CATALOG NUMBER: SQ4P-F-050U-100D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1347.8	1347.8	1347.8	1347.8	1347.8
2.5°	1352.0	1349.3	1337.7	1347.8	1346.5
5°	1346.1	1344.3	1329.9	1342.4	1340.6
7.5°	1336.2	1332.8	1318.6	1330.9	1329.0
10°	1326.1	1322.6	1309.9	1320.6	1318.9
12.5°	1313.2	1311.1	1297.0	1307.8	1307.3
15°	1291.8	1288.2	1275.5	1286.5	1286.5
17.5°	1263.8	1261.6	1249.2	1259.5	1258.5
20°	1244.8	1241.4	1230.5	1239.5	1239.5
22.5°	1221.8	1219.7	1209.0	1216.4	1217.8
25°	1187.1	1183.7	1172.8	1180.1	1183.7
27.5°	1149.0	1146.2	1137.2	1141.9	1144.3
30°	1118.6	1118.6	1109.6	1111.5	1116.8
32.5°	1091.3	1091.3	1080.7	1082.6	1085.2
35°	1046.7	1043.0	1034.0	1034.0	1039.2
37.5°	994.4	992.8	987.1	986.0	987.4
40°	960.1	958.2	950.8	952.7	952.7
42.5°	925.4	923.5	916.0	913.8	916.5
45°	867.9	869.8	860.7	858.8	860.7
47.5°	811.4	811.4	804.1	799.0	801.7
50°	772.3	772.3	765.0	761.5	761.5
52.5°	731.8	733.2	724.4	719.6	721.1
55°	673.1	673.1	664.0	658.7	660.4
57.5°	608.0	608.0	599.1	593.7	596.8
60°	564.8	564.8	555.8	550.3	552.2
62.5°	521.4	521.4	512.6	507.1	507.3
65°	454.7	453.0	445.6	440.1	440.1
67.5°	390.4	385.8	380.3	373.2	373.2
70°	342.8	340.9	335.5	328.4	328.4
72.5°	299.5	296.3	290.8	285.1	285.1
75°	232.7	230.8	225.5	222.0	220.1
77.5°	166.8	165.3	164.9	159.8	161.3
80°	126.3	126.3	124.7	120.9	120.9
82.5°	90.2	91.6	88.4	87.6	86.2
85°	37.7	41.3	43.4	45.0	45.0
87.5°	7.3	11.3	10.1	11.6	11.6
90°	3.8	5.7	5.7	3.8	1.9
92.5°	9.5	28.7	26.8	11.5	9.5
95°	17.2	59.3	172.2	44.0	26.8
97.5°	26.8	66.9	344.3	156.9	84.2
100°	36.4	70.8	401.8	376.9	243.0
102.5°	47.8	76.5	399.9	529.9	436.2
105°	59.3	84.2	373.1	629.4	585.4



TEST NUMBER: P844912

CATALOG NUMBER: SQ4P-F-050U-100D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	91.9	112.9	290.8	633.3	721.3
115°	103.3	124.3	277.4	585.4	690.6
117.5°	114.8	137.8	269.7	541.4	646.6
120°	124.3	149.2	264.0	499.3	602.6
122.5°	132.0	160.7	260.2	464.9	558.6
125°	139.7	172.2	258.3	436.2	520.4
127.5°	147.3	179.8	258.3	415.2	485.9
130°	155.0	183.6	256.4	394.1	457.3
132.5°	162.6	185.5	256.4	378.8	432.4
135°	168.3	189.4	256.4	363.5	411.4
137.5°	176.0	193.3	256.4	350.1	394.1
140°	181.7	199.0	256.4	336.7	375.0
142.5°	189.4	204.7	256.4	323.3	357.8
145°	197.1	210.5	254.5	313.8	340.5
147.5°	204.7	216.2	252.6	304.2	325.2
150°	210.5	221.9	252.6	294.7	311.9
152.5°	218.1	227.6	250.7	285.0	300.4
155°	223.8	231.5	250.7	279.3	288.8
157.5°	229.5	237.2	250.7	273.6	281.2
160°	235.3	241.1	252.6	269.7	275.5
162.5°	241.1	244.9	252.6	265.9	269.7
165°	244.9	246.8	252.6	264.0	265.9
167.5°	248.7	250.7	252.6	262.1	262.1
170°	250.7	252.6	254.5	260.2	260.2
172.5°	254.5	254.5	254.5	258.3	258.3
175°	256.4	256.4	254.5	258.3	256.4
177.5°	256.4	256.4	254.5	258.3	256.4
180°	256.4	256.4	256.4	256.4	256.4



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	70.8	93.8	338.6	673.5	681.1
110°	80.4	103.3	311.9	667.7	723.2



(END OF REPORT)