

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844978

Luminaire Tested: **SQ4P-PC3-025U-050D-B50-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P844978
REPORT IS A COMBINATION OF REPORTS P700167 AND P700243
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PC3-025U-050D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2670.5 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 23.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844978

CATALOG NUMBER: SQ4P-PC3-025U-050D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P844978

CATALOG NUMBER: SQ4P-PC3-025U-050D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74	69																			
1	102	98	94	90	96	92	89	86	83	80	77	74	72	70	65	64	62	58																			
2	93	85	79	74	88	81	75	70	72	68	64	65	61	58	57	55	53	49																			
3	85	75	67	61	80	71	64	59	64	58	54	57	53	49	51	48	45	41																			
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	45	42	38	35																			
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	33	31																			
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27																			
7	61	48	40	34	57	46	38	33	42	35	31	38	32	28	34	29	26	24																			
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21																			
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	29	24	21	19																			
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	27	22	19	17																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6227	6227	6227
5°	6276	6234	6211
10°	6259	6230	6212
15°	6227	6227	6221
20°	6187	6204	6204
25°	6127	6171	6152
30°	6052	6125	6099
35°	5963	6054	6011
40°	5864	5946	5887
45°	5758	5798	5708
50°	5606	5606	5517
55°	5429	5358	5279
60°	5167	5063	4982
65°	4774	4681	4639
70°	4181	4214	4200
75°	3362	3722	3743
80°	2391	3156	3188
85°	1461	2646	2646



TEST NUMBER: P844978

CATALOG NUMBER: SQ4P-PC3-025U-050D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.9	2.4
10°-20°	183.3	6.9
20°-30°	277.6	10.4
30°-40°	332.8	12.5
40°-50°	339.4	12.7
50°-60°	296.3	11.1
60°-70°	212.1	7.9
70°-80°	109.2	4.1
80°-90°	27.9	1.0
90°-100°	50.8	1.9
100°-110°	176.7	6.6
110°-120°	171.2	6.4
120°-130°	134.2	5.0
130°-140°	106.3	4.0
140°-150°	82.0	3.1
150°-160°	58.8	2.2
160°-170°	36.0	1.3
170°-180°	12.2	0.5
0°-30°	524.8	19.7
0°-40°	857.6	32.1
0°-60°	1493.2	55.9
0°-90°	1842.5	69.0
90°-120°	398.6	14.9
90°-150°	721.1	27.0
90°-180°	828.0	31.0
0°-180°	2670.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	675	675	675	675	675	
5°	678	671	673	671	671	64
15°	652	646	652	652	651	184
25°	602	598	606	604	604	277
35°	529	528	538	534	534	331
45°	441	440	444	439	438	340
55°	338	333	333	328	328	301
65°	219	214	214	212	212	216
75°	94	99	104	105	105	102
85°	14	21	25	26	25	19
90°	2	3	3	2	1	2
95°	9	30	86	22	13	9
105°	30	42	186	313	291	31
115°	51	62	138	291	344	51
125°	70	86	128	217	259	62
135°	84	94	128	181	205	65
145°	98	105	127	156	170	61
155°	111	115	125	139	144	51
165°	122	123	126	131	132	34
175°	128	128	127	128	128	12
180°	128	128	128	128	128	



TEST NUMBER: P844978

CATALOG NUMBER: SQ4P-PC3-025U-050D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	674.9	674.9	674.9	674.9	674.9
2.5°	679.0	673.1	674.9	673.5	671.0
5°	677.6	670.7	673.1	671.2	670.6
7.5°	672.6	665.8	669.0	667.8	667.1
10°	668.1	661.4	665.0	663.8	663.1
12.5°	662.1	655.8	659.9	658.8	658.5
15°	651.9	646.4	651.9	651.9	651.3
17.5°	639.0	634.0	639.9	640.2	639.9
20°	630.1	624.5	631.9	631.2	631.9
22.5°	619.0	614.5	622.3	620.7	621.4
25°	601.9	597.6	606.2	604.3	604.3
27.5°	581.7	578.5	588.0	586.0	586.0
30°	568.1	565.0	574.9	572.5	572.5
32.5°	553.1	551.0	560.6	557.5	557.5
35°	529.4	528.1	537.5	533.7	533.7
37.5°	504.9	503.7	512.3	507.7	506.2
40°	486.9	486.3	493.7	488.8	488.8
42.5°	468.9	468.2	474.8	468.8	468.8
45°	441.3	439.9	444.4	438.7	437.5
47.5°	411.1	409.9	412.6	406.5	405.8
50°	390.6	389.4	390.6	384.9	384.4
52.5°	369.7	367.4	367.6	362.0	361.9
55°	337.5	333.2	333.1	328.2	328.2
57.5°	303.5	297.9	298.5	294.1	293.4
60°	280.0	273.9	274.4	270.7	270.0
62.5°	257.0	249.9	251.3	247.1	247.1
65°	218.7	213.8	214.4	212.5	212.5
67.5°	181.9	177.5	180.8	179.3	179.2
70°	155.0	151.9	156.2	156.2	155.7
72.5°	130.0	130.0	135.2	135.2	135.7
75°	94.3	98.7	104.4	105.0	105.0
77.5°	63.0	70.5	76.9	77.1	77.0
80°	45.0	53.5	59.4	60.6	60.0
82.5°	30.5	39.5	44.4	45.6	45.0
85°	13.8	21.1	25.0	25.6	25.0
87.5°	4.0	8.4	10.0	10.0	9.0
90°	1.9	2.9	2.9	1.9	1.0
92.5°	4.8	14.3	13.3	5.7	4.8
95°	8.6	29.5	85.7	21.9	13.3
97.5°	13.3	33.3	171.4	78.1	41.9
100°	18.1	35.2	199.9	187.5	120.9
102.5°	23.8	38.1	199.0	263.7	217.1
105°	29.5	41.9	185.6	313.3	291.4



TEST NUMBER: P844978

CATALOG NUMBER: SQ4P-PC3-025U-050D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	45.7	56.2	144.7	315.2	359.0
115°	51.4	61.9	138.0	291.4	343.8
117.5°	57.1	68.5	134.2	269.4	321.9
120°	61.9	74.3	131.4	248.5	300.0
122.5°	65.7	80.0	129.5	231.3	278.1
125°	69.5	85.7	128.5	217.1	259.0
127.5°	73.3	89.5	128.5	206.6	241.8
130°	77.1	91.4	127.6	196.1	227.5
132.5°	80.9	92.3	127.6	188.5	215.2
135°	83.8	94.3	127.6	180.9	204.7
137.5°	87.6	96.2	127.6	174.2	196.1
140°	90.4	99.0	127.6	167.6	186.6
142.5°	94.3	101.9	127.6	160.9	178.0
145°	98.1	104.7	126.6	156.1	169.5
147.5°	101.9	107.6	125.7	151.4	161.8
150°	104.7	110.4	125.7	146.6	155.2
152.5°	108.5	113.3	124.7	141.9	149.5
155°	111.4	115.2	124.7	139.0	143.8
157.5°	114.2	118.1	124.7	136.1	139.9
160°	117.1	120.0	125.7	134.2	137.1
162.5°	120.0	121.9	125.7	132.3	134.2
165°	121.9	122.8	125.7	131.4	132.3
167.5°	123.8	124.7	125.7	130.4	130.4
170°	124.7	125.7	126.6	129.5	129.5
172.5°	126.6	126.6	126.6	128.5	128.5
175°	127.6	127.6	126.6	128.5	127.6
177.5°	127.6	127.6	126.6	128.5	127.6
180°	127.6	127.6	127.6	127.6	127.6



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	35.2	46.6	168.5	335.2	339.0
110°	40.0	51.4	155.2	332.4	360.0



(END OF REPORT)