

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845062

Luminaire Tested: **SQ4P-PP3-025U-050D-B50-1D-UNV**

Issue Date: 8/14/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P845062  
REPORT IS A COMBINATION OF REPORTS P700171 AND P700243  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PP3-025U-050D-B50-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2653.4 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 23.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845062

CATALOG NUMBER: SQ4P-PP3-025U-050D-B50-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845062

CATALOG NUMBER: SQ4P-PP3-025U-050D-B50-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69								
1	102	98	94	91	96	93	89	86	83	80	78	74	72	70	65	64	63	59								
2	93	86	80	74	88	81	76	71	73	69	65	65	62	59	58	55	53	49								
3	85	76	68	62	80	72	65	60	64	59	55	58	54	50	51	48	45	42								
4	78	67	59	53	74	64	57	51	57	52	47	52	47	43	46	42	39	36								
5	72	60	52	46	68	57	50	44	52	45	41	46	41	37	42	38	34	32								
6	66	54	46	40	62	51	44	38	47	40	36	42	37	33	38	34	30	28								
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	25								
8	57	44	37	31	54	42	35	30	39	32	28	35	30	26	32	27	24	22								
9	53	41	33	28	50	39	32	27	36	29	25	32	27	24	29	25	22	20								
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6579	6579	6579
5°	6627	6587	6564
10°	6616	6570	6540
15°	6573	6536	6500
20°	6528	6492	6443
25°	6451	6407	6343
30°	6331	6298	6218
35°	6167	6124	6046
40°	5968	5930	5863
45°	5806	5765	5708
50°	5596	5562	5507
55°	5308	5237	5197
60°	4831	4694	4670
65°	4259	4080	4065
70°	3674	3523	3523
75°	3165	3119	3073
80°	2789	2821	2752
85°	2181	2392	2392



TEST NUMBER: P845062

CATALOG NUMBER: SQ4P-PP3-025U-050D-B50-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.4	2.5
10°-20°	192.5	7.3
20°-30°	288.4	10.9
30°-40°	338.2	12.7
40°-50°	339.3	12.8
50°-60°	289.5	10.9
60°-70°	188.8	7.1
70°-80°	94.7	3.6
80°-90°	26.5	1.0
90°-100°	50.8	1.9
100°-110°	176.7	6.7
110°-120°	171.2	6.5
120°-130°	134.2	5.1
130°-140°	106.3	4.0
140°-150°	82.0	3.1
150°-160°	58.8	2.2
160°-170°	36.0	1.4
170°-180°	12.2	0.5
0°-30°	548.3	20.7
0°-40°	886.6	33.4
0°-60°	1515.3	57.1
0°-90°	1825.4	68.8
90°-120°	398.6	15.0
90°-150°	721.1	27.2
90°-180°	828.0	31.2
0°-180°	2653.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	713	713	713	713	713	
5°	716	709	711	709	709	68
15°	688	681	684	682	680	194
25°	634	626	629	624	623	291
35°	548	542	544	537	537	342
45°	445	442	442	438	438	343
55°	330	329	326	324	323	293
65°	195	191	187	186	186	195
75°	89	89	88	87	86	96
85°	21	22	23	23	23	24
90°	2	3	3	2	1	2
95°	9	30	86	22	13	9
105°	30	42	186	313	291	31
115°	51	62	138	291	344	51
125°	70	86	128	217	259	62
135°	84	94	128	181	205	65
145°	98	105	127	156	170	61
155°	111	115	125	139	144	51
165°	122	123	126	131	132	34
175°	128	128	127	128	128	12
180°	128	128	128	128	128	



TEST NUMBER: P845062

CATALOG NUMBER: SQ4P-PP3-025U-050D-B50-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	713.1	713.1	713.1	713.1	713.1
2.5°	717.5	711.7	713.1	712.0	709.1
5°	715.5	708.9	711.2	708.7	708.7
7.5°	710.7	703.4	705.6	703.2	703.1
10°	706.2	698.9	701.3	698.7	698.1
12.5°	699.7	692.4	695.2	692.2	692.1
15°	688.1	681.3	684.3	681.7	680.5
17.5°	675.0	667.7	671.2	667.8	667.2
20°	664.9	657.6	661.2	656.2	656.2
22.5°	653.0	645.7	649.8	643.2	643.2
25°	633.7	626.3	629.4	623.7	623.1
27.5°	610.8	603.6	606.7	600.3	600.2
30°	594.3	587.6	591.2	584.4	583.7
32.5°	576.4	570.1	572.7	565.8	565.1
35°	547.5	542.0	543.7	537.4	536.8
37.5°	517.0	511.5	513.4	508.0	507.8
40°	495.5	491.9	492.4	488.0	486.8
42.5°	475.6	471.4	471.9	467.5	467.3
45°	445.0	441.8	441.8	437.5	437.5
47.5°	412.5	410.1	409.5	405.8	405.7
50°	389.9	388.1	387.5	384.3	383.7
52.5°	366.4	365.6	363.5	360.8	360.7
55°	330.0	328.7	325.6	323.7	323.1
57.5°	290.4	287.9	284.4	281.7	282.1
60°	261.8	259.3	254.4	253.1	253.1
62.5°	234.4	231.4	226.4	224.7	225.6
65°	195.1	191.4	186.9	185.6	186.2
67.5°	159.3	155.9	151.1	151.1	150.6
70°	136.2	134.3	130.6	130.6	130.6
72.5°	115.8	114.8	112.1	112.1	111.7
75°	88.8	88.8	87.5	86.8	86.2
77.5°	66.5	66.7	66.2	65.5	64.4
80°	52.5	53.8	53.1	52.5	51.8
82.5°	39.5	40.7	40.7	39.5	39.3
85°	20.6	22.4	22.6	22.6	22.6
87.5°	5.5	7.4	8.0	8.0	8.5
90°	1.9	2.9	2.9	1.9	1.0
92.5°	4.8	14.3	13.3	5.7	4.8
95°	8.6	29.5	85.7	21.9	13.3
97.5°	13.3	33.3	171.4	78.1	41.9
100°	18.1	35.2	199.9	187.5	120.9
102.5°	23.8	38.1	199.0	263.7	217.1
105°	29.5	41.9	185.6	313.3	291.4



TEST NUMBER: P845062

CATALOG NUMBER: SQ4P-PP3-025U-050D-B50-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	45.7	56.2	144.7	315.2	359.0
115°	51.4	61.9	138.0	291.4	343.8
117.5°	57.1	68.5	134.2	269.4	321.9
120°	61.9	74.3	131.4	248.5	300.0
122.5°	65.7	80.0	129.5	231.3	278.1
125°	69.5	85.7	128.5	217.1	259.0
127.5°	73.3	89.5	128.5	206.6	241.8
130°	77.1	91.4	127.6	196.1	227.5
132.5°	80.9	92.3	127.6	188.5	215.2
135°	83.8	94.3	127.6	180.9	204.7
137.5°	87.6	96.2	127.6	174.2	196.1
140°	90.4	99.0	127.6	167.6	186.6
142.5°	94.3	101.9	127.6	160.9	178.0
145°	98.1	104.7	126.6	156.1	169.5
147.5°	101.9	107.6	125.7	151.4	161.8
150°	104.7	110.4	125.7	146.6	155.2
152.5°	108.5	113.3	124.7	141.9	149.5
155°	111.4	115.2	124.7	139.0	143.8
157.5°	114.2	118.1	124.7	136.1	139.9
160°	117.1	120.0	125.7	134.2	137.1
162.5°	120.0	121.9	125.7	132.3	134.2
165°	121.9	122.8	125.7	131.4	132.3
167.5°	123.8	124.7	125.7	130.4	130.4
170°	124.7	125.7	126.6	129.5	129.5
172.5°	126.6	126.6	126.6	128.5	128.5
175°	127.6	127.6	126.6	128.5	127.6
177.5°	127.6	127.6	126.6	128.5	127.6
180°	127.6	127.6	127.6	127.6	127.6



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	35.2	46.6	168.5	335.2	339.0
110°	40.0	51.4	155.2	332.4	360.0



(END OF REPORT)