

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845092

Luminaire Tested: **SQ4P-PP3-075U-100D-B50-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845092
REPORT IS A COMBINATION OF REPORTS P700229 AND P700245
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-075U-100D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT
UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5962.8 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 53.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845092

CATALOG NUMBER: SQ4P-PP3-075U-100D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845092

CATALOG NUMBER: SQ4P-PP3-075U-100D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60																			
1	100	96	92	89	94	90	86	83	78	76	74	68	66	64	58	57	56	51																			
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47	43																			
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	40	37																			
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	38	35	32																			
5	70	59	50	44	65	55	48	42	49	43	38	43	38	34	37	33	30	27																			
6	65	53	44	39	60	50	42	37	44	38	33	38	34	30	33	30	27	24																			
7	60	48	40	34	56	45	38	32	40	34	30	35	30	27	31	27	24	21																			
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19																			
9	52	40	32	27	49	37	31	26	33	28	24	30	25	21	26	22	19	17																			
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	16																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12862	12862	12862
5°	12957	12877	12833
10°	12935	12844	12787
15°	12850	12780	12708
20°	12764	12692	12596
25°	12613	12526	12402
30°	12379	12314	12158
35°	12056	11973	11821
40°	11669	11596	11463
45°	11353	11273	11160
50°	10943	10873	10768
55°	10377	10240	10163
60°	9446	9176	9132
65°	8324	7975	7949
70°	7184	6887	6887
75°	6188	6099	6007
80°	5451	5520	5382
85°	4266	4658	4658



TEST NUMBER: P845092

CATALOG NUMBER: SQ4P-PP3-075U-100D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	2.2
10°-20°	376.4	6.3
20°-30°	563.8	9.5
30°-40°	661.3	11.1
40°-50°	663.4	11.1
50°-60°	565.9	9.5
60°-70°	369.1	6.2
70°-80°	185.2	3.1
80°-90°	52.1	0.9
90°-100°	146.8	2.5
100°-110°	510.8	8.6
110°-120°	494.8	8.3
120°-130°	388.1	6.5
130°-140°	307.2	5.2
140°-150°	237.1	4.0
150°-160°	169.9	2.8
160°-170°	103.9	1.7
170°-180°	35.2	0.6
0°-30°	1072.1	18.0
0°-40°	1733.4	29.1
0°-60°	2962.7	49.7
0°-90°	3569.1	59.9
90°-120°	1152.3	19.3
90°-150°	2084.7	35.0
90°-180°	2394.0	40.1
0°-180°	5962.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1399	1386	1390	1386	1386	133
15°	1345	1332	1338	1333	1330	380
25°	1239	1225	1230	1219	1218	570
35°	1070	1060	1063	1051	1050	669
45°	870	864	864	855	855	670
55°	645	643	637	633	632	573
65°	381	374	365	363	364	380
75°	174	174	171	170	168	188
85°	40	44	44	44	44	47
90°	6	8	8	6	3	5
95°	25	85	248	63	39	26
105°	85	121	537	906	842	90
115°	149	179	399	842	994	147
125°	201	248	372	628	749	180
135°	242	272	369	523	592	188
145°	284	303	366	452	490	177
155°	322	333	360	402	416	148
165°	352	355	363	380	383	99
175°	369	369	366	372	369	35
180°	369	369	369	369	369	



TEST NUMBER: P845092

CATALOG NUMBER: SQ4P-PP3-075U-100D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1394.1	1394.1	1394.1	1394.1	1394.1
2.5°	1402.8	1391.5	1394.1	1392.1	1386.4
5°	1399.0	1386.0	1390.4	1385.6	1385.6
7.5°	1389.6	1375.2	1379.7	1374.8	1374.6
10°	1380.7	1366.3	1371.0	1366.0	1364.9
12.5°	1368.1	1353.8	1359.2	1353.3	1353.1
15°	1345.3	1332.1	1338.0	1332.9	1330.5
17.5°	1319.6	1305.3	1312.3	1305.5	1304.5
20°	1300.0	1285.7	1292.7	1282.9	1282.9
22.5°	1276.7	1262.3	1270.3	1257.4	1257.4
25°	1239.0	1224.6	1230.5	1219.4	1218.3
27.5°	1194.2	1180.1	1186.2	1173.7	1173.4
30°	1162.0	1148.8	1155.9	1142.4	1141.2
32.5°	1126.8	1114.6	1119.7	1106.3	1104.9
35°	1070.4	1059.6	1063.0	1050.8	1049.5
37.5°	1011.0	1000.0	1003.8	993.2	992.9
40°	968.9	961.7	962.8	954.1	951.8
42.5°	929.8	921.7	922.7	914.0	913.7
45°	870.1	864.0	864.0	855.3	855.3
47.5°	806.5	801.8	800.6	793.3	793.1
50°	762.4	758.9	757.5	751.4	750.2
52.5°	716.5	714.8	710.6	705.5	705.4
55°	645.1	642.7	636.6	632.8	631.8
57.5°	567.8	562.9	556.0	550.7	551.5
60°	511.9	507.0	497.3	494.9	494.9
62.5°	458.2	452.5	442.6	439.3	441.2
65°	381.3	374.1	365.3	363.0	364.1
67.5°	311.4	304.8	295.3	295.3	294.6
70°	266.3	262.7	255.3	255.3	255.3
72.5°	226.3	224.6	219.3	219.1	218.2
75°	173.6	173.6	171.1	169.8	168.5
77.5°	130.0	130.4	129.4	128.0	125.8
80°	102.6	105.1	103.9	102.6	101.3
82.5°	77.3	79.6	79.4	77.3	76.9
85°	40.3	43.8	44.0	44.0	44.0
87.5°	10.8	14.6	15.6	15.6	16.7
90°	5.5	8.3	8.3	5.5	2.8
92.5°	13.8	41.3	38.6	16.5	13.8
95°	24.8	85.3	247.7	63.3	38.6
97.5°	38.6	96.3	495.4	225.7	121.1
100°	52.3	101.9	578.0	542.3	349.6
102.5°	68.8	110.1	575.3	762.5	627.6
105°	85.3	121.1	536.8	905.6	842.3



TEST NUMBER: P845092

CATALOG NUMBER: SQ4P-PP3-075U-100D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	132.1	162.4	418.4	911.1	1037.7
115°	148.6	178.9	399.1	842.3	993.6
117.5°	165.2	198.2	388.1	778.9	930.3
120°	178.9	214.7	379.9	718.4	867.0
122.5°	189.9	231.2	374.3	668.9	803.7
125°	201.0	247.7	371.6	627.6	748.7
127.5°	211.9	258.8	371.6	597.3	699.2
130°	223.0	264.3	368.8	567.0	657.8
132.5°	233.9	266.9	368.8	545.0	622.1
135°	242.2	272.5	368.8	522.9	591.8
137.5°	253.2	278.0	368.8	503.7	567.0
140°	261.5	286.3	368.8	484.4	539.5
142.5°	272.5	294.6	368.8	465.2	514.7
145°	283.5	302.7	366.1	451.5	489.9
147.5°	294.6	311.0	363.3	437.6	467.9
150°	302.7	319.3	363.3	423.8	448.7
152.5°	313.8	327.5	360.5	410.1	432.1
155°	322.1	333.0	360.5	401.8	415.7
157.5°	330.3	341.3	360.5	393.6	404.6
160°	338.5	346.8	363.3	388.1	396.3
162.5°	346.8	352.3	363.3	382.6	388.1
165°	352.3	355.1	363.3	379.9	382.6
167.5°	357.9	360.5	363.3	377.1	377.1
170°	360.5	363.3	366.1	374.3	374.3
172.5°	366.1	366.1	366.1	371.6	371.6
175°	368.8	368.8	366.1	371.6	368.8
177.5°	368.8	368.8	366.1	371.6	368.8
180°	368.8	368.8	368.8	368.8	368.8



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	<i>101.9</i>	134.9	487.2	968.9	979.9
110°	<i>115.6</i>	148.6	448.7	960.6	1040.5



(END OF REPORT)