

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845098

Luminaire Tested: **SQ4P-PP3-0U-050D-B50-1D-UNV**

Issue Date: 8/14/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P845098  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P563482)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PP3-0U-050D-B50-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 500 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1825.1 lumens  
Efficiency: N/A  
Efficacy: 108.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845098

CATALOG NUMBER: SQ4P-PP3-0U-050D-B50-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845098

CATALOG NUMBER: SQ4P-PP3-OU-050D-B50-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85																			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72																			
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61																			
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53																			
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46																			
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40																			
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36																			
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32																			
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29																			
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6579	6579	6579
5°	6627	6587	6564
10°	6616	6570	6540
15°	6573	6536	6500
20°	6528	6492	6443
25°	6451	6407	6343
30°	6331	6298	6218
35°	6167	6124	6046
40°	5968	5930	5863
45°	5806	5765	5708
50°	5596	5562	5507
55°	5308	5237	5197
60°	4831	4694	4670
65°	4259	4080	4065
70°	3674	3523	3523
75°	3165	3119	3073
80°	2789	2821	2752
85°	2181	2392	2392



TEST NUMBER: P845098

CATALOG NUMBER: SQ4P-PP3-OU-050D-B50-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.4	3.7
10°-20°	192.5	10.5
20°-30°	288.4	15.8
30°-40°	338.2	18.5
40°-50°	339.3	18.6
50°-60°	289.5	15.9
60°-70°	188.8	10.3
70°-80°	94.7	5.2
80°-90°	26.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	548.3	30.0
0°-40°	886.6	48.6
0°-60°	1515.3	83.0
0°-90°	1825.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1825.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	713	713	713	713	713	
5°	716	709	711	709	709	68
15°	688	681	684	682	680	194
25°	634	626	629	624	623	291
35°	548	542	544	537	537	342
45°	445	442	442	438	438	343
55°	330	329	326	324	323	293
65°	195	191	187	186	186	195
75°	89	89	88	87	86	96
85°	21	22	23	23	23	25
90°	0	0	0	0	0	



TEST NUMBER: P845098

CATALOG NUMBER: SQ4P-PP3-OU-050D-B50-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	713.1	713.1	713.1	713.1	713.1
2.5°	717.5	711.7	713.1	712.0	709.1
5°	715.5	708.9	711.2	708.7	708.7
7.5°	710.7	703.4	705.6	703.2	703.1
10°	706.2	698.9	701.3	698.7	698.1
12.5°	699.7	692.4	695.2	692.2	692.1
15°	688.1	681.3	684.3	681.7	680.5
17.5°	675.0	667.7	671.2	667.8	667.2
20°	664.9	657.6	661.2	656.2	656.2
22.5°	653.0	645.7	649.8	643.2	643.2
25°	633.7	626.3	629.4	623.7	623.1
27.5°	610.8	603.6	606.7	600.3	600.2
30°	594.3	587.6	591.2	584.4	583.7
32.5°	576.4	570.1	572.7	565.8	565.1
35°	547.5	542.0	543.7	537.4	536.8
37.5°	517.0	511.5	513.4	508.0	507.8
40°	495.5	491.9	492.4	488.0	486.8
42.5°	475.6	471.4	471.9	467.5	467.3
45°	445.0	441.8	441.8	437.5	437.5
47.5°	412.5	410.1	409.5	405.8	405.7
50°	389.9	388.1	387.5	384.3	383.7
52.5°	366.4	365.6	363.5	360.8	360.7
55°	330.0	328.7	325.6	323.7	323.1
57.5°	290.4	287.9	284.4	281.7	282.1
60°	261.8	259.3	254.4	253.1	253.1
62.5°	234.4	231.4	226.4	224.7	225.6
65°	195.1	191.4	186.9	185.6	186.2
67.5°	159.3	155.9	151.1	151.1	150.6
70°	136.2	134.3	130.6	130.6	130.6
72.5°	115.8	114.8	112.1	112.1	111.7
75°	88.8	88.8	87.5	86.8	86.2
77.5°	66.5	66.7	66.2	65.5	64.4
80°	52.5	53.8	53.1	52.5	51.8
82.5°	39.5	40.7	40.7	39.5	39.3
85°	20.6	22.4	22.6	22.6	22.6
87.5°	5.5	7.4	8.0	8.0	8.5
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)