

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845104

Luminaire Tested: **SQ4P-PP3-0U-100D-B50-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845104
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P563482)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-0U-100D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3568.2 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 34.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845104

CATALOG NUMBER: SQ4P-PP3-0U-100D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845104

CATALOG NUMBER: SQ4P-PP3-OU-100D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85																			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72																			
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61																			
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53																			
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46																			
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40																			
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36																			
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32																			
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29																			
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12862	12862	12862
5°	12957	12877	12833
10°	12935	12844	12787
15°	12850	12780	12708
20°	12764	12692	12596
25°	12613	12526	12402
30°	12379	12314	12158
35°	12056	11973	11821
40°	11669	11596	11463
45°	11353	11273	11160
50°	10943	10873	10768
55°	10377	10240	10163
60°	9446	9176	9132
65°	8324	7975	7949
70°	7184	6887	6887
75°	6188	6099	6007
80°	5451	5520	5382
85°	4266	4658	4658



TEST NUMBER: P845104

CATALOG NUMBER: SQ4P-PP3-OU-100D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.8	3.7
10°-20°	376.4	10.5
20°-30°	563.8	15.8
30°-40°	661.3	18.5
40°-50°	663.4	18.6
50°-60°	565.9	15.9
60°-70°	369.1	10.3
70°-80°	185.2	5.2
80°-90°	51.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1072.1	30.0
0°-40°	1733.4	48.6
0°-60°	2962.7	83.0
0°-90°	3568.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3568.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1394	1394	1394	1394	1394	
5°	1399	1386	1390	1386	1386	133
15°	1345	1332	1338	1333	1330	380
25°	1239	1225	1230	1219	1218	570
35°	1070	1060	1063	1051	1050	669
45°	870	864	864	855	855	670
55°	645	643	637	633	632	573
65°	381	374	365	363	364	380
75°	174	174	171	170	168	188
85°	40	44	44	44	44	49
90°	0	0	0	0	0	



TEST NUMBER: P845104

CATALOG NUMBER: SQ4P-PP3-OU-100D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1394.1	1394.1	1394.1	1394.1	1394.1
2.5°	1402.8	1391.5	1394.1	1392.1	1386.4
5°	1399.0	1386.0	1390.4	1385.6	1385.6
7.5°	1389.6	1375.2	1379.7	1374.8	1374.6
10°	1380.7	1366.3	1371.0	1366.0	1364.9
12.5°	1368.1	1353.8	1359.2	1353.3	1353.1
15°	1345.3	1332.1	1338.0	1332.9	1330.5
17.5°	1319.6	1305.3	1312.3	1305.5	1304.5
20°	1300.0	1285.7	1292.7	1282.9	1282.9
22.5°	1276.7	1262.3	1270.3	1257.4	1257.4
25°	1239.0	1224.6	1230.5	1219.4	1218.3
27.5°	1194.2	1180.1	1186.2	1173.7	1173.4
30°	1162.0	1148.8	1155.9	1142.4	1141.2
32.5°	1126.8	1114.6	1119.7	1106.3	1104.9
35°	1070.4	1059.6	1063.0	1050.8	1049.5
37.5°	1011.0	1000.0	1003.8	993.2	992.9
40°	968.9	961.7	962.8	954.1	951.8
42.5°	929.8	921.7	922.7	914.0	913.7
45°	870.1	864.0	864.0	855.3	855.3
47.5°	806.5	801.8	800.6	793.3	793.1
50°	762.4	758.9	757.5	751.4	750.2
52.5°	716.5	714.8	710.6	705.5	705.4
55°	645.1	642.7	636.6	632.8	631.8
57.5°	567.8	562.9	556.0	550.7	551.5
60°	511.9	507.0	497.3	494.9	494.9
62.5°	458.2	452.5	442.6	439.3	441.2
65°	381.3	374.1	365.3	363.0	364.1
67.5°	311.4	304.8	295.3	295.3	294.6
70°	266.3	262.7	255.3	255.3	255.3
72.5°	226.3	224.6	219.3	219.1	218.2
75°	173.6	173.6	171.1	169.8	168.5
77.5°	130.0	130.4	129.4	128.0	125.8
80°	102.6	105.1	103.9	102.6	101.3
82.5°	77.3	79.6	79.4	77.3	76.9
85°	40.3	43.8	44.0	44.0	44.0
87.5°	10.8	14.6	15.6	15.6	16.7
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)