

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845332

Luminaire Tested: **SQ4P-WB-050U-100D-B50-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845332
REPORT IS A COMBINATION OF REPORTS P700213 AND P700244
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-050U-100D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT
UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4753.7 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 47.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845332

CATALOG NUMBER: SQ4P-WB-050U-100D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845332

CATALOG NUMBER: SQ4P-WB-050U-100D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65								
1	103	99	95	92	96	93	90	87	83	80	78	73	71	70	64	63	62	58								
2	95	88	83	78	89	83	78	74	74	71	67	66	63	61	58	56	55	51								
3	87	79	72	67	82	75	69	64	67	62	59	60	56	53	53	51	48	45								
4	81	71	64	58	76	67	61	56	61	56	52	54	50	47	49	46	43	40								
5	75	64	57	51	71	61	54	49	55	50	46	50	45	42	45	41	39	36								
6	70	58	51	45	66	56	49	44	51	45	41	46	41	38	41	38	35	32								
7	65	53	46	41	61	51	44	39	46	41	37	42	38	34	38	35	32	29								
8	61	49	42	37	57	47	40	36	43	37	33	39	35	31	35	32	29	27								
9	57	45	38	33	54	43	37	32	40	34	30	36	32	29	33	29	27	25								
10	53	42	35	30	51	40	34	30	37	32	28	34	29	26	31	27	25	23								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19560	19560	19560
5°	19317	19247	19360
10°	18249	18415	18842
15°	16846	17239	18012
20°	15299	15873	16924
25°	13723	14471	15768
30°	12271	13071	14568
35°	10728	11503	13151
40°	9029	9747	11384
45°	7452	8095	9504
50°	6221	6783	7916
55°	5282	5820	6537
60°	4515	5047	5218
65°	3596	4244	3369
70°	3186	3313	2058
75°	2948	2688	1262
80°	2720	2476	1089
85°	2445	2276	889



TEST NUMBER: P845332

CATALOG NUMBER: SQ4P-WB-050U-100D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.5	4.1
10°-20°	505.8	10.6
20°-30°	655.2	13.8
30°-40°	641.6	13.5
40°-50°	491.1	10.3
50°-60°	327.2	6.9
60°-70°	178.6	3.8
70°-80°	74.4	1.6
80°-90°	21.7	0.5
90°-100°	102.0	2.1
100°-110°	355.0	7.5
110°-120°	343.9	7.2
120°-130°	269.8	5.7
130°-140°	213.5	4.5
140°-150°	164.8	3.5
150°-160°	118.1	2.5
160°-170°	72.3	1.5
170°-180°	24.4	0.5
0°-30°	1355.4	28.5
0°-40°	1997.0	42.0
0°-60°	2815.3	59.2
0°-90°	3089.9	65.0
90°-120°	800.9	16.8
90°-150°	1449.0	30.5
90°-180°	1664.0	35.0
0°-180°	4753.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2120	2120	2120	2120	2120	
5°	2086	2065	2078	2083	2090	194
15°	1764	1757	1805	1854	1886	493
25°	1348	1352	1422	1483	1549	620
35°	952	957	1021	1090	1168	592
45°	571	582	620	667	728	445
55°	328	342	362	376	406	298
65°	165	178	194	170	154	171
75°	83	83	75	52	35	88
85°	23	23	22	14	8	25
90°	4	6	6	4	2	3
95°	17	59	172	44	27	18
105°	59	84	373	629	585	62
115°	103	124	277	585	691	102
125°	140	172	258	436	520	125
135°	168	189	256	364	411	130
145°	197	210	254	314	340	123
155°	224	232	251	279	289	103
165°	245	247	253	264	266	69
175°	256	256	254	258	256	24
180°	256	256	256	256	256	



TEST NUMBER: P845332

CATALOG NUMBER: SQ4P-WB-050U-100D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2120.1	2120.1	2120.1	2120.1	2120.1
2.5°	2125.3	2106.4	2111.2	2111.0	2105.1
5°	2085.7	2064.7	2078.2	2082.9	2090.4
7.5°	2008.2	1992.4	2017.1	2035.1	2049.9
10°	1947.9	1934.3	1965.6	1992.2	2011.2
12.5°	1878.1	1866.4	1905.5	1940.8	1965.9
15°	1763.7	1757.4	1804.8	1853.9	1885.7
17.5°	1641.6	1638.4	1692.7	1750.0	1790.7
20°	1558.2	1557.3	1616.7	1676.5	1723.7
22.5°	1474.1	1476.0	1538.6	1600.7	1654.6
25°	1348.0	1351.6	1421.5	1483.4	1548.9
27.5°	1231.3	1233.1	1305.0	1370.5	1440.4
30°	1151.8	1156.1	1226.9	1294.8	1367.4
32.5°	1072.2	1077.4	1146.7	1216.6	1290.8
35°	952.5	957.2	1021.3	1090.3	1167.6
37.5°	829.3	835.6	892.7	957.5	1033.8
40°	749.7	759.0	809.3	870.6	945.2
42.5°	673.1	684.4	731.2	789.3	856.4
45°	571.1	582.1	620.4	667.4	728.4
47.5°	483.3	495.9	525.4	565.9	617.9
50°	433.4	445.4	472.6	502.5	551.5
52.5°	389.6	401.4	425.7	448.8	490.7
55°	328.4	342.0	361.8	375.7	406.4
57.5°	278.2	291.2	307.0	313.1	331.9
60°	244.7	259.2	273.5	272.8	282.8
62.5°	214.2	226.6	240.7	230.8	231.4
65°	164.7	178.4	194.4	169.9	154.3
67.5°	133.1	135.9	152.5	118.5	100.1
70°	118.1	118.1	122.8	91.8	76.3
72.5°	104.1	104.1	99.9	74.5	58.4
75°	82.7	82.7	75.4	51.8	35.4
77.5°	63.8	63.2	57.7	38.6	25.7
80°	51.2	51.2	46.6	30.6	20.5
82.5°	40.0	40.0	36.0	23.8	15.1
85°	23.1	23.1	21.5	13.9	8.4
87.5°	8.2	8.2	7.3	4.4	3.8
90°	3.8	5.7	5.7	3.8	1.9
92.5°	9.5	28.7	26.8	11.5	9.5
95°	17.2	59.3	172.2	44.0	26.8
97.5°	26.8	66.9	344.3	156.9	84.2
100°	36.4	70.8	401.8	376.9	243.0
102.5°	47.8	76.5	399.9	529.9	436.2
105°	59.3	84.2	373.1	629.4	585.4



TEST NUMBER: P845332

CATALOG NUMBER: SQ4P-WB-050U-100D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	91.9	112.9	290.8	633.3	721.3
115°	103.3	124.3	277.4	585.4	690.6
117.5°	114.8	137.8	269.7	541.4	646.6
120°	124.3	149.2	264.0	499.3	602.6
122.5°	132.0	160.7	260.2	464.9	558.6
125°	139.7	172.2	258.3	436.2	520.4
127.5°	147.3	179.8	258.3	415.2	485.9
130°	155.0	183.6	256.4	394.1	457.3
132.5°	162.6	185.5	256.4	378.8	432.4
135°	168.3	189.4	256.4	363.5	411.4
137.5°	176.0	193.3	256.4	350.1	394.1
140°	181.7	199.0	256.4	336.7	375.0
142.5°	189.4	204.7	256.4	323.3	357.8
145°	197.1	210.5	254.5	313.8	340.5
147.5°	204.7	216.2	252.6	304.2	325.2
150°	210.5	221.9	252.6	294.7	311.9
152.5°	218.1	227.6	250.7	285.0	300.4
155°	223.8	231.5	250.7	279.3	288.8
157.5°	229.5	237.2	250.7	273.6	281.2
160°	235.3	241.1	252.6	269.7	275.5
162.5°	241.1	244.9	252.6	265.9	269.7
165°	244.9	246.8	252.6	264.0	265.9
167.5°	248.7	250.7	252.6	262.1	262.1
170°	250.7	252.6	254.5	260.2	260.2
172.5°	254.5	254.5	254.5	258.3	258.3
175°	256.4	256.4	254.5	258.3	256.4
177.5°	256.4	256.4	254.5	258.3	256.4
180°	256.4	256.4	256.4	256.4	256.4



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	70.8	93.8	338.6	673.5	681.1
110°	80.4	103.3	311.9	667.7	723.2



(END OF REPORT)