

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845122

Luminaire Tested: **SQ4P-PP3-125U-050D-B50-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845122
REPORT IS A COMBINATION OF REPORTS P700115 AND P700247
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-125U-050D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5844.9 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845122

CATALOG NUMBER: SQ4P-PP3-125U-050D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845122

CATALOG NUMBER: SQ4P-PP3-125U-050D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	31
1	94	90	86	82	84	81	78	75	64	62	60	49	47	46	35	34	33	33	33	33	27
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	29	28	28	28	28	22
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24	24	24	24	19
4	71	61	53	47	64	55	49	43	44	39	36	34	31	28	24	22	21	21	21	21	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	18	18	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	16	16	16	13
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	14	14	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	13	13	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	11	11	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	10	10	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6579	6579	6579
5°	6627	6587	6564
10°	6616	6570	6540
15°	6573	6536	6500
20°	6528	6492	6443
25°	6451	6407	6343
30°	6331	6298	6218
35°	6167	6124	6046
40°	5968	5930	5863
45°	5806	5765	5708
50°	5596	5562	5507
55°	5308	5237	5197
60°	4831	4694	4670
65°	4259	4080	4065
70°	3674	3523	3523
75°	3165	3119	3073
80°	2789	2821	2752
85°	2181	2392	2392



TEST NUMBER: P845122

CATALOG NUMBER: SQ4P-PP3-125U-050D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	1.2
10°-20°	192.5	3.3
20°-30°	288.4	4.9
30°-40°	338.2	5.8
40°-50°	339.3	5.8
50°-60°	289.5	5.0
60°-70°	188.8	3.2
70°-80°	94.7	1.6
80°-90°	27.7	0.5
90°-100°	246.4	4.2
100°-110°	857.4	14.7
110°-120°	830.6	14.2
120°-130°	651.5	11.1
130°-140°	515.7	8.8
140°-150°	398.0	6.8
150°-160°	285.3	4.9
160°-170°	174.5	3.0
170°-180°	59.0	1.0
0°-30°	548.3	9.4
0°-40°	886.6	15.2
0°-60°	1515.3	25.9
0°-90°	1826.6	31.3
90°-120°	1934.4	33.1
90°-150°	3499.5	59.9
90°-180°	4018.0	68.7
0°-180°	5844.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	713	713	713	713	713	
5°	716	709	711	709	709	68
15°	688	681	684	682	680	194
25°	634	626	629	624	623	291
35°	548	542	544	537	537	342
45°	445	442	442	438	438	343
55°	330	329	326	324	323	293
65°	195	191	187	186	186	195
75°	89	89	88	87	86	96
85°	21	22	23	23	23	24
90°	9	14	14	9	5	6
95°	42	143	416	106	65	44
105°	143	203	901	1520	1414	151
115°	250	300	670	1414	1668	246
125°	337	416	624	1054	1257	302
135°	407	457	619	878	993	315
145°	476	508	614	758	822	298
155°	541	559	605	675	698	249
165°	592	596	610	638	642	167
175°	619	619	614	624	619	59
180°	619	619	619	619	619	



TEST NUMBER: P845122

CATALOG NUMBER: SQ4P-PP3-125U-050D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	713.1	713.1	713.1	713.1	713.1
2.5°	717.5	711.7	713.1	712.0	709.1
5°	715.5	708.9	711.2	708.7	708.7
7.5°	710.7	703.4	705.6	703.2	703.1
10°	706.2	698.9	701.3	698.7	698.1
12.5°	699.7	692.4	695.2	692.2	692.1
15°	688.1	681.3	684.3	681.7	680.5
17.5°	675.0	667.7	671.2	667.8	667.2
20°	664.9	657.6	661.2	656.2	656.2
22.5°	653.0	645.7	649.8	643.2	643.2
25°	633.7	626.3	629.4	623.7	623.1
27.5°	610.8	603.6	606.7	600.3	600.2
30°	594.3	587.6	591.2	584.4	583.7
32.5°	576.4	570.1	572.7	565.8	565.1
35°	547.5	542.0	543.7	537.4	536.8
37.5°	517.0	511.5	513.4	508.0	507.8
40°	495.5	491.9	492.4	488.0	486.8
42.5°	475.6	471.4	471.9	467.5	467.3
45°	445.0	441.8	441.8	437.5	437.5
47.5°	412.5	410.1	409.5	405.8	405.7
50°	389.9	388.1	387.5	384.3	383.7
52.5°	366.4	365.6	363.5	360.8	360.7
55°	330.0	328.7	325.6	323.7	323.1
57.5°	290.4	287.9	284.4	281.7	282.1
60°	261.8	259.3	254.4	253.1	253.1
62.5°	234.4	231.4	226.4	224.7	225.6
65°	195.1	191.4	186.9	185.6	186.2
67.5°	159.3	155.9	151.1	151.1	150.6
70°	136.2	134.3	130.6	130.6	130.6
72.5°	115.8	114.8	112.1	112.1	111.7
75°	88.8	88.8	87.5	86.8	86.2
77.5°	66.5	66.7	66.2	65.5	64.4
80°	52.5	53.8	53.1	52.5	51.8
82.5°	39.5	40.7	40.7	39.5	39.3
85°	20.6	22.4	22.6	22.6	22.6
87.5°	5.5	7.4	8.0	8.0	8.5
90°	9.2	13.9	13.9	9.2	4.7
92.5°	23.1	69.3	64.6	27.7	23.1
95°	41.6	143.3	415.8	106.2	64.6
97.5°	64.6	161.7	831.7	378.9	203.4
100°	87.8	171.0	970.3	910.2	586.8
102.5°	115.5	184.8	965.7	1279.9	1053.5
105°	143.3	203.4	901.0	1520.2	1413.9



TEST NUMBER: P845122

CATALOG NUMBER: SQ4P-PP3-125U-050D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.8	272.7	702.3	1529.4	1742.0
115°	249.5	300.4	670.0	1413.9	1668.0
117.5°	277.2	332.7	651.5	1307.7	1561.8
120°	300.4	360.4	637.7	1206.0	1455.6
122.5°	318.8	388.1	628.4	1122.8	1349.2
125°	337.3	415.8	623.8	1053.5	1256.9
127.5°	355.8	434.3	623.8	1002.7	1173.7
130°	374.2	443.5	619.2	951.8	1104.3
132.5°	392.8	448.2	619.2	914.9	1044.3
135°	406.6	457.4	619.2	878.0	993.4
137.5°	425.1	466.7	619.2	845.6	951.8
140°	439.0	480.6	619.2	813.2	905.7
142.5°	457.4	494.4	619.2	780.9	864.1
145°	475.9	508.3	614.5	757.8	822.5
147.5°	494.4	522.1	610.0	734.7	785.5
150°	508.3	536.0	610.0	711.5	753.1
152.5°	526.8	549.9	605.3	688.5	725.4
155°	540.7	559.1	605.3	674.6	697.7
157.5°	554.5	572.9	605.3	660.8	679.3
160°	568.4	582.2	610.0	651.5	665.4
162.5°	582.2	591.5	610.0	642.2	651.5
165°	591.5	596.1	610.0	637.7	642.2
167.5°	600.7	605.3	610.0	633.0	633.0
170°	605.3	610.0	614.5	628.4	628.4
172.5°	614.5	614.5	614.5	623.8	623.8
175°	619.2	619.2	614.5	623.8	619.2
177.5°	619.2	619.2	614.5	623.8	619.2
180°	619.2	619.2	619.2	619.2	619.2



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	171.0	226.4	817.9	1626.4	1645.0
110°	194.0	249.5	753.1	1612.6	1746.6



(END OF REPORT)