

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845125

Luminaire Tested: **SQ4P-PP3-125U-075D-B50-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845125
REPORT IS A COMBINATION OF REPORTS P700116 AND P700247
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-125U-075D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT
UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6735.0 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845125

CATALOG NUMBER: SQ4P-PP3-125U-075D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845125

CATALOG NUMBER: SQ4P-PP3-125U-075D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																			
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	34																			
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	36	34	29																			
3	80	70	63	58	72	64	58	53	53	49	45	43	40	37	33	31	29	25																			
4	73	62	55	49	66	57	50	45	47	42	38	38	35	32	30	27	25	21																			
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	27	24	22	18																			
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16																			
7	57	45	37	32	52	41	34	29	34	29	25	28	24	21	22	19	17	14																			
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13																			
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																			
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9788	9788	9788
5°	9860	9799	9764
10°	9844	9773	9730
15°	9778	9725	9671
20°	9712	9657	9585
25°	9598	9532	9438
30°	9420	9371	9250
35°	9174	9111	8996
40°	8879	8823	8723
45°	8638	8578	8492
50°	8328	8275	8193
55°	7896	7793	7734
60°	7189	6984	6947
65°	6335	6069	6047
70°	5465	5241	5241
75°	4705	4638	4570
80°	4150	4197	4096
85°	3250	3546	3546



TEST NUMBER: P845125

CATALOG NUMBER: SQ4P-PP3-125U-075D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.3	1.5
10°-20°	286.4	4.3
20°-30°	429.0	6.4
30°-40°	503.2	7.5
40°-50°	504.8	7.5
50°-60°	430.7	6.4
60°-70°	280.9	4.2
70°-80°	140.9	2.1
80°-90°	40.5	0.6
90°-100°	246.4	3.7
100°-110°	857.4	12.7
110°-120°	830.6	12.3
120°-130°	651.5	9.7
130°-140°	515.7	7.7
140°-150°	398.0	5.9
150°-160°	285.3	4.2
160°-170°	174.5	2.6
170°-180°	59.0	0.9
0°-30°	815.8	12.1
0°-40°	1319.0	19.6
0°-60°	2254.5	33.5
0°-90°	2716.7	40.3
90°-120°	1934.4	28.7
90°-150°	3499.5	52.0
90°-180°	4018.0	59.7
0°-180°	6735.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1061	1061	1061	1061	1061	
5°	1065	1055	1058	1054	1054	101
15°	1024	1014	1018	1014	1012	289
25°	943	932	936	928	927	434
35°	814	806	809	800	799	509
45°	662	657	657	651	651	510
55°	491	489	484	482	481	436
65°	290	285	278	276	277	290
75°	132	132	130	129	128	143
85°	31	33	34	34	34	36
90°	9	14	14	9	5	7
95°	42	143	416	106	65	44
105°	143	203	901	1520	1414	151
115°	250	300	670	1414	1668	246
125°	337	416	624	1054	1257	302
135°	407	457	619	878	993	315
145°	476	508	614	758	822	298
155°	541	559	605	675	698	249
165°	592	596	610	638	642	167
175°	619	619	614	624	619	59
180°	619	619	619	619	619	



TEST NUMBER: P845125

CATALOG NUMBER: SQ4P-PP3-125U-075D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1060.9	1060.9	1060.9	1060.9	1060.9
2.5°	1067.5	1058.8	1060.9	1059.3	1054.9
5°	1064.6	1054.7	1058.0	1054.3	1054.3
7.5°	1057.3	1046.5	1049.8	1046.2	1046.0
10°	1050.7	1039.7	1043.2	1039.4	1038.6
12.5°	1041.0	1030.1	1034.3	1029.8	1029.6
15°	1023.7	1013.6	1018.1	1014.3	1012.5
17.5°	1004.1	993.2	998.6	993.4	992.6
20°	989.2	978.3	983.6	976.2	976.2
22.5°	971.4	960.5	966.6	956.9	956.9
25°	942.8	931.8	936.3	927.8	927.1
27.5°	908.8	898.0	902.7	893.1	892.9
30°	884.2	874.1	879.6	869.3	868.3
32.5°	857.5	848.2	852.1	841.8	840.8
35°	814.5	806.4	808.9	799.6	798.7
37.5°	769.3	761.0	763.8	755.8	755.5
40°	737.2	731.8	732.6	726.0	724.3
42.5°	707.5	701.4	702.1	695.5	695.3
45°	662.0	657.4	657.4	650.8	650.8
47.5°	613.7	610.2	609.2	603.7	603.6
50°	580.2	577.4	576.5	571.8	570.8
52.5°	545.2	543.9	540.8	536.8	536.7
55°	490.9	489.1	484.5	481.5	480.8
57.5°	432.0	428.3	423.1	419.1	419.7
60°	389.6	385.9	378.5	376.5	376.5
62.5°	348.6	344.3	336.8	334.3	335.7
65°	290.2	284.7	278.0	276.2	277.0
67.5°	237.0	231.9	224.8	224.8	224.1
70°	202.6	199.9	194.3	194.3	194.3
72.5°	172.1	170.9	166.9	166.7	166.0
75°	132.0	132.0	130.1	129.2	128.2
77.5°	98.9	99.2	98.4	97.5	95.7
80°	78.1	80.0	79.0	78.1	77.1
82.5°	58.8	60.5	60.5	58.8	58.5
85°	30.7	33.3	33.5	33.5	33.5
87.5°	8.2	11.0	11.9	11.9	12.7
90°	9.2	13.9	13.9	9.2	4.7
92.5°	23.1	69.3	64.6	27.7	23.1
95°	41.6	143.3	415.8	106.2	64.6
97.5°	64.6	161.7	831.7	378.9	203.4
100°	87.8	171.0	970.3	910.2	586.8
102.5°	115.5	184.8	965.7	1279.9	1053.5
105°	143.3	203.4	901.0	1520.2	1413.9



TEST NUMBER: P845125

CATALOG NUMBER: SQ4P-PP3-125U-075D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.8	272.7	702.3	1529.4	1742.0
115°	249.5	300.4	670.0	1413.9	1668.0
117.5°	277.2	332.7	651.5	1307.7	1561.8
120°	300.4	360.4	637.7	1206.0	1455.6
122.5°	318.8	388.1	628.4	1122.8	1349.2
125°	337.3	415.8	623.8	1053.5	1256.9
127.5°	355.8	434.3	623.8	1002.7	1173.7
130°	374.2	443.5	619.2	951.8	1104.3
132.5°	392.8	448.2	619.2	914.9	1044.3
135°	406.6	457.4	619.2	878.0	993.4
137.5°	425.1	466.7	619.2	845.6	951.8
140°	439.0	480.6	619.2	813.2	905.7
142.5°	457.4	494.4	619.2	780.9	864.1
145°	475.9	508.3	614.5	757.8	822.5
147.5°	494.4	522.1	610.0	734.7	785.5
150°	508.3	536.0	610.0	711.5	753.1
152.5°	526.8	549.9	605.3	688.5	725.4
155°	540.7	559.1	605.3	674.6	697.7
157.5°	554.5	572.9	605.3	660.8	679.3
160°	568.4	582.2	610.0	651.5	665.4
162.5°	582.2	591.5	610.0	642.2	651.5
165°	591.5	596.1	610.0	637.7	642.2
167.5°	600.7	605.3	610.0	633.0	633.0
170°	605.3	610.0	614.5	628.4	628.4
172.5°	614.5	614.5	614.5	623.8	623.8
175°	619.2	619.2	614.5	623.8	619.2
177.5°	619.2	619.2	614.5	623.8	619.2
180°	619.2	619.2	619.2	619.2	619.2



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	171.0	226.4	817.9	1626.4	1645.0
110°	194.0	249.5	753.1	1612.6	1746.6



(END OF REPORT)