

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845143

Luminaire Tested: **SQ4P-PP3-150U-125D-B50-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845143
REPORT IS A COMBINATION OF REPORTS P700146 AND P700248
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-150U-125D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9297.0 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 88.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845143

CATALOG NUMBER: SQ4P-PP3-150U-125D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845143

CATALOG NUMBER: SQ4P-PP3-150U-125D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48				48															
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41																
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39				35																
3	81	72	65	59	74	66	60	55	56	52	48	47	43	40	38	36	34				29																
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25																
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25				22																
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19																
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20				17																
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				15																
9	50	38	31	26	46	35	29	24	31	25	21	26	22	19	22	18	16				14																
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15				13																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16089	16089	16089
5°	16207	16107	16051
10°	16179	16066	15995
15°	16073	15985	15896
20°	15966	15874	15755
25°	15775	15668	15512
30°	15485	15403	15207
35°	15079	14975	14785
40°	14595	14503	14338
45°	14200	14099	13959
50°	13687	13601	13468
55°	12978	12809	12712
60°	11815	11479	11422
65°	10413	9975	9942
70°	8983	8616	8616
75°	7743	7625	7514
80°	6817	6907	6732
85°	5335	5822	5822



TEST NUMBER: P845143

CATALOG NUMBER: SQ4P-PP3-150U-125D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.9	1.8
10°-20°	470.8	5.1
20°-30°	705.2	7.6
30°-40°	827.2	8.9
40°-50°	829.7	8.9
50°-60°	707.9	7.6
60°-70°	461.6	5.0
70°-80°	231.6	2.5
80°-90°	65.9	0.7
90°-100°	296.3	3.2
100°-110°	1031.0	11.1
110°-120°	998.8	10.7
120°-130°	783.5	8.4
130°-140°	620.1	6.7
140°-150°	478.6	5.1
150°-160°	343.1	3.7
160°-170°	209.8	2.3
170°-180°	71.0	0.8
0°-30°	1340.9	14.4
0°-40°	2168.1	23.3
0°-60°	3705.7	39.9
0°-90°	4464.9	48.0
90°-120°	2326.1	25.0
90°-150°	4208.3	45.3
90°-180°	4832.0	52.0
0°-180°	9297.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1744	1744	1744	1744	1744	
5°	1750	1734	1739	1733	1733	166
15°	1683	1666	1674	1667	1664	475
25°	1550	1532	1539	1525	1524	713
35°	1339	1325	1330	1314	1313	836
45°	1088	1081	1081	1070	1070	838
55°	807	804	796	792	790	717
65°	477	468	457	454	455	476
75°	217	217	214	212	211	235
85°	50	55	55	55	55	59
90°	11	17	17	11	6	9
95°	50	172	500	128	78	53
105°	172	244	1084	1828	1700	181
115°	300	361	806	1700	2006	296
125°	406	500	750	1267	1511	363
135°	489	550	745	1056	1195	379
145°	572	611	739	911	989	358
155°	650	672	728	811	839	300
165°	711	717	733	767	772	201
175°	745	745	739	750	745	71
180°	745	745	745	745	745	



TEST NUMBER: P845143

CATALOG NUMBER: SQ4P-PP3-150U-125D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1743.8	1743.8	1743.8	1743.8	1743.8
2.5°	1754.7	1740.4	1743.8	1741.3	1734.1
5°	1749.9	1733.5	1739.1	1733.1	1733.1
7.5°	1738.0	1720.1	1725.6	1719.6	1719.4
10°	1727.0	1709.1	1714.9	1708.5	1707.3
12.5°	1711.2	1693.3	1700.1	1692.7	1692.5
15°	1682.7	1666.1	1673.5	1667.2	1664.2
17.5°	1650.5	1632.6	1641.4	1632.9	1631.6
20°	1626.1	1608.2	1616.8	1604.7	1604.7
22.5°	1596.8	1578.9	1588.9	1572.8	1572.8
25°	1549.6	1531.7	1539.1	1525.1	1523.8
27.5°	1493.8	1476.1	1483.7	1467.9	1467.7
30°	1453.5	1436.9	1445.8	1429.0	1427.4
32.5°	1409.5	1394.1	1400.5	1383.7	1382.1
35°	1338.8	1325.4	1329.6	1314.4	1312.7
37.5°	1264.6	1250.9	1255.6	1242.4	1241.9
40°	1211.8	1202.9	1204.2	1193.4	1190.5
42.5°	1163.1	1152.8	1154.1	1143.3	1142.8
45°	1088.3	1080.6	1080.6	1069.8	1069.8
47.5°	1008.7	1002.9	1001.3	992.4	992.1
50°	953.6	949.2	947.6	939.9	938.3
52.5°	896.1	894.0	888.8	882.4	882.2
55°	806.8	804.0	796.3	791.5	790.3
57.5°	710.1	704.1	695.4	688.8	689.8
60°	640.3	634.2	622.1	619.0	619.0
62.5°	573.1	566.0	553.6	549.4	551.8
65°	477.0	468.0	456.9	454.0	455.4
67.5°	389.5	381.3	369.4	369.4	368.3
70°	333.0	328.5	319.4	319.4	319.4
72.5°	283.0	280.8	274.3	274.1	272.9
75°	217.2	217.2	213.9	212.4	210.8
77.5°	162.6	163.1	161.7	160.2	157.3
80°	128.3	131.5	130.0	128.3	126.7
82.5°	96.7	99.6	99.3	96.7	96.2
85°	50.4	54.8	55.0	55.0	55.0
87.5°	13.4	18.2	19.5	19.5	20.8
90°	11.1	16.7	16.7	11.1	5.5
92.5°	27.8	83.3	77.8	33.3	27.8
95°	50.0	172.2	500.1	127.8	77.8
97.5°	77.8	194.5	1000.2	455.6	244.5
100°	105.6	205.5	1166.9	1094.6	705.6
102.5°	138.9	222.3	1161.3	1539.1	1266.9
105°	172.2	244.5	1083.5	1828.1	1700.3



TEST NUMBER: P845143

CATALOG NUMBER: SQ4P-PP3-150U-125D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.7	327.9	844.5	1839.2	2094.7
115°	300.1	361.2	805.7	1700.3	2005.9
117.5°	333.4	400.0	783.4	1572.5	1878.1
120°	361.2	433.4	766.8	1450.2	1750.3
122.5°	383.4	466.8	755.7	1350.3	1622.4
125°	405.7	500.1	750.1	1266.9	1511.3
127.5°	427.8	522.3	750.1	1205.7	1411.4
130°	450.1	533.4	744.6	1144.6	1328.0
132.5°	472.3	538.9	744.6	1100.2	1255.7
135°	489.0	550.1	744.6	1055.7	1194.6
137.5°	511.2	561.2	744.6	1016.9	1144.6
140°	527.9	577.9	744.6	977.9	1089.0
142.5°	550.1	594.5	744.6	939.1	1039.0
145°	572.4	611.2	739.0	911.3	989.1
147.5°	594.5	627.9	733.4	883.5	944.6
150°	611.2	644.5	733.4	855.7	905.7
152.5°	633.5	661.2	727.9	827.9	872.3
155°	650.1	672.3	727.9	811.2	839.0
157.5°	666.8	689.0	727.9	794.6	816.8
160°	683.5	700.1	733.4	783.4	800.1
162.5°	700.1	711.3	733.4	772.4	783.4
165°	711.3	716.8	733.4	766.8	772.4
167.5°	722.3	727.9	733.4	761.2	761.2
170°	727.9	733.4	739.0	755.7	755.7
172.5°	739.0	739.0	739.0	750.1	750.1
175°	744.6	744.6	739.0	750.1	744.6
177.5°	744.6	744.6	739.0	750.1	744.6
180°	744.6	744.6	744.6	744.6	744.6



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	205.5	272.3	983.5	1955.8	1978.1
110°	233.3	300.1	905.7	1939.2	2100.4



(END OF REPORT)