

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845377

Luminaire Tested: **SQ4P-WB-125U-075D-B50-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845377
REPORT IS A COMBINATION OF REPORTS P700128 AND P700247
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-125U-075D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6371.4 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 59.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845377

CATALOG NUMBER: SQ4P-WB-125U-075D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845377

CATALOG NUMBER: SQ4P-WB-125U-075D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37																			
1	96	92	88	85	87	83	81	78	68	66	64	53	52	51	40	40	39	33																			
2	88	81	76	71	80	74	69	65	60	57	54	48	46	44	36	35	34	29																			
3	81	72	65	60	73	66	60	56	54	50	47	43	41	38	33	31	30	26																			
4	74	64	57	52	67	59	53	48	49	44	41	39	36	34	30	28	27	23																			
5	68	58	50	45	62	53	47	42	44	39	36	36	32	30	28	26	24	20																			
6	63	52	45	39	57	48	41	37	40	35	31	32	29	26	25	23	21	18																			
7	59	47	40	35	53	44	37	32	36	32	28	30	26	24	24	21	19	17																			
8	55	43	36	31	50	40	33	29	33	29	25	27	24	21	22	19	18	15																			
9	51	40	33	28	46	37	30	26	31	26	23	25	22	19	20	18	16	14																			
10	48	36	30	25	43	34	28	24	28	24	21	24	20	18	19	17	15	13																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14888	14888	14888
5°	14703	14650	14736
10°	13892	14017	14342
15°	12823	13122	13710
20°	11645	12082	12882
25°	10446	11015	12002
30°	9339	9949	11088
35°	8167	8756	10010
40°	6872	7420	8664
45°	5672	6161	7235
50°	4735	5163	6026
55°	4020	4430	4977
60°	3438	3842	3973
65°	2738	3229	2565
70°	2428	2522	1567
75°	2246	2046	959
80°	2067	1881	824
85°	1863	1736	677



TEST NUMBER: P845377

CATALOG NUMBER: SQ4P-WB-125U-075D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.0	2.3
10°-20°	385.0	6.0
20°-30°	498.7	7.8
30°-40°	488.3	7.7
40°-50°	373.8	5.9
50°-60°	249.1	3.9
60°-70°	135.9	2.1
70°-80°	56.6	0.9
80°-90°	17.5	0.3
90°-100°	246.4	3.9
100°-110°	857.4	13.5
110°-120°	830.6	13.0
120°-130°	651.5	10.2
130°-140°	515.7	8.1
140°-150°	398.0	6.2
150°-160°	285.3	4.5
160°-170°	174.5	2.7
170°-180°	59.0	0.9
0°-30°	1031.7	16.2
0°-40°	1520.0	23.9
0°-60°	2142.9	33.6
0°-90°	2353.0	36.9
90°-120°	1934.4	30.4
90°-150°	3499.5	54.9
90°-180°	4018.0	63.1
0°-180°	6371.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1614	1614	1614	1614	1614	
5°	1588	1572	1582	1586	1591	148
15°	1342	1338	1374	1411	1435	375
25°	1026	1029	1082	1129	1179	472
35°	725	729	777	830	889	451
45°	435	443	472	508	554	339
55°	250	260	275	286	309	227
65°	125	136	148	129	118	130
75°	63	63	57	39	27	67
85°	18	18	16	11	6	19
90°	9	14	14	9	5	7
95°	42	143	416	106	65	44
105°	143	203	901	1520	1414	151
115°	250	300	670	1414	1668	246
125°	337	416	624	1054	1257	302
135°	407	457	619	878	993	315
145°	476	508	614	758	822	298
155°	541	559	605	675	698	249
165°	592	596	610	638	642	167
175°	619	619	614	624	619	59
180°	619	619	619	619	619	



TEST NUMBER: P845377

CATALOG NUMBER: SQ4P-WB-125U-075D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1613.7	1613.7	1613.7	1613.7	1613.7
2.5°	1617.7	1603.3	1607.0	1606.8	1602.4
5°	1587.6	1571.5	1581.8	1585.5	1591.1
7.5°	1528.6	1516.6	1535.3	1549.1	1560.4
10°	1482.8	1472.3	1496.2	1516.4	1530.9
12.5°	1429.6	1420.7	1450.4	1477.3	1496.4
15°	1342.5	1337.7	1373.8	1411.1	1435.3
17.5°	1249.5	1247.2	1288.5	1332.1	1363.0
20°	1186.0	1185.4	1230.6	1276.1	1312.0
22.5°	1122.1	1123.5	1171.1	1218.4	1259.4
25°	1026.1	1028.8	1082.0	1129.1	1179.0
27.5°	937.3	938.5	993.3	1043.2	1096.4
30°	876.6	880.1	933.9	985.5	1040.8
32.5°	816.1	820.1	872.8	926.0	982.5
35°	725.1	728.6	777.4	829.9	888.7
37.5°	631.3	636.0	679.5	728.9	786.9
40°	570.6	577.7	616.1	662.7	719.4
42.5°	512.3	520.9	556.6	600.8	651.9
45°	434.7	443.1	472.2	508.0	554.5
47.5°	367.9	377.5	399.9	430.7	470.3
50°	329.9	339.0	359.7	382.4	419.8
52.5°	296.6	305.5	324.0	341.6	373.5
55°	249.9	260.3	275.4	286.0	309.4
57.5°	211.7	221.7	233.7	238.4	252.7
60°	186.3	197.4	208.2	207.5	215.3
62.5°	163.0	172.5	183.3	175.6	176.1
65°	125.4	135.8	147.9	129.4	117.5
67.5°	101.3	103.4	116.1	90.3	76.2
70°	90.0	90.0	93.5	69.9	58.1
72.5°	79.2	79.2	76.0	56.7	44.4
75°	63.0	63.0	57.4	39.4	26.9
77.5°	48.6	48.1	43.9	29.3	19.5
80°	38.9	38.9	35.4	23.2	15.5
82.5°	30.5	30.5	27.4	18.1	11.5
85°	17.6	17.6	16.4	10.6	6.4
87.5°	6.3	6.3	5.6	3.3	2.9
90°	9.2	13.9	13.9	9.2	4.7
92.5°	23.1	69.3	64.6	27.7	23.1
95°	41.6	143.3	415.8	106.2	64.6
97.5°	64.6	161.7	831.7	378.9	203.4
100°	87.8	171.0	970.3	910.2	586.8
102.5°	115.5	184.8	965.7	1279.9	1053.5
105°	143.3	203.4	901.0	1520.2	1413.9



TEST NUMBER: P845377

CATALOG NUMBER: SQ4P-WB-125U-075D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.8	272.7	702.3	1529.4	1742.0
115°	249.5	300.4	670.0	1413.9	1668.0
117.5°	277.2	332.7	651.5	1307.7	1561.8
120°	300.4	360.4	637.7	1206.0	1455.6
122.5°	318.8	388.1	628.4	1122.8	1349.2
125°	337.3	415.8	623.8	1053.5	1256.9
127.5°	355.8	434.3	623.8	1002.7	1173.7
130°	374.2	443.5	619.2	951.8	1104.3
132.5°	392.8	448.2	619.2	914.9	1044.3
135°	406.6	457.4	619.2	878.0	993.4
137.5°	425.1	466.7	619.2	845.6	951.8
140°	439.0	480.6	619.2	813.2	905.7
142.5°	457.4	494.4	619.2	780.9	864.1
145°	475.9	508.3	614.5	757.8	822.5
147.5°	494.4	522.1	610.0	734.7	785.5
150°	508.3	536.0	610.0	711.5	753.1
152.5°	526.8	549.9	605.3	688.5	725.4
155°	540.7	559.1	605.3	674.6	697.7
157.5°	554.5	572.9	605.3	660.8	679.3
160°	568.4	582.2	610.0	651.5	665.4
162.5°	582.2	591.5	610.0	642.2	651.5
165°	591.5	596.1	610.0	637.7	642.2
167.5°	600.7	605.3	610.0	633.0	633.0
170°	605.3	610.0	614.5	628.4	628.4
172.5°	614.5	614.5	614.5	623.8	623.8
175°	619.2	619.2	614.5	623.8	619.2
177.5°	619.2	619.2	614.5	623.8	619.2
180°	619.2	619.2	619.2	619.2	619.2



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	171.0	226.4	817.9	1626.4	1645.0
110°	194.0	249.5	753.1	1612.6	1746.6



(END OF REPORT)