

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845200

Luminaire Tested: **SQ4P-PR1-100U-100D-B50-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845200
REPORT IS A COMBINATION OF REPORTS P700093 AND P700246
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PR1-100U-100D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1000 LUMENS PER FOOT
UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6740.6 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845200

CATALOG NUMBER: SQ4P-PR1-100U-100D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845200

CATALOG NUMBER: SQ4P-PR1-100U-100D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52			
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45			
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	42	38			
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	39	36	32			
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28			
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	33	30	28	25			
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24	22			
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19			
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17			
9	51	39	32	27	47	37	30	25	32	26	23	28	23	20	24	20	18	16			
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	18	16	14			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13021	13021	13021
5°	13138	13038	12970
10°	13096	13005	12937
15°	13040	12958	12888
20°	12974	12889	12794
25°	12882	12797	12648
30°	12743	12653	12472
35°	12556	12445	12268
40°	12268	12137	11916
45°	11770	11562	11326
50°	10889	10626	10415
55°	9502	9289	9093
60°	8006	7942	7783
65°	6925	6953	6899
70°	6358	6393	6393
75°	6110	6110	6156
80°	5749	5813	5749
85°	4637	5145	5145



TEST NUMBER: P845200

CATALOG NUMBER: SQ4P-PR1-100U-100D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.5	2.0
10°-20°	381.9	5.7
20°-30°	576.0	8.5
30°-40°	686.3	10.2
40°-50°	676.6	10.0
50°-60°	517.1	7.7
60°-70°	319.9	4.7
70°-80°	181.7	2.7
80°-90°	56.5	0.8
90°-100°	196.9	2.9
100°-110°	685.2	10.2
110°-120°	663.7	9.8
120°-130°	520.7	7.7
130°-140°	412.1	6.1
140°-150°	318.0	4.7
150°-160°	228.0	3.4
160°-170°	139.4	2.1
170°-180°	47.2	0.7
0°-30°	1091.3	16.2
0°-40°	1777.5	26.4
0°-60°	2971.2	44.1
0°-90°	3529.4	52.4
90°-120°	1545.9	22.9
90°-150°	2796.7	41.5
90°-180°	3211.0	47.6
0°-180°	6740.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1411	1411	1411	1411	1411	
5°	1419	1403	1408	1403	1400	135
15°	1365	1351	1357	1352	1349	385
25°	1265	1250	1257	1244	1242	582
35°	1115	1102	1105	1090	1089	696
45°	902	890	886	870	868	691
55°	591	581	578	568	565	529
65°	317	315	318	316	316	321
75°	171	171	171	173	173	181
85°	44	46	49	49	49	51
90°	7	11	11	7	4	6
95°	33	114	332	85	52	35
105°	114	162	720	1215	1130	120
115°	199	240	535	1130	1333	197
125°	270	332	498	842	1004	241
135°	325	366	495	702	794	252
145°	380	406	491	606	657	238
155°	432	447	484	539	558	199
165°	473	476	487	510	513	133
175°	495	495	491	498	495	47
180°	495	495	495	495	495	



TEST NUMBER: P845200

CATALOG NUMBER: SQ4P-PR1-100U-100D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1411.3	1411.3	1411.3	1411.3	1411.3
2.5°	1420.1	1407.8	1411.3	1408.3	1401.7
5°	1418.6	1403.1	1407.8	1402.7	1400.4
7.5°	1407.8	1392.4	1397.1	1392.1	1390.8
10°	1397.9	1383.7	1388.2	1383.4	1380.9
12.5°	1387.2	1372.2	1377.6	1371.7	1369.4
15°	1365.2	1350.9	1356.6	1351.8	1349.3
17.5°	1340.9	1325.6	1331.5	1325.8	1322.6
20°	1321.4	1307.1	1312.8	1304.5	1303.1
22.5°	1300.0	1285.8	1291.4	1280.1	1279.9
25°	1265.4	1249.9	1257.1	1243.6	1242.4
27.5°	1224.4	1210.1	1215.8	1202.2	1200.9
30°	1196.1	1181.8	1187.7	1173.1	1170.7
32.5°	1164.0	1150.8	1155.7	1141.0	1139.5
35°	1114.8	1101.6	1104.9	1090.4	1089.2
37.5°	1058.7	1046.7	1048.6	1032.5	1031.4
40°	1018.6	1006.9	1007.7	990.8	989.4
42.5°	975.1	963.1	962.0	945.1	943.8
45°	902.1	890.1	886.1	870.2	868.0
47.5°	818.9	806.9	799.6	786.7	784.9
50°	758.6	746.6	740.3	729.3	725.6
52.5°	693.4	681.5	676.2	666.1	662.6
55°	590.7	581.3	577.5	567.7	565.3
57.5°	493.2	487.0	485.7	476.3	475.3
60°	433.9	430.4	430.4	421.8	421.8
62.5°	383.5	380.7	382.6	377.0	376.1
65°	317.2	314.9	318.5	316.0	316.0
67.5°	265.0	265.0	267.1	266.1	266.1
70°	235.7	235.7	237.0	237.0	237.0
72.5°	209.5	208.7	211.8	211.6	210.8
75°	171.4	171.4	171.4	172.7	172.7
77.5°	133.5	133.7	134.7	134.5	133.5
80°	108.2	109.4	109.4	108.2	108.2
82.5°	83.0	84.1	84.1	83.8	83.0
85°	43.8	46.1	48.6	48.6	48.6
87.5°	12.6	16.4	19.5	19.5	18.5
90°	7.4	11.0	11.0	7.4	3.7
92.5°	18.5	55.4	51.7	22.2	18.5
95°	33.2	114.4	332.4	84.9	51.7
97.5°	51.7	129.3	664.7	302.8	162.5
100°	70.2	136.6	775.4	727.4	469.0
102.5°	92.3	147.7	771.7	1022.9	841.9
105°	114.4	162.5	720.0	1214.9	1130.0



TEST NUMBER: P845200

CATALOG NUMBER: SQ4P-PR1-100U-100D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.3	217.8	561.3	1222.2	1392.1
115°	199.4	240.0	535.4	1130.0	1333.0
117.5°	221.5	265.9	520.7	1045.0	1248.1
120°	240.0	288.0	509.6	963.7	1163.2
122.5°	254.8	310.2	502.2	897.3	1078.3
125°	269.5	332.4	498.5	841.9	1004.4
127.5°	284.4	347.1	498.5	801.3	937.9
130°	299.1	354.5	494.8	760.7	882.5
132.5°	313.9	358.2	494.8	731.2	834.5
135°	324.9	365.6	494.8	701.6	793.9
137.5°	339.7	372.9	494.8	675.7	760.7
140°	350.8	384.0	494.8	649.9	723.7
142.5°	365.6	395.1	494.8	624.1	690.5
145°	380.3	406.2	491.1	605.6	657.3
147.5°	395.1	417.3	487.4	587.1	627.8
150°	406.2	428.3	487.4	568.6	601.9
152.5°	421.0	439.5	483.7	550.2	579.8
155°	432.0	446.8	483.7	539.1	557.6
157.5°	443.1	457.9	483.7	528.1	542.8
160°	454.2	465.3	487.4	520.7	531.7
162.5°	465.3	472.7	487.4	513.2	520.7
165°	472.7	476.4	487.4	509.6	513.2
167.5°	480.0	483.7	487.4	505.9	505.9
170°	483.7	487.4	491.1	502.2	502.2
172.5°	491.1	491.1	491.1	498.5	498.5
175°	494.8	494.8	491.1	498.5	494.8
177.5°	494.8	494.8	491.1	498.5	494.8
180°	494.8	494.8	494.8	494.8	494.8



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	136.6	181.0	653.6	1299.8	1314.6
110°	155.1	199.4	601.9	1288.8	1395.8



(END OF REPORT)