

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845215

Luminaire Tested: **SQ4P-PR1-125U-125D-B50-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845215
REPORT IS A COMBINATION OF REPORTS P700122 AND P700247
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PR1-125U-125D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8432.4 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 79.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845215

CATALOG NUMBER: SQ4P-PR1-125U-125D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845215

CATALOG NUMBER: SQ4P-PR1-125U-125D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52								
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45								
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	42	38								
3	82	73	66	60	76	68	62	57	58	54	50	49	46	43	41	39	36	32								
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28								
5	69	58	50	44	64	54	47	41	47	41	37	40	35	32	33	30	28	25								
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24	22								
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19								
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17								
9	51	39	32	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16								
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	18	16	14								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16285	16285	16285
5°	16433	16306	16220
10°	16379	16266	16180
15°	16309	16206	16118
20°	16226	16121	16003
25°	16111	16005	15818
30°	15937	15825	15599
35°	15703	15566	15344
40°	15343	15179	14904
45°	14721	14461	14163
50°	13617	13290	13027
55°	11884	11618	11374
60°	10014	9933	9734
65°	8663	8695	8628
70°	7952	7996	7996
75°	7643	7643	7696
80°	7183	7268	7183
85°	5790	6436	6436



TEST NUMBER: P845215

CATALOG NUMBER: SQ4P-PR1-125U-125D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.9	2.0
10°-20°	477.6	5.7
20°-30°	720.3	8.5
30°-40°	858.3	10.2
40°-50°	846.2	10.0
50°-60°	646.7	7.7
60°-70°	400.2	4.7
70°-80°	227.3	2.7
80°-90°	70.6	0.8
90°-100°	246.4	2.9
100°-110°	857.4	10.2
110°-120°	830.6	9.8
120°-130°	651.5	7.7
130°-140°	515.7	6.1
140°-150°	398.0	4.7
150°-160°	285.3	3.4
160°-170°	174.5	2.1
170°-180°	59.0	0.7
0°-30°	1364.8	16.2
0°-40°	2223.1	26.4
0°-60°	3716.0	44.1
0°-90°	4414.1	52.3
90°-120°	1934.4	22.9
90°-150°	3499.5	41.5
90°-180°	4018.0	47.6
0°-180°	8432.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1765	1765	1765	1765	1765	
5°	1774	1755	1761	1754	1751	168
15°	1708	1690	1697	1691	1688	482
25°	1583	1563	1572	1555	1554	728
35°	1394	1378	1382	1364	1362	870
45°	1128	1113	1108	1088	1086	864
55°	739	727	722	710	707	662
65°	397	394	398	395	395	402
75°	214	214	214	216	216	226
85°	55	58	61	61	61	64
90°	9	14	14	9	5	8
95°	42	143	416	106	65	44
105°	143	203	901	1520	1414	151
115°	250	300	670	1414	1668	246
125°	337	416	624	1054	1257	302
135°	407	457	619	878	993	315
145°	476	508	614	758	822	298
155°	541	559	605	675	698	249
165°	592	596	610	638	642	167
175°	619	619	614	624	619	59
180°	619	619	619	619	619	



TEST NUMBER: P845215

CATALOG NUMBER: SQ4P-PR1-125U-125D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1765.1	1765.1	1765.1	1765.1	1765.1
2.5°	1776.1	1760.6	1765.1	1761.4	1753.1
5°	1774.3	1754.9	1760.6	1754.3	1751.4
7.5°	1760.6	1741.5	1747.3	1741.0	1739.3
10°	1748.3	1730.5	1736.2	1730.2	1727.1
12.5°	1735.0	1716.0	1722.9	1715.5	1712.7
15°	1707.5	1689.6	1696.7	1690.6	1687.5
17.5°	1677.0	1657.9	1665.2	1658.1	1654.2
20°	1652.6	1634.8	1641.9	1631.4	1629.9
22.5°	1626.0	1608.1	1615.2	1601.0	1600.7
25°	1582.6	1563.3	1572.2	1555.4	1553.8
27.5°	1531.3	1513.5	1520.6	1503.5	1501.9
30°	1495.9	1478.1	1485.4	1467.1	1464.2
32.5°	1455.8	1439.4	1445.4	1427.0	1425.2
35°	1394.2	1377.8	1382.0	1363.9	1362.3
37.5°	1324.0	1309.0	1311.4	1291.2	1289.9
40°	1273.9	1259.2	1260.3	1239.1	1237.5
42.5°	1219.4	1204.5	1203.2	1181.9	1180.4
45°	1128.2	1113.3	1108.3	1088.4	1085.5
47.5°	1024.2	1009.2	1000.1	983.8	981.7
50°	948.7	933.7	925.9	912.0	907.6
52.5°	867.2	852.3	845.7	833.1	828.6
55°	738.8	727.0	722.3	709.9	707.1
57.5°	616.9	609.1	607.5	595.7	594.3
60°	542.7	538.3	538.3	527.5	527.5
62.5°	479.6	476.2	478.6	471.4	470.4
65°	396.8	393.9	398.3	395.2	395.2
67.5°	331.5	331.5	334.2	332.8	332.8
70°	294.8	294.8	296.4	296.4	296.4
72.5°	262.1	261.0	264.9	264.7	263.6
75°	214.4	214.4	214.4	215.9	215.9
77.5°	167.0	167.2	168.5	168.2	167.0
80°	135.2	136.8	136.8	135.2	135.2
82.5°	103.8	105.1	105.1	104.8	103.8
85°	54.7	57.7	60.8	60.8	60.8
87.5°	15.7	20.5	24.4	24.4	23.0
90°	9.2	13.9	13.9	9.2	4.7
92.5°	23.1	69.3	64.6	27.7	23.1
95°	41.6	143.3	415.8	106.2	64.6
97.5°	64.6	161.7	831.7	378.9	203.4
100°	87.8	171.0	970.3	910.2	586.8
102.5°	115.5	184.8	965.7	1279.9	1053.5
105°	143.3	203.4	901.0	1520.2	1413.9



TEST NUMBER: P845215

CATALOG NUMBER: SQ4P-PR1-125U-125D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	221.8	272.7	702.3	1529.4	1742.0
115°	249.5	300.4	670.0	1413.9	1668.0
117.5°	277.2	332.7	651.5	1307.7	1561.8
120°	300.4	360.4	637.7	1206.0	1455.6
122.5°	318.8	388.1	628.4	1122.8	1349.2
125°	337.3	415.8	623.8	1053.5	1256.9
127.5°	355.8	434.3	623.8	1002.7	1173.7
130°	374.2	443.5	619.2	951.8	1104.3
132.5°	392.8	448.2	619.2	914.9	1044.3
135°	406.6	457.4	619.2	878.0	993.4
137.5°	425.1	466.7	619.2	845.6	951.8
140°	439.0	480.6	619.2	813.2	905.7
142.5°	457.4	494.4	619.2	780.9	864.1
145°	475.9	508.3	614.5	757.8	822.5
147.5°	494.4	522.1	610.0	734.7	785.5
150°	508.3	536.0	610.0	711.5	753.1
152.5°	526.8	549.9	605.3	688.5	725.4
155°	540.7	559.1	605.3	674.6	697.7
157.5°	554.5	572.9	605.3	660.8	679.3
160°	568.4	582.2	610.0	651.5	665.4
162.5°	582.2	591.5	610.0	642.2	651.5
165°	591.5	596.1	610.0	637.7	642.2
167.5°	600.7	605.3	610.0	633.0	633.0
170°	605.3	610.0	614.5	628.4	628.4
172.5°	614.5	614.5	614.5	623.8	623.8
175°	619.2	619.2	614.5	623.8	619.2
177.5°	619.2	619.2	614.5	623.8	619.2
180°	619.2	619.2	619.2	619.2	619.2



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	171.0	226.4	817.9	1626.4	1645.0
110°	194.0	249.5	753.1	1612.6	1746.6



(END OF REPORT)