

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845275

Luminaire Tested: **SQ4P-PW1-0U-125D-B50-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P564826)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PW1-0U-125D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4435.5 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 45.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845275

CATALOG NUMBER: SQ4P-PW1-0U-125D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845275

CATALOG NUMBER: SQ4P-PW1-0U-125D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85								
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71								
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60								
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52								
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45								
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40								
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35								
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31								
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28								
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16084	16084	16084
5°	16189	16061	15990
10°	16059	15929	15843
15°	15889	15712	15654
20°	15699	15457	15429
25°	15480	15199	15150
30°	15152	14924	14825
35°	14722	14514	14427
40°	14264	14041	13987
45°	13708	13529	13467
50°	13142	13031	12941
55°	12526	12526	12329
60°	11765	11990	11564
65°	10763	11300	10496
70°	9485	10399	9242
75°	8106	9304	7882
80°	6285	7837	6376
85°	4065	6023	5356



TEST NUMBER: P845275

CATALOG NUMBER: SQ4P-PW1-0U-125D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.2	3.7
10°-20°	463.5	10.4
20°-30°	687.5	15.5
30°-40°	804.4	18.1
40°-50°	800.9	18.1
50°-60°	691.6	15.6
60°-70°	497.8	11.2
70°-80°	261.0	5.9
80°-90°	64.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1315.1	29.6
0°-40°	2119.5	47.8
0°-60°	3611.9	81.4
0°-90°	4435.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4435.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1743	1743	1743	1743	1743	
5°	1748	1728	1734	1729	1726	166
15°	1664	1642	1645	1642	1639	469
25°	1521	1495	1493	1484	1488	699
35°	1307	1289	1289	1276	1281	817
45°	1051	1042	1037	1034	1032	811
55°	779	777	779	768	766	695
65°	493	508	518	497	481	489
75°	227	248	261	244	221	244
85°	38	50	57	54	51	52
90°	0	0	0	0	0	



TEST NUMBER: P845275

CATALOG NUMBER: SQ4P-PW1-0U-125D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1743.3	1743.3	1743.3	1743.3	1743.3
2.5°	1753.2	1738.7	1743.3	1739.5	1731.1
5°	1748.0	1728.4	1734.2	1729.4	1726.5
7.5°	1730.2	1712.2	1716.2	1711.5	1709.6
10°	1714.1	1696.0	1700.3	1694.2	1691.1
12.5°	1695.8	1676.5	1680.7	1674.3	1672.8
15°	1663.5	1642.3	1645.0	1641.8	1638.9
17.5°	1626.0	1604.7	1605.0	1600.3	1599.4
20°	1598.9	1576.4	1574.3	1568.2	1571.4
22.5°	1569.5	1545.7	1543.6	1535.1	1539.3
25°	1520.6	1495.2	1493.0	1483.7	1488.2
27.5°	1464.1	1439.0	1439.0	1426.0	1430.8
30°	1422.3	1398.2	1400.9	1385.5	1391.6
32.5°	1378.1	1356.3	1357.7	1342.6	1348.7
35°	1307.1	1289.1	1288.6	1276.5	1280.9
37.5°	1234.6	1218.7	1216.0	1209.2	1210.2
40°	1184.3	1170.8	1165.8	1161.3	1161.3
42.5°	1131.3	1119.2	1114.2	1110.7	1109.6
45°	1050.6	1041.6	1036.9	1033.6	1032.1
47.5°	970.6	962.4	958.2	956.0	954.5
50°	915.6	909.5	907.9	903.1	901.6
52.5°	860.2	856.5	854.9	849.1	847.5
55°	778.7	777.3	778.7	768.1	766.5
57.5°	693.9	696.3	701.4	686.8	683.1
60°	637.6	643.4	649.8	632.8	626.7
62.5°	579.6	589.4	598.1	578.5	570.1
65°	493.0	508.1	517.6	497.2	480.8
67.5°	409.6	428.1	439.5	417.8	399.0
70°	351.6	372.8	385.5	363.5	342.6
72.5°	301.3	324.8	335.2	314.3	293.3
75°	227.4	248.4	261.0	243.6	221.1
77.5°	161.3	181.1	191.6	176.6	157.8
80°	118.3	139.3	147.5	134.8	120.0
82.5°	84.0	101.4	107.0	99.3	88.9
85°	38.4	50.3	56.9	53.8	50.6
87.5°	9.8	18.3	23.3	23.3	24.7
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)