

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621835

Luminaire Tested: VLT-FB-0U-125D-830-UNV-STD-W-4

Issue Date: 9/2/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P621835  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: VLT-FB-0U-125D-830-UNV-STD-W-4  
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE  
LIGHT SHAPING LENS - BATWING  
DOWNLIGHT 1250 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4480.0 lumens  
Efficiency: N/A  
Efficacy: 115.8 lumens/watt  
Spacing Criteria (0/90/45): 1.05 / 1.83 / 1.75  
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P621835  
CATALOG NUMBER: VLT-FB-0U-125D-830-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P621835

CATALOG NUMBER: VLT-FB-OU-125D-830-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100												100																
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87												87																
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75												75																
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65												65																
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56												56																
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49												49																
6	74	61	53	47	72	60	53	47	59	52	46	57	51	46	55	50	46	44												44																
7	69	56	48	42	67	55	47	42	54	46	41	52	46	41	51	45	41	39												39																
8	64	51	43	37	62	50	43	37	49	42	37	48	41	37	47	41	37	35												35																
9	60	47	39	34	58	46	39	34	45	38	33	44	38	33	43	37	33	31												31																
10	56	43	36	31	55	43	35	31	42	35	30	41	35	30	40	34	30	28												28																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8971	8971	8971
5°	8895	9536	10214
10°	8721	11275	13923
15°	8457	13742	16952
20°	8053	15833	17813
25°	7625	17121	17986
30°	7138	17518	17896
35°	6655	17518	17184
40°	6260	16971	16638
45°	5957	16451	7968
50°	5787	15573	6865
55°	5626	10427	5436
60°	5470	6345	3938
65°	5350	4832	4099
70°	5279	4211	4211
75°	5143	4367	4228
80°	4517	4409	4199
85°	3351	4603	3977

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 16451 cd/sqm



TEST NUMBER: P621835  
 CATALOG NUMBER: VLT-FB-OU-125D-830-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.8	3.0
10°-20°	497.1	11.1
20°-30°	841.9	18.8
30°-40°	1021.3	22.8
40°-50°	899.0	20.1
50°-60°	556.3	12.4
60°-70°	301.6	6.7
70°-80°	171.8	3.8
80°-90°	56.2	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1473.8	32.9
0°-40°	2495.2	55.7
0°-60°	3950.4	88.2
0°-90°	4480.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4480.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1250	1250	1250	1250	1250	
5°	1235	1275	1324	1381	1418	117
15°	1138	1312	1850	2187	2282	319
25°	963	1318	2162	2227	2272	442
35°	760	1222	2000	1972	1962	476
45°	587	1004	1621	1374	785	455
55°	450	701	833	482	434	403
65°	315	395	285	244	241	313
75°	186	163	158	155	152	194
85°	41	56	56	51	48	51
90°	0	0	0	0	0	



TEST NUMBER: P621835

CATALOG NUMBER: VLT-FB-OU-125D-830-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1250.2	1250.2	1250.2	1250.2	1250.2
2.5°	1246.1	1260.0	1266.4	1278.7	1284.7
5°	1234.9	1274.7	1323.8	1380.6	1417.9
7.5°	1215.1	1286.1	1441.7	1620.8	1697.4
10°	1196.8	1293.7	1547.4	1806.5	1910.8
12.5°	1176.5	1301.2	1671.4	1985.4	2091.7
15°	1138.3	1312.3	1849.8	2187.4	2281.8
17.5°	1089.1	1319.1	2004.3	2294.3	2355.0
20°	1054.5	1320.3	2073.4	2307.8	2332.6
22.5°	1022.0	1321.6	2122.2	2275.1	2296.0
25°	963.0	1318.3	2162.4	2226.9	2271.6
27.5°	904.1	1303.6	2142.5	2194.6	2226.9
30°	861.4	1288.7	2114.1	2157.3	2159.8
32.5°	820.7	1264.0	2071.4	2084.0	2080.5
35°	759.7	1221.9	1999.7	1971.6	1961.6
37.5°	702.8	1165.9	1895.0	1849.8	1847.3
40°	668.3	1125.4	1811.7	1768.7	1776.1
42.5°	635.7	1079.0	1736.5	1686.1	1546.4
45°	587.0	1004.4	1621.1	1374.0	785.2
47.5°	544.8	919.4	1490.5	736.0	675.9
50°	518.4	861.2	1395.0	647.2	614.9
52.5°	491.9	807.0	1271.0	581.9	539.7
55°	449.7	700.7	833.4	481.7	434.5
57.5°	409.6	589.0	509.2	374.4	323.2
60°	381.1	522.8	442.1	301.8	274.4
62.5°	354.7	468.5	377.1	267.7	262.2
65°	315.1	394.6	284.6	243.9	241.4
67.5°	278.0	324.2	217.0	219.5	217.0
70°	251.6	273.9	200.7	203.2	200.7
72.5°	227.2	225.7	184.5	182.9	180.4
75°	185.5	163.1	157.5	154.9	152.5
77.5°	141.8	120.4	127.0	124.5	122.0
80°	109.3	101.8	106.7	104.1	101.6
82.5°	80.8	83.3	86.4	81.8	79.3
85°	40.7	55.6	55.9	50.8	48.3
87.5°	12.2	24.1	22.4	18.2	16.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)