

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845317

Luminaire Tested: **SQ4P-WB-025U-075D-B50-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845317
REPORT IS A COMBINATION OF REPORTS P700184 AND P700243
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-025U-075D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3179.8 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 32.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845317

CATALOG NUMBER: SQ4P-WB-025U-075D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845317

CATALOG NUMBER: SQ4P-WB-025U-075D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20									
RC	80					70					50					30					10					0				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																														
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74												
1	105	101	98	94	100	96	93	91	87	85	83	79	78	76	72	70	69	66												
2	97	90	85	80	92	86	81	77	79	75	72	72	69	66	65	63	61	58												
3	90	81	74	69	85	78	72	67	71	66	62	65	61	58	59	57	54	51												
4	83	73	66	60	79	70	64	59	65	59	55	59	55	52	54	51	48	46												
5	77	66	59	53	73	64	57	52	59	53	49	54	50	46	50	46	43	41												
6	72	60	53	47	68	58	51	46	54	48	44	50	45	42	46	42	39	37												
7	67	55	48	43	64	53	47	42	50	44	40	46	41	38	43	39	36	34												
8	63	51	44	39	60	49	42	38	46	40	36	43	38	34	40	36	33	31												
9	59	47	40	35	56	46	39	34	43	37	33	40	35	31	37	33	30	28												
10	55	44	37	32	53	42	36	32	40	34	30	37	32	29	35	31	28	26												

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14888	14888	14888
5°	14703	14650	14736
10°	13892	14017	14342
15°	12823	13122	13710
20°	11645	12082	12882
25°	10446	11015	12002
30°	9339	9949	11088
35°	8167	8756	10010
40°	6872	7420	8664
45°	5672	6161	7235
50°	4735	5163	6026
55°	4020	4430	4977
60°	3438	3842	3973
65°	2738	3229	2565
70°	2428	2522	1567
75°	2246	2046	959
80°	2067	1881	824
85°	1863	1736	677



TEST NUMBER: P845317

CATALOG NUMBER: SQ4P-WB-025U-075D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.0	4.7
10°-20°	385.0	12.1
20°-30°	498.7	15.7
30°-40°	488.3	15.4
40°-50°	373.8	11.8
50°-60°	249.1	7.8
60°-70°	135.9	4.3
70°-80°	56.6	1.8
80°-90°	16.3	0.5
90°-100°	50.8	1.6
100°-110°	176.7	5.6
110°-120°	171.2	5.4
120°-130°	134.2	4.2
130°-140°	106.3	3.3
140°-150°	82.0	2.6
150°-160°	58.8	1.8
160°-170°	36.0	1.1
170°-180°	12.2	0.4
0°-30°	1031.7	32.4
0°-40°	1520.0	47.8
0°-60°	2142.9	67.4
0°-90°	2351.8	74.0
90°-120°	398.6	12.5
90°-150°	721.1	22.7
90°-180°	828.0	26.0
0°-180°	3179.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1614	1614	1614	1614	1614	
5°	1588	1572	1582	1586	1591	148
15°	1342	1338	1374	1411	1435	375
25°	1026	1029	1082	1129	1179	472
35°	725	729	777	830	889	451
45°	435	443	472	508	554	339
55°	250	260	275	286	309	227
65°	125	136	148	129	118	130
75°	63	63	57	39	27	67
85°	18	18	16	11	6	19
90°	2	3	3	2	1	2
95°	9	30	86	22	13	9
105°	30	42	186	313	291	31
115°	51	62	138	291	344	51
125°	70	86	128	217	259	62
135°	84	94	128	181	205	65
145°	98	105	127	156	170	61
155°	111	115	125	139	144	51
165°	122	123	126	131	132	34
175°	128	128	127	128	128	12
180°	128	128	128	128	128	



TEST NUMBER: P845317

CATALOG NUMBER: SQ4P-WB-025U-075D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1613.7	1613.7	1613.7	1613.7	1613.7
2.5°	1617.7	1603.3	1607.0	1606.8	1602.4
5°	1587.6	1571.5	1581.8	1585.5	1591.1
7.5°	1528.6	1516.6	1535.3	1549.1	1560.4
10°	1482.8	1472.3	1496.2	1516.4	1530.9
12.5°	1429.6	1420.7	1450.4	1477.3	1496.4
15°	1342.5	1337.7	1373.8	1411.1	1435.3
17.5°	1249.5	1247.2	1288.5	1332.1	1363.0
20°	1186.0	1185.4	1230.6	1276.1	1312.0
22.5°	1122.1	1123.5	1171.1	1218.4	1259.4
25°	1026.1	1028.8	1082.0	1129.1	1179.0
27.5°	937.3	938.5	993.3	1043.2	1096.4
30°	876.6	880.1	933.9	985.5	1040.8
32.5°	816.1	820.1	872.8	926.0	982.5
35°	725.1	728.6	777.4	829.9	888.7
37.5°	631.3	636.0	679.5	728.9	786.9
40°	570.6	577.7	616.1	662.7	719.4
42.5°	512.3	520.9	556.6	600.8	651.9
45°	434.7	443.1	472.2	508.0	554.5
47.5°	367.9	377.5	399.9	430.7	470.3
50°	329.9	339.0	359.7	382.4	419.8
52.5°	296.6	305.5	324.0	341.6	373.5
55°	249.9	260.3	275.4	286.0	309.4
57.5°	211.7	221.7	233.7	238.4	252.7
60°	186.3	197.4	208.2	207.5	215.3
62.5°	163.0	172.5	183.3	175.6	176.1
65°	125.4	135.8	147.9	129.4	117.5
67.5°	101.3	103.4	116.1	90.3	76.2
70°	90.0	90.0	93.5	69.9	58.1
72.5°	79.2	79.2	76.0	56.7	44.4
75°	63.0	63.0	57.4	39.4	26.9
77.5°	48.6	48.1	43.9	29.3	19.5
80°	38.9	38.9	35.4	23.2	15.5
82.5°	30.5	30.5	27.4	18.1	11.5
85°	17.6	17.6	16.4	10.6	6.4
87.5°	6.3	6.3	5.6	3.3	2.9
90°	1.9	2.9	2.9	1.9	1.0
92.5°	4.8	14.3	13.3	5.7	4.8
95°	8.6	29.5	85.7	21.9	13.3
97.5°	13.3	33.3	171.4	78.1	41.9
100°	18.1	35.2	199.9	187.5	120.9
102.5°	23.8	38.1	199.0	263.7	217.1
105°	29.5	41.9	185.6	313.3	291.4



TEST NUMBER: P845317

CATALOG NUMBER: SQ4P-WB-025U-075D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	45.7	56.2	144.7	315.2	359.0
115°	51.4	61.9	138.0	291.4	343.8
117.5°	57.1	68.5	134.2	269.4	321.9
120°	61.9	74.3	131.4	248.5	300.0
122.5°	65.7	80.0	129.5	231.3	278.1
125°	69.5	85.7	128.5	217.1	259.0
127.5°	73.3	89.5	128.5	206.6	241.8
130°	77.1	91.4	127.6	196.1	227.5
132.5°	80.9	92.3	127.6	188.5	215.2
135°	83.8	94.3	127.6	180.9	204.7
137.5°	87.6	96.2	127.6	174.2	196.1
140°	90.4	99.0	127.6	167.6	186.6
142.5°	94.3	101.9	127.6	160.9	178.0
145°	98.1	104.7	126.6	156.1	169.5
147.5°	101.9	107.6	125.7	151.4	161.8
150°	104.7	110.4	125.7	146.6	155.2
152.5°	108.5	113.3	124.7	141.9	149.5
155°	111.4	115.2	124.7	139.0	143.8
157.5°	114.2	118.1	124.7	136.1	139.9
160°	117.1	120.0	125.7	134.2	137.1
162.5°	120.0	121.9	125.7	132.3	134.2
165°	121.9	122.8	125.7	131.4	132.3
167.5°	123.8	124.7	125.7	130.4	130.4
170°	124.7	125.7	126.6	129.5	129.5
172.5°	126.6	126.6	126.6	128.5	128.5
175°	127.6	127.6	126.6	128.5	127.6
177.5°	127.6	127.6	126.6	128.5	127.6
180°	127.6	127.6	127.6	127.6	127.6



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	35.2	46.6	168.5	335.2	339.0
110°	40.0	51.4	155.2	332.4	360.0



(END OF REPORT)