

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621976

Luminaire Tested: VLT-BB-M-125U-075D-930-UNV-STD-W-4

Issue Date: 9/2/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P621976  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-26)  
Test Lab: INNOVATION CENTER  
Issue Date: 10/28/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: VLT-BB-M-125U-075D-930-UNV-STD-W-4  
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE  
BLACK BAFFLE WITH MEDIUM OPTIC  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7000.8 lumens  
Efficiency: N/A  
Efficacy: 97.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.14  
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P621976  
CATALOG NUMBER: VLT-BB-M-125U-075D-930-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P621976

CATALOG NUMBER: VLT-BB-M-125U-075D-930-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	97	93	90	87	88	85	82	80	70	68	66	55	54	53	42	42	41	35				
2	89	83	78	74	81	76	72	68	63	60	57	51	49	47	39	38	37	32				
3	83	75	69	64	75	69	63	59	57	54	50	47	44	42	37	35	34	30				
4	77	67	61	56	70	62	56	52	52	48	45	43	40	38	34	32	31	27				
5	71	61	54	49	65	56	50	46	48	43	40	39	36	34	32	30	28	25				
6	66	55	48	43	60	51	45	41	44	39	36	36	33	31	29	27	26	23				
7	61	51	44	39	56	47	41	36	40	35	32	33	30	28	27	25	24	21				
8	57	46	39	35	53	43	37	33	37	32	29	31	28	25	26	23	22	19				
9	54	43	36	31	49	40	34	30	34	30	27	29	26	23	24	22	20	18				
10	50	39	33	29	46	37	31	27	32	27	24	27	24	21	22	20	19	17				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13932	13932	13932
5°	13766	13975	14246
10°	13957	14158	14369
15°	14241	14273	14359
20°	14185	14163	14031
25°	13779	13722	13562
30°	12956	12932	12693
35°	11643	11655	11326
40°	9453	9453	4326
45°	5436	6612	88
50°	1714	1584	80
55°	598	126	73
60°	42	83	83
65°	24	73	73
70°	29	90	90
75°	0	80	80
80°	0	120	120
85°	0	115	115

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 6612 cd/sqm



TEST NUMBER: P621976

CATALOG NUMBER: VLT-BB-M-125U-075D-930-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	185.5	2.6
10°-20°	541.4	7.7
20°-30°	790.8	11.3
30°-40°	783.2	11.2
40°-50°	327.9	4.7
50°-60°	35.1	0.5
60°-70°	4.9	0.1
70°-80°	3.0	0.0
80°-90°	3.2	0.0
90°-100°	99.0	1.4
100°-110°	705.5	10.1
110°-120°	957.8	13.7
120°-130°	779.6	11.1
130°-140°	627.0	9.0
140°-150°	494.3	7.1
150°-160°	361.4	5.2
160°-170°	224.5	3.2
170°-180°	76.6	1.1
0°-30°	1517.7	21.7
0°-40°	2300.9	32.9
0°-60°	2663.9	38.1
0°-90°	2675.0	38.2
90°-120°	1762.4	25.2
90°-150°	3663.3	52.3
90°-180°	4326.0	61.8
0°-180°	7000.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1942	1942	1942	1942	1942	
5°	1911	1945	1940	1945	1978	183
15°	1917	1956	1921	1907	1933	538
25°	1740	1770	1733	1692	1713	795
35°	1329	1332	1330	1304	1293	815
45°	536	636	652	13	9	420
55°	48	63	10	7	6	54
65°	1	6	4	4	4	2
75°	0	3	3	3	3	0
85°	0	1	1	1	1	0
90°	0	5	10	15	15	2
95°	40	75	40	46	56	45
105°	157	241	917	1171	775	166
115°	279	338	790	1642	1920	277
125°	400	455	744	1302	1540	356
135°	496	551	750	1072	1231	382
145°	588	637	755	934	1033	369
155°	689	714	770	847	886	316
165°	765	775	790	811	826	215
175°	805	810	805	800	795	76
180°	805	805	805	805	805	



TEST NUMBER: P621976

CATALOG NUMBER: VLT-BB-M-125U-075D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1941.5	1941.5	1941.5	1941.5	1941.5
2.5°	1920.7	1947.8	1939.2	1937.3	1954.2
5°	1911.1	1945.1	1940.1	1945.1	1977.7
7.5°	1912.0	1943.4	1945.3	1945.1	1977.7
10°	1915.4	1948.0	1943.0	1939.3	1971.9
12.5°	1920.1	1953.8	1934.8	1928.9	1960.3
15°	1916.9	1956.5	1921.2	1907.3	1932.8
17.5°	1887.6	1933.5	1887.1	1860.3	1879.0
20°	1857.5	1905.7	1854.6	1817.4	1837.3
22.5°	1814.7	1859.4	1810.6	1767.7	1790.9
25°	1740.3	1770.0	1733.0	1691.5	1712.8
27.5°	1638.9	1655.9	1634.9	1597.5	1610.5
30°	1563.6	1575.0	1560.7	1523.3	1531.8
32.5°	1480.2	1485.9	1477.3	1443.3	1447.2
35°	1329.1	1331.9	1330.5	1304.2	1292.9
37.5°	1142.3	1148.0	1144.6	1030.2	710.9
40°	1009.1	1014.8	1009.1	603.4	461.8
42.5°	842.3	878.6	869.0	411.5	131.8
45°	535.7	636.2	651.5	12.9	8.7
47.5°	264.7	373.1	306.4	8.4	8.4
50°	153.5	220.0	141.9	7.2	7.2
52.5°	102.5	133.9	41.1	7.2	7.2
55°	47.8	63.3	10.1	7.2	5.8
57.5°	16.8	31.8	6.9	5.8	5.8
60°	2.9	15.6	5.8	5.8	5.8
62.5°	1.7	8.8	5.8	4.7	5.8
65°	1.4	5.7	4.3	4.3	4.3
67.5°	1.4	4.3	4.3	4.3	4.3
70°	1.4	4.3	4.3	4.3	4.3
72.5°	0.3	3.1	3.2	3.2	4.3
75°	0.0	2.8	2.9	2.9	2.9
77.5°	0.0	2.8	2.9	2.9	2.9
80°	0.0	2.8	2.9	2.9	2.9
82.5°	0.0	1.7	1.7	1.8	2.9
85°	0.0	1.4	1.4	1.4	1.4
87.5°	0.0	2.1	3.2	4.2	4.2
90°	0.0	5.0	10.1	15.2	15.2
92.5°	12.2	17.1	22.3	31.5	35.5
95°	40.5	75.2	40.5	45.8	55.7
97.5°	71.9	144.2	297.8	87.9	76.0
100°	96.2	180.4	597.6	175.9	116.5
102.5°	120.5	208.7	808.3	464.2	254.2
105°	157.0	241.2	916.7	1171.1	774.9
107.5°	193.5	256.9	875.2	1704.4	1596.4
110°	217.8	277.2	850.9	1790.9	1924.6



TEST NUMBER: P621976

CATALOG NUMBER: VLT-BB-M-125U-075D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	242.1	301.5	826.6	1740.3	1965.1
115°	278.6	338.0	790.1	1642.2	1919.5
117.5°	316.0	374.5	781.0	1536.0	1821.3
120°	344.4	398.9	764.8	1455.3	1752.4
122.5°	364.7	423.1	744.5	1385.8	1659.2
125°	400.1	454.6	744.5	1302.0	1539.7
127.5°	429.5	485.0	745.5	1204.7	1439.4
130°	445.7	505.1	749.6	1139.6	1362.4
132.5°	466.0	525.4	749.6	1110.3	1293.5
135°	496.3	550.8	749.6	1072.3	1230.7
137.5°	521.7	580.1	749.6	1030.2	1165.9
140°	541.9	596.4	749.6	1005.6	1129.4
142.5°	562.2	612.7	753.6	977.1	1093.0
145°	587.5	637.0	754.6	934.2	1033.2
147.5°	617.9	661.5	760.7	903.3	979.5
150°	638.2	677.8	764.8	882.7	947.1
152.5°	658.4	694.1	764.8	866.2	918.7
155°	688.8	713.6	769.8	846.7	886.3
157.5°	713.1	736.9	775.9	834.3	863.0
160°	729.3	749.1	780.0	826.1	850.9
162.5°	741.5	761.3	784.0	821.9	838.7
165°	764.8	774.7	790.1	810.7	825.6
167.5°	777.9	786.9	795.2	805.5	814.4
170°	790.1	795.1	795.2	805.4	810.4
172.5°	794.2	803.1	799.2	801.4	806.3
175°	805.3	810.2	805.3	800.1	795.2
177.5°	805.3	809.3	805.3	805.2	801.2
180°	805.3	805.3	805.3	805.3	805.3



TEST NUMBER: P621976

CATALOG NUMBER: VLT-BB-M-125U-075D-930-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00