

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845347

Luminaire Tested: **SQ4P-WB-075U-125D-B50-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845347
REPORT IS A COMBINATION OF REPORTS P700242 AND P700245
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-075U-125D-B50-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6258.8 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 64.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845347

CATALOG NUMBER: SQ4P-WB-075U-125D-B50-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845347

CATALOG NUMBER: SQ4P-WB-075U-125D-B50-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62																			
1	102	98	95	91	95	92	89	86	81	79	77	71	69	68	61	60	59	55																			
2	94	87	82	77	88	82	77	73	73	69	66	64	61	59	56	54	52	48																			
3	87	78	71	66	81	74	68	63	65	61	57	58	54	52	51	48	46	43																			
4	80	70	63	57	75	66	60	55	59	54	50	53	49	46	46	44	41	38																			
5	74	63	56	50	70	60	53	48	54	49	45	48	44	41	43	39	37	34																			
6	69	58	50	45	65	55	48	43	49	44	40	44	40	37	39	36	33	31																			
7	64	53	45	40	60	50	43	39	45	40	36	41	36	33	36	33	30	28																			
8	60	48	41	36	56	46	39	35	42	36	32	38	33	30	34	30	28	26																			
9	56	45	38	33	53	43	36	32	39	33	30	35	31	28	32	28	25	24																			
10	53	41	34	30	50	39	33	29	36	31	27	33	28	25	30	26	24	22																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24467	24467	24467
5°	24162	24074	24216
10°	22827	23035	23567
15°	21072	21563	22529
20°	19137	19856	21169
25°	17164	18101	19724
30°	15347	16350	18222
35°	13420	14390	16449
40°	11294	12192	14238
45°	9321	10125	11889
50°	7781	8484	9902
55°	6606	7280	8178
60°	5648	6314	6528
65°	4497	5307	4216
70°	3987	4143	2573
75°	3689	3362	1579
80°	3400	3092	1355
85°	3059	2837	1122



TEST NUMBER: P845347

CATALOG NUMBER: SQ4P-WB-075U-125D-B50-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.2	3.9
10°-20°	632.7	10.1
20°-30°	819.5	13.1
30°-40°	802.5	12.8
40°-50°	614.2	9.8
50°-60°	409.3	6.5
60°-70°	223.4	3.6
70°-80°	93.1	1.5
80°-90°	27.2	0.4
90°-100°	146.8	2.3
100°-110°	510.8	8.2
110°-120°	494.8	7.9
120°-130°	388.1	6.2
130°-140°	307.2	4.9
140°-150°	237.1	3.8
150°-160°	169.9	2.7
160°-170°	103.9	1.7
170°-180°	35.2	0.6
0°-30°	1695.4	27.1
0°-40°	2497.9	39.9
0°-60°	3521.5	56.3
0°-90°	3865.1	61.8
90°-120°	1152.3	18.4
90°-150°	2084.7	33.3
90°-180°	2394.0	38.2
0°-180°	6258.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2652	2652	2652	2652	2652	
5°	2609	2583	2599	2606	2615	243
15°	2206	2198	2258	2319	2359	616
25°	1686	1691	1778	1856	1938	775
35°	1192	1197	1278	1364	1460	741
45°	714	728	776	835	911	557
55°	411	428	453	470	508	372
65°	206	223	243	213	193	214
75°	104	104	94	65	44	111
85°	29	29	27	17	11	32
90°	6	8	8	6	3	5
95°	25	85	248	63	39	26
105°	85	121	537	906	842	90
115°	149	179	399	842	994	147
125°	201	248	372	628	749	180
135°	242	272	369	523	592	188
145°	284	303	366	452	490	177
155°	322	333	360	402	416	148
165°	352	355	363	380	383	99
175°	369	369	366	372	369	35
180°	369	369	369	369	369	



TEST NUMBER: P845347

CATALOG NUMBER: SQ4P-WB-075U-125D-B50-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2651.9	2651.9	2651.9	2651.9	2651.9
2.5°	2658.4	2634.7	2640.8	2640.5	2633.1
5°	2608.9	2582.6	2599.4	2605.5	2614.7
7.5°	2512.0	2492.2	2523.1	2545.7	2564.1
10°	2436.6	2419.5	2458.8	2491.9	2515.6
12.5°	2349.2	2334.7	2383.4	2427.7	2459.0
15°	2206.1	2198.2	2257.5	2318.8	2358.6
17.5°	2053.3	2049.4	2117.4	2189.0	2239.8
20°	1949.1	1948.0	2022.3	2097.1	2156.1
22.5°	1844.0	1846.3	1924.5	2002.3	2069.7
25°	1686.1	1690.6	1778.1	1855.5	1937.5
27.5°	1540.2	1542.3	1632.4	1714.3	1801.8
30°	1440.6	1446.2	1534.7	1619.5	1710.4
32.5°	1341.0	1347.7	1434.3	1521.8	1614.5
35°	1191.5	1197.3	1277.6	1363.7	1460.4
37.5°	1037.3	1045.2	1116.6	1197.7	1293.1
40°	937.7	949.4	1012.3	1089.0	1182.2
42.5°	841.9	856.2	914.6	987.2	1071.3
45°	714.4	728.1	776.0	834.7	911.2
47.5°	604.5	620.3	657.3	707.8	772.9
50°	542.1	557.1	591.1	628.5	689.9
52.5°	487.3	502.1	532.4	561.3	613.8
55°	410.7	427.8	452.6	469.9	508.4
57.5°	348.0	364.3	384.0	391.7	415.2
60°	306.1	324.3	342.2	341.1	353.8
62.5°	267.9	283.4	301.1	288.7	289.5
65°	206.0	223.2	243.1	212.6	193.1
67.5°	166.5	169.9	190.7	148.3	125.1
70°	147.8	147.8	153.6	114.8	95.4
72.5°	130.1	130.1	124.9	93.2	72.9
75°	103.5	103.5	94.3	64.8	44.3
77.5°	79.8	79.0	72.2	48.2	32.2
80°	64.0	64.0	58.2	38.2	25.5
82.5°	50.1	50.1	45.0	29.8	18.9
85°	28.9	28.9	26.8	17.4	10.6
87.5°	10.3	10.3	9.2	5.5	4.8
90°	5.5	8.3	8.3	5.5	2.8
92.5°	13.8	41.3	38.6	16.5	13.8
95°	24.8	85.3	247.7	63.3	38.6
97.5°	38.6	96.3	495.4	225.7	121.1
100°	52.3	101.9	578.0	542.3	349.6
102.5°	68.8	110.1	575.3	762.5	627.6
105°	85.3	121.1	536.8	905.6	842.3



TEST NUMBER: P845347

CATALOG NUMBER: SQ4P-WB-075U-125D-B50-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	132.1	162.4	418.4	911.1	1037.7
115°	148.6	178.9	399.1	842.3	993.6
117.5°	165.2	198.2	388.1	778.9	930.3
120°	178.9	214.7	379.9	718.4	867.0
122.5°	189.9	231.2	374.3	668.9	803.7
125°	201.0	247.7	371.6	627.6	748.7
127.5°	211.9	258.8	371.6	597.3	699.2
130°	223.0	264.3	368.8	567.0	657.8
132.5°	233.9	266.9	368.8	545.0	622.1
135°	242.2	272.5	368.8	522.9	591.8
137.5°	253.2	278.0	368.8	503.7	567.0
140°	261.5	286.3	368.8	484.4	539.5
142.5°	272.5	294.6	368.8	465.2	514.7
145°	283.5	302.7	366.1	451.5	489.9
147.5°	294.6	311.0	363.3	437.6	467.9
150°	302.7	319.3	363.3	423.8	448.7
152.5°	313.8	327.5	360.5	410.1	432.1
155°	322.1	333.0	360.5	401.8	415.7
157.5°	330.3	341.3	360.5	393.6	404.6
160°	338.5	346.8	363.3	388.1	396.3
162.5°	346.8	352.3	363.3	382.6	388.1
165°	352.3	355.1	363.3	379.9	382.6
167.5°	357.9	360.5	363.3	377.1	377.1
170°	360.5	363.3	366.1	374.3	374.3
172.5°	366.1	366.1	366.1	371.6	371.6
175°	368.8	368.8	366.1	371.6	368.8
177.5°	368.8	368.8	366.1	371.6	368.8
180°	368.8	368.8	368.8	368.8	368.8



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	<i>101.9</i>	134.9	487.2	968.9	979.9
110°	<i>115.6</i>	148.6	448.7	960.6	1040.5



(END OF REPORT)