

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P622036

Luminaire Tested: VLT-WB-M-0U-075D-930-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P622036
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-32)
Test Lab: INNOVATION CENTER
Issue Date: 10/28/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-WB-M-0U-075D-930-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
WHITE BAFFLE WITH MEDIUM OPTIC
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2876.8 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.16 / 1.14
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P622036
CATALOG NUMBER: VLT-WB-M-0U-075D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P622036

CATALOG NUMBER: VLT-WB-M-0U-075D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	107	101	97	93	104	100	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74		81	77	73		79	75	72	71
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74	69	66	65
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	57	77	68	62	57	67	61	57		65	60	56		64	60	56	55
8	74	64	57	53	73	63	57	53	62	56	52		61	56	52		60	55	52	50
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56	52	48	47
10	67	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14882	14882	14882
5°	14727	14939	15224
10°	14876	15079	15304
15°	15102	15178	15254
20°	15030	15007	14806
25°	14619	14444	14270
30°	13755	13621	13329
35°	12459	12278	11983
40°	10133	10064	4757
45°	6271	7149	328
50°	2392	1917	196
55°	1175	349	74
60°	568	168	22
65°	523	25	25
70°	493	31	31
75°	488	42	42
80°	483	62	0
85°	486	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 7149 cd/sqm



TEST NUMBER: P622036

CATALOG NUMBER: VLT-WB-M-0U-075D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.0	6.9
10°-20°	574.5	20.0
20°-30°	835.4	29.0
30°-40°	831.3	28.9
40°-50°	365.6	12.7
50°-60°	54.0	1.9
60°-70°	12.3	0.4
70°-80°	4.6	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1608.0	55.9
0°-40°	2439.3	84.8
0°-60°	2858.8	99.4
0°-90°	2876.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2876.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2074	2074	2074	2074	2074	
5°	2044	2080	2074	2079	2114	195
15°	2033	2076	2043	2023	2053	572
25°	1846	1881	1824	1776	1802	844
35°	1422	1418	1402	1372	1368	871
45°	618	703	704	47	32	478
55°	94	101	28	10	6	95
65°	31	26	2	2	2	31
75°	18	3	2	2	2	19
85°	6	0	0	0	0	6
90°	0	0	0	0	0	



TEST NUMBER: P622036

CATALOG NUMBER: VLT-WB-M-0U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2073.9	2073.9	2073.9	2073.9	2073.9
2.5°	2050.4	2081.4	2070.3	2069.6	2087.9
5°	2044.5	2080.4	2073.9	2079.0	2113.5
7.5°	2040.4	2076.6	2076.5	2074.0	2108.5
10°	2041.6	2078.9	2069.4	2065.8	2100.3
12.5°	2041.6	2081.2	2061.2	2051.8	2087.4
15°	2032.8	2075.8	2043.0	2023.2	2053.3
17.5°	2001.1	2047.8	2002.8	1964.1	1989.3
20°	1968.2	2018.4	1965.2	1915.9	1938.8
22.5°	1927.1	1971.6	1913.6	1861.9	1886.0
25°	1846.4	1880.8	1824.3	1776.5	1802.3
27.5°	1744.5	1763.4	1721.3	1675.3	1692.0
30°	1660.0	1674.3	1643.8	1600.0	1608.6
32.5°	1569.6	1579.3	1554.6	1516.6	1524.1
35°	1422.2	1417.9	1401.6	1372.2	1367.9
37.5°	1229.6	1222.2	1211.7	1097.8	787.3
40°	1081.7	1084.6	1074.4	671.4	507.8
42.5°	925.5	943.3	928.8	457.2	166.1
45°	617.9	702.6	704.5	46.6	32.3
47.5°	334.0	426.2	346.7	28.9	23.5
50°	214.3	267.4	171.7	21.9	17.6
52.5°	153.2	178.8	67.2	17.2	12.9
55°	93.9	101.1	27.9	10.2	5.9
57.5°	56.1	66.7	17.6	3.8	1.5
60°	39.6	46.8	11.7	1.5	1.5
62.5°	34.9	35.2	8.2	1.5	1.5
65°	30.8	26.5	1.5	1.5	1.5
67.5°	27.0	19.3	1.5	1.5	1.5
70°	23.5	13.4	1.5	1.5	1.5
72.5°	21.1	8.8	1.5	1.5	1.5
75°	17.6	3.3	1.5	1.5	1.5
77.5°	14.1	1.7	1.5	1.2	1.2
80°	11.7	1.7	1.5	0.0	0.0
82.5°	9.4	1.6	0.3	0.0	0.0
85°	5.9	0.1	0.0	0.0	0.0
87.5°	2.3	0.1	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P622036

CATALOG NUMBER: VLT-WB-M-0U-075D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.62	6.71	5.99	7.02	7.33	0.00	0.00	0.00	0.00	0.00
	3H	6.08	7.03	6.46	7.36	7.73	0.00	0.00	0.00	0.00	0.00
	4H	6.25	7.13	6.66	7.48	7.87	0.00	0.00	0.00	0.00	0.00
	6H	6.45	7.25	6.86	7.62	8.02	0.00	0.00	0.00	0.00	0.00
	8H	6.54	7.29	6.97	7.68	8.09	0.00	0.00	0.00	0.00	0.00
	12H	6.61	7.33	7.04	7.71	8.14	0.00	0.00	0.00	0.00	0.00
4H	2H	5.35	6.23	5.76	6.58	6.97	0.00	0.00	0.00	0.00	0.00
	3H	5.84	6.55	6.26	6.96	7.37	0.00	0.00	0.00	0.00	0.00
	4H	6.02	6.65	6.46	7.07	7.52	0.00	0.00	0.00	0.00	0.00
	6H	6.26	6.79	6.73	7.24	7.72	0.00	0.00	0.00	0.00	0.00
	8H	6.37	6.87	6.85	7.32	7.80	0.00	0.00	0.00	0.00	0.00
	12H	6.49	6.92	6.98	7.41	7.89	0.00	0.00	0.00	0.00	0.00
8H	4H	5.85	6.35	6.32	6.80	7.28	0.00	0.00	0.00	0.00	0.00
	6H	6.08	6.48	6.59	6.98	7.47	0.00	0.00	0.00	0.00	0.00
	8H	6.20	6.56	6.73	7.08	7.58	0.00	0.00	0.00	0.00	0.00
	12H	6.35	6.66	6.87	7.16	7.74	0.00	0.00	0.00	0.00	0.00
12H	4H	5.79	6.22	6.28	6.71	7.19	0.00	0.00	0.00	0.00	0.00
	6H	6.01	6.37	6.54	6.89	7.38	0.00	0.00	0.00	0.00	0.00
	8H	6.15	6.46	6.67	6.96	7.54	0.00	0.00	0.00	0.00	0.00