

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621482

Luminaire Tested: VLT-F-0U-050D-835-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P621482
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-1)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-F-0U-050D-835-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
FROSTED LENS
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1973.9 lumens
Efficiency: N/A
Efficacy: 137.1 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.12 / 1.23
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 14.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P621482
CATALOG NUMBER: VLT-F-OU-050D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P621482

CATALOG NUMBER: VLT-F-OU-050D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			87	
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75	
3	94	85	77	72	92	83	76	71	80	74	70	78	73	69	75	71	67	65			65	
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57	
5	80	69	61	55	78	68	60	54	66	59	54	64	58	53	62	57	53	51			51	
6	75	63	54	49	73	62	54	48	60	53	48	58	52	48	57	51	47	45			45	
7	70	57	49	44	68	56	49	43	55	48	43	54	47	43	52	47	43	41			41	
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	39	37			37	
9	61	49	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33			33	
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31			31	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6946	6946	6946
5°	6872	6922	6980
10°	6835	6864	6900
15°	6760	6768	6768
20°	6651	6621	6560
25°	6524	6413	6303
30°	6372	6190	5941
35°	6202	5922	5212
40°	6023	5546	4197
45°	5835	4912	3044
50°	5638	4108	2110
55°	5442	3128	1576
60°	5238	2167	1191
65°	5009	1545	1223
70°	4679	1301	1259
75°	4325	1331	1275
80°	3761	1405	1322
85°	3046	1564	1317

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5835 cd/sqm



TEST NUMBER: P621482

CATALOG NUMBER: VLT-F-OU-050D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.2	4.6
10°-20°	256.5	13.0
20°-30°	373.1	18.9
30°-40°	412.8	20.9
40°-50°	354.4	18.0
50°-60°	245.4	12.4
60°-70°	146.2	7.4
70°-80°	72.0	3.7
80°-90°	22.2	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	720.8	36.5
0°-40°	1133.6	57.4
0°-60°	1733.4	87.8
0°-90°	1973.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1973.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	968	968	968	968	968	
5°	954	969	961	960	969	91
15°	910	922	911	906	911	256
25°	824	830	810	796	796	379
35°	708	706	676	621	595	442
45°	575	565	484	350	300	444
55°	435	416	250	144	126	389
65°	295	237	91	73	72	292
75°	156	68	48	47	46	165
85°	37	18	19	17	16	45
90°	0	0	0	0	0	



TEST NUMBER: P621482

CATALOG NUMBER: VLT-F-OU-050D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	968.0	968.0	968.0	968.0	968.0
2.5°	960.0	971.0	965.6	965.7	969.6
5°	954.0	968.7	961.0	960.2	969.0
7.5°	945.2	958.7	950.8	949.8	957.4
10°	938.0	950.7	942.0	940.2	947.0
12.5°	927.6	940.3	930.8	927.4	934.2
15°	910.0	921.7	911.0	906.1	911.0
17.5°	887.8	897.6	885.4	877.7	880.6
20°	871.0	880.8	867.0	856.1	859.0
22.5°	852.6	860.8	845.4	832.9	835.0
25°	824.0	829.9	810.0	796.0	796.0
27.5°	792.2	795.7	772.6	757.9	753.8
30°	769.0	771.0	747.0	729.7	717.0
32.5°	745.0	746.2	719.0	691.2	671.4
35°	708.0	706.0	676.0	621.4	595.0
37.5°	668.6	664.3	628.8	545.7	506.4
40°	643.0	637.1	592.0	492.0	448.0
42.5°	616.6	608.4	551.2	436.7	388.0
45°	575.0	565.2	484.0	349.9	300.0
47.5°	533.8	520.9	415.2	271.0	228.2
50°	505.0	491.3	368.0	223.2	189.0
52.5°	476.2	462.5	320.0	187.4	160.2
55°	435.0	416.4	250.0	143.6	126.0
57.5°	393.0	366.4	186.2	111.9	98.2
60°	365.0	329.8	151.0	92.8	83.0
62.5°	337.8	293.2	123.8	81.0	79.0
65°	295.0	237.3	91.0	73.0	72.0
67.5°	254.2	181.1	67.6	65.8	64.8
70°	223.0	142.8	62.0	61.0	60.0
72.5°	195.0	109.3	56.4	55.4	54.4
75°	156.0	68.0	48.0	47.0	46.0
77.5°	116.6	42.9	39.6	38.6	37.6
80°	91.0	35.3	34.0	33.0	32.0
82.5°	68.6	28.5	27.6	26.6	25.6
85°	37.0	18.4	19.0	17.0	16.0
87.5°	12.8	8.9	8.8	7.2	6.4
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P621482

CATALOG NUMBER: VLT-F-0U-050D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.30	19.77	18.67	20.08	20.40	10.53	12.01	10.90	12.32	12.63
	3H	19.84	21.15	20.22	21.48	21.84	11.93	13.25	12.31	13.57	13.94
	4H	20.38	21.61	20.78	21.96	22.34	12.61	13.84	13.01	14.19	14.57
	6H	20.80	21.94	21.22	22.31	22.70	13.23	14.37	13.64	14.73	15.13
	8H	20.95	22.03	21.38	22.42	22.82	13.47	14.55	13.90	14.94	15.34
	12H	21.05	22.08	21.48	22.46	22.89	13.66	14.69	14.09	15.07	15.50
4H	2H	18.20	19.43	18.60	19.78	20.16	11.22	12.45	11.62	12.80	13.18
	3H	19.89	20.91	20.30	21.31	21.71	12.83	13.84	13.24	14.24	14.65
	4H	20.50	21.41	20.93	21.83	22.27	13.64	14.56	14.08	14.97	15.41
	6H	21.02	21.82	21.48	22.26	22.72	14.41	15.20	14.87	15.65	16.11
	8H	21.22	21.96	21.68	22.41	22.87	14.71	15.45	15.18	15.90	16.37
	12H	21.38	22.04	21.86	22.52	22.99	14.96	15.62	15.44	16.10	16.57
8H	4H	20.46	21.20	20.92	21.64	22.11	14.14	14.88	14.60	15.32	15.79
	6H	21.01	21.62	21.51	22.11	22.59	15.04	15.65	15.54	16.14	16.62
	8H	21.24	21.79	21.76	22.31	22.79	15.43	15.98	15.95	16.49	16.98
	12H	21.46	21.94	21.97	22.44	23.00	15.78	16.26	16.29	16.76	17.32
12H	4H	20.43	21.09	20.92	21.57	22.04	14.21	14.87	14.69	15.35	15.82
	6H	20.98	21.53	21.50	22.04	22.53	15.15	15.70	15.67	16.21	16.70
	8H	21.25	21.74	21.76	22.23	22.80	15.62	16.11	16.13	16.60	17.17