

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P622028

Luminaire Tested: VLT-WB-M-075U-100D-935-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P622028
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-32)
Test Lab: INNOVATION CENTER
Issue Date: 10/28/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-WB-M-075U-100D-935-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
WHITE BAFFLE WITH MEDIUM OPTIC
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6447.1 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.16 / 1.14
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 62.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P622028
CATALOG NUMBER: VLT-WB-M-075U-100D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P622028

CATALOG NUMBER: VLT-WB-M-075U-100D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	102	99	96	93	96	93	90	88	82	80	78	71	70	69	62	61	60	56
2	96	90	85	81	89	84	80	77	75	72	69	66	64	62	58	56	55	51
3	89	81	75	71	83	77	72	67	69	65	61	61	58	56	54	52	50	46
4	83	74	67	62	78	70	64	60	63	58	55	56	53	50	50	47	46	43
5	77	68	61	56	73	64	58	54	58	53	50	52	48	46	46	44	42	39
6	72	62	55	50	68	59	53	48	53	48	45	48	44	41	43	40	38	36
7	68	57	50	45	64	54	48	44	49	44	41	45	41	38	40	37	35	33
8	63	53	46	41	60	50	44	40	46	41	37	42	38	35	38	35	32	30
9	59	49	42	37	56	47	40	36	43	38	34	39	35	32	35	32	30	28
10	56	45	39	34	53	43	37	33	40	35	31	36	32	30	33	30	28	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20078	20078	20078
5°	19870	20155	20540
10°	20070	20345	20647
15°	20375	20478	20581
20°	20278	20248	19976
25°	19724	19489	19254
30°	18557	18377	17983
35°	16809	16566	16167
40°	13671	13578	6418
45°	8461	9646	442
50°	3227	2587	266
55°	1585	470	99
60°	768	227	29
65°	706	34	34
70°	665	42	42
75°	660	55	55
80°	653	83	0
85°	650	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 9646 cd/sqm



TEST NUMBER: P622028

CATALOG NUMBER: VLT-WB-M-075U-100D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.2	4.1
10°-20°	775.2	12.0
20°-30°	1127.1	17.5
30°-40°	1121.6	17.4
40°-50°	493.2	7.7
50°-60°	72.8	1.1
60°-70°	16.6	0.3
70°-80°	6.2	0.1
80°-90°	2.5	0.0
90°-100°	58.7	0.9
100°-110°	418.3	6.5
110°-120°	567.9	8.8
120°-130°	462.2	7.2
130°-140°	371.7	5.8
140°-150°	293.1	4.5
150°-160°	214.3	3.3
160°-170°	133.1	2.1
170°-180°	45.4	0.7
0°-30°	2169.4	33.6
0°-40°	3291.0	51.0
0°-60°	3857.1	59.8
0°-90°	3882.4	60.2
90°-120°	1044.9	16.2
90°-150°	2171.9	33.7
90°-180°	2565.0	39.8
0°-180°	6447.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2798	2798	2798	2798	2798	
5°	2758	2807	2798	2805	2852	263
15°	2743	2801	2756	2730	2770	771
25°	2491	2538	2461	2397	2432	1139
35°	1919	1913	1891	1851	1846	1175
45°	834	948	950	63	44	646
55°	127	136	38	14	8	128
65°	42	36	2	2	2	41
75°	24	4	2	2	2	25
85°	8	0	0	0	0	8
90°	0	3	6	9	9	1
95°	24	45	24	27	33	27
105°	93	143	544	694	459	98
115°	165	200	468	974	1138	164
125°	237	270	441	772	913	211
135°	294	327	444	636	730	226
145°	348	378	447	554	613	219
155°	408	423	456	502	526	187
165°	453	459	468	481	490	127
175°	478	480	478	474	471	45
180°	478	478	478	478	478	



TEST NUMBER: P622028

CATALOG NUMBER: VLT-WB-M-075U-100D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2798.0	2798.0	2798.0	2798.0	2798.0
2.5°	2766.3	2808.1	2793.2	2792.2	2817.0
5°	2758.4	2806.8	2798.0	2805.0	2851.5
7.5°	2752.9	2801.6	2801.6	2798.3	2844.7
10°	2754.4	2804.8	2792.1	2787.2	2833.6
12.5°	2754.4	2807.9	2781.0	2768.2	2816.2
15°	2742.6	2800.6	2756.4	2729.6	2770.3
17.5°	2699.8	2762.9	2702.2	2649.9	2683.9
20°	2655.4	2723.2	2651.5	2584.8	2615.8
22.5°	2600.0	2660.0	2581.8	2512.0	2544.5
25°	2491.1	2537.5	2461.4	2396.8	2431.7
27.5°	2353.6	2379.2	2322.4	2260.3	2282.8
30°	2239.6	2259.0	2217.8	2158.7	2170.3
32.5°	2117.6	2130.8	2097.4	2046.2	2056.2
35°	1918.8	1913.0	1891.1	1851.3	1845.5
37.5°	1659.0	1648.9	1634.8	1481.2	1062.2
40°	1459.4	1463.3	1449.5	905.9	685.1
42.5°	1248.7	1272.7	1253.1	616.8	224.2
45°	833.7	947.9	950.5	62.9	43.6
47.5°	450.7	575.0	467.7	39.0	31.7
50°	289.1	360.7	231.7	29.6	23.8
52.5°	206.7	241.2	90.7	23.2	17.4
55°	126.7	136.4	37.6	13.7	7.9
57.5°	75.6	90.0	23.8	5.1	2.0
60°	53.5	63.1	15.8	2.0	2.0
62.5°	47.1	47.5	11.1	2.0	2.0
65°	41.6	35.8	2.0	2.0	2.0
67.5°	36.4	26.0	2.0	2.0	2.0
70°	31.7	18.1	2.0	2.0	2.0
72.5°	28.5	11.9	2.0	2.0	2.0
75°	23.8	4.4	2.0	2.0	2.0
77.5°	19.0	2.4	2.0	1.6	1.6
80°	15.8	2.3	2.0	0.0	0.0
82.5°	12.7	2.2	0.4	0.0	0.0
85°	7.9	0.2	0.0	0.0	0.0
87.5°	3.2	0.7	1.2	1.8	1.8
90°	0.0	2.9	6.0	9.0	9.0
92.5°	7.2	10.1	13.2	18.7	21.0
95°	24.0	44.6	24.0	27.2	33.0
97.5°	42.6	85.5	176.6	52.1	45.0
100°	57.1	107.0	354.3	104.3	69.1
102.5°	71.5	123.7	479.3	275.2	150.7
105°	93.1	143.0	543.5	694.3	459.4
107.5°	114.7	152.3	518.9	1010.5	946.5
110°	129.1	164.4	504.5	1061.8	1141.1

TEST NUMBER: P622028

CATALOG NUMBER: VLT-WB-M-075U-100D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	143.5	178.8	490.1	1031.8	<i>1165.1</i>
115°	165.2	200.4	468.4	973.7	<i>1138.1</i>
117.5°	187.4	222.0	463.0	910.7	<i>1079.8</i>
120°	204.2	236.5	453.4	862.8	<i>1039.0</i>
122.5°	216.2	250.9	441.4	821.7	<i>983.7</i>
125°	237.2	269.5	441.4	771.9	<i>912.9</i>
127.5°	254.6	287.5	442.0	714.2	<i>853.4</i>
130°	264.3	299.5	444.4	675.6	<i>807.8</i>
132.5°	276.3	311.5	444.4	658.3	<i>766.9</i>
135°	294.3	326.6	444.4	635.7	<i>729.7</i>
137.5°	309.3	343.9	444.4	610.8	<i>691.3</i>
140°	321.3	353.6	444.4	596.2	<i>669.6</i>
142.5°	333.3	363.3	446.8	579.3	<i>648.0</i>
145°	348.3	377.7	447.4	553.9	<i>612.6</i>
147.5°	366.3	392.2	451.0	535.5	<i>580.8</i>
150°	378.4	401.8	453.4	523.4	<i>561.5</i>
152.5°	390.4	411.5	453.4	513.6	<i>544.7</i>
155°	408.4	423.1	456.4	502.0	<i>525.5</i>
157.5°	422.8	436.9	460.0	494.7	<i>511.7</i>
160°	432.4	444.2	462.4	489.8	<i>504.5</i>
162.5°	439.6	451.4	464.8	487.3	<i>497.3</i>
165°	453.4	459.3	468.4	480.7	<i>489.5</i>
167.5°	461.2	466.5	471.4	477.6	<i>482.9</i>
170°	468.4	471.4	471.4	477.5	<i>480.5</i>
172.5°	470.8	476.1	473.8	475.1	<i>478.1</i>
175°	477.5	480.4	477.5	474.4	<i>471.4</i>
177.5°	477.5	479.8	477.5	477.4	<i>475.1</i>
180°	477.5	477.5	477.5	477.5	<i>477.5</i>



TEST NUMBER: P622028

CATALOG NUMBER: VLT-WB-M-075U-100D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.33	4.07	4.24	4.97	6.10	0.00	0.00	0.00	0.00	0.00
	3H	3.78	4.43	4.69	5.33	6.49	0.00	0.00	0.00	0.00	0.00
	4H	3.94	4.55	4.87	5.46	6.63	0.00	0.00	0.00	0.00	0.00
	6H	4.12	4.68	5.06	5.60	6.78	0.00	0.00	0.00	0.00	0.00
	8H	4.20	4.74	5.15	5.67	6.85	0.00	0.00	0.00	0.00	0.00
	12H	4.27	4.78	5.22	5.70	6.90	0.00	0.00	0.00	0.00	0.00
4H	2H	3.04	3.65	3.97	4.56	5.73	0.00	0.00	0.00	0.00	0.00
	3H	3.51	4.02	4.46	4.96	6.14	0.00	0.00	0.00	0.00	0.00
	4H	3.69	4.14	4.64	5.08	6.29	0.00	0.00	0.00	0.00	0.00
	6H	3.92	4.31	4.88	5.27	6.48	0.00	0.00	0.00	0.00	0.00
	8H	4.04	4.40	5.00	5.35	6.57	0.00	0.00	0.00	0.00	0.00
	12H	4.14	4.47	5.12	5.44	6.66	0.00	0.00	0.00	0.00	0.00
8H	4H	3.52	3.88	4.48	4.83	6.05	0.00	0.00	0.00	0.00	0.00
	6H	3.75	4.04	4.74	5.04	6.26	0.00	0.00	0.00	0.00	0.00
	8H	3.88	4.14	4.88	5.13	6.37	0.00	0.00	0.00	0.00	0.00
	12H	4.02	4.25	5.02	5.22	6.51	0.00	0.00	0.00	0.00	0.00
12H	4H	3.44	3.77	4.43	4.74	5.96	0.00	0.00	0.00	0.00	0.00
	6H	3.69	3.95	4.69	4.93	6.17	0.00	0.00	0.00	0.00	0.00
	8H	3.82	4.05	4.81	5.02	6.31	0.00	0.00	0.00	0.00	0.00