

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621913

Luminaire Tested: VLT-BB-M-025U-050D-930-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P621913
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-26)
Test Lab: INNOVATION CENTER
Issue Date: 10/28/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-BB-M-025U-050D-930-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
BLACK BAFFLE WITH MEDIUM OPTIC
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2666.5 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.14
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P621913
CATALOG NUMBER: VLT-BB-M-025U-050D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P621913

CATALOG NUMBER: VLT-BB-M-025U-050D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67				
1	104	101	98	95	99	96	93	91	86	84	82	77	75	74	68	67	66	62				
2	98	92	87	83	92	87	83	80	79	76	73	71	69	67	64	62	61	57				
3	91	84	78	73	86	80	75	71	72	69	65	66	63	60	59	57	55	52				
4	85	76	70	65	81	73	67	63	67	62	59	61	57	55	55	53	51	48				
5	80	70	63	58	76	67	61	57	62	57	53	56	53	50	52	49	46	44				
6	75	64	58	53	71	62	56	51	57	52	48	52	48	45	48	45	43	40				
7	70	59	53	48	66	57	51	47	53	48	44	49	45	42	45	42	39	37				
8	66	55	48	44	62	53	47	42	49	44	40	45	41	38	42	39	36	34				
9	62	51	44	40	59	49	43	39	46	41	37	42	38	35	39	36	34	32				
10	58	47	41	37	55	46	40	36	43	38	34	40	36	33	37	34	31	29				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9372	9372	9372
5°	9260	9400	9583
10°	9389	9524	9665
15°	9579	9601	9659
20°	9542	9527	9438
25°	9269	9231	9122
30°	8715	8700	8538
35°	7832	7840	7619
40°	6359	6359	2910
45°	3656	4448	59
50°	1152	1065	55
55°	402	85	49
60°	27	56	56
65°	17	49	49
70°	21	61	61
75°	0	53	53
80°	0	79	79
85°	0	82	82

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 4448 cd/sqm



TEST NUMBER: P621913

CATALOG NUMBER: VLT-BB-M-025U-050D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	4.7
10°-20°	364.2	13.7
20°-30°	532.0	20.0
30°-40°	526.9	19.8
40°-50°	220.6	8.3
50°-60°	23.6	0.9
60°-70°	3.3	0.1
70°-80°	2.0	0.1
80°-90°	1.3	0.0
90°-100°	19.9	0.7
100°-110°	141.6	5.3
110°-120°	192.2	7.2
120°-130°	156.4	5.9
130°-140°	125.8	4.7
140°-150°	99.2	3.7
150°-160°	72.5	2.7
160°-170°	45.0	1.7
170°-180°	15.4	0.6
0°-30°	1020.9	38.3
0°-40°	1547.8	58.0
0°-60°	1791.9	67.2
0°-90°	1798.5	67.5
90°-120°	353.6	13.3
90°-150°	735.0	27.6
90°-180°	868.0	32.6
0°-180°	2666.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1306	1306	1306	1306	1306	
5°	1286	1308	1305	1308	1330	123
15°	1289	1316	1292	1283	1300	362
25°	1171	1191	1166	1138	1152	535
35°	894	896	895	877	870	548
45°	360	428	438	9	6	283
55°	32	43	7	5	4	36
65°	1	4	3	3	3	1
75°	0	2	2	2	2	0
85°	0	1	1	1	1	0
90°	0	1	2	3	3	0
95°	8	15	8	9	11	9
105°	32	48	184	235	156	33
115°	56	68	158	330	385	55
125°	80	91	149	261	309	71
135°	100	110	150	215	247	77
145°	118	128	151	187	207	74
155°	138	143	154	170	178	63
165°	154	155	158	163	166	43
175°	162	163	162	160	160	15
180°	162	162	162	162	162	

TEST NUMBER: P621913

CATALOG NUMBER: VLT-BB-M-025U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1306.0	1306.0	1306.0	1306.0	1306.0
2.5°	1292.0	1310.3	1304.4	1303.1	1314.6
5°	1285.5	1308.4	1305.0	1308.4	1330.3
7.5°	1286.1	1307.3	1308.5	1308.4	1330.3
10°	1288.5	1310.4	1307.0	1304.5	1326.4
12.5°	1291.6	1314.2	1301.5	1297.5	1318.7
15°	1289.4	1316.1	1292.4	1283.0	1300.1
17.5°	1269.8	1300.6	1269.4	1251.4	1263.9
20°	1249.5	1281.9	1247.6	1222.5	1235.9
22.5°	1220.7	1250.8	1218.0	1189.1	1204.7
25°	1170.6	1190.6	1165.8	1137.8	1152.1
27.5°	1102.4	1113.9	1099.7	1074.6	1083.4
30°	1051.8	1059.4	1049.9	1024.7	1030.4
32.5°	995.7	999.5	993.8	970.8	973.5
35°	894.0	895.9	895.0	877.3	869.7
37.5°	768.4	772.2	770.0	693.0	478.2
40°	678.8	682.6	678.8	405.9	310.7
42.5°	566.6	591.0	584.5	276.8	88.6
45°	360.3	428.0	438.3	8.7	5.8
47.5°	178.0	251.0	206.1	5.6	5.6
50°	103.2	148.0	95.4	4.9	4.9
52.5°	69.0	90.1	27.7	4.9	4.9
55°	32.1	42.6	6.8	4.8	3.9
57.5°	11.3	21.4	4.7	3.9	3.9
60°	1.9	10.5	3.9	3.9	3.9
62.5°	1.2	5.9	3.9	3.1	3.9
65°	1.0	3.8	2.9	2.9	2.9
67.5°	1.0	2.9	2.9	2.9	2.9
70°	1.0	2.9	2.9	2.9	2.9
72.5°	0.2	2.1	2.1	2.2	2.9
75°	0.0	1.9	1.9	1.9	1.9
77.5°	0.0	1.9	1.9	1.9	1.9
80°	0.0	1.9	1.9	1.9	1.9
82.5°	0.0	1.1	1.2	1.2	1.9
85°	0.0	1.0	1.0	1.0	1.0
87.5°	0.0	1.0	1.2	1.4	1.4
90°	0.0	1.0	2.0	3.0	3.0
92.5°	2.4	3.4	4.5	6.3	7.1
95°	8.1	15.1	8.1	9.2	11.2
97.5°	14.4	28.9	59.8	17.6	15.2
100°	19.3	36.2	119.9	35.3	23.4
102.5°	24.2	41.9	162.2	93.1	51.0
105°	31.5	48.4	183.9	235.0	155.5
107.5°	38.8	51.5	175.6	342.0	320.3
110°	43.7	55.6	170.7	359.3	386.2



TEST NUMBER: P621913

CATALOG NUMBER: VLT-BB-M-025U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	48.6	60.5	165.8	349.2	394.3
115°	55.9	67.8	158.5	329.5	385.2
117.5°	63.4	75.1	156.7	308.2	365.4
120°	69.1	80.0	153.5	292.0	351.6
122.5°	73.2	84.9	149.4	278.1	332.9
125°	80.3	91.2	149.4	261.2	308.9
127.5°	86.2	97.3	149.6	241.7	288.8
130°	89.4	101.4	150.4	228.7	273.4
132.5°	93.5	105.4	150.4	222.8	259.5
135°	99.6	110.5	150.4	215.1	246.9
137.5°	104.7	116.4	150.4	206.7	233.9
140°	108.7	119.7	150.4	201.8	226.6
142.5°	112.8	122.9	151.2	196.1	219.3
145°	117.9	127.8	151.4	187.4	207.3
147.5°	124.0	132.7	152.6	181.2	196.5
150°	128.0	136.0	153.5	177.1	190.0
152.5°	132.1	139.3	153.5	173.8	184.3
155°	138.2	143.2	154.5	169.9	177.8
157.5°	143.1	147.9	155.7	167.4	173.2
160°	146.3	150.3	156.5	165.8	170.7
162.5°	148.8	152.8	157.3	164.9	168.3
165°	153.5	155.4	158.5	162.7	165.6
167.5°	156.1	157.9	159.5	161.6	163.4
170°	158.5	159.5	159.5	161.6	162.6
172.5°	159.3	161.1	160.4	160.8	161.8
175°	161.6	162.6	161.6	160.5	159.5
177.5°	161.6	162.4	161.6	161.6	160.8
180°	161.6	161.6	161.6	161.6	161.6



TEST NUMBER: P621913

CATALOG NUMBER: VLT-BB-M-025U-050D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00