

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P622057

Luminaire Tested: VLT-WB-M-125U-050D-930-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P622057
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-32)
Test Lab: INNOVATION CENTER
Issue Date: 10/28/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-WB-M-125U-050D-930-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
WHITE BAFFLE WITH MEDIUM OPTIC
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6262.8 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.16 / 1.14
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 62
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P622057
CATALOG NUMBER: VLT-WB-M-125U-050D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P622057

CATALOG NUMBER: VLT-WB-M-125U-050D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	95	91	88	85	85	82	79	77	65	64	62	50	49	48	36	35	35	29
2	87	81	76	71	79	73	69	65	59	56	54	46	44	42	33	32	32	26
3	81	72	66	61	73	66	61	56	53	50	47	42	39	37	31	30	29	24
4	74	65	58	53	67	59	53	49	48	44	41	38	35	33	29	27	26	22
5	69	59	52	46	62	54	47	43	44	40	36	35	32	30	26	25	23	20
6	64	53	46	41	58	49	42	38	40	36	32	32	29	27	25	23	21	18
7	59	48	41	36	54	44	38	34	37	32	29	30	27	24	23	21	20	17
8	55	44	37	32	50	41	35	30	34	29	26	27	24	22	21	19	18	16
9	51	40	34	29	47	37	31	27	31	27	24	25	22	20	20	18	17	14
10	48	37	31	26	44	34	29	25	29	25	22	24	21	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10010	10010	10010
5°	9907	10049	10241
10°	10007	10144	10295
15°	10159	10210	10261
20°	10110	10095	9959
25°	9834	9717	9600
30°	9252	9162	8966
35°	8381	8259	8060
40°	6816	6770	3200
45°	4218	4809	220
50°	1609	1289	132
55°	791	235	49
60°	383	113	14
65°	351	17	17
70°	332	21	21
75°	327	28	28
80°	326	41	0
85°	321	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 4809 cd/sqm



TEST NUMBER: P622057

CATALOG NUMBER: VLT-WB-M-125U-050D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.2	2.1
10°-20°	386.5	6.2
20°-30°	561.9	9.0
30°-40°	559.2	8.9
40°-50°	245.9	3.9
50°-60°	36.3	0.6
60°-70°	8.3	0.1
70°-80°	3.1	0.0
80°-90°	2.5	0.0
90°-100°	99.0	1.6
100°-110°	705.5	11.3
110°-120°	957.8	15.3
120°-130°	779.6	12.4
130°-140°	627.0	10.0
140°-150°	494.3	7.9
150°-160°	361.4	5.8
160°-170°	224.5	3.6
170°-180°	76.6	1.2
0°-30°	1081.6	17.3
0°-40°	1640.8	26.2
0°-60°	1923.0	30.7
0°-90°	1936.9	30.9
90°-120°	1762.4	28.1
90°-150°	3663.3	58.5
90°-180°	4326.0	69.1
0°-180°	6262.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1395	1395	1395	1395	1395	
5°	1375	1399	1395	1398	1422	131
15°	1367	1396	1374	1361	1381	384
25°	1242	1265	1227	1195	1212	568
35°	957	954	943	923	920	586
45°	416	473	474	31	22	322
55°	63	68	19	7	4	64
65°	21	18	1	1	1	21
75°	12	2	1	1	1	12
85°	4	0	0	0	0	4
90°	0	5	10	15	15	2
95°	40	75	40	46	56	45
105°	157	241	917	1171	775	166
115°	279	338	790	1642	1920	277
125°	400	455	744	1302	1540	356
135°	496	551	750	1072	1231	382
145°	588	637	755	934	1033	369
155°	689	714	770	847	886	316
165°	765	775	790	811	826	215
175°	805	810	805	800	795	76
180°	805	805	805	805	805	



TEST NUMBER: P622057

CATALOG NUMBER: VLT-WB-M-125U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1395.0	1395.0	1395.0	1395.0	1395.0
2.5°	1379.2	1400.1	1392.6	1392.1	1404.5
5°	1375.3	1399.4	1395.0	1398.5	1421.7
7.5°	1372.5	1396.8	1396.8	1395.2	1418.3
10°	1373.3	1398.4	1392.1	1389.6	1412.8
12.5°	1373.3	1399.9	1386.5	1380.2	1404.1
15°	1367.4	1396.3	1374.3	1360.9	1381.2
17.5°	1346.0	1377.5	1347.2	1321.2	1338.2
20°	1323.9	1357.7	1322.0	1288.7	1304.2
22.5°	1296.3	1326.2	1287.2	1252.4	1268.6
25°	1242.0	1265.2	1227.2	1195.0	1212.4
27.5°	1173.5	1186.2	1157.9	1126.9	1138.1
30°	1116.6	1126.3	1105.7	1076.3	1082.1
32.5°	1055.8	1062.4	1045.7	1020.2	1025.2
35°	956.7	953.8	942.8	923.0	920.1
37.5°	827.1	822.1	815.1	738.5	529.6
40°	727.6	729.6	722.7	451.6	341.6
42.5°	622.6	634.5	624.7	307.5	111.8
45°	415.6	472.6	473.9	31.4	21.7
47.5°	224.7	286.7	233.2	19.5	15.8
50°	144.1	179.9	115.5	14.7	11.8
52.5°	103.1	120.3	45.2	11.6	8.7
55°	63.2	68.0	18.8	6.8	3.9
57.5°	37.7	44.9	11.8	2.5	1.0
60°	26.7	31.5	7.9	1.0	1.0
62.5°	23.5	23.7	5.5	1.0	1.0
65°	20.7	17.8	1.0	1.0	1.0
67.5°	18.2	13.0	1.0	1.0	1.0
70°	15.8	9.0	1.0	1.0	1.0
72.5°	14.2	5.9	1.0	1.0	1.0
75°	11.8	2.2	1.0	1.0	1.0
77.5°	9.5	1.2	1.0	0.8	0.8
80°	7.9	1.1	1.0	0.0	0.0
82.5°	6.3	1.1	0.2	0.0	0.0
85°	3.9	0.1	0.0	0.0	0.0
87.5°	1.6	1.0	2.0	3.0	3.0
90°	0.0	5.0	10.1	15.2	15.2
92.5°	12.2	17.1	22.3	31.5	35.5
95°	40.5	75.2	40.5	45.8	55.7
97.5°	71.9	144.2	297.8	87.9	76.0
100°	96.2	180.4	597.6	175.9	116.5
102.5°	120.5	208.7	808.3	464.2	254.2
105°	157.0	241.2	916.7	1171.1	774.9
107.5°	193.5	256.9	875.2	1704.4	1596.4
110°	217.8	277.2	850.9	1790.9	1924.6



TEST NUMBER: P622057

CATALOG NUMBER: VLT-WB-M-125U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	242.1	301.5	826.6	1740.3	1965.1
115°	278.6	338.0	790.1	1642.2	1919.5
117.5°	316.0	374.5	781.0	1536.0	1821.3
120°	344.4	398.9	764.8	1455.3	1752.4
122.5°	364.7	423.1	744.5	1385.8	1659.2
125°	400.1	454.6	744.5	1302.0	1539.7
127.5°	429.5	485.0	745.5	1204.7	1439.4
130°	445.7	505.1	749.6	1139.6	1362.4
132.5°	466.0	525.4	749.6	1110.3	1293.5
135°	496.3	550.8	749.6	1072.3	1230.7
137.5°	521.7	580.1	749.6	1030.2	1165.9
140°	541.9	596.4	749.6	1005.6	1129.4
142.5°	562.2	612.7	753.6	977.1	1093.0
145°	587.5	637.0	754.6	934.2	1033.2
147.5°	617.9	661.5	760.7	903.3	979.5
150°	638.2	677.8	764.8	882.7	947.1
152.5°	658.4	694.1	764.8	866.2	918.7
155°	688.8	713.6	769.8	846.7	886.3
157.5°	713.1	736.9	775.9	834.3	863.0
160°	729.3	749.1	780.0	826.1	850.9
162.5°	741.5	761.3	784.0	821.9	838.7
165°	764.8	774.7	790.1	810.7	825.6
167.5°	777.9	786.9	795.2	805.5	814.4
170°	790.1	795.1	795.2	805.4	810.4
172.5°	794.2	803.1	799.2	801.4	806.3
175°	805.3	810.2	805.3	800.1	795.2
177.5°	805.3	809.3	805.3	805.2	801.2
180°	805.3	805.3	805.3	805.3	805.3



TEST NUMBER: P622057

CATALOG NUMBER: VLT-WB-M-125U-050D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	1.04	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	1.43	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	1.56	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.14	1.71	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.21	1.77	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.25	1.82	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.66	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	1.08	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	1.22	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	1.40	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	1.51	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	1.59	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.99	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	1.20	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	1.31	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	1.44	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.90	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	1.11	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	1.24	0.00	0.00	0.00	0.00	0.00