

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621659

Luminaire Tested: VLT-FA-0U-075D-935-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P621659
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-21)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-FA-0U-075D-935-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
LIGHT SHAPING LENS - ASYMMETRIC
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2100.3 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.19 / 1.3
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 21.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P621659
CATALOG NUMBER: VLT-FA-0U-075D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P621659

CATALOG NUMBER: VLT-FA-OU-075D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90					88				
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78					76				
3	94	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	68					66				
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60					58				
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	54					52				
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48					46				
7	70	58	50	44	68	57	49	44	56	49	44	54	48	43	53	47	43					41				
8	66	53	45	40	64	52	45	40	51	44	40	50	44	39	49	43	39					37				
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36					34				
10	58	45	38	33	57	45	38	33	44	37	33	43	37	33	42	37	33					31				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7309	7309	7309	7309
5°	7322	9196	7210	6270
10°	7225	8600	7120	5444
15°	7028	8468	7051	4996
20°	6813	8205	6892	5856
25°	6604	8295	6678	6284
30°	6370	7590	6457	5933
35°	5837	7034	5692	5319
40°	4756	6260	4591	4329
45°	4322	2324	4364	3944
50°	4395	1769	4315	3748
55°	4149	1374	4006	2243
60°	3822	1056	3792	1249
65°	3518	1090	3449	1319
70°	3130	1152	3044	1370
75°	2673	1206	2556	1408
80°	2013	1240	1884	1455
85°	1367	1112	1194	1367

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 8003 cd/sqm



TEST NUMBER: P621659
 CATALOG NUMBER: VLT-FA-OU-075D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.3	4.7
10°-20°	269.2	12.8
20°-30°	402.7	19.2
30°-40°	458.0	21.8
40°-50°	391.7	18.7
50°-60°	264.2	12.6
60°-70°	136.3	6.5
70°-80°	61.6	2.9
80°-90°	18.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	770.2	36.7
0°-40°	1228.2	58.5
0°-60°	1884.1	89.7
0°-90°	2100.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2100.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1019	1019	1019	1019	1019	
5°	1016	1277	1001	870	1016	96
15°	946	1140	949	672	946	266
25°	834	1048	843	794	834	384
35°	666	803	650	607	666	407
45°	426	229	430	389	426	338
55°	332	110	320	179	332	295
65°	207	64	203	78	207	205
75°	96	44	92	51	96	103
85°	17	14	14	17	17	22
90°	0	0	0	0	0	



TEST NUMBER: P621659

CATALOG NUMBER: VLT-FA-OU-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	1018.6	1018.6	1018.6	1018.6	1018.6	1018.6	1018.6	1018.6	1018.6	1018.6	1018.6
2.5°	1021.9	1056.7	1100.6	1130.8	1143.7	1130.8	1093.2	1056.5	1010.3	996.5	963.9
5°	1016.5	1123.9	1253.8	1269.5	1276.6	1269.5	1242.4	1117.5	1000.9	951.3	897.3
7.5°	1004.1	1191.9	1252.3	1217.3	1217.5	1224.0	1254.2	1186.1	987.9	909.9	843.7
10°	991.6	1229.7	1221.7	1171.1	1180.2	1176.2	1231.0	1222.3	977.1	886.9	811.3
12.5°	975.0	1241.5	1181.0	1164.5	1174.4	1168.7	1187.0	1235.1	968.0	870.5	774.0
15°	946.0	1224.6	1147.0	1139.8	1139.8	1144.9	1152.2	1229.8	949.1	840.7	728.4
17.5°	916.2	1191.0	1123.4	1087.5	1083.6	1090.3	1131.9	1199.6	922.4	807.7	684.3
20°	892.1	1167.7	1099.4	1057.3	1074.5	1059.3	1108.7	1174.0	902.5	787.0	656.9
22.5°	870.6	1138.9	1068.7	1050.8	1073.7	1051.2	1077.2	1145.1	879.3	763.8	636.2
25°	834.1	1090.4	1022.7	1039.5	1047.6	1039.5	1026.8	1094.7	843.4	734.0	614.5
27.5°	797.9	1039.4	988.3	999.6	974.8	993.9	993.9	1039.6	806.6	699.4	607.8
30°	768.8	1003.9	970.9	954.5	916.0	946.4	978.1	1004.1	779.2	676.9	606.2
32.5°	730.7	971.4	953.5	896.8	872.0	892.7	961.6	970.8	736.9	656.5	604.5
35°	666.3	925.6	922.2	828.4	803.0	822.3	929.4	923.2	649.7	624.4	591.7
37.5°	579.8	884.8	862.3	759.2	718.9	754.2	869.1	880.4	546.5	594.9	561.6
40°	507.7	857.3	817.5	707.8	668.3	702.8	822.7	854.8	490.1	574.2	528.4
42.5°	467.1	832.9	770.3	653.4	408.9	645.1	775.5	829.8	455.3	547.5	499.4
45°	425.9	788.6	701.5	361.7	229.0	344.5	702.5	777.5	430.0	507.0	454.9
47.5°	407.8	734.1	629.6	217.9	193.4	211.6	629.0	722.1	408.0	466.4	412.4
50°	393.7	699.7	578.2	192.0	158.5	184.9	579.2	688.4	386.5	439.2	383.4
52.5°	370.5	658.7	504.4	159.1	137.0	155.2	492.2	645.8	364.1	409.5	346.9
55°	331.6	579.8	210.3	125.0	109.8	120.0	200.0	560.3	320.2	362.7	304.6
57.5°	290.3	493.6	147.6	97.3	85.2	96.3	146.5	473.8	284.9	307.2	265.7
60°	266.3	435.5	120.2	81.7	73.6	80.7	119.2	418.2	264.2	270.3	230.0
62.5°	242.3	376.6	99.5	71.9	69.4	70.8	99.3	357.7	238.5	238.9	162.1
65°	207.2	285.2	73.6	65.3	64.2	64.2	71.5	275.0	203.1	197.0	93.3
67.5°	171.6	204.8	59.1	60.1	59.1	59.1	58.0	199.1	167.4	157.1	70.5
70°	149.2	157.3	54.9	55.9	54.9	54.9	53.9	153.2	145.1	121.8	66.3
72.5°	127.7	107.4	50.8	51.0	50.8	50.8	49.7	100.8	123.5	85.6	60.5
75°	96.4	53.8	43.5	43.5	43.5	43.5	42.5	51.7	92.2	55.7	51.8
77.5°	66.9	35.5	36.1	35.9	35.9	35.0	35.0	35.2	63.0	38.5	41.9
80°	48.7	29.5	31.1	30.0	30.0	30.0	30.0	28.4	45.6	32.4	35.2
82.5°	34.6	23.5	25.3	24.2	24.2	24.2	24.2	23.2	31.5	26.4	28.6
85°	16.6	15.6	16.6	14.5	13.5	14.5	15.5	15.5	14.5	17.5	18.7
87.5°	5.0	7.4	6.6	5.0	5.0	5.0	5.8	6.6	4.1	8.2	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P621659

CATALOG NUMBER: VLT-FA-OU-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	1018.6	1018.6	1018.6	1018.6	1018.6	1018.6
2.5°	952.2	951.4	953.0	967.2	995.9	1021.9
5°	867.3	870.4	873.4	897.3	947.6	1016.5
7.5°	802.1	797.6	804.5	843.4	905.2	1004.1
10°	757.2	747.1	757.2	810.3	882.2	991.6
12.5°	714.9	702.3	718.1	776.3	863.2	975.0
15°	660.3	672.5	665.4	730.5	834.6	946.0
17.5°	673.2	734.4	686.2	690.7	806.2	916.2
20°	704.0	766.8	724.2	664.2	787.8	892.1
22.5°	731.8	779.2	740.7	641.8	769.5	870.6
25°	753.2	793.7	751.2	621.7	742.9	834.1
27.5°	754.3	759.9	754.7	620.0	710.1	797.9
30°	740.3	716.0	738.3	621.7	686.8	768.8
32.5°	700.4	672.9	691.9	618.4	663.2	730.7
35°	643.7	607.2	633.5	601.0	626.7	666.3
37.5°	583.8	537.6	574.0	566.6	595.6	579.8
40°	543.2	462.1	535.1	532.6	578.6	507.7
42.5°	491.2	422.3	483.9	505.2	559.9	467.1
45°	396.7	388.6	392.6	459.0	520.1	425.9
47.5°	362.7	357.3	360.7	417.0	475.1	407.8
50°	342.8	335.7	340.8	389.6	446.4	393.7
52.5°	315.2	295.9	313.2	352.3	416.7	370.5
55°	237.0	179.3	236.0	309.8	372.1	331.6
57.5°	139.1	103.6	136.0	269.6	315.3	290.3
60°	94.1	87.0	95.1	237.3	277.4	266.3
62.5°	86.0	83.7	86.2	165.2	243.7	242.3
65°	78.7	77.7	78.7	95.3	201.2	207.2
67.5°	71.3	70.3	72.1	73.2	158.8	171.6
70°	66.3	65.3	66.3	67.4	121.9	149.2
72.5°	60.5	59.5	60.5	61.5	85.7	127.7
75°	51.8	50.8	51.8	52.8	56.9	96.4
77.5°	41.9	41.9	42.9	42.9	39.8	66.9
80°	35.2	35.2	36.2	36.3	34.5	48.7
82.5°	28.6	27.8	29.6	30.5	28.5	34.6
85°	17.6	16.6	18.6	19.7	18.6	16.6
87.5°	6.6	5.8	7.4	9.1	9.0	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)