

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621917

Luminaire Tested: VLT-BB-M-025U-075D-935-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P621917
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-26)
Test Lab: INNOVATION CENTER
Issue Date: 10/28/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-BB-M-025U-075D-935-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
BLACK BAFFLE WITH MEDIUM OPTIC
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3587.2 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.14
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 37.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P621917
CATALOG NUMBER: VLT-BB-M-025U-075D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P621917

CATALOG NUMBER: VLT-BB-M-025U-075D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	113	113	113	113	108	108	108	108	97	97	97		88	88	88		80	80	80	75
1	107	103	100	98	102	99	96	94	90	88	87		82	81	80		75	74	73	70
2	100	94	90	86	95	90	86	83	83	80	77		77	74	72		70	69	67	64
3	94	86	80	76	89	83	78	74	77	73	69		71	68	65		66	63	61	59
4	88	79	73	68	84	76	70	66	71	66	63		66	62	59		61	58	56	54
5	82	73	66	61	79	70	64	60	65	61	57		61	57	54		57	54	51	49
6	77	67	60	55	74	65	59	54	61	56	52		57	53	50		53	50	47	45
7	72	62	55	50	69	60	54	49	56	51	47		53	49	45		50	46	44	42
8	68	57	51	46	65	56	49	45	52	47	43		49	45	42		47	43	40	38
9	64	53	47	42	61	52	46	41	49	44	40		46	42	39		44	40	37	36
10	60	50	43	39	58	48	42	38	46	41	37		43	39	36		41	37	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14111	14111	14111
5°	13944	14155	14430
10°	14137	14340	14554
15°	14424	14457	14544
20°	14368	14345	14211
25°	13957	13899	13736
30°	13123	13099	12856
35°	11793	11806	11472
40°	9575	9575	4382
45°	5506	6697	89
50°	1735	1604	81
55°	606	129	74
60°	42	85	85
65°	25	75	75
70°	31	92	92
75°	0	80	80
80°	0	120	120
85°	0	124	124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 6697 cd/sqm



TEST NUMBER: P621917

CATALOG NUMBER: VLT-BB-M-025U-075D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.9	5.2
10°-20°	548.3	15.3
20°-30°	801.0	22.3
30°-40°	793.3	22.1
40°-50°	332.1	9.3
50°-60°	35.5	1.0
60°-70°	5.0	0.1
70°-80°	3.0	0.1
80°-90°	1.8	0.1
90°-100°	20.1	0.6
100°-110°	143.4	4.0
110°-120°	194.7	5.4
120°-130°	158.4	4.4
130°-140°	127.4	3.6
140°-150°	100.5	2.8
150°-160°	73.5	2.0
160°-170°	45.6	1.3
170°-180°	15.6	0.4
0°-30°	1537.3	42.9
0°-40°	2330.6	65.0
0°-60°	2698.3	75.2
0°-90°	2708.1	75.5
90°-120°	358.2	10.0
90°-150°	744.5	20.8
90°-180°	879.0	24.5
0°-180°	3587.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1936	1970	1965	1970	2003	185
15°	1942	1982	1946	1932	1958	545
25°	1763	1793	1755	1713	1735	805
35°	1346	1349	1348	1321	1310	826
45°	543	644	660	13	9	426
55°	48	64	10	7	6	54
65°	2	6	4	4	4	2
75°	0	3	3	3	3	0
85°	0	1	2	2	2	0
90°	0	1	2	3	3	0
95°	8	15	8	9	11	9
105°	32	49	186	238	158	34
115°	57	69	161	334	390	56
125°	81	92	151	265	313	72
135°	101	112	152	218	250	78
145°	119	130	153	190	210	75
155°	140	145	156	172	180	64
165°	155	157	161	165	168	44
175°	164	165	164	163	162	15
180°	164	164	164	164	164	



TEST NUMBER: P621917

CATALOG NUMBER: VLT-BB-M-025U-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1966.5	1966.5	1966.5	1966.5	1966.5
2.5°	1945.4	1972.9	1964.2	1962.2	1979.4
5°	1935.7	1970.1	1965.1	1970.2	2003.2
7.5°	1936.6	1968.4	1970.3	1970.2	2003.2
10°	1940.1	1973.1	1968.0	1964.3	1997.3
12.5°	1944.8	1978.9	1959.8	1953.8	1985.6
15°	1941.6	1981.7	1946.0	1931.9	1957.7
17.5°	1912.0	1958.4	1911.4	1884.2	1903.2
20°	1881.5	1930.2	1878.5	1840.9	1860.9
22.5°	1838.1	1883.4	1834.0	1790.5	1814.0
25°	1762.7	1792.8	1755.4	1713.3	1734.8
27.5°	1660.0	1677.2	1655.9	1618.1	1631.3
30°	1583.8	1595.3	1580.8	1542.9	1551.5
32.5°	1499.3	1505.0	1496.4	1461.9	1465.9
35°	1346.2	1349.1	1347.7	1321.0	1309.6
37.5°	1157.0	1162.8	1159.4	1043.5	720.0
40°	1022.1	1027.9	1022.1	611.2	467.8
42.5°	853.2	889.9	880.2	416.8	133.4
45°	542.6	644.4	659.9	13.1	8.8
47.5°	268.1	377.9	310.3	8.5	8.5
50°	155.4	222.8	143.7	7.3	7.3
52.5°	103.8	135.7	41.6	7.3	7.3
55°	48.4	64.2	10.3	7.3	5.9
57.5°	17.0	32.2	7.0	5.9	5.9
60°	2.9	15.8	5.9	5.9	5.9
62.5°	1.8	8.9	5.9	4.7	5.9
65°	1.5	5.8	4.4	4.4	4.4
67.5°	1.5	4.3	4.4	4.4	4.4
70°	1.5	4.3	4.4	4.4	4.4
72.5°	0.3	3.2	3.2	3.3	4.4
75°	0.0	2.9	2.9	2.9	2.9
77.5°	0.0	2.9	2.9	2.9	2.9
80°	0.0	2.9	2.9	2.9	2.9
82.5°	0.0	1.7	1.8	1.8	2.9
85°	0.0	1.4	1.5	1.5	1.5
87.5°	0.0	1.3	1.6	1.8	1.8
90°	0.0	1.0	2.1	3.1	3.1
92.5°	2.5	3.5	4.5	6.4	7.2
95°	8.2	15.3	8.2	9.3	11.3
97.5°	14.6	29.3	60.5	17.9	15.4
100°	19.6	36.7	121.5	35.8	23.7
102.5°	24.5	42.4	164.3	94.3	51.7
105°	31.9	49.0	186.3	238.0	157.5
107.5°	39.3	52.2	177.9	346.4	324.4
110°	44.3	56.3	172.9	364.0	391.1



TEST NUMBER: P621917

CATALOG NUMBER: VLT-BB-M-025U-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	49.2	61.3	168.0	353.7	399.4
115°	56.6	68.7	160.6	333.8	390.1
117.5°	64.2	76.1	158.7	312.2	370.1
120°	70.0	81.1	155.4	295.8	356.1
122.5°	74.1	86.0	151.3	281.7	337.2
125°	81.3	92.4	151.3	264.6	312.9
127.5°	87.3	98.6	151.5	244.8	292.5
130°	90.6	102.7	152.3	231.6	276.9
132.5°	94.7	106.8	152.3	225.7	262.9
135°	100.9	111.9	152.3	217.9	250.1
137.5°	106.0	117.9	152.3	209.4	237.0
140°	110.1	121.2	152.3	204.4	229.5
142.5°	114.3	124.5	153.2	198.6	222.1
145°	119.4	129.5	153.4	189.9	210.0
147.5°	125.6	134.4	154.6	183.6	199.1
150°	129.7	137.7	155.4	179.4	192.5
152.5°	133.8	141.1	155.4	176.1	186.7
155°	140.0	145.0	156.5	172.1	180.1
157.5°	144.9	149.8	157.7	169.6	175.4
160°	148.2	152.3	158.5	167.9	172.9
162.5°	150.7	154.7	159.3	167.0	170.5
165°	155.4	157.4	160.6	164.8	167.8
167.5°	158.1	159.9	161.6	163.7	165.5
170°	160.6	161.6	161.6	163.7	164.7
172.5°	161.4	163.2	162.4	162.9	163.9
175°	163.7	164.7	163.7	162.6	161.6
177.5°	163.7	164.5	163.7	163.6	162.8
180°	163.7	163.7	163.7	163.7	163.7



TEST NUMBER: P621917

CATALOG NUMBER: VLT-BB-M-025U-075D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.39	1.26	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.17	1.08	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.04	0.96	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.82	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.75	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.68	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.92	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.77	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.67	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.58	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.50	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.43	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.51	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.51	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.49	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.48	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.44	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.47	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.52	0.00	0.00	0.00	0.00	0.00