

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P622041

Luminaire Tested: VLT-WB-M-0U-100D-940-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P622041
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-32)
Test Lab: INNOVATION CENTER
Issue Date: 10/28/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-WB-M-0U-100D-940-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
WHITE BAFFLE WITH MEDIUM OPTIC
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3990.8 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.16 / 1.14
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P622041
CATALOG NUMBER: VLT-WB-M-0U-100D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P622041

CATALOG NUMBER: VLT-WB-M-OU-100D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92	
2	107	101	97	93	104	100	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84	
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77	
4	95	86	80	75	93	85	79	75	83	78	74	81	77	73	79	75	72	71	71	71	71	
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65	65	65	65	
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59	59	59	59	
7	79	69	62	57	77	68	62	57	67	61	57	65	60	56	64	60	56	55	55	55	55	
8	74	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50	50	50	50	
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47	47	47	47	
10	67	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43	43	43	43	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20645	20645	20645
5°	20431	20724	21120
10°	20637	20919	21231
15°	20950	21056	21162
20°	20851	20819	20540
25°	20281	20039	19797
30°	19081	18896	18491
35°	17284	17034	16623
40°	14057	13961	6599
45°	8699	9918	455
50°	3319	2659	272
55°	1630	484	101
60°	789	234	29
65°	727	34	34
70°	684	42	42
75°	677	55	55
80°	674	83	0
85°	667	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 9918 cd/sqm



TEST NUMBER: P622041

CATALOG NUMBER: VLT-WB-M-0U-100D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.7	6.9
10°-20°	797.0	20.0
20°-30°	1158.9	29.0
30°-40°	1153.3	28.9
40°-50°	507.1	12.7
50°-60°	74.9	1.9
60°-70°	17.1	0.4
70°-80°	6.3	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2230.7	55.9
0°-40°	3383.9	84.8
0°-60°	3965.9	99.4
0°-90°	3990.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3990.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2877	2877	2877	2877	2877	
5°	2836	2886	2877	2884	2932	271
15°	2820	2880	2834	2807	2848	793
25°	2561	2609	2531	2464	2500	1171
35°	1973	1967	1944	1904	1898	1208
45°	857	975	977	65	45	664
55°	130	140	39	14	8	132
65°	43	37	2	2	2	43
75°	24	4	2	2	2	26
85°	8	0	0	0	0	9
90°	0	0	0	0	0	



TEST NUMBER: P622041

CATALOG NUMBER: VLT-WB-M-OU-100D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2877.0	2877.0	2877.0	2877.0	2877.0
2.5°	2844.4	2887.4	2872.1	2871.1	2896.6
5°	2836.3	2886.1	2877.0	2884.2	2932.0
7.5°	2830.6	2880.8	2880.7	2877.3	2925.1
10°	2832.2	2884.0	2870.9	2865.9	2913.7
12.5°	2832.2	2887.2	2859.5	2846.4	2895.7
15°	2820.0	2879.7	2834.3	2806.7	2848.5
17.5°	2776.0	2840.9	2778.5	2724.7	2759.7
20°	2730.4	2800.1	2726.3	2657.8	2689.7
22.5°	2673.4	2735.1	2654.7	2582.9	2616.4
25°	2561.4	2609.2	2530.9	2464.5	2500.3
27.5°	2420.1	2446.4	2387.9	2324.1	2347.2
30°	2302.8	2322.7	2280.4	2219.6	2231.6
32.5°	2177.4	2190.9	2156.6	2103.9	2114.3
35°	1973.0	1967.0	1944.5	1903.6	1897.6
37.5°	1705.8	1695.5	1681.0	1523.0	1092.2
40°	1500.6	1504.6	1490.4	931.4	704.5
42.5°	1284.0	1308.7	1288.4	634.2	230.5
45°	857.2	974.7	977.3	64.7	44.8
47.5°	463.4	591.2	480.9	40.1	32.6
50°	297.3	370.9	238.2	30.4	24.4
52.5°	212.6	248.0	93.3	23.9	17.9
55°	130.3	140.3	38.7	14.1	8.1
57.5°	77.8	92.5	24.4	5.2	2.0
60°	55.0	64.9	16.3	2.0	2.0
62.5°	48.5	48.9	11.4	2.0	2.0
65°	42.8	36.8	2.0	2.0	2.0
67.5°	37.5	26.7	2.0	2.0	2.0
70°	32.6	18.6	2.0	2.0	2.0
72.5°	29.3	12.2	2.0	2.0	2.0
75°	24.4	4.5	2.0	2.0	2.0
77.5°	19.5	2.4	2.0	1.6	1.6
80°	16.3	2.4	2.0	0.0	0.0
82.5°	13.0	2.3	0.4	0.0	0.0
85°	8.1	0.2	0.0	0.0	0.0
87.5°	3.3	0.1	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P622041

CATALOG NUMBER: VLT-WB-M-OU-100D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.76	7.85	7.13	8.16	8.47	0.00	0.00	0.00	0.00	0.00
	3H	7.22	8.17	7.60	8.50	8.87	0.00	0.00	0.00	0.00	0.00
	4H	7.39	8.27	7.80	8.62	9.01	0.00	0.00	0.00	0.00	0.00
	6H	7.58	8.39	8.00	8.76	9.16	0.00	0.00	0.00	0.00	0.00
	8H	7.68	8.43	8.11	8.82	9.23	0.00	0.00	0.00	0.00	0.00
	12H	7.75	8.47	8.18	8.85	9.28	0.00	0.00	0.00	0.00	0.00
4H	2H	6.49	7.37	6.90	7.72	8.11	0.00	0.00	0.00	0.00	0.00
	3H	6.98	7.69	7.40	8.10	8.50	0.00	0.00	0.00	0.00	0.00
	4H	7.16	7.79	7.59	8.21	8.66	0.00	0.00	0.00	0.00	0.00
	6H	7.40	7.93	7.86	8.38	8.86	0.00	0.00	0.00	0.00	0.00
	8H	7.51	8.01	7.99	8.46	8.94	0.00	0.00	0.00	0.00	0.00
	12H	7.63	8.06	8.12	8.55	9.03	0.00	0.00	0.00	0.00	0.00
8H	4H	6.99	7.49	7.46	7.94	8.41	0.00	0.00	0.00	0.00	0.00
	6H	7.22	7.62	7.73	8.12	8.61	0.00	0.00	0.00	0.00	0.00
	8H	7.34	7.70	7.87	8.22	8.72	0.00	0.00	0.00	0.00	0.00
	12H	7.49	7.80	8.01	8.30	8.88	0.00	0.00	0.00	0.00	0.00
12H	4H	6.93	7.36	7.42	7.85	8.33	0.00	0.00	0.00	0.00	0.00
	6H	7.14	7.51	7.68	8.03	8.52	0.00	0.00	0.00	0.00	0.00
	8H	7.29	7.60	7.81	8.10	8.68	0.00	0.00	0.00	0.00	0.00