

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P622059

Luminaire Tested: VLT-WB-M-125U-050D-940-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P622059
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-32)
Test Lab: INNOVATION CENTER
Issue Date: 10/28/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-WB-M-125U-050D-940-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
WHITE BAFFLE WITH MEDIUM OPTIC
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6522.6 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.16 / 1.14
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 62
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P622059
CATALOG NUMBER: VLT-WB-M-125U-050D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P622059

CATALOG NUMBER: VLT-WB-M-125U-050D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	95	91	88	85	85	82	79	77	65	64	62	50	49	48	36	35	35	29
2	87	81	76	71	79	73	69	65	59	56	54	46	44	42	33	32	32	26
3	81	72	66	61	73	66	61	56	53	50	47	42	39	37	31	30	29	24
4	74	65	58	53	67	59	53	49	48	44	41	38	35	33	29	27	26	22
5	69	59	52	46	62	54	47	43	44	40	36	35	32	30	26	25	23	20
6	64	53	46	41	58	49	42	38	40	36	32	32	29	27	25	23	21	18
7	59	48	41	36	54	44	38	34	37	32	29	30	27	24	23	21	20	17
8	55	44	37	32	50	41	35	30	34	29	26	27	24	22	21	19	18	16
9	51	40	34	29	47	37	31	27	31	27	24	25	22	20	20	18	17	14
10	48	37	31	26	44	34	29	25	29	25	22	24	21	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10426	10426	10426
5°	10317	10466	10666
10°	10422	10564	10722
15°	10580	10633	10687
20°	10530	10514	10373
25°	10242	10120	9998
30°	9636	9542	9338
35°	8729	8603	8395
40°	7099	7051	3333
45°	4393	5009	229
50°	1676	1343	137
55°	823	244	51
60°	399	118	14
65°	367	17	17
70°	346	21	21
75°	341	28	28
80°	339	41	0
85°	338	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 5009 cd/sqm



TEST NUMBER: P622059

CATALOG NUMBER: VLT-WB-M-125U-050D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.7	2.1
10°-20°	402.5	6.2
20°-30°	585.2	9.0
30°-40°	582.4	8.9
40°-50°	256.1	3.9
50°-60°	37.8	0.6
60°-70°	8.6	0.1
70°-80°	3.2	0.0
80°-90°	2.6	0.0
90°-100°	103.1	1.6
100°-110°	734.8	11.3
110°-120°	997.6	15.3
120°-130°	811.9	12.4
130°-140°	653.0	10.0
140°-150°	514.8	7.9
150°-160°	376.4	5.8
160°-170°	233.8	3.6
170°-180°	79.7	1.2
0°-30°	1126.5	17.3
0°-40°	1708.9	26.2
0°-60°	2002.8	30.7
0°-90°	2017.3	30.9
90°-120°	1835.5	28.1
90°-150°	3815.3	58.5
90°-180°	4505.0	69.1
0°-180°	6522.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1453	1453	1453	1453	1453	
5°	1432	1458	1453	1456	1481	137
15°	1424	1454	1431	1417	1438	400
25°	1294	1318	1278	1245	1263	591
35°	996	993	982	961	958	610
45°	433	492	494	33	23	335
55°	66	71	20	7	4	66
65°	22	19	1	1	1	22
75°	12	2	1	1	1	13
85°	4	0	0	0	0	4
90°	0	5	10	16	16	2
95°	42	78	42	48	58	47
105°	164	251	955	1220	807	172
115°	290	352	823	1710	1999	288
125°	417	473	775	1356	1604	370
135°	517	574	781	1117	1282	398
145°	612	664	786	973	1076	384
155°	717	743	802	882	923	329
165°	796	807	823	844	860	224
175°	839	844	839	833	828	79
180°	839	839	839	839	839	



TEST NUMBER: P622059

CATALOG NUMBER: VLT-WB-M-125U-050D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1452.9	1452.9	1452.9	1452.9	1452.9
2.5°	1436.4	1458.2	1450.4	1449.9	1462.8
5°	1432.3	1457.5	1452.9	1456.5	1480.7
7.5°	1429.5	1454.8	1454.8	1453.0	1477.2
10°	1430.3	1456.4	1449.8	1447.3	1471.4
12.5°	1430.3	1458.0	1444.1	1437.4	1462.4
15°	1424.1	1454.3	1431.3	1417.4	1438.5
17.5°	1401.9	1434.7	1403.1	1376.0	1393.7
20°	1378.9	1414.1	1376.8	1342.2	1358.3
22.5°	1350.1	1381.2	1340.6	1304.4	1321.3
25°	1293.5	1317.7	1278.1	1244.6	1262.7
27.5°	1222.2	1235.4	1205.9	1173.7	1185.4
30°	1162.9	1173.0	1151.6	1120.9	1126.9
32.5°	1099.6	1106.4	1089.1	1062.5	1067.7
35°	996.4	993.3	982.0	961.3	958.3
37.5°	861.5	856.2	848.9	769.1	551.5
40°	757.8	759.8	752.7	470.4	355.8
42.5°	648.4	660.9	650.7	320.3	116.4
45°	432.9	492.2	493.6	32.7	22.6
47.5°	234.0	298.6	242.9	20.3	16.5
50°	150.1	187.3	120.3	15.4	12.3
52.5°	107.3	125.2	47.1	12.1	9.0
55°	65.8	70.8	19.5	7.1	4.1
57.5°	39.3	46.7	12.3	2.6	1.0
60°	27.8	32.8	8.2	1.0	1.0
62.5°	24.5	24.7	5.8	1.0	1.0
65°	21.6	18.6	1.0	1.0	1.0
67.5°	18.9	13.5	1.0	1.0	1.0
70°	16.5	9.4	1.0	1.0	1.0
72.5°	14.8	6.2	1.0	1.0	1.0
75°	12.3	2.3	1.0	1.0	1.0
77.5°	9.9	1.2	1.0	0.8	0.8
80°	8.2	1.2	1.0	0.0	0.0
82.5°	6.6	1.2	0.2	0.0	0.0
85°	4.1	0.1	0.0	0.0	0.0
87.5°	1.6	1.1	2.1	3.2	3.2
90°	0.0	5.2	10.5	15.8	15.8
92.5°	12.7	17.8	23.2	32.8	36.9
95°	42.2	78.3	42.2	47.7	58.0
97.5°	74.9	150.2	310.2	91.5	79.1
100°	100.2	187.9	622.4	183.2	121.3
102.5°	125.5	217.3	841.9	483.5	264.8
105°	163.5	251.2	954.8	1219.7	807.1
107.5°	201.5	267.5	911.5	1775.1	1662.6
110°	226.8	288.7	886.2	1865.2	2004.5

TEST NUMBER: P622059

CATALOG NUMBER: VLT-WB-M-125U-050D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.1	314.0	860.9	1812.5	2046.7
115°	290.1	352.0	822.9	1710.4	1999.2
117.5°	329.2	390.0	813.4	1599.8	1896.8
120°	358.7	415.4	796.5	1515.6	1825.1
122.5°	379.8	440.7	775.4	1443.3	1728.1
125°	416.7	473.4	775.4	1356.0	1603.6
127.5°	447.3	505.1	776.5	1254.6	1499.1
130°	464.2	526.1	780.7	1186.8	1418.9
132.5°	485.3	547.2	780.7	1156.4	1347.2
135°	516.9	573.7	780.7	1116.8	1281.8
137.5°	543.3	604.2	780.7	1073.0	1214.3
140°	564.4	621.1	780.7	1047.4	1176.3
142.5°	585.5	638.1	784.9	1017.6	1138.3
145°	611.9	663.5	786.0	972.9	1076.1
147.5°	643.5	688.9	792.3	940.7	1020.2
150°	664.6	705.9	796.5	919.4	986.4
152.5°	685.7	722.9	796.5	902.2	956.9
155°	717.4	743.2	801.8	881.8	923.1
157.5°	742.7	767.5	808.1	868.9	898.8
160°	759.6	780.2	812.3	860.4	886.2
162.5°	772.2	792.9	816.6	856.0	873.5
165°	796.5	806.8	822.9	844.3	859.8
167.5°	810.2	819.5	828.2	838.9	848.2
170°	822.9	828.0	828.2	838.8	844.0
172.5°	827.1	836.4	832.4	834.6	839.8
175°	838.7	843.9	838.7	833.3	828.2
177.5°	838.7	842.8	838.7	838.6	834.5
180°	838.7	838.7	838.7	838.7	838.7



TEST NUMBER: P622059

CATALOG NUMBER: VLT-WB-M-125U-050D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	1.17	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.02	1.57	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.15	1.70	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.29	1.85	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.36	1.91	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.39	1.97	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.80	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	1.22	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	1.36	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	1.55	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.06	1.65	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.15	1.74	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	1.13	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	1.34	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	1.45	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	1.58	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	1.04	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	1.25	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	1.38	0.00	0.00	0.00	0.00	0.00