

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621953

Luminaire Tested: VLT-BB-M-0U-075D-935-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P621953
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26)
Test Lab: INNOVATION CENTER
Issue Date: 10/28/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-BB-M-0U-075D-935-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
BLACK BAFFLE WITH MEDIUM OPTIC
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2707.7 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.14
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P621953
CATALOG NUMBER: VLT-BB-M-0U-075D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P621953

CATALOG NUMBER: VLT-BB-M-OU-075D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91	88	86	85
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85	82	79	78
4	95	87	80	76	93	85	80	75	83	78	74		81	77	74		79	76	73	71
5	89	80	74	69	88	79	73	69	77	72	68		76	71	67		74	70	67	65
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69	65	61	60
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65	60	57	55
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61	56	52	51
9	71	60	54	49	70	60	53	49	59	53	49		58	52	49		57	52	49	47
10	67	56	50	46	66	56	50	46	55	49	45		54	49	45		53	49	45	44

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14111	14111	14111
5°	13944	14155	14430
10°	14137	14340	14554
15°	14424	14457	14544
20°	14368	14345	14211
25°	13957	13899	13736
30°	13123	13099	12856
35°	11793	11806	11472
40°	9575	9575	4382
45°	5506	6697	89
50°	1735	1604	81
55°	606	129	74
60°	42	85	85
65°	25	75	75
70°	31	92	92
75°	0	80	80
80°	0	120	120
85°	0	124	124

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 6697 cd/sqm



TEST NUMBER: P621953

CATALOG NUMBER: VLT-BB-M-OU-075D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.9	6.9
10°-20°	548.3	20.3
20°-30°	801.0	29.6
30°-40°	793.3	29.3
40°-50°	332.1	12.3
50°-60°	35.5	1.3
60°-70°	5.0	0.2
70°-80°	3.0	0.1
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1537.3	56.8
0°-40°	2330.6	86.1
0°-60°	2698.3	99.7
0°-90°	2707.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2707.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1936	1970	1965	1970	2003	185
15°	1942	1982	1946	1932	1958	545
25°	1763	1793	1755	1713	1735	805
35°	1346	1349	1348	1321	1310	826
45°	543	644	660	13	9	426
55°	48	64	10	7	6	54
65°	2	6	4	4	4	2
75°	0	3	3	3	3	0
85°	0	1	2	2	2	0
90°	0	0	0	0	0	



TEST NUMBER: P621953

CATALOG NUMBER: VLT-BB-M-OU-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1966.5	1966.5	1966.5	1966.5	1966.5
2.5°	1945.4	1972.9	1964.2	1962.2	1979.4
5°	1935.7	1970.1	1965.1	1970.2	2003.2
7.5°	1936.6	1968.4	1970.3	1970.2	2003.2
10°	1940.1	1973.1	1968.0	1964.3	1997.3
12.5°	1944.8	1978.9	1959.8	1953.8	1985.6
15°	1941.6	1981.7	1946.0	1931.9	1957.7
17.5°	1912.0	1958.4	1911.4	1884.2	1903.2
20°	1881.5	1930.2	1878.5	1840.9	1860.9
22.5°	1838.1	1883.4	1834.0	1790.5	1814.0
25°	1762.7	1792.8	1755.4	1713.3	1734.8
27.5°	1660.0	1677.2	1655.9	1618.1	1631.3
30°	1583.8	1595.3	1580.8	1542.9	1551.5
32.5°	1499.3	1505.0	1496.4	1461.9	1465.9
35°	1346.2	1349.1	1347.7	1321.0	1309.6
37.5°	1157.0	1162.8	1159.4	1043.5	720.0
40°	1022.1	1027.9	1022.1	611.2	467.8
42.5°	853.2	889.9	880.2	416.8	133.4
45°	542.6	644.4	659.9	13.1	8.8
47.5°	268.1	377.9	310.3	8.5	8.5
50°	155.4	222.8	143.7	7.3	7.3
52.5°	103.8	135.7	41.6	7.3	7.3
55°	48.4	64.2	10.3	7.3	5.9
57.5°	17.0	32.2	7.0	5.9	5.9
60°	2.9	15.8	5.9	5.9	5.9
62.5°	1.8	8.9	5.9	4.7	5.9
65°	1.5	5.8	4.4	4.4	4.4
67.5°	1.5	4.3	4.4	4.4	4.4
70°	1.5	4.3	4.4	4.4	4.4
72.5°	0.3	3.2	3.2	3.3	4.4
75°	0.0	2.9	2.9	2.9	2.9
77.5°	0.0	2.9	2.9	2.9	2.9
80°	0.0	2.9	2.9	2.9	2.9
82.5°	0.0	1.7	1.8	1.8	2.9
85°	0.0	1.4	1.5	1.5	1.5
87.5°	0.0	1.1	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P621953

CATALOG NUMBER: VLT-BB-M-0U-075D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.87	1.93	1.23	2.24	2.56	0.00	0.00	0.00	0.00	0.00
	3H	0.75	1.68	1.13	2.01	2.38	0.00	0.00	0.00	0.00	0.00
	4H	0.66	1.53	1.07	1.88	2.27	0.00	0.00	0.00	0.00	0.00
	6H	0.57	1.36	0.99	1.73	2.13	0.00	0.00	0.00	0.00	0.00
	8H	0.52	1.26	0.95	1.65	2.06	0.00	0.00	0.00	0.00	0.00
	12H	0.46	1.17	0.90	1.55	1.98	0.00	0.00	0.00	0.00	0.00
4H	2H	0.62	1.48	1.03	1.84	2.22	0.00	0.00	0.00	0.00	0.00
	3H	0.55	1.25	0.97	1.66	2.06	0.00	0.00	0.00	0.00	0.00
	4H	0.48	1.10	0.92	1.52	1.97	0.00	0.00	0.00	0.00	0.00
	6H	0.43	0.96	0.90	1.41	1.88	0.00	0.00	0.00	0.00	0.00
	8H	0.38	0.87	0.86	1.33	1.80	0.00	0.00	0.00	0.00	0.00
	12H	0.33	0.76	0.82	1.24	1.72	0.00	0.00	0.00	0.00	0.00
8H	4H	0.38	0.88	0.86	1.33	1.80	0.00	0.00	0.00	0.00	0.00
	6H	0.41	0.80	0.92	1.31	1.79	0.00	0.00	0.00	0.00	0.00
	8H	0.40	0.76	0.94	1.28	1.78	0.00	0.00	0.00	0.00	0.00
	12H	0.39	0.70	0.91	1.20	1.78	0.00	0.00	0.00	0.00	0.00
12H	4H	0.35	0.77	0.84	1.26	1.74	0.00	0.00	0.00	0.00	0.00
	6H	0.39	0.74	0.92	1.26	1.76	0.00	0.00	0.00	0.00	0.00
	8H	0.43	0.74	0.95	1.24	1.82	0.00	0.00	0.00	0.00	0.00