

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P622037

Luminaire Tested: VLT-WB-M-0U-075D-935-UNV-STD-W-4

Issue Date: 9/2/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P622037  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 10/28/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: VLT-WB-M-0U-075D-935-UNV-STD-W-4  
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE  
WHITE BAFFLE WITH MEDIUM OPTIC  
DOWNLIGHT 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2913.9 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.16 / 1.14  
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 28  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P622037  
CATALOG NUMBER: VLT-WB-M-0U-075D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P622037

CATALOG NUMBER: VLT-WB-M-0U-075D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	107	101	97	93	104	100	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74		81	77	73		79	75	72	71
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74	69	66	65
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	57	77	68	62	57	67	61	57		65	60	56		64	60	56	55
8	74	64	57	53	73	63	57	53	62	56	52		61	56	52		60	55	52	50
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56	52	48	47
10	67	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15074	15074	15074
5°	14917	15131	15420
10°	15068	15274	15501
15°	15296	15374	15451
20°	15223	15201	14997
25°	14808	14631	14455
30°	13932	13796	13500
35°	12619	12437	12137
40°	10263	10194	4819
45°	6352	7242	332
50°	2423	1941	199
55°	1190	353	74
60°	576	171	22
65°	530	25	25
70°	499	31	31
75°	494	42	42
80°	492	62	0
85°	486	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 7242 cd/sqm



TEST NUMBER: P622037

CATALOG NUMBER: VLT-WB-M-0U-075D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.6	6.9
10°-20°	581.9	20.0
20°-30°	846.1	29.0
30°-40°	842.0	28.9
40°-50°	370.3	12.7
50°-60°	54.6	1.9
60°-70°	12.5	0.4
70°-80°	4.7	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1628.7	55.9
0°-40°	2470.7	84.8
0°-60°	2895.6	99.4
0°-90°	2913.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2913.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2101	2101	2101	2101	2101	
5°	2071	2107	2101	2106	2141	198
15°	2059	2103	2069	2049	2080	579
25°	1870	1905	1848	1799	1826	855
35°	1440	1436	1420	1390	1386	882
45°	626	712	714	47	33	485
55°	95	102	28	10	6	96
65°	31	27	2	2	2	31
75°	18	3	2	2	2	19
85°	6	0	0	0	0	6
90°	0	0	0	0	0	



TEST NUMBER: P622037

CATALOG NUMBER: VLT-WB-M-0U-075D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2100.6	2100.6	2100.6	2100.6	2100.6
2.5°	2076.8	2108.2	2097.0	2096.2	2114.9
5°	2070.8	2107.2	2100.6	2105.8	2140.7
7.5°	2066.7	2103.3	2103.3	2100.8	2135.7
10°	2067.9	2105.7	2096.1	2092.5	2127.3
12.5°	2067.9	2108.0	2087.8	2078.2	2114.3
15°	2059.0	2102.6	2069.4	2049.2	2079.8
17.5°	2026.8	2074.2	2028.6	1989.4	2015.0
20°	1993.5	2044.4	1990.6	1940.6	1963.8
22.5°	1951.9	1997.0	1938.2	1885.9	1910.3
25°	1870.2	1905.0	1847.9	1799.4	1825.6
27.5°	1767.0	1786.2	1743.5	1696.9	1713.8
30°	1681.4	1695.9	1665.0	1620.6	1629.3
32.5°	1589.8	1599.7	1574.6	1536.1	1543.7
35°	1440.5	1436.2	1419.7	1389.9	1385.5
37.5°	1245.5	1237.9	1227.3	1112.0	797.4
40°	1095.6	1098.5	1088.2	680.1	514.4
42.5°	937.5	955.5	940.7	463.1	168.3
45°	625.9	711.6	713.6	47.2	32.7
47.5°	338.4	431.7	351.1	29.3	23.8
50°	217.0	270.8	173.9	22.2	17.8
52.5°	155.2	181.1	68.1	17.4	13.1
55°	95.1	102.4	28.2	10.3	5.9
57.5°	56.8	67.5	17.8	3.8	1.5
60°	40.1	47.4	11.9	1.5	1.5
62.5°	35.4	35.7	8.3	1.5	1.5
65°	31.2	26.9	1.5	1.5	1.5
67.5°	27.4	19.5	1.5	1.5	1.5
70°	23.8	13.6	1.5	1.5	1.5
72.5°	21.4	8.9	1.5	1.5	1.5
75°	17.8	3.3	1.5	1.5	1.5
77.5°	14.3	1.8	1.5	1.2	1.2
80°	11.9	1.7	1.5	0.0	0.0
82.5°	9.5	1.7	0.3	0.0	0.0
85°	5.9	0.1	0.0	0.0	0.0
87.5°	2.4	0.1	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P622037

CATALOG NUMBER: VLT-WB-M-OU-075D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.67	6.75	6.03	7.06	7.38	0.00	0.00	0.00	0.00	0.00
	3H	6.13	7.07	6.51	7.41	7.77	0.00	0.00	0.00	0.00	0.00
	4H	6.30	7.17	6.70	7.53	7.91	0.00	0.00	0.00	0.00	0.00
	6H	6.49	7.29	6.91	7.66	8.06	0.00	0.00	0.00	0.00	0.00
	8H	6.58	7.33	7.01	7.73	8.13	0.00	0.00	0.00	0.00	0.00
	12H	6.65	7.37	7.09	7.75	8.18	0.00	0.00	0.00	0.00	0.00
4H	2H	5.40	6.27	5.80	6.63	7.01	0.00	0.00	0.00	0.00	0.00
	3H	5.89	6.60	6.30	7.00	7.41	0.00	0.00	0.00	0.00	0.00
	4H	6.06	6.69	6.50	7.11	7.56	0.00	0.00	0.00	0.00	0.00
	6H	6.30	6.84	6.77	7.29	7.76	0.00	0.00	0.00	0.00	0.00
	8H	6.41	6.92	6.89	7.37	7.84	0.00	0.00	0.00	0.00	0.00
	12H	6.53	6.97	7.02	7.45	7.93	0.00	0.00	0.00	0.00	0.00
8H	4H	5.89	6.39	6.37	6.84	7.32	0.00	0.00	0.00	0.00	0.00
	6H	6.12	6.52	6.63	7.03	7.51	0.00	0.00	0.00	0.00	0.00
	8H	6.24	6.61	6.78	7.13	7.62	0.00	0.00	0.00	0.00	0.00
	12H	6.39	6.70	6.91	7.20	7.78	0.00	0.00	0.00	0.00	0.00
12H	4H	5.83	6.27	6.32	6.76	7.23	0.00	0.00	0.00	0.00	0.00
	6H	6.05	6.41	6.58	6.93	7.43	0.00	0.00	0.00	0.00	0.00
	8H	6.19	6.51	6.71	7.00	7.58	0.00	0.00	0.00	0.00	0.00