

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P622040

Luminaire Tested: VLT-WB-M-0U-100D-935-UNV-STD-W-4

Issue Date: 9/2/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P622040  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 10/28/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: VLT-WB-M-0U-100D-935-UNV-STD-W-4  
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE  
WHITE BAFFLE WITH MEDIUM OPTIC  
DOWNLIGHT 1000 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3881.3 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.16 / 1.14  
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P622040  
CATALOG NUMBER: VLT-WB-M-0U-100D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P622040

CATALOG NUMBER: VLT-WB-M-OU-100D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	75	93	85	79	75	83	78	74	81	77	73	79	75	72	71				71
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65				65
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59
7	79	69	62	57	77	68	62	57	67	61	57	65	60	56	64	60	56	55				55
8	74	64	57	53	73	63	57	53	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43				43

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20078	20078	20078
5°	19870	20155	20540
10°	20070	20345	20647
15°	20375	20478	20581
20°	20278	20248	19976
25°	19724	19489	19254
30°	18557	18377	17983
35°	16809	16566	16167
40°	13671	13578	6418
45°	8461	9646	442
50°	3227	2587	266
55°	1585	470	99
60°	768	227	29
65°	706	34	34
70°	665	42	42
75°	660	55	55
80°	653	83	0
85°	650	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 9646 cd/sqm



TEST NUMBER: P622040

CATALOG NUMBER: VLT-WB-M-OU-100D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	267.2	6.9
10°-20°	775.2	20.0
20°-30°	1127.1	29.0
30°-40°	1121.6	28.9
40°-50°	493.2	12.7
50°-60°	72.8	1.9
60°-70°	16.6	0.4
70°-80°	6.2	0.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2169.4	55.9
0°-40°	3291.0	84.8
0°-60°	3857.1	99.4
0°-90°	3881.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3881.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2798	2798	2798	2798	2798	
5°	2758	2807	2798	2805	2852	263
15°	2743	2801	2756	2730	2770	771
25°	2491	2538	2461	2397	2432	1139
35°	1919	1913	1891	1851	1846	1175
45°	834	948	950	63	44	646
55°	127	136	38	14	8	128
65°	42	36	2	2	2	41
75°	24	4	2	2	2	25
85°	8	0	0	0	0	9
90°	0	0	0	0	0	



TEST NUMBER: P622040

CATALOG NUMBER: VLT-WB-M-OU-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2798.0	2798.0	2798.0	2798.0	2798.0
2.5°	2766.3	2808.1	2793.2	2792.2	2817.0
5°	2758.4	2806.8	2798.0	2805.0	2851.5
7.5°	2752.9	2801.6	2801.6	2798.3	2844.7
10°	2754.4	2804.8	2792.1	2787.2	2833.6
12.5°	2754.4	2807.9	2781.0	2768.2	2816.2
15°	2742.6	2800.6	2756.4	2729.6	2770.3
17.5°	2699.8	2762.9	2702.2	2649.9	2683.9
20°	2655.4	2723.2	2651.5	2584.8	2615.8
22.5°	2600.0	2660.0	2581.8	2512.0	2544.5
25°	2491.1	2537.5	2461.4	2396.8	2431.7
27.5°	2353.6	2379.2	2322.4	2260.3	2282.8
30°	2239.6	2259.0	2217.8	2158.7	2170.3
32.5°	2117.6	2130.8	2097.4	2046.2	2056.2
35°	1918.8	1913.0	1891.1	1851.3	1845.5
37.5°	1659.0	1648.9	1634.8	1481.2	1062.2
40°	1459.4	1463.3	1449.5	905.9	685.1
42.5°	1248.7	1272.7	1253.1	616.8	224.2
45°	833.7	947.9	950.5	62.9	43.6
47.5°	450.7	575.0	467.7	39.0	31.7
50°	289.1	360.7	231.7	29.6	23.8
52.5°	206.7	241.2	90.7	23.2	17.4
55°	126.7	136.4	37.6	13.7	7.9
57.5°	75.6	90.0	23.8	5.1	2.0
60°	53.5	63.1	15.8	2.0	2.0
62.5°	47.1	47.5	11.1	2.0	2.0
65°	41.6	35.8	2.0	2.0	2.0
67.5°	36.4	26.0	2.0	2.0	2.0
70°	31.7	18.1	2.0	2.0	2.0
72.5°	28.5	11.9	2.0	2.0	2.0
75°	23.8	4.4	2.0	2.0	2.0
77.5°	19.0	2.4	2.0	1.6	1.6
80°	15.8	2.3	2.0	0.0	0.0
82.5°	12.7	2.2	0.4	0.0	0.0
85°	7.9	0.2	0.0	0.0	0.0
87.5°	3.2	0.1	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P622040

CATALOG NUMBER: VLT-WB-M-OU-100D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.66	7.75	7.03	8.06	8.37	0.00	0.00	0.00	0.00	0.00
	3H	7.12	8.07	7.50	8.40	8.77	0.00	0.00	0.00	0.00	0.00
	4H	7.29	8.17	7.70	8.52	8.91	0.00	0.00	0.00	0.00	0.00
	6H	7.49	8.29	7.90	8.66	9.06	0.00	0.00	0.00	0.00	0.00
	8H	7.58	8.33	8.01	8.72	9.13	0.00	0.00	0.00	0.00	0.00
	12H	7.65	8.37	8.08	8.75	9.18	0.00	0.00	0.00	0.00	0.00
4H	2H	6.39	7.27	6.80	7.62	8.01	0.00	0.00	0.00	0.00	0.00
	3H	6.88	7.59	7.30	8.00	8.41	0.00	0.00	0.00	0.00	0.00
	4H	7.06	7.69	7.50	8.11	8.56	0.00	0.00	0.00	0.00	0.00
	6H	7.30	7.84	7.77	8.29	8.76	0.00	0.00	0.00	0.00	0.00
	8H	7.41	7.91	7.89	8.36	8.84	0.00	0.00	0.00	0.00	0.00
	12H	7.53	7.96	8.02	8.45	8.93	0.00	0.00	0.00	0.00	0.00
8H	4H	6.89	7.39	7.37	7.84	8.32	0.00	0.00	0.00	0.00	0.00
	6H	7.12	7.52	7.63	8.02	8.51	0.00	0.00	0.00	0.00	0.00
	8H	7.24	7.60	7.77	8.12	8.62	0.00	0.00	0.00	0.00	0.00
	12H	7.39	7.70	7.91	8.20	8.78	0.00	0.00	0.00	0.00	0.00
12H	4H	6.83	7.26	7.32	7.75	8.23	0.00	0.00	0.00	0.00	0.00
	6H	7.05	7.41	7.58	7.93	8.43	0.00	0.00	0.00	0.00	0.00
	8H	7.19	7.50	7.71	8.00	8.58	0.00	0.00	0.00	0.00	0.00