

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: EPHESUS

Report Number: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **EPH-LS-08-0680R-57-70-4S-HEG-S**

Issue Date: 8/15/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-906-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/15/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: EPHESUS  
Catalog Number: EPH-LS-08-0680R-57-70-4S-HEG-S  
Description: EPHESUS LUMASPORT 8 LUMINAIRE  
(8) 5700K, 70 CRI LEDS AND 4S BEAM SHAPE  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	108758.9 lumens	Max Intensity:	235505.9 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	155.9 lumens/watt		
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')		
Beam Angle (50%):	37.2°H x 37.2°V	Field Angle (10%):	67.2°H x 67.2°V
Beam Lumens:	56618.9 lumens	Field Lumens:	95110.2 lumens
Beam Efficiency:	52.1%	Field Efficiency:	87.5%

Input Watts (W): 697.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

### Iso-Candela Plot






REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

### Lumen Table

90	0.1	0.8	3.2	7.7	10.1	7.7	3.2	0.8	0.1							
80	0.1	0.8	3.2	7.7	10.1	7.7	3.2	0.8	0.1							
70	0.4	0.5	1.9	5.4	11.3	18.4	24.6	28.0	28.0	24.6	18.4	11.3	5.4	1.9	0.5	0.4
60		1.5	6.4	17.5	32.1	45.2	54.7	60.0	60.0	54.7	45.2	32.1	17.5	6.4	1.5	
50	1.1	3.3	14.3	32.6	50.7	70.3	101.0	133.3	133.3	101.0	70.3	50.7	32.6	14.3	3.3	1.1
40		6.0	22.7	43.8	76.1	204.6	432.9	600.5	600.5	432.9	204.6	76.1	43.8	22.7	6.0	
30	2.2	8.9	28.9	55.1	186.3	582.0	1138.2	1692.5	1692.5	1138.2	582.0	186.3	55.1	28.9	8.9	2.2
20		11.1	32.8	74.8	370.8	1071.7	2654.1	4356.9	4356.9	2654.1	1071.7	370.8	74.8	32.8	11.1	
10	2.8	12.3	34.9	96.4	499.0	1549.7	4233.8	6377.4	6377.4	4233.8	1549.7	499.0	96.4	34.9	12.3	2.8
0		12.3	34.9	96.4	499.0	1549.7	4233.8	6377.4	6377.4	4233.8	1549.7	499.0	96.4	34.9	12.3	
-10	2.2	11.1	32.8	74.8	370.8	1071.7	2654.1	4356.9	4356.9	2654.1	1071.7	370.8	74.8	32.8	11.1	2.2
-20		8.9	28.9	55.1	186.3	582.0	1138.2	1692.5	1692.5	1138.2	582.0	186.3	55.1	28.9	8.9	
-30	1.1	6.0	22.7	43.8	76.1	204.6	432.9	600.5	600.5	432.9	204.6	76.1	43.8	22.7	6.0	1.1
-40		3.3	14.3	32.6	50.7	70.3	101.0	133.3	133.3	101.0	70.3	50.7	32.6	14.3	3.3	
-50	0.4	1.5	6.4	17.5	32.1	45.2	54.7	60.0	60.0	54.7	45.2	32.1	17.5	6.4	1.5	0.4
-60		0.5	1.9	5.4	11.3	18.4	24.6	28.0	28.0	24.6	18.4	11.3	5.4	1.9	0.5	
-70	0.1	0.8	3.2	7.7	10.1	7.7	3.2	0.8	0.1							
-80		0.1	0.8	3.2	7.7	10.1	7.7	3.2	0.8	0.1						
-90	0.1	0.8	3.2	7.7	10.1	7.7	3.2	0.8	0.1							

REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S


### Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg      - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

### Luminous Intensity Plot



**Beam:**  
 H Angle: 37.2°  
 V Angle: 37.2°  
 Lumens: 56618.9  
 Efficiency: 52.1%

**Field:**  
 H Angle: 67.2°  
 V Angle: 67.2°  
 Lumens: 95110.2  
 Efficiency: 87.5%

**Spill:**  
 Lumens: 13648.7  
 Efficiency: 12.5%

- Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.2	0.5	0.7	0.9	1.2	1.4	1.6	1.8	2.1	2.3
85°	0.0	0.5	0.9	1.4	1.9	2.3	2.8	3.2	3.7	4.1	4.6
82.5°	0.0	0.7	1.4	2.1	2.8	3.5	4.2	4.9	5.5	6.2	6.9
80°	0.0	0.9	1.9	2.8	3.7	4.7	5.6	6.5	7.4	8.3	9.2
77.5°	0.0	1.2	2.3	3.5	4.7	5.8	7.0	8.1	9.2	10.4	11.8
75°	0.0	1.4	2.8	4.2	5.6	7.0	8.4	9.7	11.2	13.4	15.5
72.5°	0.0	1.6	3.2	4.9	6.5	8.1	9.7	11.6	14.2	16.7	19.2
70°	0.0	1.8	3.7	5.5	7.4	9.2	11.2	14.2	17.1	20.0	22.9
67.5°	0.0	2.1	4.1	6.2	8.3	10.4	13.4	16.7	20.0	23.3	26.5
65°	0.0	2.3	4.6	6.9	9.2	11.8	15.5	19.2	22.9	26.5	32.3
62.5°	0.0	2.5	5.0	7.5	10.0	13.5	17.6	21.7	25.7	31.1	43.5
60°	0.0	2.7	5.4	8.1	10.9	15.3	19.7	24.1	28.4	40.9	54.4
57.5°	0.0	2.9	5.8	8.7	12.2	16.9	21.7	26.4	35.8	50.6	75.5
55°	0.0	3.1	6.2	9.3	13.5	18.6	23.7	28.8	44.2	63.0	101.1
52.5°	0.0	3.3	6.6	9.9	14.7	20.2	25.6	35.3	52.3	85.3	125.9
50°	0.0	3.5	7.0	10.5	16.0	21.7	27.5	42.2	63.5	107.0	158.3
47.5°	0.0	3.6	7.3	11.1	17.2	23.2	29.8	48.9	82.2	128.0	190.7
45°	0.0	3.8	7.7	12.0	18.3	24.6	35.3	55.3	100.1	155.9	221.9
42.5°	0.0	4.0	8.0	12.8	19.4	26.0	40.6	66.6	117.4	182.8	269.9
40°	0.0	4.1	8.3	13.6	20.4	27.3	45.6	81.0	135.9	208.6	318.9
37.5°	0.0	4.3	8.6	14.3	21.4	28.6	50.4	94.7	157.6	237.9	365.6
35°	0.0	4.4	8.9	15.0	22.4	31.5	54.9	107.6	178.2	277.5	417.2
32.5°	0.0	4.6	9.2	15.7	23.3	35.0	61.0	119.8	197.6	314.9	477.1
30°	0.0	4.7	9.4	16.3	24.1	38.3	70.7	132.2	215.7	349.9	533.3
27.5°	0.0	4.8	9.7	16.8	24.9	41.4	79.7	146.9	237.0	382.4	585.6
25°	0.0	4.9	9.9	17.4	25.6	44.2	88.0	160.4	263.5	421.0	634.3
22.5°	0.0	5.0	10.1	17.8	26.2	46.7	95.6	172.7	287.6	460.3	687.4
20°	0.0	5.1	10.2	18.3	26.8	49.1	102.4	183.8	309.4	495.8	735.4
17.5°	0.0	5.1	10.4	18.6	27.3	51.1	108.5	193.7	328.8	527.3	778.0
15°	0.0	5.2	10.5	19.0	27.7	52.9	113.7	202.3	345.7	554.8	815.3
12.5°	0.0	5.3	10.6	19.3	28.1	54.4	118.2	209.6	360.0	578.2	847.0
10°	0.0	5.3	10.7	19.5	28.4	55.7	121.9	215.6	371.8	597.5	873.0
7.5°	0.0	5.4	10.8	19.7	28.7	56.6	124.8	220.3	381.0	612.5	893.4
5°	0.0	5.4	10.9	19.8	28.9	57.3	126.9	223.6	387.6	623.3	908.0
2.5°	0.0	5.4	10.9	19.9	29.0	57.8	128.1	225.6	391.6	629.7	916.8
0°	0.0	5.4	10.9	19.9	29.0	57.8	128.1	225.6	391.6	629.7	916.8
-2.5°	0.0	5.4	10.9	19.9	29.0	57.8	128.1	225.6	391.6	629.7	916.8
-5°	0.0	5.4	10.9	19.8	28.9	57.3	126.9	223.6	387.6	623.3	908.0
-7.5°	0.0	5.4	10.8	19.7	28.7	56.6	124.8	220.3	381.0	612.5	893.4
-10°	0.0	5.3	10.7	19.5	28.4	55.7	121.9	215.6	371.8	597.5	873.0
-12.5°	0.0	5.3	10.6	19.3	28.1	54.4	118.2	209.6	360.0	578.2	847.0
-15°	0.0	5.2	10.5	19.0	27.7	52.9	113.7	202.3	345.7	554.8	815.3
-17.5°	0.0	5.1	10.4	18.6	27.3	51.1	108.5	193.7	328.8	527.3	778.0
-20°	0.0	5.1	10.2	18.3	26.8	49.1	102.4	183.8	309.4	495.8	735.4



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0.0	5.0	10.1	17.8	26.2	46.7	95.6	172.7	287.6	460.3	687.4
-25°	0.0	4.9	9.9	17.4	25.6	44.2	88.0	160.4	263.5	421.0	634.3
-27.5°	0.0	4.8	9.7	16.8	24.9	41.4	79.7	146.9	237.0	382.4	585.6
-30°	0.0	4.7	9.4	16.3	24.1	38.3	70.7	132.2	215.7	349.9	533.3
-32.5°	0.0	4.6	9.2	15.7	23.3	35.0	61.0	119.8	197.6	314.9	477.1
-35°	0.0	4.4	8.9	15.0	22.4	31.5	54.9	107.6	178.2	277.5	417.2
-37.5°	0.0	4.3	8.6	14.3	21.4	28.6	50.4	94.7	157.6	237.9	365.6
-40°	0.0	4.1	8.3	13.6	20.4	27.3	45.6	81.0	135.9	208.6	318.9
-42.5°	0.0	4.0	8.0	12.8	19.4	26.0	40.6	66.6	117.4	182.8	269.9
-45°	0.0	3.8	7.7	12.0	18.3	24.6	35.3	55.3	100.1	155.9	221.9
-47.5°	0.0	3.6	7.3	11.1	17.2	23.2	29.8	48.9	82.2	128.0	190.7
-50°	0.0	3.5	7.0	10.5	16.0	21.7	27.5	42.2	63.5	107.0	158.3
-52.5°	0.0	3.3	6.6	9.9	14.7	20.2	25.6	35.3	52.3	85.3	125.9
-55°	0.0	3.1	6.2	9.3	13.5	18.6	23.7	28.8	44.2	63.0	101.1
-57.5°	0.0	2.9	5.8	8.7	12.2	16.9	21.7	26.4	35.8	50.6	75.5
-60°	0.0	2.7	5.4	8.1	10.9	15.3	19.7	24.1	28.4	40.9	54.4
-62.5°	0.0	2.5	5.0	7.5	10.0	13.5	17.6	21.7	25.7	31.1	43.5
-65°	0.0	2.3	4.6	6.9	9.2	11.8	15.5	19.2	22.9	26.5	32.3
-67.5°	0.0	2.1	4.1	6.2	8.3	10.4	13.4	16.7	20.0	23.3	26.5
-70°	0.0	1.8	3.7	5.5	7.4	9.2	11.2	14.2	17.1	20.0	22.9
-72.5°	0.0	1.6	3.2	4.9	6.5	8.1	9.7	11.6	14.2	16.7	19.2
-75°	0.0	1.4	2.8	4.2	5.6	7.0	8.4	9.7	11.2	13.4	15.5
-77.5°	0.0	1.2	2.3	3.5	4.7	5.8	7.0	8.1	9.2	10.4	11.8
-80°	0.0	0.9	1.9	2.8	3.7	4.7	5.6	6.5	7.4	8.3	9.2
-82.5°	0.0	0.7	1.4	2.1	2.8	3.5	4.2	4.9	5.5	6.2	6.9
-85°	0.0	0.5	0.9	1.4	1.9	2.3	2.8	3.2	3.7	4.1	4.6
-87.5°	0.0	0.2	0.5	0.7	0.9	1.2	1.4	1.6	1.8	2.1	2.3
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	2.5	2.7	2.9	3.1	3.3	3.5	3.6	3.8	4.0	4.1	4.3
85°	5.0	5.4	5.8	6.2	6.6	7.0	7.3	7.7	8.0	8.3	8.6
82.5°	7.5	8.1	8.7	9.3	9.9	10.5	11.1	12.0	12.8	13.6	14.3
80°	10.0	10.9	12.2	13.5	14.7	16.0	17.2	18.3	19.4	20.4	21.4
77.5°	13.5	15.3	16.9	18.6	20.2	21.7	23.2	24.6	26.0	27.3	28.6
75°	17.6	19.7	21.7	23.7	25.6	27.5	29.8	35.3	40.6	45.6	50.4
72.5°	21.7	24.1	26.4	28.8	35.3	42.2	48.9	55.3	66.6	81.0	94.7
70°	25.7	28.4	35.8	44.2	52.3	63.5	82.2	100.1	117.4	135.9	157.6
67.5°	31.1	40.9	50.6	63.0	85.3	107.0	128.0	155.9	182.8	208.6	237.9
65°	43.5	54.4	75.5	101.1	125.9	158.3	190.7	221.9	269.9	318.9	365.6
62.5°	55.7	81.9	110.6	142.5	180.4	217.1	271.4	330.0	386.5	461.3	535.3
60°	81.9	113.7	151.3	193.7	241.0	309.4	375.7	460.3	548.9	634.3	732.1
57.5°	110.6	151.3	198.1	256.3	332.4	412.4	515.7	615.6	728.3	839.7	949.3
55°	142.5	193.7	256.3	340.1	434.6	549.2	666.3	796.2	921.9	1056.2	1184.8
52.5°	180.4	241.0	332.4	434.6	560.4	693.6	837.4	983.4	1133.6	1276.8	1410.0
50°	217.1	309.4	412.4	549.2	693.6	851.1	1014.3	1180.5	1337.3	1486.3	1610.2
47.5°	271.4	375.7	515.7	666.3	837.4	1014.3	1196.2	1367.8	1532.5	1657.8	1774.9
45°	330.0	460.3	615.6	796.2	983.4	1180.5	1367.8	1548.0	1681.8	1805.1	1902.1
42.5°	386.5	548.9	728.3	921.9	1133.6	1337.3	1532.5	1681.8	1814.6	1921.4	2043.6
40°	461.3	634.3	839.7	1056.2	1276.8	1486.3	1657.8	1805.1	1921.4	2056.6	2201.7
37.5°	535.3	732.1	949.3	1184.8	1410.0	1610.2	1774.9	1902.1	2043.6	2201.7	2415.0
35°	605.6	825.1	1062.3	1304.8	1537.2	1714.8	1863.9	2004.7	2175.1	2395.8	2616.1
32.5°	680.2	913.0	1169.2	1416.3	1632.0	1807.3	1946.8	2122.5	2338.7	2581.1	2795.5
30°	755.2	1004.2	1268.6	1521.4	1719.0	1880.3	2044.7	2244.6	2507.2	2742.0	3007.8
27.5°	825.1	1089.9	1358.8	1602.8	1796.6	1948.7	2142.5	2392.9	2654.0	2907.9	3230.8
25°	889.7	1169.2	1442.2	1672.4	1855.4	2027.4	2243.8	2531.2	2786.9	3103.7	4301.6
22.5°	952.0	1241.7	1518.7	1736.2	1909.4	2105.1	2362.2	2647.6	2929.8	3330.3	5523.9
20°	1011.4	1304.8	1578.5	1791.7	1958.4	2175.7	2470.1	2751.8	3084.3	4373.2	7061.4
17.5°	1064.3	1360.9	1625.7	1831.8	2013.9	2251.2	2565.1	2845.4	3223.2	5313.9	8646.6
15°	1110.5	1410.0	1667.0	1867.0	2064.8	2329.4	2641.0	2954.3	3708.9	6279.4	10059.6
12.5°	1149.8	1451.8	1702.2	1897.0	2108.4	2396.3	2706.1	3051.4	4369.2	7397.6	11492.0
10°	1182.2	1486.3	1731.3	1921.8	2144.3	2451.5	2759.9	3131.8	4916.8	8326.7	12684.9
7.5°	1207.5	1513.2	1754.0	1941.1	2172.4	2494.9	2802.1	3194.9	5347.5	9058.6	13626.2
5°	1225.7	1532.5	1770.2	1955.0	2192.6	2526.0	2832.5	3240.3	5657.8	9586.5	14306.2
2.5°	1236.6	1544.1	1780.0	1963.4	2204.7	2544.7	2850.8	3267.7	5845.0	9905.3	14717.3
0°	1240.2	1548.0	1783.3	1966.2	2208.8	2551.0	2856.9	3276.9	5907.6	10011.9	14854.9
-2.5°	1236.6	1544.1	1780.0	1963.4	2204.7	2544.7	2850.8	3267.7	5845.0	9905.3	14717.3
-5°	1225.7	1532.5	1770.2	1955.0	2192.6	2526.0	2832.5	3240.3	5657.8	9586.5	14306.2
-7.5°	1207.5	1513.2	1754.0	1941.1	2172.4	2494.9	2802.1	3194.9	5347.5	9058.6	13626.2
-10°	1182.2	1486.3	1731.3	1921.8	2144.3	2451.5	2759.9	3131.8	4916.8	8326.7	12684.9
-12.5°	1149.8	1451.8	1702.2	1897.0	2108.4	2396.3	2706.1	3051.4	4369.2	7397.6	11492.0
-15°	1110.5	1410.0	1667.0	1867.0	2064.8	2329.4	2641.0	2954.3	3708.9	6279.4	10059.6
-17.5°	1064.3	1360.9	1625.7	1831.8	2013.9	2251.2	2565.1	2845.4	3223.2	5313.9	8646.6
-20°	1011.4	1304.8	1578.5	1791.7	1958.4	2175.7	2470.1	2751.8	3084.3	4373.2	7061.4



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	952.0	1241.7	1518.7	1736.2	1909.4	2105.1	2362.2	2647.6	2929.8	3330.3	5523.9
-25°	889.7	1169.2	1442.2	1672.4	1855.4	2027.4	2243.8	2531.2	2786.9	3103.7	4301.6
-27.5°	825.1	1089.9	1358.8	1602.8	1796.6	1948.7	2142.5	2392.9	2654.0	2907.9	3230.8
-30°	755.2	1004.2	1268.6	1521.4	1719.0	1880.3	2044.7	2244.6	2507.2	2742.0	3007.8
-32.5°	680.2	913.0	1169.2	1416.3	1632.0	1807.3	1946.8	2122.5	2338.7	2581.1	2795.5
-35°	605.6	825.1	1062.3	1304.8	1537.2	1714.8	1863.9	2004.7	2175.1	2395.8	2616.1
-37.5°	535.3	732.1	949.3	1184.8	1410.0	1610.2	1774.9	1902.1	2043.6	2201.7	2415.0
-40°	461.3	634.3	839.7	1056.2	1276.8	1486.3	1657.8	1805.1	1921.4	2056.6	2201.7
-42.5°	386.5	548.9	728.3	921.9	1133.6	1337.3	1532.5	1681.8	1814.6	1921.4	2043.6
-45°	330.0	460.3	615.6	796.2	983.4	1180.5	1367.8	1548.0	1681.8	1805.1	1902.1
-47.5°	271.4	375.7	515.7	666.3	837.4	1014.3	1196.2	1367.8	1532.5	1657.8	1774.9
-50°	217.1	309.4	412.4	549.2	693.6	851.1	1014.3	1180.5	1337.3	1486.3	1610.2
-52.5°	180.4	241.0	332.4	434.6	560.4	693.6	837.4	983.4	1133.6	1276.8	1410.0
-55°	142.5	193.7	256.3	340.1	434.6	549.2	666.3	796.2	921.9	1056.2	1184.8
-57.5°	110.6	151.3	198.1	256.3	332.4	412.4	515.7	615.6	728.3	839.7	949.3
-60°	81.9	113.7	151.3	193.7	241.0	309.4	375.7	460.3	548.9	634.3	732.1
-62.5°	55.7	81.9	110.6	142.5	180.4	217.1	271.4	330.0	386.5	461.3	535.3
-65°	43.5	54.4	75.5	101.1	125.9	158.3	190.7	221.9	269.9	318.9	365.6
-67.5°	31.1	40.9	50.6	63.0	85.3	107.0	128.0	155.9	182.8	208.6	237.9
-70°	25.7	28.4	35.8	44.2	52.3	63.5	82.2	100.1	117.4	135.9	157.6
-72.5°	21.7	24.1	26.4	28.8	35.3	42.2	48.9	55.3	66.6	81.0	94.7
-75°	17.6	19.7	21.7	23.7	25.6	27.5	29.8	35.3	40.6	45.6	50.4
-77.5°	13.5	15.3	16.9	18.6	20.2	21.7	23.2	24.6	26.0	27.3	28.6
-80°	10.0	10.9	12.2	13.5	14.7	16.0	17.2	18.3	19.4	20.4	21.4
-82.5°	7.5	8.1	8.7	9.3	9.9	10.5	11.1	12.0	12.8	13.6	14.3
-85°	5.0	5.4	5.8	6.2	6.6	7.0	7.3	7.7	8.0	8.3	8.6
-87.5°	2.5	2.7	2.9	3.1	3.3	3.5	3.6	3.8	4.0	4.1	4.3
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.4	4.6	4.7	4.8	4.9	5.0	5.1	5.1	5.2	5.3	5.3
85°	8.9	9.2	9.4	9.7	9.9	10.1	10.2	10.4	10.5	10.6	10.7
82.5°	15.0	15.7	16.3	16.8	17.4	17.8	18.3	18.6	19.0	19.3	19.5
80°	22.4	23.3	24.1	24.9	25.6	26.2	26.8	27.3	27.7	28.1	28.4
77.5°	31.5	35.0	38.3	41.4	44.2	46.7	49.1	51.1	52.9	54.4	55.7
75°	54.9	61.0	70.7	79.7	88.0	95.6	102.4	108.5	113.7	118.2	121.9
72.5°	107.6	119.8	132.2	146.9	160.4	172.7	183.8	193.7	202.3	209.6	215.6
70°	178.2	197.6	215.7	237.0	263.5	287.6	309.4	328.8	345.7	360.0	371.8
67.5°	277.5	314.9	349.9	382.4	421.0	460.3	495.8	527.3	554.8	578.2	597.5
65°	417.2	477.1	533.3	585.6	634.3	687.4	735.4	778.0	815.3	847.0	873.0
62.5°	605.6	680.2	755.2	825.1	889.7	952.0	1011.4	1064.3	1110.5	1149.8	1182.2
60°	825.1	913.0	1004.2	1089.9	1169.2	1241.7	1304.8	1360.9	1410.0	1451.8	1486.3
57.5°	1062.3	1169.2	1268.6	1358.8	1442.2	1518.7	1578.5	1625.7	1667.0	1702.2	1731.3
55°	1304.8	1416.3	1521.4	1602.8	1672.4	1736.2	1791.7	1831.8	1867.0	1897.0	1921.8
52.5°	1537.2	1632.0	1719.0	1796.6	1855.4	1909.4	1958.4	2013.9	2064.8	2108.4	2144.3
50°	1714.8	1807.3	1880.3	1948.7	2027.4	2105.1	2175.7	2251.2	2329.4	2396.3	2451.5
47.5°	1863.9	1946.8	2044.7	2142.5	2243.8	2362.2	2470.1	2565.1	2641.0	2706.1	2759.9
45°	2004.7	2122.5	2244.6	2392.9	2531.2	2647.6	2751.8	2845.4	2954.3	3051.4	3131.8
42.5°	2175.1	2338.7	2507.2	2654.0	2786.9	2929.8	3084.3	3223.2	3708.9	4369.2	4916.8
40°	2395.8	2581.1	2742.0	2907.9	3103.7	3330.3	4373.2	5313.9	6279.4	7397.6	8326.7
37.5°	2616.1	2795.5	3007.8	3230.8	4301.6	5523.9	7061.4	8646.6	10059.6	11492.0	12684.9
35°	2813.5	3058.3	3473.3	4962.5	6624.4	8670.1	10654.2	12674.0	14470.5	16145.2	17576.0
32.5°	3058.3	3636.3	5297.1	7427.6	9767.6	12310.7	14704.7	17091.1	19235.1	21230.8	23018.5
30°	3473.3	5297.1	7697.7	10380.3	13324.7	16220.2	19054.9	21860.4	24523.3	26937.2	29210.0
27.5°	4962.5	7427.6	10380.3	13666.2	16998.2	20271.3	23760.3	27077.6	30439.4	33388.3	36423.3
25°	6624.4	9767.6	13324.7	16998.2	20737.2	24728.7	28831.0	32861.0	37197.3	41128.6	45838.6
22.5°	8670.1	12310.7	16220.2	20271.3	24728.7	29423.8	34253.3	39561.5	45742.0	52502.8	59320.7
20°	10654.2	14704.7	19054.9	23760.3	28831.0	34253.3	40363.4	48389.2	57065.4	67401.8	76876.0
17.5°	12674.0	17091.1	21860.4	27077.6	32861.0	39561.5	48389.2	59041.1	71591.5	85584.1	98625.2
15°	14470.5	19235.1	24523.3	30439.4	37197.3	45742.0	57065.4	71591.5	88571.0	106745.8	125801.3
12.5°	16145.2	21230.8	26937.2	33388.3	41128.6	52502.8	67401.8	85584.1	106745.8	130429.5	147953.8
10°	17576.0	23018.5	29210.0	36423.3	45838.6	59320.7	76876.0	98625.2	125801.3	147953.8	166008.8
7.5°	18707.8	24436.4	31018.9	38851.3	50051.0	65836.3	86433.0	112454.1	139854.1	162051.0	179802.7
5°	19526.8	25464.7	32334.3	40623.1	53138.6	70639.9	93533.3	123014.5	149677.2	171718.5	189640.8
2.5°	20022.5	26088.2	33133.4	41702.0	55024.7	73586.8	97914.6	129584.4	155862.1	177650.6	195942.4
0°	20188.5	26297.1	33401.4	42064.4	55659.3	74580.5	99396.6	131816.7	157977.9	179617.6	198170.4
-2.5°	20022.5	26088.2	33133.4	41702.0	55024.7	73586.8	97914.6	129584.4	155862.1	177650.6	195942.4
-5°	19526.8	25464.7	32334.3	40623.1	53138.6	70639.9	93533.3	123014.5	149677.2	171718.5	189640.8
-7.5°	18707.8	24436.4	31018.9	38851.3	50051.0	65836.3	86433.0	112454.1	139854.1	162051.0	179802.7
-10°	17576.0	23018.5	29210.0	36423.3	45838.6	59320.7	76876.0	98625.2	125801.3	147953.8	166008.8
-12.5°	16145.2	21230.8	26937.2	33388.3	41128.6	52502.8	67401.8	85584.1	106745.8	130429.5	147953.8
-15°	14470.5	19235.1	24523.3	30439.4	37197.3	45742.0	57065.4	71591.5	88571.0	106745.8	125801.3
-17.5°	12674.0	17091.1	21860.4	27077.6	32861.0	39561.5	48389.2	59041.1	71591.5	85584.1	98625.2
-20°	10654.2	14704.7	19054.9	23760.3	28831.0	34253.3	40363.4	48389.2	57065.4	67401.8	76876.0



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	8670.1	12310.7	16220.2	20271.3	24728.7	29423.8	34253.3	39561.5	45742.0	52502.8	59320.7
-25°	6624.4	9767.6	13324.7	16998.2	20737.2	24728.7	28831.0	32861.0	37197.3	41128.6	45838.6
-27.5°	4962.5	7427.6	10380.3	13666.2	16998.2	20271.3	23760.3	27077.6	30439.4	33388.3	36423.3
-30°	3473.3	5297.1	7697.7	10380.3	13324.7	16220.2	19054.9	21860.4	24523.3	26937.2	29210.0
-32.5°	3058.3	3636.3	5297.1	7427.6	9767.6	12310.7	14704.7	17091.1	19235.1	21230.8	23018.5
-35°	2813.5	3058.3	3473.3	4962.5	6624.4	8670.1	10654.2	12674.0	14470.5	16145.2	17576.0
-37.5°	2616.1	2795.5	3007.8	3230.8	4301.6	5523.9	7061.4	8646.6	10059.6	11492.0	12684.9
-40°	2395.8	2581.1	2742.0	2907.9	3103.7	3330.3	4373.2	5313.9	6279.4	7397.6	8326.7
-42.5°	2175.1	2338.7	2507.2	2654.0	2786.9	2929.8	3084.3	3223.2	3708.9	4369.2	4916.8
-45°	2004.7	2122.5	2244.6	2392.9	2531.2	2647.6	2751.8	2845.4	2954.3	3051.4	3131.8
-47.5°	1863.9	1946.8	2044.7	2142.5	2243.8	2362.2	2470.1	2565.1	2641.0	2706.1	2759.9
-50°	1714.8	1807.3	1880.3	1948.7	2027.4	2105.1	2175.7	2251.2	2329.4	2396.3	2451.5
-52.5°	1537.2	1632.0	1719.0	1796.6	1855.4	1909.4	1958.4	2013.9	2064.8	2108.4	2144.3
-55°	1304.8	1416.3	1521.4	1602.8	1672.4	1736.2	1791.7	1831.8	1867.0	1897.0	1921.8
-57.5°	1062.3	1169.2	1268.6	1358.8	1442.2	1518.7	1578.5	1625.7	1667.0	1702.2	1731.3
-60°	825.1	913.0	1004.2	1089.9	1169.2	1241.7	1304.8	1360.9	1410.0	1451.8	1486.3
-62.5°	605.6	680.2	755.2	825.1	889.7	952.0	1011.4	1064.3	1110.5	1149.8	1182.2
-65°	417.2	477.1	533.3	585.6	634.3	687.4	735.4	778.0	815.3	847.0	873.0
-67.5°	277.5	314.9	349.9	382.4	421.0	460.3	495.8	527.3	554.8	578.2	597.5
-70°	178.2	197.6	215.7	237.0	263.5	287.6	309.4	328.8	345.7	360.0	371.8
-72.5°	107.6	119.8	132.2	146.9	160.4	172.7	183.8	193.7	202.3	209.6	215.6
-75°	54.9	61.0	70.7	79.7	88.0	95.6	102.4	108.5	113.7	118.2	121.9
-77.5°	31.5	35.0	38.3	41.4	44.2	46.7	49.1	51.1	52.9	54.4	55.7
-80°	22.4	23.3	24.1	24.9	25.6	26.2	26.8	27.3	27.7	28.1	28.4
-82.5°	15.0	15.7	16.3	16.8	17.4	17.8	18.3	18.6	19.0	19.3	19.5
-85°	8.9	9.2	9.4	9.7	9.9	10.1	10.2	10.4	10.5	10.6	10.7
-87.5°	4.4	4.6	4.7	4.8	4.9	5.0	5.1	5.1	5.2	5.3	5.3
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.3	5.3	5.2	5.1
85°	10.8	10.9	10.9	10.9	10.9	10.9	10.8	10.7	10.6	10.5	10.4
82.5°	19.7	19.8	19.9	19.9	19.9	19.8	19.7	19.5	19.3	19.0	18.6
80°	28.7	28.9	29.0	29.0	29.0	28.9	28.7	28.4	28.1	27.7	27.3
77.5°	56.6	57.3	57.8	57.9	57.8	57.3	56.6	55.7	54.4	52.9	51.1
75°	124.8	126.9	128.1	128.5	128.1	126.9	124.8	121.9	118.2	113.7	108.5
72.5°	220.3	223.6	225.6	226.3	225.6	223.6	220.3	215.6	209.6	202.3	193.7
70°	381.0	387.6	391.6	392.9	391.6	387.6	381.0	371.8	360.0	345.7	328.8
67.5°	612.5	623.3	629.7	631.9	629.7	623.3	612.5	597.5	578.2	554.8	527.3
65°	893.4	908.0	916.8	919.7	916.8	908.0	893.4	873.0	847.0	815.3	778.0
62.5°	1207.5	1225.7	1236.6	1240.2	1236.6	1225.7	1207.5	1182.2	1149.8	1110.5	1064.3
60°	1513.2	1532.5	1544.1	1548.0	1544.1	1532.5	1513.2	1486.3	1451.8	1410.0	1360.9
57.5°	1754.0	1770.2	1780.0	1783.3	1780.0	1770.2	1754.0	1731.3	1702.2	1667.0	1625.7
55°	1941.1	1955.0	1963.4	1966.2	1963.4	1955.0	1941.1	1921.8	1897.0	1867.0	1831.8
52.5°	2172.4	2192.6	2204.7	2208.8	2204.7	2192.6	2172.4	2144.3	2108.4	2064.8	2013.9
50°	2494.9	2526.0	2544.7	2551.0	2544.7	2526.0	2494.9	2451.5	2396.3	2329.4	2251.2
47.5°	2802.1	2832.5	2850.8	2856.9	2850.8	2832.5	2802.1	2759.9	2706.1	2641.0	2565.1
45°	3194.9	3240.3	3267.7	3276.9	3267.7	3240.3	3194.9	3131.8	3051.4	2954.3	2845.4
42.5°	5347.5	5657.8	5845.0	5907.6	5845.0	5657.8	5347.5	4916.8	4369.2	3708.9	3223.2
40°	9058.6	9586.5	9905.3	10011.9	9905.3	9586.5	9058.6	8326.7	7397.6	6279.4	5313.9
37.5°	13626.2	14306.2	14717.3	14854.9	14717.3	14306.2	13626.2	12684.9	11492.0	10059.6	8646.6
35°	18707.8	19526.8	20022.5	20188.5	20022.5	19526.8	18707.8	17576.0	16145.2	14470.5	12674.0
32.5°	24436.4	25464.7	26088.2	26297.1	26088.2	25464.7	24436.4	23018.5	21230.8	19235.1	17091.1
30°	31018.9	32334.3	33133.4	33401.4	33133.4	32334.3	31018.9	29210.0	26937.2	24523.3	21860.4
27.5°	38851.3	40623.1	41702.0	42064.4	41702.0	40623.1	38851.3	36423.3	33388.3	30439.4	27077.6
25°	50051.0	53138.6	55024.7	55659.3	55024.7	53138.6	50051.0	45838.6	41128.6	37197.3	32861.0
22.5°	65836.3	70639.9	73586.8	74580.5	73586.8	70639.9	65836.3	59320.7	52502.8	45742.0	39561.5
20°	86433.0	93533.3	97914.6	99396.6	97914.6	93533.3	86433.0	76876.0	67401.8	57065.4	48389.2
17.5°	112454.1	123014.5	129584.4	131816.7	129584.4	123014.5	112454.1	98625.2	85584.1	71591.5	59041.1
15°	139854.1	149677.2	155862.1	157977.9	155862.1	149677.2	139854.1	125801.3	106745.8	88571.0	71591.5
12.5°	162051.0	171718.5	177650.6	179617.6	177650.6	171718.5	162051.0	147953.8	130429.5	106745.8	85584.1
10°	179802.7	189640.8	195942.4	198170.4	195942.4	189640.8	179802.7	166008.8	147953.8	125801.3	98625.2
7.5°	193845.7	204949.9	211675.4	214069.0	211675.4	204949.9	193845.7	179802.7	162051.0	139854.1	112454.1
5°	204949.9	216640.5	224601.0	227402.2	224601.0	216640.5	204949.9	189640.8	171718.5	149677.2	123014.5
2.5°	211675.4	224601.0	232290.9	234500.2	232290.9	224601.0	211675.4	195942.4	177650.6	155862.1	129584.4
0°	214069.0	227402.2	234500.2	235505.9	234500.2	227402.2	214069.0	198170.4	179617.6	157977.9	131816.7
-2.5°	211675.4	224601.0	232290.9	234500.2	232290.9	224601.0	211675.4	195942.4	177650.6	155862.1	129584.4
-5°	204949.9	216640.5	224601.0	227402.2	224601.0	216640.5	204949.9	189640.8	171718.5	149677.2	123014.5
-7.5°	193845.7	204949.9	211675.4	214069.0	211675.4	204949.9	193845.7	179802.7	162051.0	139854.1	112454.1
-10°	179802.7	189640.8	195942.4	198170.4	195942.4	189640.8	179802.7	166008.8	147953.8	125801.3	98625.2
-12.5°	162051.0	171718.5	177650.6	179617.6	177650.6	171718.5	162051.0	147953.8	130429.5	106745.8	85584.1
-15°	139854.1	149677.2	155862.1	157977.9	155862.1	149677.2	139854.1	125801.3	106745.8	88571.0	71591.5
-17.5°	112454.1	123014.5	129584.4	131816.7	129584.4	123014.5	112454.1	98625.2	85584.1	71591.5	59041.1
-20°	86433.0	93533.3	97914.6	99396.6	97914.6	93533.3	86433.0	76876.0	67401.8	57065.4	48389.2



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	65836.3	70639.9	73586.8	74580.5	73586.8	70639.9	65836.3	59320.7	52502.8	45742.0	39561.5
-25°	50051.0	53138.6	55024.7	55659.3	55024.7	53138.6	50051.0	45838.6	41128.6	37197.3	32861.0
-27.5°	38851.3	40623.1	41702.0	42064.4	41702.0	40623.1	38851.3	36423.3	33388.3	30439.4	27077.6
-30°	31018.9	32334.3	33133.4	33401.4	33133.4	32334.3	31018.9	29210.0	26937.2	24523.3	21860.4
-32.5°	24436.4	25464.7	26088.2	26297.1	26088.2	25464.7	24436.4	23018.5	21230.8	19235.1	17091.1
-35°	18707.8	19526.8	20022.5	20188.5	20022.5	19526.8	18707.8	17576.0	16145.2	14470.5	12674.0
-37.5°	13626.2	14306.2	14717.3	14854.9	14717.3	14306.2	13626.2	12684.9	11492.0	10059.6	8646.6
-40°	9058.6	9586.5	9905.3	10011.9	9905.3	9586.5	9058.6	8326.7	7397.6	6279.4	5313.9
-42.5°	5347.5	5657.8	5845.0	5907.6	5845.0	5657.8	5347.5	4916.8	4369.2	3708.9	3223.2
-45°	3194.9	3240.3	3267.7	3276.9	3267.7	3240.3	3194.9	3131.8	3051.4	2954.3	2845.4
-47.5°	2802.1	2832.5	2850.8	2856.9	2850.8	2832.5	2802.1	2759.9	2706.1	2641.0	2565.1
-50°	2494.9	2526.0	2544.7	2551.0	2544.7	2526.0	2494.9	2451.5	2396.3	2329.4	2251.2
-52.5°	2172.4	2192.6	2204.7	2208.8	2204.7	2192.6	2172.4	2144.3	2108.4	2064.8	2013.9
-55°	1941.1	1955.0	1963.4	1966.2	1963.4	1955.0	1941.1	1921.8	1897.0	1867.0	1831.8
-57.5°	1754.0	1770.2	1780.0	1783.3	1780.0	1770.2	1754.0	1731.3	1702.2	1667.0	1625.7
-60°	1513.2	1532.5	1544.1	1548.0	1544.1	1532.5	1513.2	1486.3	1451.8	1410.0	1360.9
-62.5°	1207.5	1225.7	1236.6	1240.2	1236.6	1225.7	1207.5	1182.2	1149.8	1110.5	1064.3
-65°	893.4	908.0	916.8	919.7	916.8	908.0	893.4	873.0	847.0	815.3	778.0
-67.5°	612.5	623.3	629.7	631.9	629.7	623.3	612.5	597.5	578.2	554.8	527.3
-70°	381.0	387.6	391.6	392.9	391.6	387.6	381.0	371.8	360.0	345.7	328.8
-72.5°	220.3	223.6	225.6	226.3	225.6	223.6	220.3	215.6	209.6	202.3	193.7
-75°	124.8	126.9	128.1	128.5	128.1	126.9	124.8	121.9	118.2	113.7	108.5
-77.5°	56.6	57.3	57.8	57.9	57.8	57.3	56.6	55.7	54.4	52.9	51.1
-80°	28.7	28.9	29.0	29.0	29.0	28.9	28.7	28.4	28.1	27.7	27.3
-82.5°	19.7	19.8	19.9	19.9	19.9	19.8	19.7	19.5	19.3	19.0	18.6
-85°	10.8	10.9	10.9	10.9	10.9	10.9	10.8	10.7	10.6	10.5	10.4
-87.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.3	5.3	5.2	5.1
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	5.1	5.0	4.9	4.8	4.7	4.6	4.4	4.3	4.1	4.0	3.8
85°	10.2	10.1	9.9	9.7	9.4	9.2	8.9	8.6	8.3	8.0	7.7
82.5°	18.3	17.8	17.4	16.8	16.3	15.7	15.0	14.3	13.6	12.8	12.0
80°	26.8	26.2	25.6	24.9	24.1	23.3	22.4	21.4	20.4	19.4	18.3
77.5°	49.1	46.7	44.2	41.4	38.3	35.0	31.5	28.6	27.3	26.0	24.6
75°	102.4	95.6	88.0	79.7	70.7	61.0	54.9	50.4	45.6	40.6	35.3
72.5°	183.8	172.7	160.4	146.9	132.2	119.8	107.6	94.7	81.0	66.6	55.3
70°	309.4	287.6	263.5	237.0	215.7	197.6	178.2	157.6	135.9	117.4	100.1
67.5°	495.8	460.3	421.0	382.4	349.9	314.9	277.5	237.9	208.6	182.8	155.9
65°	735.4	687.4	634.3	585.6	533.3	477.1	417.2	365.6	318.9	269.9	221.9
62.5°	1011.4	952.0	889.7	825.1	755.2	680.2	605.6	535.3	461.3	386.5	330.0
60°	1304.8	1241.7	1169.2	1089.9	1004.2	913.0	825.1	732.1	634.3	548.9	460.3
57.5°	1578.5	1518.7	1442.2	1358.8	1268.6	1169.2	1062.3	949.3	839.7	728.3	615.6
55°	1791.7	1736.2	1672.4	1602.8	1521.4	1416.3	1304.8	1184.8	1056.2	921.9	796.2
52.5°	1958.4	1909.4	1855.4	1796.6	1719.0	1632.0	1537.2	1410.0	1276.8	1133.6	983.4
50°	2175.7	2105.1	2027.4	1948.7	1880.3	1807.3	1714.8	1610.2	1486.3	1337.3	1180.5
47.5°	2470.1	2362.2	2243.8	2142.5	2044.7	1946.8	1863.9	1774.9	1657.8	1532.5	1367.8
45°	2751.8	2647.6	2531.2	2392.9	2244.6	2122.5	2004.7	1902.1	1805.1	1681.8	1548.0
42.5°	3084.3	2929.8	2786.9	2654.0	2507.2	2338.7	2175.1	2043.6	1921.4	1814.6	1681.8
40°	4373.2	3330.3	3103.7	2907.9	2742.0	2581.1	2395.8	2201.7	2056.6	1921.4	1805.1
37.5°	7061.4	5523.9	4301.6	3230.8	3007.8	2795.5	2616.1	2415.0	2201.7	2043.6	1902.1
35°	10654.2	8670.1	6624.4	4962.5	3473.3	3058.3	2813.5	2616.1	2395.8	2175.1	2004.7
32.5°	14704.7	12310.7	9767.6	7427.6	5297.1	3636.3	3058.3	2795.5	2581.1	2338.7	2122.5
30°	19054.9	16220.2	13324.7	10380.3	7697.7	5297.1	3473.3	3007.8	2742.0	2507.2	2244.6
27.5°	23760.3	20271.3	16998.2	13666.2	10380.3	7427.6	4962.5	3230.8	2907.9	2654.0	2392.9
25°	28831.0	24728.7	20737.2	16998.2	13324.7	9767.6	6624.4	4301.6	3103.7	2786.9	2531.2
22.5°	34253.3	29423.8	24728.7	20271.3	16220.2	12310.7	8670.1	5523.9	3330.3	2929.8	2647.6
20°	40363.4	34253.3	28831.0	23760.3	19054.9	14704.7	10654.2	7061.4	4373.2	3084.3	2751.8
17.5°	48389.2	39561.5	32861.0	27077.6	21860.4	17091.1	12674.0	8646.6	5313.9	3223.2	2845.4
15°	57065.4	45742.0	37197.3	30439.4	24523.3	19235.1	14470.5	10059.6	6279.4	3708.9	2954.3
12.5°	67401.8	52502.8	41128.6	33388.3	26937.2	21230.8	16145.2	11492.0	7397.6	4369.2	3051.4
10°	76876.0	59320.7	45838.6	36423.3	29210.0	23018.5	17576.0	12684.9	8326.7	4916.8	3131.8
7.5°	86433.0	65836.3	50051.0	38851.3	31018.9	24436.4	18707.8	13626.2	9058.6	5347.5	3194.9
5°	93533.3	70639.9	53138.6	40623.1	32334.3	25464.7	19526.8	14306.2	9586.5	5657.8	3240.3
2.5°	97914.6	73586.8	55024.7	41702.0	33133.4	26088.2	20022.5	14717.3	9905.3	5845.0	3267.7
0°	99396.6	74580.5	55659.3	42064.4	33401.4	26297.1	20188.5	14854.9	10011.9	5907.6	3276.9
-2.5°	97914.6	73586.8	55024.7	41702.0	33133.4	26088.2	20022.5	14717.3	9905.3	5845.0	3267.7
-5°	93533.3	70639.9	53138.6	40623.1	32334.3	25464.7	19526.8	14306.2	9586.5	5657.8	3240.3
-7.5°	86433.0	65836.3	50051.0	38851.3	31018.9	24436.4	18707.8	13626.2	9058.6	5347.5	3194.9
-10°	76876.0	59320.7	45838.6	36423.3	29210.0	23018.5	17576.0	12684.9	8326.7	4916.8	3131.8
-12.5°	67401.8	52502.8	41128.6	33388.3	26937.2	21230.8	16145.2	11492.0	7397.6	4369.2	3051.4
-15°	57065.4	45742.0	37197.3	30439.4	24523.3	19235.1	14470.5	10059.6	6279.4	3708.9	2954.3
-17.5°	48389.2	39561.5	32861.0	27077.6	21860.4	17091.1	12674.0	8646.6	5313.9	3223.2	2845.4
-20°	40363.4	34253.3	28831.0	23760.3	19054.9	14704.7	10654.2	7061.4	4373.2	3084.3	2751.8



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	34253.3	29423.8	24728.7	20271.3	16220.2	12310.7	8670.1	5523.9	3330.3	2929.8	2647.6
-25°	28831.0	24728.7	20737.2	16998.2	13324.7	9767.6	6624.4	4301.6	3103.7	2786.9	2531.2
-27.5°	23760.3	20271.3	16998.2	13666.2	10380.3	7427.6	4962.5	3230.8	2907.9	2654.0	2392.9
-30°	19054.9	16220.2	13324.7	10380.3	7697.7	5297.1	3473.3	3007.8	2742.0	2507.2	2244.6
-32.5°	14704.7	12310.7	9767.6	7427.6	5297.1	3636.3	3058.3	2795.5	2581.1	2338.7	2122.5
-35°	10654.2	8670.1	6624.4	4962.5	3473.3	3058.3	2813.5	2616.1	2395.8	2175.1	2004.7
-37.5°	7061.4	5523.9	4301.6	3230.8	3007.8	2795.5	2616.1	2415.0	2201.7	2043.6	1902.1
-40°	4373.2	3330.3	3103.7	2907.9	2742.0	2581.1	2395.8	2201.7	2056.6	1921.4	1805.1
-42.5°	3084.3	2929.8	2786.9	2654.0	2507.2	2338.7	2175.1	2043.6	1921.4	1814.6	1681.8
-45°	2751.8	2647.6	2531.2	2392.9	2244.6	2122.5	2004.7	1902.1	1805.1	1681.8	1548.0
-47.5°	2470.1	2362.2	2243.8	2142.5	2044.7	1946.8	1863.9	1774.9	1657.8	1532.5	1367.8
-50°	2175.7	2105.1	2027.4	1948.7	1880.3	1807.3	1714.8	1610.2	1486.3	1337.3	1180.5
-52.5°	1958.4	1909.4	1855.4	1796.6	1719.0	1632.0	1537.2	1410.0	1276.8	1133.6	983.4
-55°	1791.7	1736.2	1672.4	1602.8	1521.4	1416.3	1304.8	1184.8	1056.2	921.9	796.2
-57.5°	1578.5	1518.7	1442.2	1358.8	1268.6	1169.2	1062.3	949.3	839.7	728.3	615.6
-60°	1304.8	1241.7	1169.2	1089.9	1004.2	913.0	825.1	732.1	634.3	548.9	460.3
-62.5°	1011.4	952.0	889.7	825.1	755.2	680.2	605.6	535.3	461.3	386.5	330.0
-65°	735.4	687.4	634.3	585.6	533.3	477.1	417.2	365.6	318.9	269.9	221.9
-67.5°	495.8	460.3	421.0	382.4	349.9	314.9	277.5	237.9	208.6	182.8	155.9
-70°	309.4	287.6	263.5	237.0	215.7	197.6	178.2	157.6	135.9	117.4	100.1
-72.5°	183.8	172.7	160.4	146.9	132.2	119.8	107.6	94.7	81.0	66.6	55.3
-75°	102.4	95.6	88.0	79.7	70.7	61.0	54.9	50.4	45.6	40.6	35.3
-77.5°	49.1	46.7	44.2	41.4	38.3	35.0	31.5	28.6	27.3	26.0	24.6
-80°	26.8	26.2	25.6	24.9	24.1	23.3	22.4	21.4	20.4	19.4	18.3
-82.5°	18.3	17.8	17.4	16.8	16.3	15.7	15.0	14.3	13.6	12.8	12.0
-85°	10.2	10.1	9.9	9.7	9.4	9.2	8.9	8.6	8.3	8.0	7.7
-87.5°	5.1	5.0	4.9	4.8	4.7	4.6	4.4	4.3	4.1	4.0	3.8
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	3.6	3.5	3.3	3.1	2.9	2.7	2.5	2.3	2.1	1.8	1.6
85°	7.3	7.0	6.6	6.2	5.8	5.4	5.0	4.6	4.1	3.7	3.2
82.5°	11.1	10.5	9.9	9.3	8.7	8.1	7.5	6.9	6.2	5.5	4.9
80°	17.2	16.0	14.7	13.5	12.2	10.9	10.0	9.2	8.3	7.4	6.5
77.5°	23.2	21.7	20.2	18.6	16.9	15.3	13.5	11.8	10.4	9.2	8.1
75°	29.8	27.5	25.6	23.7	21.7	19.7	17.6	15.5	13.4	11.2	9.7
72.5°	48.9	42.2	35.3	28.8	26.4	24.1	21.7	19.2	16.7	14.2	11.6
70°	82.2	63.5	52.3	44.2	35.8	28.4	25.7	22.9	20.0	17.1	14.2
67.5°	128.0	107.0	85.3	63.0	50.6	40.9	31.1	26.5	23.3	20.0	16.7
65°	190.7	158.3	125.9	101.1	75.5	54.4	43.5	32.3	26.5	22.9	19.2
62.5°	271.4	217.1	180.4	142.5	110.6	81.9	55.7	43.5	31.1	25.7	21.7
60°	375.7	309.4	241.0	193.7	151.3	113.7	81.9	54.4	40.9	28.4	24.1
57.5°	515.7	412.4	332.4	256.3	198.1	151.3	110.6	75.5	50.6	35.8	26.4
55°	666.3	549.2	434.6	340.1	256.3	193.7	142.5	101.1	63.0	44.2	28.8
52.5°	837.4	693.6	560.4	434.6	332.4	241.0	180.4	125.9	85.3	52.3	35.3
50°	1014.3	851.1	693.6	549.2	412.4	309.4	217.1	158.3	107.0	63.5	42.2
47.5°	1196.2	1014.3	837.4	666.3	515.7	375.7	271.4	190.7	128.0	82.2	48.9
45°	1367.8	1180.5	983.4	796.2	615.6	460.3	330.0	221.9	155.9	100.1	55.3
42.5°	1532.5	1337.3	1133.6	921.9	728.3	548.9	386.5	269.9	182.8	117.4	66.6
40°	1657.8	1486.3	1276.8	1056.2	839.7	634.3	461.3	318.9	208.6	135.9	81.0
37.5°	1774.9	1610.2	1410.0	1184.8	949.3	732.1	535.3	365.6	237.9	157.6	94.7
35°	1863.9	1714.8	1537.2	1304.8	1062.3	825.1	605.6	417.2	277.5	178.2	107.6
32.5°	1946.8	1807.3	1632.0	1416.3	1169.2	913.0	680.2	477.1	314.9	197.6	119.8
30°	2044.7	1880.3	1719.0	1521.4	1268.6	1004.2	755.2	533.3	349.9	215.7	132.2
27.5°	2142.5	1948.7	1796.6	1602.8	1358.8	1089.9	825.1	585.6	382.4	237.0	146.9
25°	2243.8	2027.4	1855.4	1672.4	1442.2	1169.2	889.7	634.3	421.0	263.5	160.4
22.5°	2362.2	2105.1	1909.4	1736.2	1518.7	1241.7	952.0	687.4	460.3	287.6	172.7
20°	2470.1	2175.7	1958.4	1791.7	1578.5	1304.8	1011.4	735.4	495.8	309.4	183.8
17.5°	2565.1	2251.2	2013.9	1831.8	1625.7	1360.9	1064.3	778.0	527.3	328.8	193.7
15°	2641.0	2329.4	2064.8	1867.0	1667.0	1410.0	1110.5	815.3	554.8	345.7	202.3
12.5°	2706.1	2396.3	2108.4	1897.0	1702.2	1451.8	1149.8	847.0	578.2	360.0	209.6
10°	2759.9	2451.5	2144.3	1921.8	1731.3	1486.3	1182.2	873.0	597.5	371.8	215.6
7.5°	2802.1	2494.9	2172.4	1941.1	1754.0	1513.2	1207.5	893.4	612.5	381.0	220.3
5°	2832.5	2526.0	2192.6	1955.0	1770.2	1532.5	1225.7	908.0	623.3	387.6	223.6
2.5°	2850.8	2544.7	2204.7	1963.4	1780.0	1544.1	1236.6	916.8	629.7	391.6	225.6
0°	2856.9	2551.0	2208.8	1966.2	1783.3	1548.0	1240.2	919.7	631.9	392.9	226.3
-2.5°	2850.8	2544.7	2204.7	1963.4	1780.0	1544.1	1236.6	916.8	629.7	391.6	225.6
-5°	2832.5	2526.0	2192.6	1955.0	1770.2	1532.5	1225.7	908.0	623.3	387.6	223.6
-7.5°	2802.1	2494.9	2172.4	1941.1	1754.0	1513.2	1207.5	893.4	612.5	381.0	220.3
-10°	2759.9	2451.5	2144.3	1921.8	1731.3	1486.3	1182.2	873.0	597.5	371.8	215.6
-12.5°	2706.1	2396.3	2108.4	1897.0	1702.2	1451.8	1149.8	847.0	578.2	360.0	209.6
-15°	2641.0	2329.4	2064.8	1867.0	1667.0	1410.0	1110.5	815.3	554.8	345.7	202.3
-17.5°	2565.1	2251.2	2013.9	1831.8	1625.7	1360.9	1064.3	778.0	527.3	328.8	193.7
-20°	2470.1	2175.7	1958.4	1791.7	1578.5	1304.8	1011.4	735.4	495.8	309.4	183.8



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	2362.2	2105.1	1909.4	1736.2	1518.7	1241.7	952.0	687.4	460.3	287.6	172.7
-25°	2243.8	2027.4	1855.4	1672.4	1442.2	1169.2	889.7	634.3	421.0	263.5	160.4
-27.5°	2142.5	1948.7	1796.6	1602.8	1358.8	1089.9	825.1	585.6	382.4	237.0	146.9
-30°	2044.7	1880.3	1719.0	1521.4	1268.6	1004.2	755.2	533.3	349.9	215.7	132.2
-32.5°	1946.8	1807.3	1632.0	1416.3	1169.2	913.0	680.2	477.1	314.9	197.6	119.8
-35°	1863.9	1714.8	1537.2	1304.8	1062.3	825.1	605.6	417.2	277.5	178.2	107.6
-37.5°	1774.9	1610.2	1410.0	1184.8	949.3	732.1	535.3	365.6	237.9	157.6	94.7
-40°	1657.8	1486.3	1276.8	1056.2	839.7	634.3	461.3	318.9	208.6	135.9	81.0
-42.5°	1532.5	1337.3	1133.6	921.9	728.3	548.9	386.5	269.9	182.8	117.4	66.6
-45°	1367.8	1180.5	983.4	796.2	615.6	460.3	330.0	221.9	155.9	100.1	55.3
-47.5°	1196.2	1014.3	837.4	666.3	515.7	375.7	271.4	190.7	128.0	82.2	48.9
-50°	1014.3	851.1	693.6	549.2	412.4	309.4	217.1	158.3	107.0	63.5	42.2
-52.5°	837.4	693.6	560.4	434.6	332.4	241.0	180.4	125.9	85.3	52.3	35.3
-55°	666.3	549.2	434.6	340.1	256.3	193.7	142.5	101.1	63.0	44.2	28.8
-57.5°	515.7	412.4	332.4	256.3	198.1	151.3	110.6	75.5	50.6	35.8	26.4
-60°	375.7	309.4	241.0	193.7	151.3	113.7	81.9	54.4	40.9	28.4	24.1
-62.5°	271.4	217.1	180.4	142.5	110.6	81.9	55.7	43.5	31.1	25.7	21.7
-65°	190.7	158.3	125.9	101.1	75.5	54.4	43.5	32.3	26.5	22.9	19.2
-67.5°	128.0	107.0	85.3	63.0	50.6	40.9	31.1	26.5	23.3	20.0	16.7
-70°	82.2	63.5	52.3	44.2	35.8	28.4	25.7	22.9	20.0	17.1	14.2
-72.5°	48.9	42.2	35.3	28.8	26.4	24.1	21.7	19.2	16.7	14.2	11.6
-75°	29.8	27.5	25.6	23.7	21.7	19.7	17.6	15.5	13.4	11.2	9.7
-77.5°	23.2	21.7	20.2	18.6	16.9	15.3	13.5	11.8	10.4	9.2	8.1
-80°	17.2	16.0	14.7	13.5	12.2	10.9	10.0	9.2	8.3	7.4	6.5
-82.5°	11.1	10.5	9.9	9.3	8.7	8.1	7.5	6.9	6.2	5.5	4.9
-85°	7.3	7.0	6.6	6.2	5.8	5.4	5.0	4.6	4.1	3.7	3.2
-87.5°	3.6	3.5	3.3	3.1	2.9	2.7	2.5	2.3	2.1	1.8	1.6
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	1.4	1.2	0.9	0.7	0.5	0.2	0.0
85°	2.8	2.3	1.9	1.4	0.9	0.5	0.0
82.5°	4.2	3.5	2.8	2.1	1.4	0.7	0.0
80°	5.6	4.7	3.7	2.8	1.9	0.9	0.0
77.5°	7.0	5.8	4.7	3.5	2.3	1.2	0.0
75°	8.4	7.0	5.6	4.2	2.8	1.4	0.0
72.5°	9.7	8.1	6.5	4.9	3.2	1.6	0.0
70°	11.2	9.2	7.4	5.5	3.7	1.8	0.0
67.5°	13.4	10.4	8.3	6.2	4.1	2.1	0.0
65°	15.5	11.8	9.2	6.9	4.6	2.3	0.0
62.5°	17.6	13.5	10.0	7.5	5.0	2.5	0.0
60°	19.7	15.3	10.9	8.1	5.4	2.7	0.0
57.5°	21.7	16.9	12.2	8.7	5.8	2.9	0.0
55°	23.7	18.6	13.5	9.3	6.2	3.1	0.0
52.5°	25.6	20.2	14.7	9.9	6.6	3.3	0.0
50°	27.5	21.7	16.0	10.5	7.0	3.5	0.0
47.5°	29.8	23.2	17.2	11.1	7.3	3.6	0.0
45°	35.3	24.6	18.3	12.0	7.7	3.8	0.0
42.5°	40.6	26.0	19.4	12.8	8.0	4.0	0.0
40°	45.6	27.3	20.4	13.6	8.3	4.1	0.0
37.5°	50.4	28.6	21.4	14.3	8.6	4.3	0.0
35°	54.9	31.5	22.4	15.0	8.9	4.4	0.0
32.5°	61.0	35.0	23.3	15.7	9.2	4.6	0.0
30°	70.7	38.3	24.1	16.3	9.4	4.7	0.0
27.5°	79.7	41.4	24.9	16.8	9.7	4.8	0.0
25°	88.0	44.2	25.6	17.4	9.9	4.9	0.0
22.5°	95.6	46.7	26.2	17.8	10.1	5.0	0.0
20°	102.4	49.1	26.8	18.3	10.2	5.1	0.0
17.5°	108.5	51.1	27.3	18.6	10.4	5.1	0.0
15°	113.7	52.9	27.7	19.0	10.5	5.2	0.0
12.5°	118.2	54.4	28.1	19.3	10.6	5.3	0.0
10°	121.9	55.7	28.4	19.5	10.7	5.3	0.0
7.5°	124.8	56.6	28.7	19.7	10.8	5.4	0.0
5°	126.9	57.3	28.9	19.8	10.9	5.4	0.0
2.5°	128.1	57.8	29.0	19.9	10.9	5.4	0.0
0°	128.5	57.9	29.0	19.9	10.9	5.4	0.0
-2.5°	128.1	57.8	29.0	19.9	10.9	5.4	0.0
-5°	126.9	57.3	28.9	19.8	10.9	5.4	0.0
-7.5°	124.8	56.6	28.7	19.7	10.8	5.4	0.0
-10°	121.9	55.7	28.4	19.5	10.7	5.3	0.0
-12.5°	118.2	54.4	28.1	19.3	10.6	5.3	0.0
-15°	113.7	52.9	27.7	19.0	10.5	5.2	0.0
-17.5°	108.5	51.1	27.3	18.6	10.4	5.1	0.0
-20°	102.4	49.1	26.8	18.3	10.2	5.1	0.0



REPORT NUMBER: P701490 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-70-4S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	95.6	46.7	26.2	17.8	10.1	5.0	0.0
-25°	88.0	44.2	25.6	17.4	9.9	4.9	0.0
-27.5°	79.7	41.4	24.9	16.8	9.7	4.8	0.0
-30°	70.7	38.3	24.1	16.3	9.4	4.7	0.0
-32.5°	61.0	35.0	23.3	15.7	9.2	4.6	0.0
-35°	54.9	31.5	22.4	15.0	8.9	4.4	0.0
-37.5°	50.4	28.6	21.4	14.3	8.6	4.3	0.0
-40°	45.6	27.3	20.4	13.6	8.3	4.1	0.0
-42.5°	40.6	26.0	19.4	12.8	8.0	4.0	0.0
-45°	35.3	24.6	18.3	12.0	7.7	3.8	0.0
-47.5°	29.8	23.2	17.2	11.1	7.3	3.6	0.0
-50°	27.5	21.7	16.0	10.5	7.0	3.5	0.0
-52.5°	25.6	20.2	14.7	9.9	6.6	3.3	0.0
-55°	23.7	18.6	13.5	9.3	6.2	3.1	0.0
-57.5°	21.7	16.9	12.2	8.7	5.8	2.9	0.0
-60°	19.7	15.3	10.9	8.1	5.4	2.7	0.0
-62.5°	17.6	13.5	10.0	7.5	5.0	2.5	0.0
-65°	15.5	11.8	9.2	6.9	4.6	2.3	0.0
-67.5°	13.4	10.4	8.3	6.2	4.1	2.1	0.0
-70°	11.2	9.2	7.4	5.5	3.7	1.8	0.0
-72.5°	9.7	8.1	6.5	4.9	3.2	1.6	0.0
-75°	8.4	7.0	5.6	4.2	2.8	1.4	0.0
-77.5°	7.0	5.8	4.7	3.5	2.3	1.2	0.0
-80°	5.6	4.7	3.7	2.8	1.9	0.9	0.0
-82.5°	4.2	3.5	2.8	2.1	1.4	0.7	0.0
-85°	2.8	2.3	1.9	1.4	0.9	0.5	0.0
-87.5°	1.4	1.2	0.9	0.7	0.5	0.2	0.0
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Horizontal Angle (degrees)



Horizontal Angle (degrees)



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report

