

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621888

Luminaire Tested: VLT-FB-125U-125D-940-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P621888
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-19)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-FB-125U-125D-940-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
LIGHT SHAPING LENS - BATWING
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8768.1 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.05 / 1.83 / 1.75
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 76.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P621888
CATALOG NUMBER: VLT-FB-125U-125D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P621888

CATALOG NUMBER: VLT-FB-125U-125D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	87	90	86	83	80	73	70	68	60	58	57	48	47	46	41
2	89	82	77	72	82	76	71	67	64	61	57	53	51	49	43	41	40	35
3	82	73	66	60	75	67	61	57	57	53	49	48	44	42	39	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	27
5	69	58	50	44	63	54	47	42	46	41	37	39	35	32	32	29	27	23
6	64	52	44	39	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8298	8298	8298
5°	8228	8821	9447
10°	8066	10430	12879
15°	7823	12712	15681
20°	7449	14646	16477
25°	7053	15837	16638
30°	6602	16203	16554
35°	6157	16205	15895
40°	5791	15698	15390
45°	5510	15218	7371
50°	5353	14406	6350
55°	5205	9645	5028
60°	5060	5870	3643
65°	4948	4469	3792
70°	4882	3896	3896
75°	4758	4040	3909
80°	4178	4079	3885
85°	3096	4257	3680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 15218 cd/sqm



TEST NUMBER: P621888

CATALOG NUMBER: VLT-FB-125U-125D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	1.4
10°-20°	459.8	5.2
20°-30°	778.8	8.9
30°-40°	944.7	10.8
40°-50°	831.6	9.5
50°-60°	514.6	5.9
60°-70°	279.0	3.2
70°-80°	158.9	1.8
80°-90°	53.9	0.6
90°-100°	105.8	1.2
100°-110°	753.9	8.6
110°-120°	1023.4	11.7
120°-130°	833.0	9.5
130°-140°	670.0	7.6
140°-150°	528.2	6.0
150°-160°	386.2	4.4
160°-170°	239.9	2.7
170°-180°	81.8	0.9
0°-30°	1363.3	15.5
0°-40°	2308.0	26.3
0°-60°	3654.2	41.7
0°-90°	4146.0	47.3
90°-120°	1883.1	21.5
90°-150°	3914.2	44.6
90°-180°	4622.0	52.7
0°-180°	8768.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1156	1156	1156	1156	1156	
5°	1142	1179	1225	1277	1312	108
15°	1053	1214	1711	2023	2111	295
25°	891	1219	2000	2060	2101	409
35°	703	1130	1850	1824	1814	440
45°	543	929	1500	1271	726	421
55°	416	648	771	446	402	372
65°	291	365	263	226	223	289
75°	172	151	146	143	141	179
85°	38	51	52	47	45	46
90°	0	5	11	16	16	3
95°	43	80	43	49	60	48
105°	168	258	980	1251	828	177
115°	298	361	844	1755	2051	295
125°	428	486	796	1391	1645	380
135°	530	588	801	1146	1315	408
145°	628	681	806	998	1104	394
155°	736	762	823	905	947	338
165°	817	828	844	866	882	229
175°	860	866	860	855	850	81
180°	860	860	860	860	860	



TEST NUMBER: P621888

CATALOG NUMBER: VLT-FB-125U-125D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1156.4	1156.4	1156.4	1156.4	1156.4
2.5°	1152.6	1165.5	1171.4	1182.8	1188.4
5°	1142.3	1179.1	1224.6	1277.0	1311.5
7.5°	1124.0	1189.7	1333.6	1499.3	1570.1
10°	1107.0	1196.7	1431.4	1671.0	1767.5
12.5°	1088.2	1203.6	1546.1	1836.5	1934.8
15°	1053.0	1213.8	1711.1	2023.3	2110.7
17.5°	1007.4	1220.2	1854.0	2122.3	2178.3
20°	975.4	1221.3	1917.9	2134.7	2157.7
22.5°	945.3	1222.5	1963.1	2104.5	2123.8
25°	890.8	1219.4	2000.2	2059.9	2101.3
27.5°	836.3	1205.8	1981.9	2030.0	2059.9
30°	796.8	1192.1	1955.5	1995.5	1997.8
32.5°	759.2	1169.2	1916.0	1927.7	1924.5
35°	702.8	1130.2	1849.8	1823.7	1814.5
37.5°	650.1	1078.5	1752.9	1711.0	1708.7
40°	618.2	1041.0	1675.8	1636.0	1642.9
42.5°	588.1	998.1	1606.3	1559.6	1430.5
45°	542.9	929.0	1499.6	1270.9	726.3
47.5°	503.9	850.5	1378.7	680.8	625.2
50°	479.5	796.6	1290.4	598.7	568.8
52.5°	455.0	746.4	1175.7	538.3	499.2
55°	416.0	648.1	770.9	445.6	401.9
57.5°	378.9	544.8	471.0	346.3	299.0
60°	352.6	483.6	409.0	279.1	253.8
62.5°	328.1	433.4	348.8	247.6	242.6
65°	291.4	365.0	263.2	225.6	223.3
67.5°	257.1	299.9	200.7	203.0	200.7
70°	232.7	253.4	185.7	188.0	185.7
72.5°	210.1	208.7	170.6	169.2	166.9
75°	171.6	150.9	145.7	143.3	141.0
77.5°	131.2	111.4	117.5	115.1	112.8
80°	101.1	94.2	98.7	96.3	94.0
82.5°	74.7	77.0	79.9	75.6	73.3
85°	37.6	51.4	51.7	47.0	44.7
87.5°	11.3	23.4	22.8	20.1	18.3
90°	0.0	5.3	10.8	16.2	16.2
92.5°	13.0	18.3	23.8	33.6	37.9
95°	43.3	80.3	43.3	48.9	59.5
97.5°	76.8	154.1	318.2	93.9	81.2
100°	102.8	192.8	638.6	188.0	124.5
102.5°	128.8	223.0	863.7	496.0	271.7
105°	167.8	257.7	979.5	1251.3	828.0
107.5°	206.7	274.5	935.1	1821.1	1705.8
110°	232.7	296.2	909.2	1913.6	2056.4



TEST NUMBER: P621888

CATALOG NUMBER: VLT-FB-125U-125D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	258.7	322.2	883.2	1859.5	2099.7
115°	297.6	361.1	844.2	1754.7	2051.0
117.5°	337.7	400.1	834.5	1641.2	1946.0
120°	368.0	426.2	817.2	1554.9	1872.4
122.5°	389.6	452.1	795.5	1480.8	1772.9
125°	427.5	485.7	795.5	1391.2	1645.1
127.5°	458.9	518.2	796.6	1287.2	1538.0
130°	476.2	539.7	800.9	1217.6	1455.7
132.5°	497.9	561.4	800.9	1186.4	1382.1
135°	530.3	588.5	800.9	1145.7	1315.0
137.5°	557.4	619.8	800.9	1100.8	1245.8
140°	579.0	637.3	800.9	1074.5	1206.8
142.5°	600.7	654.7	805.3	1044.0	1167.8
145°	627.8	680.7	806.3	998.1	1104.0
147.5°	660.2	706.8	812.8	965.1	1046.6
150°	681.9	724.2	817.2	943.2	1012.0
152.5°	703.5	741.6	817.2	925.6	981.7
155°	736.0	762.4	822.6	904.7	947.0
157.5°	762.0	787.4	829.1	891.5	922.1
160°	779.3	800.4	833.4	882.7	909.2
162.5°	792.3	813.4	837.7	878.2	896.2
165°	817.2	827.7	844.2	866.2	882.1
167.5°	831.2	840.8	849.6	860.7	870.2
170°	844.2	849.5	849.6	860.6	865.9
172.5°	848.5	858.1	854.0	856.2	861.5
175°	860.5	865.7	860.5	854.9	849.6
177.5°	860.5	864.7	860.5	860.4	856.1
180°	860.5	860.5	860.5	860.5	860.5

(END OF REPORT)