

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: EPHESUS

Report Number: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **EPH-LS-08-0680N-57-70-2S-HEG**

Issue Date: 11/16/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-906-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 11/16/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: EPHESUS  
Catalog Number: EPH-LS-08-0680N-57-70-2S-HEG  
Description: EPHESUS LUMASPORT 8 INTEGRAL LUMINAIRE  
(8) 5700K, 70 CRI LEDS AND 2S BEAM SHAPE  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	106209.6 lumens	Max Intensity:	589622.6 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	151.0 lumens/watt		
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')		
Beam Angle (50%):	22°H x 22°V	Field Angle (10%):	39.6°H x 39.6°V
Beam Lumens:	46941.1 lumens	Field Lumens:	87180.9 lumens
Beam Efficiency:	44.2%	Field Efficiency:	82.1%

Input Watts (W): 703.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

### Iso-Candela Plot






REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

### Lumen Table

90	0.2		1.1		3.7		9.3		12.3		9.3		3.7		1.1		0.2	
80	0.2		1.1		3.7		9.3		12.3		9.3		3.7		1.1		0.2	
70	0.5	0.6	2.2	6.7	13.3	20.4	26.4	29.6	29.6	26.4	20.4	13.3	6.7	2.2	0.6	0.5		
60		1.7	7.8	18.9	32.7	45.4	54.1	58.6	58.6	54.1	45.4	32.7	18.9	7.8	1.7			
50	1.2	4.1	15.4	32.8	50.0	81.0	123.9	148.4	148.4	123.9	81.0	50.0	32.8	15.4	4.1	1.2		
40		7.1	23.1	43.2	95.5	163.9	192.0	201.9	201.9	192.0	163.9	95.5	43.2	23.1	7.1			
30	2.7	9.8	29.0	63.8	148.3	184.5	252.3	514.9	514.9	252.3	184.5	148.3	63.8	29.0	9.8	2.7		
20		11.9	32.4	92.0	163.0	237.5	1502.2	4451.2	4451.2	1502.2	237.5	163.0	92.0	32.4	11.9			
10	3.4	13.0	34.0	106.6	166.1	474.6	4338.1	12200.2	12200.2	4338.1	474.6	166.1	106.6	34.0	13.0	3.4		
0		13.0	34.0	106.6	166.1	474.6	4338.1	12200.2	12200.2	4338.1	474.6	166.1	106.6	34.0	13.0			
-10	2.7	11.9	32.4	92.0	163.0	237.5	1502.2	4451.2	4451.2	1502.2	237.5	163.0	92.0	32.4	11.9	2.7		
-20		9.8	29.0	63.8	148.3	184.5	252.3	514.9	514.9	252.3	184.5	148.3	63.8	29.0	9.8			
-30	1.2	7.1	23.1	43.2	95.5	163.9	192.0	201.9	201.9	192.0	163.9	95.5	43.2	23.1	7.1	1.2		
-40		4.1	15.4	32.8	50.0	81.0	123.9	148.4	148.4	123.9	81.0	50.0	32.8	15.4	4.1			
-50	0.5	1.7	7.8	18.9	32.7	45.4	54.1	58.6	58.6	54.1	45.4	32.7	18.9	7.8	1.7	0.5		
-60		0.6	2.2	6.7	13.3	20.4	26.4	29.6	29.6	26.4	20.4	13.3	6.7	2.2	0.6			
-70	0.2		1.1		3.7		9.3		12.3		9.3		3.7		1.1		0.2	
-80	0.2		1.1		3.7		9.3		12.3		9.3		3.7		1.1		0.2	
-90	0.2		1.1		3.7		9.3		12.3		9.3		3.7		1.1		0.2	

REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG


### Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg      - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

### Luminous Intensity Plot



**Beam:**  
 H Angle: 22°  
 V Angle: 22°  
 Lumens: 46941.1  
 Efficiency: 44.2%

**Field:**  
 H Angle: 39.6°  
 V Angle: 39.6°  
 Lumens: 87180.9  
 Efficiency: 82.1%

**Spill:**  
 Lumens: 19028.7  
 Efficiency: 17.9%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.5	1.0	1.4	1.9	2.4	2.8	3.3	3.8	4.2	4.6
85°	0.0	1.0	1.9	2.9	3.8	4.8	5.7	6.6	7.5	8.4	9.3
82.5°	0.0	1.4	2.9	4.3	5.7	7.1	8.5	9.9	11.1	11.8	12.5
80°	0.0	1.9	3.8	5.7	7.6	9.5	11.2	12.1	13.0	13.9	14.8
77.5°	0.0	2.4	4.8	7.1	9.5	11.4	12.6	13.7	14.8	16.0	17.2
75°	0.0	2.8	5.7	8.5	11.2	12.6	14.0	15.3	16.7	18.5	20.2
72.5°	0.0	3.3	6.6	9.9	12.1	13.7	15.3	17.0	19.1	21.2	23.2
70°	0.0	3.8	7.5	11.1	13.0	14.8	16.7	19.1	21.5	23.9	28.0
67.5°	0.0	4.2	8.4	11.8	13.9	16.0	18.5	21.2	23.9	28.6	33.1
65°	0.0	4.6	9.3	12.5	14.8	17.2	20.2	23.2	28.0	33.1	39.2
62.5°	0.0	5.1	10.1	13.1	15.6	18.6	21.9	26.3	32.0	38.3	47.7
60°	0.0	5.5	11.0	13.7	16.5	20.0	23.6	29.7	35.9	45.8	56.1
57.5°	0.0	5.9	11.4	14.3	17.5	21.4	26.3	33.1	41.9	53.1	77.5
55°	0.0	6.3	11.8	14.9	18.6	22.7	29.2	36.3	48.3	64.1	104.7
52.5°	0.0	6.7	12.2	15.5	19.6	24.2	31.9	41.5	54.5	87.9	131.1
50°	0.0	7.1	12.6	16.1	20.6	26.4	34.5	46.8	64.7	111.0	183.7
47.5°	0.0	7.4	12.9	16.7	21.6	28.5	37.3	51.8	84.6	133.4	237.7
45°	0.0	7.8	13.3	17.4	22.5	30.5	41.5	56.7	103.7	179.6	289.8
42.5°	0.0	8.1	13.6	18.0	23.4	32.5	45.5	68.0	122.0	224.5	350.4
40°	0.0	8.4	13.9	18.7	24.5	34.3	49.3	83.3	146.2	267.5	410.3
37.5°	0.0	8.7	14.2	19.3	26.0	36.1	53.0	97.9	182.5	311.3	467.3
35°	0.0	9.0	14.5	19.8	27.3	38.6	56.4	111.6	216.8	359.7	522.5
32.5°	0.0	9.3	14.8	20.4	28.6	41.3	62.0	124.6	249.2	405.4	576.3
30°	0.0	9.5	15.0	20.9	29.7	43.8	72.3	140.1	279.4	448.1	626.8
27.5°	0.0	9.8	15.3	21.3	30.8	46.1	81.9	164.6	310.2	487.9	673.8
25°	0.0	10.0	15.5	21.7	31.8	48.3	90.8	187.1	342.5	525.9	717.5
22.5°	0.0	10.2	15.7	22.1	32.7	50.2	98.8	207.7	372.1	561.2	766.6
20°	0.0	10.3	15.8	22.5	33.6	52.0	106.1	226.2	398.7	593.1	810.9
17.5°	0.0	10.5	16.0	22.8	34.3	53.5	112.6	242.6	422.3	621.4	850.4
15°	0.0	10.6	16.1	23.0	34.9	54.9	118.2	257.0	443.0	646.1	884.8
12.5°	0.0	10.7	16.2	23.3	35.5	56.1	123.0	269.2	460.5	667.1	914.1
10°	0.0	10.8	16.3	23.5	35.9	57.0	126.9	279.2	474.9	684.4	938.2
7.5°	0.0	10.9	16.4	23.6	36.3	57.7	130.0	287.0	486.2	697.9	957.0
5°	0.0	11.0	16.5	23.7	36.5	58.3	132.1	292.6	494.2	707.6	970.5
2.5°	0.0	11.0	16.5	23.8	36.7	58.6	133.5	296.0	499.1	713.4	978.6
0°	0.0	11.0	16.5	23.8	36.7	58.6	133.5	296.0	499.1	713.4	978.6
-2.5°	0.0	11.0	16.5	23.8	36.7	58.6	133.5	296.0	499.1	713.4	978.6
-5°	0.0	11.0	16.5	23.7	36.5	58.3	132.1	292.6	494.2	707.6	970.5
-7.5°	0.0	10.9	16.4	23.6	36.3	57.7	130.0	287.0	486.2	697.9	957.0
-10°	0.0	10.8	16.3	23.5	35.9	57.0	126.9	279.2	474.9	684.4	938.2
-12.5°	0.0	10.7	16.2	23.3	35.5	56.1	123.0	269.2	460.5	667.1	914.1
-15°	0.0	10.6	16.1	23.0	34.9	54.9	118.2	257.0	443.0	646.1	884.8
-17.5°	0.0	10.5	16.0	22.8	34.3	53.5	112.6	242.6	422.3	621.4	850.4
-20°	0.0	10.3	15.8	22.5	33.6	52.0	106.1	226.2	398.7	593.1	810.9



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0.0	10.2	15.7	22.1	32.7	50.2	98.8	207.7	372.1	561.2	766.6
-25°	0.0	10.0	15.5	21.7	31.8	48.3	90.8	187.1	342.5	525.9	717.5
-27.5°	0.0	9.8	15.3	21.3	30.8	46.1	81.9	164.6	310.2	487.9	673.8
-30°	0.0	9.5	15.0	20.9	29.7	43.8	72.3	140.1	279.4	448.1	626.8
-32.5°	0.0	9.3	14.8	20.4	28.6	41.3	62.0	124.6	249.2	405.4	576.3
-35°	0.0	9.0	14.5	19.8	27.3	38.6	56.4	111.6	216.8	359.7	522.5
-37.5°	0.0	8.7	14.2	19.3	26.0	36.1	53.0	97.9	182.5	311.3	467.3
-40°	0.0	8.4	13.9	18.7	24.5	34.3	49.3	83.3	146.2	267.5	410.3
-42.5°	0.0	8.1	13.6	18.0	23.4	32.5	45.5	68.0	122.0	224.5	350.4
-45°	0.0	7.8	13.3	17.4	22.5	30.5	41.5	56.7	103.7	179.6	289.8
-47.5°	0.0	7.4	12.9	16.7	21.6	28.5	37.3	51.8	84.6	133.4	237.7
-50°	0.0	7.1	12.6	16.1	20.6	26.4	34.5	46.8	64.7	111.0	183.7
-52.5°	0.0	6.7	12.2	15.5	19.6	24.2	31.9	41.5	54.5	87.9	131.1
-55°	0.0	6.3	11.8	14.9	18.6	22.7	29.2	36.3	48.3	64.1	104.7
-57.5°	0.0	5.9	11.4	14.3	17.5	21.4	26.3	33.1	41.9	53.1	77.5
-60°	0.0	5.5	11.0	13.7	16.5	20.0	23.6	29.7	35.9	45.8	56.1
-62.5°	0.0	5.1	10.1	13.1	15.6	18.6	21.9	26.3	32.0	38.3	47.7
-65°	0.0	4.6	9.3	12.5	14.8	17.2	20.2	23.2	28.0	33.1	39.2
-67.5°	0.0	4.2	8.4	11.8	13.9	16.0	18.5	21.2	23.9	28.6	33.1
-70°	0.0	3.8	7.5	11.1	13.0	14.8	16.7	19.1	21.5	23.9	28.0
-72.5°	0.0	3.3	6.6	9.9	12.1	13.7	15.3	17.0	19.1	21.2	23.2
-75°	0.0	2.8	5.7	8.5	11.2	12.6	14.0	15.3	16.7	18.5	20.2
-77.5°	0.0	2.4	4.8	7.1	9.5	11.4	12.6	13.7	14.8	16.0	17.2
-80°	0.0	1.9	3.8	5.7	7.6	9.5	11.2	12.1	13.0	13.9	14.8
-82.5°	0.0	1.4	2.9	4.3	5.7	7.1	8.5	9.9	11.1	11.8	12.5
-85°	0.0	1.0	1.9	2.9	3.8	4.8	5.7	6.6	7.5	8.4	9.3
-87.5°	0.0	0.5	1.0	1.4	1.9	2.4	2.8	3.3	3.8	4.2	4.6
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	5.1	5.5	5.9	6.3	6.7	7.1	7.4	7.8	8.1	8.4	8.7
85°	10.1	11.0	11.4	11.8	12.2	12.6	12.9	13.3	13.6	13.9	14.2
82.5°	13.1	13.7	14.3	14.9	15.5	16.1	16.7	17.4	18.0	18.7	19.3
80°	15.6	16.5	17.5	18.6	19.6	20.6	21.6	22.5	23.4	24.5	26.0
77.5°	18.6	20.0	21.4	22.7	24.2	26.4	28.5	30.5	32.5	34.3	36.1
75°	21.9	23.6	26.3	29.2	31.9	34.5	37.3	41.5	45.5	49.3	53.0
72.5°	26.3	29.7	33.1	36.3	41.5	46.8	51.8	56.7	68.0	83.3	97.9
70°	32.0	35.9	41.9	48.3	54.5	64.7	84.6	103.7	122.0	146.2	182.5
67.5°	38.3	45.8	53.1	64.1	87.9	111.0	133.4	179.6	224.5	267.5	311.3
65°	47.7	56.1	77.5	104.7	131.1	183.7	237.7	289.8	350.4	410.3	467.3
62.5°	57.0	84.2	114.8	157.3	220.4	281.8	352.2	423.9	492.8	562.1	628.6
60°	84.2	118.2	172.0	242.6	315.1	398.7	479.7	561.2	640.8	717.5	807.9
57.5°	114.8	172.0	250.1	333.7	426.8	518.2	610.9	700.6	804.4	907.4	1006.9
55°	157.3	242.6	333.7	436.2	538.2	641.0	747.1	867.2	983.2	1099.3	1210.4
52.5°	220.4	315.1	426.8	538.2	651.1	772.3	905.2	1036.3	1166.2	1289.9	1405.0
50°	281.8	398.7	518.2	641.0	772.3	917.9	1063.1	1206.7	1342.2	1470.9	1599.9
47.5°	352.2	479.7	610.9	747.1	905.2	1063.1	1220.2	1368.5	1510.8	1657.8	1800.2
45°	423.9	561.2	700.6	867.2	1036.3	1206.7	1368.5	1524.2	1687.0	1834.2	1940.3
42.5°	492.8	640.8	804.4	983.2	1166.2	1342.2	1510.8	1687.0	1844.6	1961.3	2029.0
40°	562.1	717.5	907.4	1099.3	1289.9	1470.9	1657.8	1834.2	1961.3	2032.2	2067.3
37.5°	628.6	807.9	1006.9	1210.4	1405.0	1599.9	1800.2	1940.3	2029.0	2067.3	2200.6
35°	691.7	893.9	1104.5	1314.1	1514.8	1727.1	1898.5	2019.6	2060.8	2188.3	2674.7
32.5°	759.9	975.1	1196.9	1410.5	1626.3	1836.6	1989.1	2048.1	2151.8	2466.6	3741.6
30°	829.3	1054.3	1282.8	1501.2	1732.2	1916.4	2029.3	2091.8	2259.4	3423.2	4637.9
27.5°	893.9	1128.4	1360.7	1590.8	1825.0	1991.2	2053.0	2186.4	2900.0	4286.4	5423.0
25°	953.5	1196.9	1432.8	1675.5	1889.2	2025.1	2091.3	2274.7	3690.7	4975.6	5756.7
22.5°	1009.2	1259.6	1498.9	1753.1	1948.2	2043.9	2166.9	2861.9	4363.4	5594.1	5961.2
20°	1060.6	1314.1	1561.3	1819.6	2001.8	2061.0	2235.7	3481.7	4907.1	5768.6	6129.0
17.5°	1106.3	1362.6	1618.8	1863.5	2021.8	2096.0	2370.9	4038.4	5396.3	5926.1	6271.5
15°	1146.2	1405.0	1669.0	1901.9	2034.2	2145.9	2822.7	4449.5	5657.5	6058.8	6397.1
12.5°	1180.2	1441.1	1711.8	1934.7	2044.7	2188.6	3209.8	4791.3	5768.0	6159.3	6486.0
10°	1208.2	1470.9	1747.1	1961.7	2053.4	2223.9	3529.9	5074.3	5859.6	6242.7	6560.1
7.5°	1230.1	1494.1	1774.7	1982.9	2060.2	2251.5	3781.1	5296.6	5931.7	6308.5	6618.6
5°	1245.7	1510.8	1794.5	1998.1	2065.1	2271.3	3961.6	5456.5	5983.6	6355.9	6660.8
2.5°	1255.2	1520.9	1806.4	2007.2	2068.0	2283.3	4070.4	5553.0	6014.9	6384.5	6686.4
0°	1258.3	1524.2	1810.4	2010.3	2069.0	2287.3	4106.8	5585.2	6025.4	6394.1	6694.9
-2.5°	1255.2	1520.9	1806.4	2007.2	2068.0	2283.3	4070.4	5553.0	6014.9	6384.5	6686.4
-5°	1245.7	1510.8	1794.5	1998.1	2065.1	2271.3	3961.6	5456.5	5983.6	6355.9	6660.8
-7.5°	1230.1	1494.1	1774.7	1982.9	2060.2	2251.5	3781.1	5296.6	5931.7	6308.5	6618.6
-10°	1208.2	1470.9	1747.1	1961.7	2053.4	2223.9	3529.9	5074.3	5859.6	6242.7	6560.1
-12.5°	1180.2	1441.1	1711.8	1934.7	2044.7	2188.6	3209.8	4791.3	5768.0	6159.3	6486.0
-15°	1146.2	1405.0	1669.0	1901.9	2034.2	2145.9	2822.7	4449.5	5657.5	6058.8	6397.1
-17.5°	1106.3	1362.6	1618.8	1863.5	2021.8	2096.0	2370.9	4038.4	5396.3	5926.1	6271.5
-20°	1060.6	1314.1	1561.3	1819.6	2001.8	2061.0	2235.7	3481.7	4907.1	5768.6	6129.0



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	1009.2	1259.6	1498.9	1753.1	1948.2	2043.9	2166.9	2861.9	4363.4	5594.1	5961.2
-25°	953.5	1196.9	1432.8	1675.5	1889.2	2025.1	2091.3	2274.7	3690.7	4975.6	5756.7
-27.5°	893.9	1128.4	1360.7	1590.8	1825.0	1991.2	2053.0	2186.4	2900.0	4286.4	5423.0
-30°	829.3	1054.3	1282.8	1501.2	1732.2	1916.4	2029.3	2091.8	2259.4	3423.2	4637.9
-32.5°	759.9	975.1	1196.9	1410.5	1626.3	1836.6	1989.1	2048.1	2151.8	2466.6	3741.6
-35°	691.7	893.9	1104.5	1314.1	1514.8	1727.1	1898.5	2019.6	2060.8	2188.3	2674.7
-37.5°	628.6	807.9	1006.9	1210.4	1405.0	1599.9	1800.2	1940.3	2029.0	2067.3	2200.6
-40°	562.1	717.5	907.4	1099.3	1289.9	1470.9	1657.8	1834.2	1961.3	2032.2	2067.3
-42.5°	492.8	640.8	804.4	983.2	1166.2	1342.2	1510.8	1687.0	1844.6	1961.3	2029.0
-45°	423.9	561.2	700.6	867.2	1036.3	1206.7	1368.5	1524.2	1687.0	1834.2	1940.3
-47.5°	352.2	479.7	610.9	747.1	905.2	1063.1	1220.2	1368.5	1510.8	1657.8	1800.2
-50°	281.8	398.7	518.2	641.0	772.3	917.9	1063.1	1206.7	1342.2	1470.9	1599.9
-52.5°	220.4	315.1	426.8	538.2	651.1	772.3	905.2	1036.3	1166.2	1289.9	1405.0
-55°	157.3	242.6	333.7	436.2	538.2	641.0	747.1	867.2	983.2	1099.3	1210.4
-57.5°	114.8	172.0	250.1	333.7	426.8	518.2	610.9	700.6	804.4	907.4	1006.9
-60°	84.2	118.2	172.0	242.6	315.1	398.7	479.7	561.2	640.8	717.5	807.9
-62.5°	57.0	84.2	114.8	157.3	220.4	281.8	352.2	423.9	492.8	562.1	628.6
-65°	47.7	56.1	77.5	104.7	131.1	183.7	237.7	289.8	350.4	410.3	467.3
-67.5°	38.3	45.8	53.1	64.1	87.9	111.0	133.4	179.6	224.5	267.5	311.3
-70°	32.0	35.9	41.9	48.3	54.5	64.7	84.6	103.7	122.0	146.2	182.5
-72.5°	26.3	29.7	33.1	36.3	41.5	46.8	51.8	56.7	68.0	83.3	97.9
-75°	21.9	23.6	26.3	29.2	31.9	34.5	37.3	41.5	45.5	49.3	53.0
-77.5°	18.6	20.0	21.4	22.7	24.2	26.4	28.5	30.5	32.5	34.3	36.1
-80°	15.6	16.5	17.5	18.6	19.6	20.6	21.6	22.5	23.4	24.5	26.0
-82.5°	13.1	13.7	14.3	14.9	15.5	16.1	16.7	17.4	18.0	18.7	19.3
-85°	10.1	11.0	11.4	11.8	12.2	12.6	12.9	13.3	13.6	13.9	14.2
-87.5°	5.1	5.5	5.9	6.3	6.7	7.1	7.4	7.8	8.1	8.4	8.7
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	9.0	9.3	9.5	9.8	10.0	10.2	10.3	10.5	10.6	10.7	10.8
85°	14.5	14.8	15.0	15.3	15.5	15.7	15.8	16.0	16.1	16.2	16.3
82.5°	19.8	20.4	20.9	21.3	21.7	22.1	22.5	22.8	23.0	23.3	23.5
80°	27.3	28.6	29.7	30.8	31.8	32.7	33.6	34.3	34.9	35.5	35.9
77.5°	38.6	41.3	43.8	46.1	48.3	50.2	52.0	53.5	54.9	56.1	57.0
75°	56.4	62.0	72.3	81.9	90.8	98.8	106.1	112.6	118.2	123.0	126.9
72.5°	111.6	124.6	140.1	164.6	187.1	207.7	226.2	242.6	257.0	269.2	279.2
70°	216.8	249.2	279.4	310.2	342.5	372.1	398.7	422.3	443.0	460.5	474.9
67.5°	359.7	405.4	448.1	487.9	525.9	561.2	593.1	621.4	646.1	667.1	684.4
65°	522.5	576.3	626.8	673.8	717.5	766.6	810.9	850.4	884.8	914.1	938.2
62.5°	691.7	759.9	829.3	893.9	953.5	1009.2	1060.6	1106.3	1146.2	1180.2	1208.2
60°	893.9	975.1	1054.3	1128.4	1196.9	1259.6	1314.1	1362.6	1405.0	1441.1	1470.9
57.5°	1104.5	1196.9	1282.8	1360.7	1432.8	1498.9	1561.3	1618.8	1669.0	1711.8	1747.1
55°	1314.1	1410.5	1501.2	1590.8	1675.5	1753.1	1819.6	1863.5	1901.9	1934.7	1961.7
52.5°	1514.8	1626.3	1732.2	1825.0	1889.2	1948.2	2001.8	2021.8	2034.2	2044.7	2053.4
50°	1727.1	1836.6	1916.4	1991.2	2025.1	2043.9	2061.0	2096.0	2145.9	2188.6	2223.9
47.5°	1898.5	1989.1	2029.3	2053.0	2091.3	2166.9	2235.7	2370.9	2822.7	3209.8	3529.9
45°	2019.6	2048.1	2091.8	2186.4	2274.7	2861.9	3481.7	4038.4	4449.5	4791.3	5074.3
42.5°	2060.8	2151.8	2259.4	2900.0	3690.7	4363.4	4907.1	5396.3	5657.5	5768.0	5859.6
40°	2188.3	2466.6	3423.2	4286.4	4975.6	5594.1	5768.6	5926.1	6058.8	6159.3	6242.7
37.5°	2674.7	3741.6	4637.9	5423.0	5756.7	5961.2	6129.0	6271.5	6397.1	6486.0	6560.1
35°	3848.5	4815.7	5618.1	5867.3	6089.8	6273.6	6434.0	6559.4	6671.0	6709.5	6725.8
32.5°	4815.7	5645.3	5923.2	6161.9	6372.2	6536.9	6685.6	6720.3	6744.6	6754.2	6752.0
30°	5618.1	5923.2	6186.2	6417.0	6599.9	6710.4	6742.5	6753.4	6750.2	6738.4	6703.7
27.5°	5867.3	6161.9	6417.0	6621.1	6719.2	6755.3	6751.1	6736.2	6685.0	6640.1	6790.2
25°	6089.8	6372.2	6599.9	6719.2	6754.7	6750.0	6709.5	6648.1	6828.8	7024.3	8412.2
22.5°	6273.6	6536.9	6710.4	6755.3	6750.0	6700.5	6682.3	6946.4	8377.8	10780.5	15075.3
20°	6434.0	6685.6	6742.5	6751.1	6709.5	6682.3	6986.3	9318.6	13120.8	22078.8	30766.2
17.5°	6559.4	6720.3	6753.4	6736.2	6648.1	6946.4	9318.6	14833.0	25709.7	40121.5	54131.6
15°	6671.0	6744.6	6750.2	6685.0	6828.8	8377.8	13120.8	25709.7	43330.3	65253.7	91943.1
12.5°	6709.5	6754.2	6738.4	6640.1	7024.3	10780.5	22078.8	40121.5	65253.7	98425.3	139045.2
10°	6725.8	6752.0	6703.7	6790.2	8412.2	15075.3	30766.2	54131.6	91943.1	139045.2	189894.7
7.5°	6738.6	6750.3	6676.2	6911.0	9909.1	20722.0	41033.5	73248.8	119632.2	176675.3	244170.5
5°	6747.9	6749.1	6656.2	6999.2	11006.4	24885.0	48661.4	88039.8	143175.9	211305.6	290018.1
2.5°	6753.5	6748.3	6644.0	7052.9	11676.7	27438.9	53368.3	97241.7	157999.7	234962.2	319912.3
0°	6755.4	6748.1	6639.9	7070.9	11902.2	28300.1	54960.4	100368.2	163070.8	243378.2	330395.1
-2.5°	6753.5	6748.3	6644.0	7052.9	11676.7	27438.9	53368.3	97241.7	157999.7	234962.2	319912.3
-5°	6747.9	6749.1	6656.2	6999.2	11006.4	24885.0	48661.4	88039.8	143175.9	211305.6	290018.1
-7.5°	6738.6	6750.3	6676.2	6911.0	9909.1	20722.0	41033.5	73248.8	119632.2	176675.3	244170.5
-10°	6725.8	6752.0	6703.7	6790.2	8412.2	15075.3	30766.2	54131.6	91943.1	139045.2	189894.7
-12.5°	6709.5	6754.2	6738.4	6640.1	7024.3	10780.5	22078.8	40121.5	65253.7	98425.3	139045.2
-15°	6671.0	6744.6	6750.2	6685.0	6828.8	8377.8	13120.8	25709.7	43330.3	65253.7	91943.1
-17.5°	6559.4	6720.3	6753.4	6736.2	6648.1	6946.4	9318.6	14833.0	25709.7	40121.5	54131.6
-20°	6434.0	6685.6	6742.5	6751.1	6709.5	6682.3	6986.3	9318.6	13120.8	22078.8	30766.2



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	6273.6	6536.9	6710.4	6755.3	6750.0	6700.5	6682.3	6946.4	8377.8	10780.5	15075.3
-25°	6089.8	6372.2	6599.9	6719.2	6754.7	6750.0	6709.5	6648.1	6828.8	7024.3	8412.2
-27.5°	5867.3	6161.9	6417.0	6621.1	6719.2	6755.3	6751.1	6736.2	6685.0	6640.1	6790.2
-30°	5618.1	5923.2	6186.2	6417.0	6599.9	6710.4	6742.5	6753.4	6750.2	6738.4	6703.7
-32.5°	4815.7	5645.3	5923.2	6161.9	6372.2	6536.9	6685.6	6720.3	6744.6	6754.2	6752.0
-35°	3848.5	4815.7	5618.1	5867.3	6089.8	6273.6	6434.0	6559.4	6671.0	6709.5	6725.8
-37.5°	2674.7	3741.6	4637.9	5423.0	5756.7	5961.2	6129.0	6271.5	6397.1	6486.0	6560.1
-40°	2188.3	2466.6	3423.2	4286.4	4975.6	5594.1	5768.6	5926.1	6058.8	6159.3	6242.7
-42.5°	2060.8	2151.8	2259.4	2900.0	3690.7	4363.4	4907.1	5396.3	5657.5	5768.0	5859.6
-45°	2019.6	2048.1	2091.8	2186.4	2274.7	2861.9	3481.7	4038.4	4449.5	4791.3	5074.3
-47.5°	1898.5	1989.1	2029.3	2053.0	2091.3	2166.9	2235.7	2370.9	2822.7	3209.8	3529.9
-50°	1727.1	1836.6	1916.4	1991.2	2025.1	2043.9	2061.0	2096.0	2145.9	2188.6	2223.9
-52.5°	1514.8	1626.3	1732.2	1825.0	1889.2	1948.2	2001.8	2021.8	2034.2	2044.7	2053.4
-55°	1314.1	1410.5	1501.2	1590.8	1675.5	1753.1	1819.6	1863.5	1901.9	1934.7	1961.7
-57.5°	1104.5	1196.9	1282.8	1360.7	1432.8	1498.9	1561.3	1618.8	1669.0	1711.8	1747.1
-60°	893.9	975.1	1054.3	1128.4	1196.9	1259.6	1314.1	1362.6	1405.0	1441.1	1470.9
-62.5°	691.7	759.9	829.3	893.9	953.5	1009.2	1060.6	1106.3	1146.2	1180.2	1208.2
-65°	522.5	576.3	626.8	673.8	717.5	766.6	810.9	850.4	884.8	914.1	938.2
-67.5°	359.7	405.4	448.1	487.9	525.9	561.2	593.1	621.4	646.1	667.1	684.4
-70°	216.8	249.2	279.4	310.2	342.5	372.1	398.7	422.3	443.0	460.5	474.9
-72.5°	111.6	124.6	140.1	164.6	187.1	207.7	226.2	242.6	257.0	269.2	279.2
-75°	56.4	62.0	72.3	81.9	90.8	98.8	106.1	112.6	118.2	123.0	126.9
-77.5°	38.6	41.3	43.8	46.1	48.3	50.2	52.0	53.5	54.9	56.1	57.0
-80°	27.3	28.6	29.7	30.8	31.8	32.7	33.6	34.3	34.9	35.5	35.9
-82.5°	19.8	20.4	20.9	21.3	21.7	22.1	22.5	22.8	23.0	23.3	23.5
-85°	14.5	14.8	15.0	15.3	15.5	15.7	15.8	16.0	16.1	16.2	16.3
-87.5°	9.0	9.3	9.5	9.8	10.0	10.2	10.3	10.5	10.6	10.7	10.8
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	10.9	11.0	11.0	11.0	11.0	11.0	10.9	10.8	10.7	10.6	10.5
85°	16.4	16.5	16.5	16.5	16.5	16.5	16.4	16.3	16.2	16.1	16.0
82.5°	23.6	23.7	23.8	23.8	23.8	23.7	23.6	23.5	23.3	23.0	22.8
80°	36.3	36.5	36.7	36.7	36.7	36.5	36.3	35.9	35.5	34.9	34.3
77.5°	57.7	58.3	58.6	58.7	58.6	58.3	57.7	57.0	56.1	54.9	53.5
75°	130.0	132.1	133.5	133.9	133.5	132.1	130.0	126.9	123.0	118.2	112.6
72.5°	287.0	292.6	296.0	297.1	296.0	292.6	287.0	279.2	269.2	257.0	242.6
70°	486.2	494.2	499.1	500.7	499.1	494.2	486.2	474.9	460.5	443.0	422.3
67.5°	697.9	707.6	713.4	715.3	713.4	707.6	697.9	684.4	667.1	646.1	621.4
65°	957.0	970.5	978.6	981.3	978.6	970.5	957.0	938.2	914.1	884.8	850.4
62.5°	1230.1	1245.7	1255.2	1258.3	1255.2	1245.7	1230.1	1208.2	1180.2	1146.2	1106.3
60°	1494.1	1510.8	1520.9	1524.2	1520.9	1510.8	1494.1	1470.9	1441.1	1405.0	1362.6
57.5°	1774.7	1794.5	1806.4	1810.4	1806.4	1794.5	1774.7	1747.1	1711.8	1669.0	1618.8
55°	1982.9	1998.1	2007.2	2010.3	2007.2	1998.1	1982.9	1961.7	1934.7	1901.9	1863.5
52.5°	2060.2	2065.1	2068.0	2069.0	2068.0	2065.1	2060.2	2053.4	2044.7	2034.2	2021.8
50°	2251.5	2271.3	2283.3	2287.3	2283.3	2271.3	2251.5	2223.9	2188.6	2145.9	2096.0
47.5°	3781.1	3961.6	4070.4	4106.8	4070.4	3961.6	3781.1	3529.9	3209.8	2822.7	2370.9
45°	5296.6	5456.5	5553.0	5585.2	5553.0	5456.5	5296.6	5074.3	4791.3	4449.5	4038.4
42.5°	5931.7	5983.6	6014.9	6025.4	6014.9	5983.6	5931.7	5859.6	5768.0	5657.5	5396.3
40°	6308.5	6355.9	6384.5	6394.1	6384.5	6355.9	6308.5	6242.7	6159.3	6058.8	5926.1
37.5°	6618.6	6660.8	6686.4	6694.9	6686.4	6660.8	6618.6	6560.1	6486.0	6397.1	6271.5
35°	6738.6	6747.9	6753.5	6755.4	6753.5	6747.9	6738.6	6725.8	6709.5	6671.0	6559.4
32.5°	6750.3	6749.1	6748.3	6748.1	6748.3	6749.1	6750.3	6752.0	6754.2	6744.6	6720.3
30°	6676.2	6656.2	6644.0	6639.9	6644.0	6656.2	6676.2	6703.7	6738.4	6750.2	6753.4
27.5°	6911.0	6999.2	7052.9	7070.9	7052.9	6999.2	6911.0	6790.2	6640.1	6685.0	6736.2
25°	9909.1	11006.4	11676.7	11902.2	11676.7	11006.4	9909.1	8412.2	7024.3	6828.8	6648.1
22.5°	20722.0	24885.0	27438.9	28300.1	27438.9	24885.0	20722.0	15075.3	10780.5	8377.8	6946.4
20°	41033.5	48661.4	53368.3	54960.4	53368.3	48661.4	41033.5	30766.2	22078.8	13120.8	9318.6
17.5°	73248.8	88039.8	97241.7	100368.2	97241.7	88039.8	73248.8	54131.6	40121.5	25709.7	14833.0
15°	119632.2	143175.9	157999.7	163070.8	157999.7	143175.9	119632.2	91943.1	65253.7	43330.3	25709.7
12.5°	176675.3	211305.6	234962.2	243378.2	234962.2	211305.6	176675.3	139045.2	98425.3	65253.7	40121.5
10°	244170.5	290018.1	319912.3	330395.1	319912.3	290018.1	244170.5	189894.7	139045.2	91943.1	54131.6
7.5°	310046.9	364478.3	404628.0	419159.1	404628.0	364478.3	310046.9	244170.5	176675.3	119632.2	73248.8
5°	364478.3	434770.4	477870.1	491494.0	477870.1	434770.4	364478.3	290018.1	211305.6	143175.9	88039.8
2.5°	404628.0	477870.1	524460.2	548617.9	524460.2	477870.1	404628.0	319912.3	234962.2	157999.7	97241.7
0°	419159.1	491494.0	548617.9	589622.6	548617.9	491494.0	419159.1	330395.1	243378.2	163070.8	100368.2
-2.5°	404628.0	477870.1	524460.2	548617.9	524460.2	477870.1	404628.0	319912.3	234962.2	157999.7	97241.7
-5°	364478.3	434770.4	477870.1	491494.0	477870.1	434770.4	364478.3	290018.1	211305.6	143175.9	88039.8
-7.5°	310046.9	364478.3	404628.0	419159.1	404628.0	364478.3	310046.9	244170.5	176675.3	119632.2	73248.8
-10°	244170.5	290018.1	319912.3	330395.1	319912.3	290018.1	244170.5	189894.7	139045.2	91943.1	54131.6
-12.5°	176675.3	211305.6	234962.2	243378.2	234962.2	211305.6	176675.3	139045.2	98425.3	65253.7	40121.5
-15°	119632.2	143175.9	157999.7	163070.8	157999.7	143175.9	119632.2	91943.1	65253.7	43330.3	25709.7
-17.5°	73248.8	88039.8	97241.7	100368.2	97241.7	88039.8	73248.8	54131.6	40121.5	25709.7	14833.0
-20°	41033.5	48661.4	53368.3	54960.4	53368.3	48661.4	41033.5	30766.2	22078.8	13120.8	9318.6



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	20722.0	24885.0	27438.9	28300.1	27438.9	24885.0	20722.0	15075.3	10780.5	8377.8	6946.4
-25°	9909.1	11006.4	11676.7	11902.2	11676.7	11006.4	9909.1	8412.2	7024.3	6828.8	6648.1
-27.5°	6911.0	6999.2	7052.9	7070.9	7052.9	6999.2	6911.0	6790.2	6640.1	6685.0	6736.2
-30°	6676.2	6656.2	6644.0	6639.9	6644.0	6656.2	6676.2	6703.7	6738.4	6750.2	6753.4
-32.5°	6750.3	6749.1	6748.3	6748.1	6748.3	6749.1	6750.3	6752.0	6754.2	6744.6	6720.3
-35°	6738.6	6747.9	6753.5	6755.4	6753.5	6747.9	6738.6	6725.8	6709.5	6671.0	6559.4
-37.5°	6618.6	6660.8	6686.4	6694.9	6686.4	6660.8	6618.6	6560.1	6486.0	6397.1	6271.5
-40°	6308.5	6355.9	6384.5	6394.1	6384.5	6355.9	6308.5	6242.7	6159.3	6058.8	5926.1
-42.5°	5931.7	5983.6	6014.9	6025.4	6014.9	5983.6	5931.7	5859.6	5768.0	5657.5	5396.3
-45°	5296.6	5456.5	5553.0	5585.2	5553.0	5456.5	5296.6	5074.3	4791.3	4449.5	4038.4
-47.5°	3781.1	3961.6	4070.4	4106.8	4070.4	3961.6	3781.1	3529.9	3209.8	2822.7	2370.9
-50°	2251.5	2271.3	2283.3	2287.3	2283.3	2271.3	2251.5	2223.9	2188.6	2145.9	2096.0
-52.5°	2060.2	2065.1	2068.0	2069.0	2068.0	2065.1	2060.2	2053.4	2044.7	2034.2	2021.8
-55°	1982.9	1998.1	2007.2	2010.3	2007.2	1998.1	1982.9	1961.7	1934.7	1901.9	1863.5
-57.5°	1774.7	1794.5	1806.4	1810.4	1806.4	1794.5	1774.7	1747.1	1711.8	1669.0	1618.8
-60°	1494.1	1510.8	1520.9	1524.2	1520.9	1510.8	1494.1	1470.9	1441.1	1405.0	1362.6
-62.5°	1230.1	1245.7	1255.2	1258.3	1255.2	1245.7	1230.1	1208.2	1180.2	1146.2	1106.3
-65°	957.0	970.5	978.6	981.3	978.6	970.5	957.0	938.2	914.1	884.8	850.4
-67.5°	697.9	707.6	713.4	715.3	713.4	707.6	697.9	684.4	667.1	646.1	621.4
-70°	486.2	494.2	499.1	500.7	499.1	494.2	486.2	474.9	460.5	443.0	422.3
-72.5°	287.0	292.6	296.0	297.1	296.0	292.6	287.0	279.2	269.2	257.0	242.6
-75°	130.0	132.1	133.5	133.9	133.5	132.1	130.0	126.9	123.0	118.2	112.6
-77.5°	57.7	58.3	58.6	58.7	58.6	58.3	57.7	57.0	56.1	54.9	53.5
-80°	36.3	36.5	36.7	36.7	36.7	36.5	36.3	35.9	35.5	34.9	34.3
-82.5°	23.6	23.7	23.8	23.8	23.8	23.7	23.6	23.5	23.3	23.0	22.8
-85°	16.4	16.5	16.5	16.5	16.5	16.5	16.4	16.3	16.2	16.1	16.0
-87.5°	10.9	11.0	11.0	11.0	11.0	11.0	10.9	10.8	10.7	10.6	10.5
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	10.3	10.2	10.0	9.8	9.5	9.3	9.0	8.7	8.4	8.1	7.8
85°	15.8	15.7	15.5	15.3	15.0	14.8	14.5	14.2	13.9	13.6	13.3
82.5°	22.5	22.1	21.7	21.3	20.9	20.4	19.8	19.3	18.7	18.0	17.4
80°	33.6	32.7	31.8	30.8	29.7	28.6	27.3	26.0	24.5	23.4	22.5
77.5°	52.0	50.2	48.3	46.1	43.8	41.3	38.6	36.1	34.3	32.5	30.5
75°	106.1	98.8	90.8	81.9	72.3	62.0	56.4	53.0	49.3	45.5	41.5
72.5°	226.2	207.7	187.1	164.6	140.1	124.6	111.6	97.9	83.3	68.0	56.7
70°	398.7	372.1	342.5	310.2	279.4	249.2	216.8	182.5	146.2	122.0	103.7
67.5°	593.1	561.2	525.9	487.9	448.1	405.4	359.7	311.3	267.5	224.5	179.6
65°	810.9	766.6	717.5	673.8	626.8	576.3	522.5	467.3	410.3	350.4	289.8
62.5°	1060.6	1009.2	953.5	893.9	829.3	759.9	691.7	628.6	562.1	492.8	423.9
60°	1314.1	1259.6	1196.9	1128.4	1054.3	975.1	893.9	807.9	717.5	640.8	561.2
57.5°	1561.3	1498.9	1432.8	1360.7	1282.8	1196.9	1104.5	1006.9	907.4	804.4	700.6
55°	1819.6	1753.1	1675.5	1590.8	1501.2	1410.5	1314.1	1210.4	1099.3	983.2	867.2
52.5°	2001.8	1948.2	1889.2	1825.0	1732.2	1626.3	1514.8	1405.0	1289.9	1166.2	1036.3
50°	2061.0	2043.9	2025.1	1991.2	1916.4	1836.6	1727.1	1599.9	1470.9	1342.2	1206.7
47.5°	2235.7	2166.9	2091.3	2053.0	2029.3	1989.1	1898.5	1800.2	1657.8	1510.8	1368.5
45°	3481.7	2861.9	2274.7	2186.4	2091.8	2048.1	2019.6	1940.3	1834.2	1687.0	1524.2
42.5°	4907.1	4363.4	3690.7	2900.0	2259.4	2151.8	2060.8	2029.0	1961.3	1844.6	1687.0
40°	5768.6	5594.1	4975.6	4286.4	3423.2	2466.6	2188.3	2067.3	2032.2	1961.3	1834.2
37.5°	6129.0	5961.2	5756.7	5423.0	4637.9	3741.6	2674.7	2200.6	2067.3	2029.0	1940.3
35°	6434.0	6273.6	6089.8	5867.3	5618.1	4815.7	3848.5	2674.7	2188.3	2060.8	2019.6
32.5°	6685.6	6536.9	6372.2	6161.9	5923.2	5645.3	4815.7	3741.6	2466.6	2151.8	2048.1
30°	6742.5	6710.4	6599.9	6417.0	6186.2	5923.2	5618.1	4637.9	3423.2	2259.4	2091.8
27.5°	6751.1	6755.3	6719.2	6621.1	6417.0	6161.9	5867.3	5423.0	4286.4	2900.0	2186.4
25°	6709.5	6750.0	6754.7	6719.2	6599.9	6372.2	6089.8	5756.7	4975.6	3690.7	2274.7
22.5°	6682.3	6700.5	6750.0	6755.3	6710.4	6536.9	6273.6	5961.2	5594.1	4363.4	2861.9
20°	6986.3	6682.3	6709.5	6751.1	6742.5	6685.6	6434.0	6129.0	5768.6	4907.1	3481.7
17.5°	9318.6	6946.4	6648.1	6736.2	6753.4	6720.3	6559.4	6271.5	5926.1	5396.3	4038.4
15°	13120.8	8377.8	6828.8	6685.0	6750.2	6744.6	6671.0	6397.1	6058.8	5657.5	4449.5
12.5°	22078.8	10780.5	7024.3	6640.1	6738.4	6754.2	6709.5	6486.0	6159.3	5768.0	4791.3
10°	30766.2	15075.3	8412.2	6790.2	6703.7	6752.0	6725.8	6560.1	6242.7	5859.6	5074.3
7.5°	41033.5	20722.0	9909.1	6911.0	6676.2	6750.3	6738.6	6618.6	6308.5	5931.7	5296.6
5°	48661.4	24885.0	11006.4	6999.2	6656.2	6749.1	6747.9	6660.8	6355.9	5983.6	5456.5
2.5°	53368.3	27438.9	11676.7	7052.9	6644.0	6748.3	6753.5	6686.4	6384.5	6014.9	5553.0
0°	54960.4	28300.1	11902.2	7070.9	6639.9	6748.1	6755.4	6694.9	6394.1	6025.4	5585.2
-2.5°	53368.3	27438.9	11676.7	7052.9	6644.0	6748.3	6753.5	6686.4	6384.5	6014.9	5553.0
-5°	48661.4	24885.0	11006.4	6999.2	6656.2	6749.1	6747.9	6660.8	6355.9	5983.6	5456.5
-7.5°	41033.5	20722.0	9909.1	6911.0	6676.2	6750.3	6738.6	6618.6	6308.5	5931.7	5296.6
-10°	30766.2	15075.3	8412.2	6790.2	6703.7	6752.0	6725.8	6560.1	6242.7	5859.6	5074.3
-12.5°	22078.8	10780.5	7024.3	6640.1	6738.4	6754.2	6709.5	6486.0	6159.3	5768.0	4791.3
-15°	13120.8	8377.8	6828.8	6685.0	6750.2	6744.6	6671.0	6397.1	6058.8	5657.5	4449.5
-17.5°	9318.6	6946.4	6648.1	6736.2	6753.4	6720.3	6559.4	6271.5	5926.1	5396.3	4038.4
-20°	6986.3	6682.3	6709.5	6751.1	6742.5	6685.6	6434.0	6129.0	5768.6	4907.1	3481.7



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	6682.3	6700.5	6750.0	6755.3	6710.4	6536.9	6273.6	5961.2	5594.1	4363.4	2861.9
-25°	6709.5	6750.0	6754.7	6719.2	6599.9	6372.2	6089.8	5756.7	4975.6	3690.7	2274.7
-27.5°	6751.1	6755.3	6719.2	6621.1	6417.0	6161.9	5867.3	5423.0	4286.4	2900.0	2186.4
-30°	6742.5	6710.4	6599.9	6417.0	6186.2	5923.2	5618.1	4637.9	3423.2	2259.4	2091.8
-32.5°	6685.6	6536.9	6372.2	6161.9	5923.2	5645.3	4815.7	3741.6	2466.6	2151.8	2048.1
-35°	6434.0	6273.6	6089.8	5867.3	5618.1	4815.7	3848.5	2674.7	2188.3	2060.8	2019.6
-37.5°	6129.0	5961.2	5756.7	5423.0	4637.9	3741.6	2674.7	2200.6	2067.3	2029.0	1940.3
-40°	5768.6	5594.1	4975.6	4286.4	3423.2	2466.6	2188.3	2067.3	2032.2	1961.3	1834.2
-42.5°	4907.1	4363.4	3690.7	2900.0	2259.4	2151.8	2060.8	2029.0	1961.3	1844.6	1687.0
-45°	3481.7	2861.9	2274.7	2186.4	2091.8	2048.1	2019.6	1940.3	1834.2	1687.0	1524.2
-47.5°	2235.7	2166.9	2091.3	2053.0	2029.3	1989.1	1898.5	1800.2	1657.8	1510.8	1368.5
-50°	2061.0	2043.9	2025.1	1991.2	1916.4	1836.6	1727.1	1599.9	1470.9	1342.2	1206.7
-52.5°	2001.8	1948.2	1889.2	1825.0	1732.2	1626.3	1514.8	1405.0	1289.9	1166.2	1036.3
-55°	1819.6	1753.1	1675.5	1590.8	1501.2	1410.5	1314.1	1210.4	1099.3	983.2	867.2
-57.5°	1561.3	1498.9	1432.8	1360.7	1282.8	1196.9	1104.5	1006.9	907.4	804.4	700.6
-60°	1314.1	1259.6	1196.9	1128.4	1054.3	975.1	893.9	807.9	717.5	640.8	561.2
-62.5°	1060.6	1009.2	953.5	893.9	829.3	759.9	691.7	628.6	562.1	492.8	423.9
-65°	810.9	766.6	717.5	673.8	626.8	576.3	522.5	467.3	410.3	350.4	289.8
-67.5°	593.1	561.2	525.9	487.9	448.1	405.4	359.7	311.3	267.5	224.5	179.6
-70°	398.7	372.1	342.5	310.2	279.4	249.2	216.8	182.5	146.2	122.0	103.7
-72.5°	226.2	207.7	187.1	164.6	140.1	124.6	111.6	97.9	83.3	68.0	56.7
-75°	106.1	98.8	90.8	81.9	72.3	62.0	56.4	53.0	49.3	45.5	41.5
-77.5°	52.0	50.2	48.3	46.1	43.8	41.3	38.6	36.1	34.3	32.5	30.5
-80°	33.6	32.7	31.8	30.8	29.7	28.6	27.3	26.0	24.5	23.4	22.5
-82.5°	22.5	22.1	21.7	21.3	20.9	20.4	19.8	19.3	18.7	18.0	17.4
-85°	15.8	15.7	15.5	15.3	15.0	14.8	14.5	14.2	13.9	13.6	13.3
-87.5°	10.3	10.2	10.0	9.8	9.5	9.3	9.0	8.7	8.4	8.1	7.8
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	7.4	7.1	6.7	6.3	5.9	5.5	5.1	4.6	4.2	3.8	3.3
85°	12.9	12.6	12.2	11.8	11.4	11.0	10.1	9.3	8.4	7.5	6.6
82.5°	16.7	16.1	15.5	14.9	14.3	13.7	13.1	12.5	11.8	11.1	9.9
80°	21.6	20.6	19.6	18.6	17.5	16.5	15.6	14.8	13.9	13.0	12.1
77.5°	28.5	26.4	24.2	22.7	21.4	20.0	18.6	17.2	16.0	14.8	13.7
75°	37.3	34.5	31.9	29.2	26.3	23.6	21.9	20.2	18.5	16.7	15.3
72.5°	51.8	46.8	41.5	36.3	33.1	29.7	26.3	23.2	21.2	19.1	17.0
70°	84.6	64.7	54.5	48.3	41.9	35.9	32.0	28.0	23.9	21.5	19.1
67.5°	133.4	111.0	87.9	64.1	53.1	45.8	38.3	33.1	28.6	23.9	21.2
65°	237.7	183.7	131.1	104.7	77.5	56.1	47.7	39.2	33.1	28.0	23.2
62.5°	352.2	281.8	220.4	157.3	114.8	84.2	57.0	47.7	38.3	32.0	26.3
60°	479.7	398.7	315.1	242.6	172.0	118.2	84.2	56.1	45.8	35.9	29.7
57.5°	610.9	518.2	426.8	333.7	250.1	172.0	114.8	77.5	53.1	41.9	33.1
55°	747.1	641.0	538.2	436.2	333.7	242.6	157.3	104.7	64.1	48.3	36.3
52.5°	905.2	772.3	651.1	538.2	426.8	315.1	220.4	131.1	87.9	54.5	41.5
50°	1063.1	917.9	772.3	641.0	518.2	398.7	281.8	183.7	111.0	64.7	46.8
47.5°	1220.2	1063.1	905.2	747.1	610.9	479.7	352.2	237.7	133.4	84.6	51.8
45°	1368.5	1206.7	1036.3	867.2	700.6	561.2	423.9	289.8	179.6	103.7	56.7
42.5°	1510.8	1342.2	1166.2	983.2	804.4	640.8	492.8	350.4	224.5	122.0	68.0
40°	1657.8	1470.9	1289.9	1099.3	907.4	717.5	562.1	410.3	267.5	146.2	83.3
37.5°	1800.2	1599.9	1405.0	1210.4	1006.9	807.9	628.6	467.3	311.3	182.5	97.9
35°	1898.5	1727.1	1514.8	1314.1	1104.5	893.9	691.7	522.5	359.7	216.8	111.6
32.5°	1989.1	1836.6	1626.3	1410.5	1196.9	975.1	759.9	576.3	405.4	249.2	124.6
30°	2029.3	1916.4	1732.2	1501.2	1282.8	1054.3	829.3	626.8	448.1	279.4	140.1
27.5°	2053.0	1991.2	1825.0	1590.8	1360.7	1128.4	893.9	673.8	487.9	310.2	164.6
25°	2091.3	2025.1	1889.2	1675.5	1432.8	1196.9	953.5	717.5	525.9	342.5	187.1
22.5°	2166.9	2043.9	1948.2	1753.1	1498.9	1259.6	1009.2	766.6	561.2	372.1	207.7
20°	2235.7	2061.0	2001.8	1819.6	1561.3	1314.1	1060.6	810.9	593.1	398.7	226.2
17.5°	2370.9	2096.0	2021.8	1863.5	1618.8	1362.6	1106.3	850.4	621.4	422.3	242.6
15°	2822.7	2145.9	2034.2	1901.9	1669.0	1405.0	1146.2	884.8	646.1	443.0	257.0
12.5°	3209.8	2188.6	2044.7	1934.7	1711.8	1441.1	1180.2	914.1	667.1	460.5	269.2
10°	3529.9	2223.9	2053.4	1961.7	1747.1	1470.9	1208.2	938.2	684.4	474.9	279.2
7.5°	3781.1	2251.5	2060.2	1982.9	1774.7	1494.1	1230.1	957.0	697.9	486.2	287.0
5°	3961.6	2271.3	2065.1	1998.1	1794.5	1510.8	1245.7	970.5	707.6	494.2	292.6
2.5°	4070.4	2283.3	2068.0	2007.2	1806.4	1520.9	1255.2	978.6	713.4	499.1	296.0
0°	4106.8	2287.3	2069.0	2010.3	1810.4	1524.2	1258.3	981.3	715.3	500.7	297.1
-2.5°	4070.4	2283.3	2068.0	2007.2	1806.4	1520.9	1255.2	978.6	713.4	499.1	296.0
-5°	3961.6	2271.3	2065.1	1998.1	1794.5	1510.8	1245.7	970.5	707.6	494.2	292.6
-7.5°	3781.1	2251.5	2060.2	1982.9	1774.7	1494.1	1230.1	957.0	697.9	486.2	287.0
-10°	3529.9	2223.9	2053.4	1961.7	1747.1	1470.9	1208.2	938.2	684.4	474.9	279.2
-12.5°	3209.8	2188.6	2044.7	1934.7	1711.8	1441.1	1180.2	914.1	667.1	460.5	269.2
-15°	2822.7	2145.9	2034.2	1901.9	1669.0	1405.0	1146.2	884.8	646.1	443.0	257.0
-17.5°	2370.9	2096.0	2021.8	1863.5	1618.8	1362.6	1106.3	850.4	621.4	422.3	242.6
-20°	2235.7	2061.0	2001.8	1819.6	1561.3	1314.1	1060.6	810.9	593.1	398.7	226.2



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	2166.9	2043.9	1948.2	1753.1	1498.9	1259.6	1009.2	766.6	561.2	372.1	207.7
-25°	2091.3	2025.1	1889.2	1675.5	1432.8	1196.9	953.5	717.5	525.9	342.5	187.1
-27.5°	2053.0	1991.2	1825.0	1590.8	1360.7	1128.4	893.9	673.8	487.9	310.2	164.6
-30°	2029.3	1916.4	1732.2	1501.2	1282.8	1054.3	829.3	626.8	448.1	279.4	140.1
-32.5°	1989.1	1836.6	1626.3	1410.5	1196.9	975.1	759.9	576.3	405.4	249.2	124.6
-35°	1898.5	1727.1	1514.8	1314.1	1104.5	893.9	691.7	522.5	359.7	216.8	111.6
-37.5°	1800.2	1599.9	1405.0	1210.4	1006.9	807.9	628.6	467.3	311.3	182.5	97.9
-40°	1657.8	1470.9	1289.9	1099.3	907.4	717.5	562.1	410.3	267.5	146.2	83.3
-42.5°	1510.8	1342.2	1166.2	983.2	804.4	640.8	492.8	350.4	224.5	122.0	68.0
-45°	1368.5	1206.7	1036.3	867.2	700.6	561.2	423.9	289.8	179.6	103.7	56.7
-47.5°	1220.2	1063.1	905.2	747.1	610.9	479.7	352.2	237.7	133.4	84.6	51.8
-50°	1063.1	917.9	772.3	641.0	518.2	398.7	281.8	183.7	111.0	64.7	46.8
-52.5°	905.2	772.3	651.1	538.2	426.8	315.1	220.4	131.1	87.9	54.5	41.5
-55°	747.1	641.0	538.2	436.2	333.7	242.6	157.3	104.7	64.1	48.3	36.3
-57.5°	610.9	518.2	426.8	333.7	250.1	172.0	114.8	77.5	53.1	41.9	33.1
-60°	479.7	398.7	315.1	242.6	172.0	118.2	84.2	56.1	45.8	35.9	29.7
-62.5°	352.2	281.8	220.4	157.3	114.8	84.2	57.0	47.7	38.3	32.0	26.3
-65°	237.7	183.7	131.1	104.7	77.5	56.1	47.7	39.2	33.1	28.0	23.2
-67.5°	133.4	111.0	87.9	64.1	53.1	45.8	38.3	33.1	28.6	23.9	21.2
-70°	84.6	64.7	54.5	48.3	41.9	35.9	32.0	28.0	23.9	21.5	19.1
-72.5°	51.8	46.8	41.5	36.3	33.1	29.7	26.3	23.2	21.2	19.1	17.0
-75°	37.3	34.5	31.9	29.2	26.3	23.6	21.9	20.2	18.5	16.7	15.3
-77.5°	28.5	26.4	24.2	22.7	21.4	20.0	18.6	17.2	16.0	14.8	13.7
-80°	21.6	20.6	19.6	18.6	17.5	16.5	15.6	14.8	13.9	13.0	12.1
-82.5°	16.7	16.1	15.5	14.9	14.3	13.7	13.1	12.5	11.8	11.1	9.9
-85°	12.9	12.6	12.2	11.8	11.4	11.0	10.1	9.3	8.4	7.5	6.6
-87.5°	7.4	7.1	6.7	6.3	5.9	5.5	5.1	4.6	4.2	3.8	3.3
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	2.8	2.4	1.9	1.4	1.0	0.5	0.0
85°	5.7	4.8	3.8	2.9	1.9	1.0	0.0
82.5°	8.5	7.1	5.7	4.3	2.9	1.4	0.0
80°	11.2	9.5	7.6	5.7	3.8	1.9	0.0
77.5°	12.6	11.4	9.5	7.1	4.8	2.4	0.0
75°	14.0	12.6	11.2	8.5	5.7	2.8	0.0
72.5°	15.3	13.7	12.1	9.9	6.6	3.3	0.0
70°	16.7	14.8	13.0	11.1	7.5	3.8	0.0
67.5°	18.5	16.0	13.9	11.8	8.4	4.2	0.0
65°	20.2	17.2	14.8	12.5	9.3	4.6	0.0
62.5°	21.9	18.6	15.6	13.1	10.1	5.1	0.0
60°	23.6	20.0	16.5	13.7	11.0	5.5	0.0
57.5°	26.3	21.4	17.5	14.3	11.4	5.9	0.0
55°	29.2	22.7	18.6	14.9	11.8	6.3	0.0
52.5°	31.9	24.2	19.6	15.5	12.2	6.7	0.0
50°	34.5	26.4	20.6	16.1	12.6	7.1	0.0
47.5°	37.3	28.5	21.6	16.7	12.9	7.4	0.0
45°	41.5	30.5	22.5	17.4	13.3	7.8	0.0
42.5°	45.5	32.5	23.4	18.0	13.6	8.1	0.0
40°	49.3	34.3	24.5	18.7	13.9	8.4	0.0
37.5°	53.0	36.1	26.0	19.3	14.2	8.7	0.0
35°	56.4	38.6	27.3	19.8	14.5	9.0	0.0
32.5°	62.0	41.3	28.6	20.4	14.8	9.3	0.0
30°	72.3	43.8	29.7	20.9	15.0	9.5	0.0
27.5°	81.9	46.1	30.8	21.3	15.3	9.8	0.0
25°	90.8	48.3	31.8	21.7	15.5	10.0	0.0
22.5°	98.8	50.2	32.7	22.1	15.7	10.2	0.0
20°	106.1	52.0	33.6	22.5	15.8	10.3	0.0
17.5°	112.6	53.5	34.3	22.8	16.0	10.5	0.0
15°	118.2	54.9	34.9	23.0	16.1	10.6	0.0
12.5°	123.0	56.1	35.5	23.3	16.2	10.7	0.0
10°	126.9	57.0	35.9	23.5	16.3	10.8	0.0
7.5°	130.0	57.7	36.3	23.6	16.4	10.9	0.0
5°	132.1	58.3	36.5	23.7	16.5	11.0	0.0
2.5°	133.5	58.6	36.7	23.8	16.5	11.0	0.0
0°	133.9	58.7	36.7	23.8	16.5	11.0	0.0
-2.5°	133.5	58.6	36.7	23.8	16.5	11.0	0.0
-5°	132.1	58.3	36.5	23.7	16.5	11.0	0.0
-7.5°	130.0	57.7	36.3	23.6	16.4	10.9	0.0
-10°	126.9	57.0	35.9	23.5	16.3	10.8	0.0
-12.5°	123.0	56.1	35.5	23.3	16.2	10.7	0.0
-15°	118.2	54.9	34.9	23.0	16.1	10.6	0.0
-17.5°	112.6	53.5	34.3	22.8	16.0	10.5	0.0
-20°	106.1	52.0	33.6	22.5	15.8	10.3	0.0



REPORT NUMBER: P731295 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680N-57-70-2S-HEG

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	98.8	50.2	32.7	22.1	15.7	10.2	0.0
-25°	90.8	48.3	31.8	21.7	15.5	10.0	0.0
-27.5°	81.9	46.1	30.8	21.3	15.3	9.8	0.0
-30°	72.3	43.8	29.7	20.9	15.0	9.5	0.0
-32.5°	62.0	41.3	28.6	20.4	14.8	9.3	0.0
-35°	56.4	38.6	27.3	19.8	14.5	9.0	0.0
-37.5°	53.0	36.1	26.0	19.3	14.2	8.7	0.0
-40°	49.3	34.3	24.5	18.7	13.9	8.4	0.0
-42.5°	45.5	32.5	23.4	18.0	13.6	8.1	0.0
-45°	41.5	30.5	22.5	17.4	13.3	7.8	0.0
-47.5°	37.3	28.5	21.6	16.7	12.9	7.4	0.0
-50°	34.5	26.4	20.6	16.1	12.6	7.1	0.0
-52.5°	31.9	24.2	19.6	15.5	12.2	6.7	0.0
-55°	29.2	22.7	18.6	14.9	11.8	6.3	0.0
-57.5°	26.3	21.4	17.5	14.3	11.4	5.9	0.0
-60°	23.6	20.0	16.5	13.7	11.0	5.5	0.0
-62.5°	21.9	18.6	15.6	13.1	10.1	5.1	0.0
-65°	20.2	17.2	14.8	12.5	9.3	4.6	0.0
-67.5°	18.5	16.0	13.9	11.8	8.4	4.2	0.0
-70°	16.7	14.8	13.0	11.1	7.5	3.8	0.0
-72.5°	15.3	13.7	12.1	9.9	6.6	3.3	0.0
-75°	14.0	12.6	11.2	8.5	5.7	2.8	0.0
-77.5°	12.6	11.4	9.5	7.1	4.8	2.4	0.0
-80°	11.2	9.5	7.6	5.7	3.8	1.9	0.0
-82.5°	8.5	7.1	5.7	4.3	2.9	1.4	0.0
-85°	5.7	4.8	3.8	2.9	1.9	1.0	0.0
-87.5°	2.8	2.4	1.9	1.4	1.0	0.5	0.0
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Horizontal Angle (degrees)



Horizontal Angle (degrees)



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report

