

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: EPHESUS

Report Number: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **EPH-LS-08-0680R-57-80-2S-HEG-S**

Issue Date: 8/15/2023

**Test Information**


Test Method: LM-79-08  
Report Number: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2301-906-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/15/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: EPHESUS  
Catalog Number: EPH-LS-08-0680R-57-80-2S-HEG-S  
Description: EPHESUS LUMASPORT 8 LUMINAIRE  
(8) 5700K, 80 CRI LEDS AND 2S BEAM SHAPE  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	99732.9 lumens	Max Intensity:	553667.2 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	141.7 lumens/watt		
Luminous Opening:	Rectangular (W 1.5' x L: 1' x H: 0')		
Beam Angle (50%):	22°H x 22°V	Field Angle (10%):	39.6°H x 39.6°V
Beam Lumens:	44078.7 lumens	Field Lumens:	81864.6 lumens
Beam Efficiency:	44.2%	Field Efficiency:	82.1%
Input Watts (W):	703.6		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

### Iso-Candela Plot






REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

### Lumen Table

90	0.2	1.0	3.5	8.8	11.6	8.8	3.5	1.0	0.2							
80	0.2	1.0	3.5	8.8	11.6	8.8	3.5	1.0	0.2							
70	0.5	0.5	2.1	6.3	12.5	19.2	24.8	27.8	27.8	24.8	19.2	12.5	6.3	2.1	0.5	0.5
60		1.6	7.4	17.7	30.7	42.7	50.8	55.0	55.0	50.8	42.7	30.7	17.7	7.4	1.6	
50	1.1	3.9	14.5	30.8	46.9	76.0	116.4	139.4	139.4	116.4	76.0	46.9	30.8	14.5	3.9	1.1
40		6.7	21.7	40.6	89.6	153.9	180.3	189.6	189.6	180.3	153.9	89.6	40.6	21.7	6.7	
30	2.5	9.2	27.2	59.9	139.3	173.3	236.9	483.5	483.5	236.9	173.3	139.3	59.9	27.2	9.2	2.5
20		11.2	30.4	86.4	153.0	223.0	1410.6	4179.8	4179.8	1410.6	223.0	153.0	86.4	30.4	11.2	
10	3.2	12.2	31.9	100.1	155.9	445.6	4073.6	11456.2	11456.2	4073.6	445.6	155.9	100.1	31.9	12.2	3.2
0		12.2	31.9	100.1	155.9	445.6	4073.6	11456.2	11456.2	4073.6	445.6	155.9	100.1	31.9	12.2	
-10	2.5	11.2	30.4	86.4	153.0	223.0	1410.6	4179.8	4179.8	1410.6	223.0	153.0	86.4	30.4	11.2	2.5
-20		9.2	27.2	59.9	139.3	173.3	236.9	483.5	483.5	236.9	173.3	139.3	59.9	27.2	9.2	
-30	1.1	6.7	21.7	40.6	89.6	153.9	180.3	189.6	189.6	180.3	153.9	89.6	40.6	21.7	6.7	1.1
-40		3.9	14.5	30.8	46.9	76.0	116.4	139.4	139.4	116.4	76.0	46.9	30.8	14.5	3.9	
-50	0.5	1.6	7.4	17.7	30.7	42.7	50.8	55.0	55.0	50.8	42.7	30.7	17.7	7.4	1.6	0.5
-60		0.5	2.1	6.3	12.5	19.2	24.8	27.8	27.8	24.8	19.2	12.5	6.3	2.1	0.5	
-70	0.2	1.0	3.5	8.8	11.6	8.8	3.5	1.0	0.2							
-80		0.2	1.0	3.5	8.8	11.6	8.8	3.5	1.0	0.2						
-90	0.2	1.0	3.5	8.8	11.6	8.8	3.5	1.0	0.2							

REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S


### Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg      - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

### Luminous Intensity Plot



**Beam:**  
 H Angle: 22°  
 V Angle: 22°  
 Lumens: 44078.7  
 Efficiency: 44.2%

**Field:**  
 H Angle: 39.6°  
 V Angle: 39.6°  
 Lumens: 81864.6  
 Efficiency: 82.1%

**Spill:**  
 Lumens: 17868.3  
 Efficiency: 17.9%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.4	0.9	1.3	1.8	2.2	2.7	3.1	3.5	3.9	4.4
85°	0.0	0.9	1.8	2.7	3.6	4.5	5.3	6.2	7.0	7.9	8.7
82.5°	0.0	1.3	2.7	4.0	5.4	6.7	8.0	9.3	10.4	11.1	11.7
80°	0.0	1.8	3.6	5.4	7.1	8.9	10.5	11.3	12.2	13.0	13.9
77.5°	0.0	2.2	4.5	6.7	8.9	10.7	11.8	12.9	13.9	15.0	16.2
75°	0.0	2.7	5.3	8.0	10.5	11.8	13.1	14.4	15.7	17.4	19.0
72.5°	0.0	3.1	6.2	9.3	11.3	12.9	14.4	16.0	18.0	19.9	21.9
70°	0.0	3.5	7.0	10.4	12.2	13.9	15.7	18.0	20.2	22.5	26.3
67.5°	0.0	3.9	7.9	11.1	13.0	15.0	17.4	19.9	22.5	26.8	31.1
65°	0.0	4.4	8.7	11.7	13.9	16.2	19.0	21.9	26.3	31.1	36.8
62.5°	0.0	4.8	9.5	12.3	14.7	17.5	20.6	24.7	30.0	35.9	44.8
60°	0.0	5.1	10.3	12.9	15.5	18.8	22.2	27.9	33.7	42.9	52.6
57.5°	0.0	5.5	10.7	13.5	16.5	20.1	24.8	31.0	39.3	49.8	72.7
55°	0.0	5.9	11.1	14.0	17.5	21.4	27.4	34.1	45.3	60.2	98.3
52.5°	0.0	6.3	11.4	14.6	18.4	22.7	29.9	38.9	51.1	82.5	123.1
50°	0.0	6.6	11.8	15.1	19.4	24.8	32.4	43.9	60.7	104.2	172.5
47.5°	0.0	7.0	12.1	15.7	20.3	26.8	35.0	48.7	79.4	125.2	223.2
45°	0.0	7.3	12.4	16.3	21.2	28.7	38.9	53.3	97.3	168.6	272.1
42.5°	0.0	7.6	12.8	16.9	22.0	30.5	42.7	63.8	114.6	210.8	329.1
40°	0.0	7.9	13.1	17.5	23.1	32.2	46.3	78.2	137.3	251.2	385.3
37.5°	0.0	8.2	13.3	18.1	24.4	33.9	49.7	91.9	171.3	292.3	438.8
35°	0.0	8.4	13.6	18.6	25.7	36.2	52.9	104.8	203.6	337.8	490.7
32.5°	0.0	8.7	13.9	19.1	26.8	38.7	58.2	117.0	234.0	380.7	541.2
30°	0.0	8.9	14.1	19.6	27.9	41.1	67.9	131.5	262.4	420.8	588.6
27.5°	0.0	9.1	14.3	20.0	28.9	43.2	76.9	154.5	291.3	458.2	632.7
25°	0.0	9.3	14.5	20.5	29.9	45.3	85.2	175.7	321.7	493.9	673.8
22.5°	0.0	9.5	14.7	20.8	30.7	47.1	92.8	195.0	349.4	527.0	719.9
20°	0.0	9.7	14.9	21.1	31.5	48.8	99.6	212.4	374.4	556.9	761.5
17.5°	0.0	9.8	15.0	21.4	32.2	50.2	105.7	227.8	396.6	583.5	798.5
15°	0.0	9.9	15.1	21.7	32.7	51.5	110.9	241.3	416.0	606.7	830.9
12.5°	0.0	10.1	15.3	21.9	33.3	52.6	115.4	252.8	432.5	626.4	858.4
10°	0.0	10.1	15.3	22.1	33.7	53.5	119.1	262.2	446.0	642.7	881.0
7.5°	0.0	10.2	15.4	22.2	34.0	54.2	122.0	269.5	456.6	655.3	898.7
5°	0.0	10.3	15.5	22.3	34.2	54.7	124.1	274.8	464.1	664.4	911.3
2.5°	0.0	10.3	15.5	22.4	34.4	55.0	125.3	277.9	468.7	669.9	919.0
0°	0.0	10.3	15.5	22.4	34.4	55.0	125.3	277.9	468.7	669.9	919.0
-2.5°	0.0	10.3	15.5	22.4	34.4	55.0	125.3	277.9	468.7	669.9	919.0
-5°	0.0	10.3	15.5	22.3	34.2	54.7	124.1	274.8	464.1	664.4	911.3
-7.5°	0.0	10.2	15.4	22.2	34.0	54.2	122.0	269.5	456.6	655.3	898.7
-10°	0.0	10.1	15.3	22.1	33.7	53.5	119.1	262.2	446.0	642.7	881.0
-12.5°	0.0	10.1	15.3	21.9	33.3	52.6	115.4	252.8	432.5	626.4	858.4
-15°	0.0	9.9	15.1	21.7	32.7	51.5	110.9	241.3	416.0	606.7	830.9
-17.5°	0.0	9.8	15.0	21.4	32.2	50.2	105.7	227.8	396.6	583.5	798.5
-20°	0.0	9.7	14.9	21.1	31.5	48.8	99.6	212.4	374.4	556.9	761.5



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0.0	9.5	14.7	20.8	30.7	47.1	92.8	195.0	349.4	527.0	719.9
-25°	0.0	9.3	14.5	20.5	29.9	45.3	85.2	175.7	321.7	493.9	673.8
-27.5°	0.0	9.1	14.3	20.0	28.9	43.2	76.9	154.5	291.3	458.2	632.7
-30°	0.0	8.9	14.1	19.6	27.9	41.1	67.9	131.5	262.4	420.8	588.6
-32.5°	0.0	8.7	13.9	19.1	26.8	38.7	58.2	117.0	234.0	380.7	541.2
-35°	0.0	8.4	13.6	18.6	25.7	36.2	52.9	104.8	203.6	337.8	490.7
-37.5°	0.0	8.2	13.3	18.1	24.4	33.9	49.7	91.9	171.3	292.3	438.8
-40°	0.0	7.9	13.1	17.5	23.1	32.2	46.3	78.2	137.3	251.2	385.3
-42.5°	0.0	7.6	12.8	16.9	22.0	30.5	42.7	63.8	114.6	210.8	329.1
-45°	0.0	7.3	12.4	16.3	21.2	28.7	38.9	53.3	97.3	168.6	272.1
-47.5°	0.0	7.0	12.1	15.7	20.3	26.8	35.0	48.7	79.4	125.2	223.2
-50°	0.0	6.6	11.8	15.1	19.4	24.8	32.4	43.9	60.7	104.2	172.5
-52.5°	0.0	6.3	11.4	14.6	18.4	22.7	29.9	38.9	51.1	82.5	123.1
-55°	0.0	5.9	11.1	14.0	17.5	21.4	27.4	34.1	45.3	60.2	98.3
-57.5°	0.0	5.5	10.7	13.5	16.5	20.1	24.8	31.0	39.3	49.8	72.7
-60°	0.0	5.1	10.3	12.9	15.5	18.8	22.2	27.9	33.7	42.9	52.6
-62.5°	0.0	4.8	9.5	12.3	14.7	17.5	20.6	24.7	30.0	35.9	44.8
-65°	0.0	4.4	8.7	11.7	13.9	16.2	19.0	21.9	26.3	31.1	36.8
-67.5°	0.0	3.9	7.9	11.1	13.0	15.0	17.4	19.9	22.5	26.8	31.1
-70°	0.0	3.5	7.0	10.4	12.2	13.9	15.7	18.0	20.2	22.5	26.3
-72.5°	0.0	3.1	6.2	9.3	11.3	12.9	14.4	16.0	18.0	19.9	21.9
-75°	0.0	2.7	5.3	8.0	10.5	11.8	13.1	14.4	15.7	17.4	19.0
-77.5°	0.0	2.2	4.5	6.7	8.9	10.7	11.8	12.9	13.9	15.0	16.2
-80°	0.0	1.8	3.6	5.4	7.1	8.9	10.5	11.3	12.2	13.0	13.9
-82.5°	0.0	1.3	2.7	4.0	5.4	6.7	8.0	9.3	10.4	11.1	11.7
-85°	0.0	0.9	1.8	2.7	3.6	4.5	5.3	6.2	7.0	7.9	8.7
-87.5°	0.0	0.4	0.9	1.3	1.8	2.2	2.7	3.1	3.5	3.9	4.4
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	4.8	5.1	5.5	5.9	6.3	6.6	7.0	7.3	7.6	7.9	8.2
85°	9.5	10.3	10.7	11.1	11.4	11.8	12.1	12.4	12.8	13.1	13.3
82.5°	12.3	12.9	13.5	14.0	14.6	15.1	15.7	16.3	16.9	17.5	18.1
80°	14.7	15.5	16.5	17.5	18.4	19.4	20.3	21.2	22.0	23.1	24.4
77.5°	17.5	18.8	20.1	21.4	22.7	24.8	26.8	28.7	30.5	32.2	33.9
75°	20.6	22.2	24.8	27.4	29.9	32.4	35.0	38.9	42.7	46.3	49.7
72.5°	24.7	27.9	31.0	34.1	38.9	43.9	48.7	53.3	63.8	78.2	91.9
70°	30.0	33.7	39.3	45.3	51.1	60.7	79.4	97.3	114.6	137.3	171.3
67.5°	35.9	42.9	49.8	60.2	82.5	104.2	125.2	168.6	210.8	251.2	292.3
65°	44.8	52.6	72.7	98.3	123.1	172.5	223.2	272.1	329.1	385.3	438.8
62.5°	53.5	79.1	107.8	147.6	207.0	264.6	330.8	398.1	462.8	527.8	590.2
60°	79.1	110.9	161.5	227.8	295.9	374.4	450.5	527.0	601.7	673.8	758.7
57.5°	107.8	161.5	234.8	313.4	400.8	486.7	573.7	657.9	755.3	852.1	945.5
55°	147.6	227.8	313.4	409.6	505.4	602.0	701.6	814.3	923.3	1032.2	1136.6
52.5°	207.0	295.9	400.8	505.4	611.4	725.2	850.0	973.2	1095.0	1211.2	1319.3
50°	264.6	374.4	486.7	602.0	725.2	862.0	998.3	1133.0	1260.3	1381.2	1502.3
47.5°	330.8	450.5	573.7	701.6	850.0	998.3	1145.8	1285.0	1418.7	1556.7	1690.4
45°	398.1	527.0	657.9	814.3	973.2	1133.0	1285.0	1431.3	1584.1	1722.4	1821.9
42.5°	462.8	601.7	755.3	923.3	1095.0	1260.3	1418.7	1584.1	1732.1	1841.7	1905.3
40°	527.8	673.8	852.1	1032.2	1211.2	1381.2	1556.7	1722.4	1841.7	1908.2	1941.2
37.5°	590.2	758.7	945.5	1136.6	1319.3	1502.3	1690.4	1821.9	1905.3	1941.2	2066.3
35°	649.5	839.4	1037.2	1233.9	1422.5	1621.8	1782.7	1896.4	1935.1	2054.8	2511.6
32.5°	713.6	915.7	1123.9	1324.4	1527.2	1724.6	1867.8	1923.2	2020.6	2316.2	3513.5
30°	778.7	990.0	1204.5	1409.7	1626.6	1799.5	1905.5	1964.2	2121.6	3214.5	4355.1
27.5°	839.4	1059.6	1277.7	1493.8	1713.7	1869.8	1927.7	2053.1	2723.1	4025.1	5092.3
25°	895.4	1123.9	1345.5	1573.3	1774.0	1901.6	1963.7	2136.0	3465.7	4672.2	5405.6
22.5°	947.7	1182.7	1407.5	1646.2	1829.4	1919.2	2034.7	2687.4	4097.4	5253.0	5597.7
20°	995.9	1233.9	1466.2	1708.6	1879.7	1935.3	2099.3	3269.4	4607.9	5416.9	5755.3
17.5°	1038.8	1279.5	1520.1	1749.8	1898.5	1968.2	2226.3	3792.2	5067.2	5564.7	5889.0
15°	1076.3	1319.3	1567.2	1785.9	1910.1	2015.0	2650.6	4178.2	5312.5	5689.4	6007.0
12.5°	1108.2	1353.3	1607.4	1816.7	1920.0	2055.1	3014.1	4499.1	5416.3	5783.7	6090.5
10°	1134.5	1381.2	1640.6	1842.1	1928.1	2088.2	3314.7	4764.9	5502.3	5862.1	6160.1
7.5°	1155.0	1403.1	1666.5	1862.0	1934.5	2114.2	3550.5	4973.6	5570.0	5923.8	6215.0
5°	1169.7	1418.7	1685.1	1876.2	1939.1	2132.8	3720.1	5123.8	5618.7	5968.3	6254.6
2.5°	1178.5	1428.2	1696.3	1884.8	1941.9	2144.0	3822.3	5214.3	5648.2	5995.2	6278.6
0°	1181.5	1431.3	1700.0	1887.7	1942.8	2147.8	3856.4	5244.6	5658.0	6004.2	6286.6
-2.5°	1178.5	1428.2	1696.3	1884.8	1941.9	2144.0	3822.3	5214.3	5648.2	5995.2	6278.6
-5°	1169.7	1418.7	1685.1	1876.2	1939.1	2132.8	3720.1	5123.8	5618.7	5968.3	6254.6
-7.5°	1155.0	1403.1	1666.5	1862.0	1934.5	2114.2	3550.5	4973.6	5570.0	5923.8	6215.0
-10°	1134.5	1381.2	1640.6	1842.1	1928.1	2088.2	3314.7	4764.9	5502.3	5862.1	6160.1
-12.5°	1108.2	1353.3	1607.4	1816.7	1920.0	2055.1	3014.1	4499.1	5416.3	5783.7	6090.5
-15°	1076.3	1319.3	1567.2	1785.9	1910.1	2015.0	2650.6	4178.2	5312.5	5689.4	6007.0
-17.5°	1038.8	1279.5	1520.1	1749.8	1898.5	1968.2	2226.3	3792.2	5067.2	5564.7	5889.0
-20°	995.9	1233.9	1466.2	1708.6	1879.7	1935.3	2099.3	3269.4	4607.9	5416.9	5755.3



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	947.7	1182.7	1407.5	1646.2	1829.4	1919.2	2034.7	2687.4	4097.4	5253.0	5597.7
-25°	895.4	1123.9	1345.5	1573.3	1774.0	1901.6	1963.7	2136.0	3465.7	4672.2	5405.6
-27.5°	839.4	1059.6	1277.7	1493.8	1713.7	1869.8	1927.7	2053.1	2723.1	4025.1	5092.3
-30°	778.7	990.0	1204.5	1409.7	1626.6	1799.5	1905.5	1964.2	2121.6	3214.5	4355.1
-32.5°	713.6	915.7	1123.9	1324.4	1527.2	1724.6	1867.8	1923.2	2020.6	2316.2	3513.5
-35°	649.5	839.4	1037.2	1233.9	1422.5	1621.8	1782.7	1896.4	1935.1	2054.8	2511.6
-37.5°	590.2	758.7	945.5	1136.6	1319.3	1502.3	1690.4	1821.9	1905.3	1941.2	2066.3
-40°	527.8	673.8	852.1	1032.2	1211.2	1381.2	1556.7	1722.4	1841.7	1908.2	1941.2
-42.5°	462.8	601.7	755.3	923.3	1095.0	1260.3	1418.7	1584.1	1732.1	1841.7	1905.3
-45°	398.1	527.0	657.9	814.3	973.2	1133.0	1285.0	1431.3	1584.1	1722.4	1821.9
-47.5°	330.8	450.5	573.7	701.6	850.0	998.3	1145.8	1285.0	1418.7	1556.7	1690.4
-50°	264.6	374.4	486.7	602.0	725.2	862.0	998.3	1133.0	1260.3	1381.2	1502.3
-52.5°	207.0	295.9	400.8	505.4	611.4	725.2	850.0	973.2	1095.0	1211.2	1319.3
-55°	147.6	227.8	313.4	409.6	505.4	602.0	701.6	814.3	923.3	1032.2	1136.6
-57.5°	107.8	161.5	234.8	313.4	400.8	486.7	573.7	657.9	755.3	852.1	945.5
-60°	79.1	110.9	161.5	227.8	295.9	374.4	450.5	527.0	601.7	673.8	758.7
-62.5°	53.5	79.1	107.8	147.6	207.0	264.6	330.8	398.1	462.8	527.8	590.2
-65°	44.8	52.6	72.7	98.3	123.1	172.5	223.2	272.1	329.1	385.3	438.8
-67.5°	35.9	42.9	49.8	60.2	82.5	104.2	125.2	168.6	210.8	251.2	292.3
-70°	30.0	33.7	39.3	45.3	51.1	60.7	79.4	97.3	114.6	137.3	171.3
-72.5°	24.7	27.9	31.0	34.1	38.9	43.9	48.7	53.3	63.8	78.2	91.9
-75°	20.6	22.2	24.8	27.4	29.9	32.4	35.0	38.9	42.7	46.3	49.7
-77.5°	17.5	18.8	20.1	21.4	22.7	24.8	26.8	28.7	30.5	32.2	33.9
-80°	14.7	15.5	16.5	17.5	18.4	19.4	20.3	21.2	22.0	23.1	24.4
-82.5°	12.3	12.9	13.5	14.0	14.6	15.1	15.7	16.3	16.9	17.5	18.1
-85°	9.5	10.3	10.7	11.1	11.4	11.8	12.1	12.4	12.8	13.1	13.3
-87.5°	4.8	5.1	5.5	5.9	6.3	6.6	7.0	7.3	7.6	7.9	8.2
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	8.4	8.7	8.9	9.1	9.3	9.5	9.7	9.8	9.9	10.1	10.1
85°	13.6	13.9	14.1	14.3	14.5	14.7	14.9	15.0	15.1	15.3	15.3
82.5°	18.6	19.1	19.6	20.0	20.5	20.8	21.1	21.4	21.7	21.9	22.1
80°	25.7	26.8	27.9	28.9	29.9	30.7	31.5	32.2	32.7	33.3	33.7
77.5°	36.2	38.7	41.1	43.2	45.3	47.1	48.8	50.2	51.5	52.6	53.5
75°	52.9	58.2	67.9	76.9	85.2	92.8	99.6	105.7	110.9	115.4	119.1
72.5°	104.8	117.0	131.5	154.5	175.7	195.0	212.4	227.8	241.3	252.8	262.2
70°	203.6	234.0	262.4	291.3	321.7	349.4	374.4	396.6	416.0	432.5	446.0
67.5°	337.8	380.7	420.8	458.2	493.9	527.0	556.9	583.5	606.7	626.4	642.7
65°	490.7	541.2	588.6	632.7	673.8	719.9	761.5	798.5	830.9	858.4	881.0
62.5°	649.5	713.6	778.7	839.4	895.4	947.7	995.9	1038.8	1076.3	1108.2	1134.5
60°	839.4	915.7	990.0	1059.6	1123.9	1182.7	1233.9	1279.5	1319.3	1353.3	1381.2
57.5°	1037.2	1123.9	1204.5	1277.7	1345.5	1407.5	1466.2	1520.1	1567.2	1607.4	1640.6
55°	1233.9	1324.4	1409.7	1493.8	1573.3	1646.2	1708.6	1749.8	1785.9	1816.7	1842.1
52.5°	1422.5	1527.2	1626.6	1713.7	1774.0	1829.4	1879.7	1898.5	1910.1	1920.0	1928.1
50°	1621.8	1724.6	1799.5	1869.8	1901.6	1919.2	1935.3	1968.2	2015.0	2055.1	2088.2
47.5°	1782.7	1867.8	1905.5	1927.7	1963.7	2034.7	2099.3	2226.3	2650.6	3014.1	3314.7
45°	1896.4	1923.2	1964.2	2053.1	2136.0	2687.4	3269.4	3792.2	4178.2	4499.1	4764.9
42.5°	1935.1	2020.6	2121.6	2723.1	3465.7	4097.4	4607.9	5067.2	5312.5	5416.3	5502.3
40°	2054.8	2316.2	3214.5	4025.1	4672.2	5253.0	5416.9	5564.7	5689.4	5783.7	5862.1
37.5°	2511.6	3513.5	4355.1	5092.3	5405.6	5597.7	5755.3	5889.0	6007.0	6090.5	6160.1
35°	3613.8	4522.0	5275.5	5509.5	5718.5	5891.0	6041.7	6159.4	6264.2	6300.4	6315.6
32.5°	4522.0	5301.1	5562.1	5786.2	5983.6	6138.2	6277.8	6310.5	6333.3	6342.3	6340.3
30°	5275.5	5562.1	5809.0	6025.7	6197.4	6301.2	6331.4	6341.6	6338.6	6327.4	6294.9
27.5°	5509.5	5786.2	6025.7	6217.3	6309.5	6343.4	6339.5	6325.4	6277.4	6235.2	6376.2
25°	5718.5	5983.6	6197.4	6309.5	6342.9	6338.4	6300.4	6242.7	6412.3	6596.0	7899.2
22.5°	5891.0	6138.2	6301.2	6343.4	6338.4	6291.9	6274.8	6522.8	7866.9	10123.1	14156.0
20°	6041.7	6277.8	6331.4	6339.5	6300.4	6274.8	6560.2	8750.3	12320.7	20732.4	28890.1
17.5°	6159.4	6310.5	6341.6	6325.4	6242.7	6522.8	8750.3	13928.5	24141.9	37674.8	50830.7
15°	6264.2	6333.3	6338.6	6277.4	6412.3	7866.9	12320.7	24141.9	40688.0	61274.5	86336.3
12.5°	6300.4	6342.3	6327.4	6235.2	6596.0	10123.1	20732.4	37674.8	61274.5	92423.3	130566.1
10°	6315.6	6340.3	6294.9	6376.2	7899.2	14156.0	28890.1	50830.7	86336.3	130566.1	178314.9
7.5°	6327.7	6338.7	6269.1	6489.6	9304.9	19458.4	38531.2	68782.1	112336.9	165901.6	229280.9
5°	6336.4	6337.5	6250.3	6572.4	10335.2	23367.5	45694.0	82671.1	134444.9	198420.1	272332.7
2.5°	6341.7	6336.8	6238.8	6622.8	10964.6	25765.7	50113.9	91311.8	148364.7	220634.1	300403.8
0°	6343.5	6336.6	6235.0	6639.7	11176.4	26574.3	51608.9	94247.7	153126.6	228536.9	310247.4
-2.5°	6341.7	6336.8	6238.8	6622.8	10964.6	25765.7	50113.9	91311.8	148364.7	220634.1	300403.8
-5°	6336.4	6337.5	6250.3	6572.4	10335.2	23367.5	45694.0	82671.1	134444.9	198420.1	272332.7
-7.5°	6327.7	6338.7	6269.1	6489.6	9304.9	19458.4	38531.2	68782.1	112336.9	165901.6	229280.9
-10°	6315.6	6340.3	6294.9	6376.2	7899.2	14156.0	28890.1	50830.7	86336.3	130566.1	178314.9
-12.5°	6300.4	6342.3	6327.4	6235.2	6596.0	10123.1	20732.4	37674.8	61274.5	92423.3	130566.1
-15°	6264.2	6333.3	6338.6	6277.4	6412.3	7866.9	12320.7	24141.9	40688.0	61274.5	86336.3
-17.5°	6159.4	6310.5	6341.6	6325.4	6242.7	6522.8	8750.3	13928.5	24141.9	37674.8	50830.7
-20°	6041.7	6277.8	6331.4	6339.5	6300.4	6274.8	6560.2	8750.3	12320.7	20732.4	28890.1



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	5891.0	6138.2	6301.2	6343.4	6338.4	6291.9	6274.8	6522.8	7866.9	10123.1	14156.0
-25°	5718.5	5983.6	6197.4	6309.5	6342.9	6338.4	6300.4	6242.7	6412.3	6596.0	7899.2
-27.5°	5509.5	5786.2	6025.7	6217.3	6309.5	6343.4	6339.5	6325.4	6277.4	6235.2	6376.2
-30°	5275.5	5562.1	5809.0	6025.7	6197.4	6301.2	6331.4	6341.6	6338.6	6327.4	6294.9
-32.5°	4522.0	5301.1	5562.1	5786.2	5983.6	6138.2	6277.8	6310.5	6333.3	6342.3	6340.3
-35°	3613.8	4522.0	5275.5	5509.5	5718.5	5891.0	6041.7	6159.4	6264.2	6300.4	6315.6
-37.5°	2511.6	3513.5	4355.1	5092.3	5405.6	5597.7	5755.3	5889.0	6007.0	6090.5	6160.1
-40°	2054.8	2316.2	3214.5	4025.1	4672.2	5253.0	5416.9	5564.7	5689.4	5783.7	5862.1
-42.5°	1935.1	2020.6	2121.6	2723.1	3465.7	4097.4	4607.9	5067.2	5312.5	5416.3	5502.3
-45°	1896.4	1923.2	1964.2	2053.1	2136.0	2687.4	3269.4	3792.2	4178.2	4499.1	4764.9
-47.5°	1782.7	1867.8	1905.5	1927.7	1963.7	2034.7	2099.3	2226.3	2650.6	3014.1	3314.7
-50°	1621.8	1724.6	1799.5	1869.8	1901.6	1919.2	1935.3	1968.2	2015.0	2055.1	2088.2
-52.5°	1422.5	1527.2	1626.6	1713.7	1774.0	1829.4	1879.7	1898.5	1910.1	1920.0	1928.1
-55°	1233.9	1324.4	1409.7	1493.8	1573.3	1646.2	1708.6	1749.8	1785.9	1816.7	1842.1
-57.5°	1037.2	1123.9	1204.5	1277.7	1345.5	1407.5	1466.2	1520.1	1567.2	1607.4	1640.6
-60°	839.4	915.7	990.0	1059.6	1123.9	1182.7	1233.9	1279.5	1319.3	1353.3	1381.2
-62.5°	649.5	713.6	778.7	839.4	895.4	947.7	995.9	1038.8	1076.3	1108.2	1134.5
-65°	490.7	541.2	588.6	632.7	673.8	719.9	761.5	798.5	830.9	858.4	881.0
-67.5°	337.8	380.7	420.8	458.2	493.9	527.0	556.9	583.5	606.7	626.4	642.7
-70°	203.6	234.0	262.4	291.3	321.7	349.4	374.4	396.6	416.0	432.5	446.0
-72.5°	104.8	117.0	131.5	154.5	175.7	195.0	212.4	227.8	241.3	252.8	262.2
-75°	52.9	58.2	67.9	76.9	85.2	92.8	99.6	105.7	110.9	115.4	119.1
-77.5°	36.2	38.7	41.1	43.2	45.3	47.1	48.8	50.2	51.5	52.6	53.5
-80°	25.7	26.8	27.9	28.9	29.9	30.7	31.5	32.2	32.7	33.3	33.7
-82.5°	18.6	19.1	19.6	20.0	20.5	20.8	21.1	21.4	21.7	21.9	22.1
-85°	13.6	13.9	14.1	14.3	14.5	14.7	14.9	15.0	15.1	15.3	15.3
-87.5°	8.4	8.7	8.9	9.1	9.3	9.5	9.7	9.8	9.9	10.1	10.1
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	10.2	10.3	10.3	10.3	10.3	10.3	10.2	10.1	10.1	9.9	9.8
85°	15.4	15.5	15.5	15.5	15.5	15.5	15.4	15.3	15.3	15.1	15.0
82.5°	22.2	22.3	22.4	22.4	22.4	22.3	22.2	22.1	21.9	21.7	21.4
80°	34.0	34.2	34.4	34.4	34.4	34.2	34.0	33.7	33.3	32.7	32.2
77.5°	54.2	54.7	55.0	55.1	55.0	54.7	54.2	53.5	52.6	51.5	50.2
75°	122.0	124.1	125.3	125.7	125.3	124.1	122.0	119.1	115.4	110.9	105.7
72.5°	269.5	274.8	277.9	279.0	277.9	274.8	269.5	262.2	252.8	241.3	227.8
70°	456.6	464.1	468.7	470.2	468.7	464.1	456.6	446.0	432.5	416.0	396.6
67.5°	655.3	664.4	669.9	671.7	669.9	664.4	655.3	642.7	626.4	606.7	583.5
65°	898.7	911.3	919.0	921.5	919.0	911.3	898.7	881.0	858.4	830.9	798.5
62.5°	1155.0	1169.7	1178.5	1181.5	1178.5	1169.7	1155.0	1134.5	1108.2	1076.3	1038.8
60°	1403.1	1418.7	1428.2	1431.3	1428.2	1418.7	1403.1	1381.2	1353.3	1319.3	1279.5
57.5°	1666.5	1685.1	1696.3	1700.0	1696.3	1685.1	1666.5	1640.6	1607.4	1567.2	1520.1
55°	1862.0	1876.2	1884.8	1887.7	1884.8	1876.2	1862.0	1842.1	1816.7	1785.9	1749.8
52.5°	1934.5	1939.1	1941.9	1942.8	1941.9	1939.1	1934.5	1928.1	1920.0	1910.1	1898.5
50°	2114.2	2132.8	2144.0	2147.8	2144.0	2132.8	2114.2	2088.2	2055.1	2015.0	1968.2
47.5°	3550.5	3720.1	3822.3	3856.4	3822.3	3720.1	3550.5	3314.7	3014.1	2650.6	2226.3
45°	4973.6	5123.8	5214.3	5244.6	5214.3	5123.8	4973.6	4764.9	4499.1	4178.2	3792.2
42.5°	5570.0	5618.7	5648.2	5658.0	5648.2	5618.7	5570.0	5502.3	5416.3	5312.5	5067.2
40°	5923.8	5968.3	5995.2	6004.2	5995.2	5968.3	5923.8	5862.1	5783.7	5689.4	5564.7
37.5°	6215.0	6254.6	6278.6	6286.6	6278.6	6254.6	6215.0	6160.1	6090.5	6007.0	5889.0
35°	6327.7	6336.4	6341.7	6343.5	6341.7	6336.4	6327.7	6315.6	6300.4	6264.2	6159.4
32.5°	6338.7	6337.5	6336.8	6336.6	6336.8	6337.5	6338.7	6340.3	6342.3	6333.3	6310.5
30°	6269.1	6250.3	6238.8	6235.0	6238.8	6250.3	6269.1	6294.9	6327.4	6338.6	6341.6
27.5°	6489.6	6572.4	6622.8	6639.7	6622.8	6572.4	6489.6	6376.2	6235.2	6277.4	6325.4
25°	9304.9	10335.2	10964.6	11176.4	10964.6	10335.2	9304.9	7899.2	6596.0	6412.3	6242.7
22.5°	19458.4	23367.5	25765.7	26574.3	25765.7	23367.5	19458.4	14156.0	10123.1	7866.9	6522.8
20°	38531.2	45694.0	50113.9	51608.9	50113.9	45694.0	38531.2	28890.1	20732.4	12320.7	8750.3
17.5°	68782.1	82671.1	91311.8	94247.7	91311.8	82671.1	68782.1	50830.7	37674.8	24141.9	13928.5
15°	112336.9	134444.9	148364.7	153126.6	148364.7	134444.9	112336.9	86336.3	61274.5	40688.0	24141.9
12.5°	165901.6	198420.1	220634.1	228536.9	220634.1	198420.1	165901.6	130566.1	92423.3	61274.5	37674.8
10°	229280.9	272332.7	300403.8	310247.4	300403.8	272332.7	229280.9	178314.9	130566.1	86336.3	50830.7
7.5°	291140.1	342252.2	379953.7	393598.6	379953.7	342252.2	291140.1	229280.9	165901.6	112336.9	68782.1
5°	342252.2	408257.9	448729.4	461522.5	448729.4	408257.9	342252.2	272332.7	198420.1	134444.9	82671.1
2.5°	379953.7	448729.4	492478.4	515162.9	492478.4	448729.4	379953.7	300403.8	220634.1	148364.7	91311.8
0°	393598.6	461522.5	515162.9	553667.2	515162.9	461522.5	393598.6	310247.4	228536.9	153126.6	94247.7
-2.5°	379953.7	448729.4	492478.4	515162.9	492478.4	448729.4	379953.7	300403.8	220634.1	148364.7	91311.8
-5°	342252.2	408257.9	448729.4	461522.5	448729.4	408257.9	342252.2	272332.7	198420.1	134444.9	82671.1
-7.5°	291140.1	342252.2	379953.7	393598.6	379953.7	342252.2	291140.1	229280.9	165901.6	112336.9	68782.1
-10°	229280.9	272332.7	300403.8	310247.4	300403.8	272332.7	229280.9	178314.9	130566.1	86336.3	50830.7
-12.5°	165901.6	198420.1	220634.1	228536.9	220634.1	198420.1	165901.6	130566.1	92423.3	61274.5	37674.8
-15°	112336.9	134444.9	148364.7	153126.6	148364.7	134444.9	112336.9	86336.3	61274.5	40688.0	24141.9
-17.5°	68782.1	82671.1	91311.8	94247.7	91311.8	82671.1	68782.1	50830.7	37674.8	24141.9	13928.5
-20°	38531.2	45694.0	50113.9	51608.9	50113.9	45694.0	38531.2	28890.1	20732.4	12320.7	8750.3



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	19458.4	23367.5	25765.7	26574.3	25765.7	23367.5	19458.4	14156.0	10123.1	7866.9	6522.8
-25°	9304.9	10335.2	10964.6	11176.4	10964.6	10335.2	9304.9	7899.2	6596.0	6412.3	6242.7
-27.5°	6489.6	6572.4	6622.8	6639.7	6622.8	6572.4	6489.6	6376.2	6235.2	6277.4	6325.4
-30°	6269.1	6250.3	6238.8	6235.0	6238.8	6250.3	6269.1	6294.9	6327.4	6338.6	6341.6
-32.5°	6338.7	6337.5	6336.8	6336.6	6336.8	6337.5	6338.7	6340.3	6342.3	6333.3	6310.5
-35°	6327.7	6336.4	6341.7	6343.5	6341.7	6336.4	6327.7	6315.6	6300.4	6264.2	6159.4
-37.5°	6215.0	6254.6	6278.6	6286.6	6278.6	6254.6	6215.0	6160.1	6090.5	6007.0	5889.0
-40°	5923.8	5968.3	5995.2	6004.2	5995.2	5968.3	5923.8	5862.1	5783.7	5689.4	5564.7
-42.5°	5570.0	5618.7	5648.2	5658.0	5648.2	5618.7	5570.0	5502.3	5416.3	5312.5	5067.2
-45°	4973.6	5123.8	5214.3	5244.6	5214.3	5123.8	4973.6	4764.9	4499.1	4178.2	3792.2
-47.5°	3550.5	3720.1	3822.3	3856.4	3822.3	3720.1	3550.5	3314.7	3014.1	2650.6	2226.3
-50°	2114.2	2132.8	2144.0	2147.8	2144.0	2132.8	2114.2	2088.2	2055.1	2015.0	1968.2
-52.5°	1934.5	1939.1	1941.9	1942.8	1941.9	1939.1	1934.5	1928.1	1920.0	1910.1	1898.5
-55°	1862.0	1876.2	1884.8	1887.7	1884.8	1876.2	1862.0	1842.1	1816.7	1785.9	1749.8
-57.5°	1666.5	1685.1	1696.3	1700.0	1696.3	1685.1	1666.5	1640.6	1607.4	1567.2	1520.1
-60°	1403.1	1418.7	1428.2	1431.3	1428.2	1418.7	1403.1	1381.2	1353.3	1319.3	1279.5
-62.5°	1155.0	1169.7	1178.5	1181.5	1178.5	1169.7	1155.0	1134.5	1108.2	1076.3	1038.8
-65°	898.7	911.3	919.0	921.5	919.0	911.3	898.7	881.0	858.4	830.9	798.5
-67.5°	655.3	664.4	669.9	671.7	669.9	664.4	655.3	642.7	626.4	606.7	583.5
-70°	456.6	464.1	468.7	470.2	468.7	464.1	456.6	446.0	432.5	416.0	396.6
-72.5°	269.5	274.8	277.9	279.0	277.9	274.8	269.5	262.2	252.8	241.3	227.8
-75°	122.0	124.1	125.3	125.7	125.3	124.1	122.0	119.1	115.4	110.9	105.7
-77.5°	54.2	54.7	55.0	55.1	55.0	54.7	54.2	53.5	52.6	51.5	50.2
-80°	34.0	34.2	34.4	34.4	34.4	34.2	34.0	33.7	33.3	32.7	32.2
-82.5°	22.2	22.3	22.4	22.4	22.4	22.3	22.2	22.1	21.9	21.7	21.4
-85°	15.4	15.5	15.5	15.5	15.5	15.5	15.4	15.3	15.3	15.1	15.0
-87.5°	10.2	10.3	10.3	10.3	10.3	10.3	10.2	10.1	10.1	9.9	9.8
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	9.7	9.5	9.3	9.1	8.9	8.7	8.4	8.2	7.9	7.6	7.3
85°	14.9	14.7	14.5	14.3	14.1	13.9	13.6	13.3	13.1	12.8	12.4
82.5°	21.1	20.8	20.5	20.0	19.6	19.1	18.6	18.1	17.5	16.9	16.3
80°	31.5	30.7	29.9	28.9	27.9	26.8	25.7	24.4	23.1	22.0	21.2
77.5°	48.8	47.1	45.3	43.2	41.1	38.7	36.2	33.9	32.2	30.5	28.7
75°	99.6	92.8	85.2	76.9	67.9	58.2	52.9	49.7	46.3	42.7	38.9
72.5°	212.4	195.0	175.7	154.5	131.5	117.0	104.8	91.9	78.2	63.8	53.3
70°	374.4	349.4	321.7	291.3	262.4	234.0	203.6	171.3	137.3	114.6	97.3
67.5°	556.9	527.0	493.9	458.2	420.8	380.7	337.8	292.3	251.2	210.8	168.6
65°	761.5	719.9	673.8	632.7	588.6	541.2	490.7	438.8	385.3	329.1	272.1
62.5°	995.9	947.7	895.4	839.4	778.7	713.6	649.5	590.2	527.8	462.8	398.1
60°	1233.9	1182.7	1123.9	1059.6	990.0	915.7	839.4	758.7	673.8	601.7	527.0
57.5°	1466.2	1407.5	1345.5	1277.7	1204.5	1123.9	1037.2	945.5	852.1	755.3	657.9
55°	1708.6	1646.2	1573.3	1493.8	1409.7	1324.4	1233.9	1136.6	1032.2	923.3	814.3
52.5°	1879.7	1829.4	1774.0	1713.7	1626.6	1527.2	1422.5	1319.3	1211.2	1095.0	973.2
50°	1935.3	1919.2	1901.6	1869.8	1799.5	1724.6	1621.8	1502.3	1381.2	1260.3	1133.0
47.5°	2099.3	2034.7	1963.7	1927.7	1905.5	1867.8	1782.7	1690.4	1556.7	1418.7	1285.0
45°	3269.4	2687.4	2136.0	2053.1	1964.2	1923.2	1896.4	1821.9	1722.4	1584.1	1431.3
42.5°	4607.9	4097.4	3465.7	2723.1	2121.6	2020.6	1935.1	1905.3	1841.7	1732.1	1584.1
40°	5416.9	5253.0	4672.2	4025.1	3214.5	2316.2	2054.8	1941.2	1908.2	1841.7	1722.4
37.5°	5755.3	5597.7	5405.6	5092.3	4355.1	3513.5	2511.6	2066.3	1941.2	1905.3	1821.9
35°	6041.7	5891.0	5718.5	5509.5	5275.5	4522.0	3613.8	2511.6	2054.8	1935.1	1896.4
32.5°	6277.8	6138.2	5983.6	5786.2	5562.1	5301.1	4522.0	3513.5	2316.2	2020.6	1923.2
30°	6331.4	6301.2	6197.4	6025.7	5809.0	5562.1	5275.5	4355.1	3214.5	2121.6	1964.2
27.5°	6339.5	6343.4	6309.5	6217.3	6025.7	5786.2	5509.5	5092.3	4025.1	2723.1	2053.1
25°	6300.4	6338.4	6342.9	6309.5	6197.4	5983.6	5718.5	5405.6	4672.2	3465.7	2136.0
22.5°	6274.8	6291.9	6338.4	6343.4	6301.2	6138.2	5891.0	5597.7	5253.0	4097.4	2687.4
20°	6560.2	6274.8	6300.4	6339.5	6331.4	6277.8	6041.7	5755.3	5416.9	4607.9	3269.4
17.5°	8750.3	6522.8	6242.7	6325.4	6341.6	6310.5	6159.4	5889.0	5564.7	5067.2	3792.2
15°	12320.7	7866.9	6412.3	6277.4	6338.6	6333.3	6264.2	6007.0	5689.4	5312.5	4178.2
12.5°	20732.4	10123.1	6596.0	6235.2	6327.4	6342.3	6300.4	6090.5	5783.7	5416.3	4499.1
10°	28890.1	14156.0	7899.2	6376.2	6294.9	6340.3	6315.6	6160.1	5862.1	5502.3	4764.9
7.5°	38531.2	19458.4	9304.9	6489.6	6269.1	6338.7	6327.7	6215.0	5923.8	5570.0	4973.6
5°	45694.0	23367.5	10335.2	6572.4	6250.3	6337.5	6336.4	6254.6	5968.3	5618.7	5123.8
2.5°	50113.9	25765.7	10964.6	6622.8	6238.8	6336.8	6341.7	6278.6	5995.2	5648.2	5214.3
0°	51608.9	26574.3	11176.4	6639.7	6235.0	6336.6	6343.5	6286.6	6004.2	5658.0	5244.6
-2.5°	50113.9	25765.7	10964.6	6622.8	6238.8	6336.8	6341.7	6278.6	5995.2	5648.2	5214.3
-5°	45694.0	23367.5	10335.2	6572.4	6250.3	6337.5	6336.4	6254.6	5968.3	5618.7	5123.8
-7.5°	38531.2	19458.4	9304.9	6489.6	6269.1	6338.7	6327.7	6215.0	5923.8	5570.0	4973.6
-10°	28890.1	14156.0	7899.2	6376.2	6294.9	6340.3	6315.6	6160.1	5862.1	5502.3	4764.9
-12.5°	20732.4	10123.1	6596.0	6235.2	6327.4	6342.3	6300.4	6090.5	5783.7	5416.3	4499.1
-15°	12320.7	7866.9	6412.3	6277.4	6338.6	6333.3	6264.2	6007.0	5689.4	5312.5	4178.2
-17.5°	8750.3	6522.8	6242.7	6325.4	6341.6	6310.5	6159.4	5889.0	5564.7	5067.2	3792.2
-20°	6560.2	6274.8	6300.4	6339.5	6331.4	6277.8	6041.7	5755.3	5416.9	4607.9	3269.4



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	6274.8	6291.9	6338.4	6343.4	6301.2	6138.2	5891.0	5597.7	5253.0	4097.4	2687.4
-25°	6300.4	6338.4	6342.9	6309.5	6197.4	5983.6	5718.5	5405.6	4672.2	3465.7	2136.0
-27.5°	6339.5	6343.4	6309.5	6217.3	6025.7	5786.2	5509.5	5092.3	4025.1	2723.1	2053.1
-30°	6331.4	6301.2	6197.4	6025.7	5809.0	5562.1	5275.5	4355.1	3214.5	2121.6	1964.2
-32.5°	6277.8	6138.2	5983.6	5786.2	5562.1	5301.1	4522.0	3513.5	2316.2	2020.6	1923.2
-35°	6041.7	5891.0	5718.5	5509.5	5275.5	4522.0	3613.8	2511.6	2054.8	1935.1	1896.4
-37.5°	5755.3	5597.7	5405.6	5092.3	4355.1	3513.5	2511.6	2066.3	1941.2	1905.3	1821.9
-40°	5416.9	5253.0	4672.2	4025.1	3214.5	2316.2	2054.8	1941.2	1908.2	1841.7	1722.4
-42.5°	4607.9	4097.4	3465.7	2723.1	2121.6	2020.6	1935.1	1905.3	1841.7	1732.1	1584.1
-45°	3269.4	2687.4	2136.0	2053.1	1964.2	1923.2	1896.4	1821.9	1722.4	1584.1	1431.3
-47.5°	2099.3	2034.7	1963.7	1927.7	1905.5	1867.8	1782.7	1690.4	1556.7	1418.7	1285.0
-50°	1935.3	1919.2	1901.6	1869.8	1799.5	1724.6	1621.8	1502.3	1381.2	1260.3	1133.0
-52.5°	1879.7	1829.4	1774.0	1713.7	1626.6	1527.2	1422.5	1319.3	1211.2	1095.0	973.2
-55°	1708.6	1646.2	1573.3	1493.8	1409.7	1324.4	1233.9	1136.6	1032.2	923.3	814.3
-57.5°	1466.2	1407.5	1345.5	1277.7	1204.5	1123.9	1037.2	945.5	852.1	755.3	657.9
-60°	1233.9	1182.7	1123.9	1059.6	990.0	915.7	839.4	758.7	673.8	601.7	527.0
-62.5°	995.9	947.7	895.4	839.4	778.7	713.6	649.5	590.2	527.8	462.8	398.1
-65°	761.5	719.9	673.8	632.7	588.6	541.2	490.7	438.8	385.3	329.1	272.1
-67.5°	556.9	527.0	493.9	458.2	420.8	380.7	337.8	292.3	251.2	210.8	168.6
-70°	374.4	349.4	321.7	291.3	262.4	234.0	203.6	171.3	137.3	114.6	97.3
-72.5°	212.4	195.0	175.7	154.5	131.5	117.0	104.8	91.9	78.2	63.8	53.3
-75°	99.6	92.8	85.2	76.9	67.9	58.2	52.9	49.7	46.3	42.7	38.9
-77.5°	48.8	47.1	45.3	43.2	41.1	38.7	36.2	33.9	32.2	30.5	28.7
-80°	31.5	30.7	29.9	28.9	27.9	26.8	25.7	24.4	23.1	22.0	21.2
-82.5°	21.1	20.8	20.5	20.0	19.6	19.1	18.6	18.1	17.5	16.9	16.3
-85°	14.9	14.7	14.5	14.3	14.1	13.9	13.6	13.3	13.1	12.8	12.4
-87.5°	9.7	9.5	9.3	9.1	8.9	8.7	8.4	8.2	7.9	7.6	7.3
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0





REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	7.0	6.6	6.3	5.9	5.5	5.1	4.8	4.4	3.9	3.5	3.1
85°	12.1	11.8	11.4	11.1	10.7	10.3	9.5	8.7	7.9	7.0	6.2
82.5°	15.7	15.1	14.6	14.0	13.5	12.9	12.3	11.7	11.1	10.4	9.3
80°	20.3	19.4	18.4	17.5	16.5	15.5	14.7	13.9	13.0	12.2	11.3
77.5°	26.8	24.8	22.7	21.4	20.1	18.8	17.5	16.2	15.0	13.9	12.9
75°	35.0	32.4	29.9	27.4	24.8	22.2	20.6	19.0	17.4	15.7	14.4
72.5°	48.7	43.9	38.9	34.1	31.0	27.9	24.7	21.9	19.9	18.0	16.0
70°	79.4	60.7	51.1	45.3	39.3	33.7	30.0	26.3	22.5	20.2	18.0
67.5°	125.2	104.2	82.5	60.2	49.8	42.9	35.9	31.1	26.8	22.5	19.9
65°	223.2	172.5	123.1	98.3	72.7	52.6	44.8	36.8	31.1	26.3	21.9
62.5°	330.8	264.6	207.0	147.6	107.8	79.1	53.5	44.8	35.9	30.0	24.7
60°	450.5	374.4	295.9	227.8	161.5	110.9	79.1	52.6	42.9	33.7	27.9
57.5°	573.7	486.7	400.8	313.4	234.8	161.5	107.8	72.7	49.8	39.3	31.0
55°	701.6	602.0	505.4	409.6	313.4	227.8	147.6	98.3	60.2	45.3	34.1
52.5°	850.0	725.2	611.4	505.4	400.8	295.9	207.0	123.1	82.5	51.1	38.9
50°	998.3	862.0	725.2	602.0	486.7	374.4	264.6	172.5	104.2	60.7	43.9
47.5°	1145.8	998.3	850.0	701.6	573.7	450.5	330.8	223.2	125.2	79.4	48.7
45°	1285.0	1133.0	973.2	814.3	657.9	527.0	398.1	272.1	168.6	97.3	53.3
42.5°	1418.7	1260.3	1095.0	923.3	755.3	601.7	462.8	329.1	210.8	114.6	63.8
40°	1556.7	1381.2	1211.2	1032.2	852.1	673.8	527.8	385.3	251.2	137.3	78.2
37.5°	1690.4	1502.3	1319.3	1136.6	945.5	758.7	590.2	438.8	292.3	171.3	91.9
35°	1782.7	1621.8	1422.5	1233.9	1037.2	839.4	649.5	490.7	337.8	203.6	104.8
32.5°	1867.8	1724.6	1527.2	1324.4	1123.9	915.7	713.6	541.2	380.7	234.0	117.0
30°	1905.5	1799.5	1626.6	1409.7	1204.5	990.0	778.7	588.6	420.8	262.4	131.5
27.5°	1927.7	1869.8	1713.7	1493.8	1277.7	1059.6	839.4	632.7	458.2	291.3	154.5
25°	1963.7	1901.6	1774.0	1573.3	1345.5	1123.9	895.4	673.8	493.9	321.7	175.7
22.5°	2034.7	1919.2	1829.4	1646.2	1407.5	1182.7	947.7	719.9	527.0	349.4	195.0
20°	2099.3	1935.3	1879.7	1708.6	1466.2	1233.9	995.9	761.5	556.9	374.4	212.4
17.5°	2226.3	1968.2	1898.5	1749.8	1520.1	1279.5	1038.8	798.5	583.5	396.6	227.8
15°	2650.6	2015.0	1910.1	1785.9	1567.2	1319.3	1076.3	830.9	606.7	416.0	241.3
12.5°	3014.1	2055.1	1920.0	1816.7	1607.4	1353.3	1108.2	858.4	626.4	432.5	252.8
10°	3314.7	2088.2	1928.1	1842.1	1640.6	1381.2	1134.5	881.0	642.7	446.0	262.2
7.5°	3550.5	2114.2	1934.5	1862.0	1666.5	1403.1	1155.0	898.7	655.3	456.6	269.5
5°	3720.1	2132.8	1939.1	1876.2	1685.1	1418.7	1169.7	911.3	664.4	464.1	274.8
2.5°	3822.3	2144.0	1941.9	1884.8	1696.3	1428.2	1178.5	919.0	669.9	468.7	277.9
0°	3856.4	2147.8	1942.8	1887.7	1700.0	1431.3	1181.5	921.5	671.7	470.2	279.0
-2.5°	3822.3	2144.0	1941.9	1884.8	1696.3	1428.2	1178.5	919.0	669.9	468.7	277.9
-5°	3720.1	2132.8	1939.1	1876.2	1685.1	1418.7	1169.7	911.3	664.4	464.1	274.8
-7.5°	3550.5	2114.2	1934.5	1862.0	1666.5	1403.1	1155.0	898.7	655.3	456.6	269.5
-10°	3314.7	2088.2	1928.1	1842.1	1640.6	1381.2	1134.5	881.0	642.7	446.0	262.2
-12.5°	3014.1	2055.1	1920.0	1816.7	1607.4	1353.3	1108.2	858.4	626.4	432.5	252.8
-15°	2650.6	2015.0	1910.1	1785.9	1567.2	1319.3	1076.3	830.9	606.7	416.0	241.3
-17.5°	2226.3	1968.2	1898.5	1749.8	1520.1	1279.5	1038.8	798.5	583.5	396.6	227.8
-20°	2099.3	1935.3	1879.7	1708.6	1466.2	1233.9	995.9	761.5	556.9	374.4	212.4



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	2034.7	1919.2	1829.4	1646.2	1407.5	1182.7	947.7	719.9	527.0	349.4	195.0
-25°	1963.7	1901.6	1774.0	1573.3	1345.5	1123.9	895.4	673.8	493.9	321.7	175.7
-27.5°	1927.7	1869.8	1713.7	1493.8	1277.7	1059.6	839.4	632.7	458.2	291.3	154.5
-30°	1905.5	1799.5	1626.6	1409.7	1204.5	990.0	778.7	588.6	420.8	262.4	131.5
-32.5°	1867.8	1724.6	1527.2	1324.4	1123.9	915.7	713.6	541.2	380.7	234.0	117.0
-35°	1782.7	1621.8	1422.5	1233.9	1037.2	839.4	649.5	490.7	337.8	203.6	104.8
-37.5°	1690.4	1502.3	1319.3	1136.6	945.5	758.7	590.2	438.8	292.3	171.3	91.9
-40°	1556.7	1381.2	1211.2	1032.2	852.1	673.8	527.8	385.3	251.2	137.3	78.2
-42.5°	1418.7	1260.3	1095.0	923.3	755.3	601.7	462.8	329.1	210.8	114.6	63.8
-45°	1285.0	1133.0	973.2	814.3	657.9	527.0	398.1	272.1	168.6	97.3	53.3
-47.5°	1145.8	998.3	850.0	701.6	573.7	450.5	330.8	223.2	125.2	79.4	48.7
-50°	998.3	862.0	725.2	602.0	486.7	374.4	264.6	172.5	104.2	60.7	43.9
-52.5°	850.0	725.2	611.4	505.4	400.8	295.9	207.0	123.1	82.5	51.1	38.9
-55°	701.6	602.0	505.4	409.6	313.4	227.8	147.6	98.3	60.2	45.3	34.1
-57.5°	573.7	486.7	400.8	313.4	234.8	161.5	107.8	72.7	49.8	39.3	31.0
-60°	450.5	374.4	295.9	227.8	161.5	110.9	79.1	52.6	42.9	33.7	27.9
-62.5°	330.8	264.6	207.0	147.6	107.8	79.1	53.5	44.8	35.9	30.0	24.7
-65°	223.2	172.5	123.1	98.3	72.7	52.6	44.8	36.8	31.1	26.3	21.9
-67.5°	125.2	104.2	82.5	60.2	49.8	42.9	35.9	31.1	26.8	22.5	19.9
-70°	79.4	60.7	51.1	45.3	39.3	33.7	30.0	26.3	22.5	20.2	18.0
-72.5°	48.7	43.9	38.9	34.1	31.0	27.9	24.7	21.9	19.9	18.0	16.0
-75°	35.0	32.4	29.9	27.4	24.8	22.2	20.6	19.0	17.4	15.7	14.4
-77.5°	26.8	24.8	22.7	21.4	20.1	18.8	17.5	16.2	15.0	13.9	12.9
-80°	20.3	19.4	18.4	17.5	16.5	15.5	14.7	13.9	13.0	12.2	11.3
-82.5°	15.7	15.1	14.6	14.0	13.5	12.9	12.3	11.7	11.1	10.4	9.3
-85°	12.1	11.8	11.4	11.1	10.7	10.3	9.5	8.7	7.9	7.0	6.2
-87.5°	7.0	6.6	6.3	5.9	5.5	5.1	4.8	4.4	3.9	3.5	3.1
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	2.7	2.2	1.8	1.3	0.9	0.4	0.0
85°	5.3	4.5	3.6	2.7	1.8	0.9	0.0
82.5°	8.0	6.7	5.4	4.0	2.7	1.3	0.0
80°	10.5	8.9	7.1	5.4	3.6	1.8	0.0
77.5°	11.8	10.7	8.9	6.7	4.5	2.2	0.0
75°	13.1	11.8	10.5	8.0	5.3	2.7	0.0
72.5°	14.4	12.9	11.3	9.3	6.2	3.1	0.0
70°	15.7	13.9	12.2	10.4	7.0	3.5	0.0
67.5°	17.4	15.0	13.0	11.1	7.9	3.9	0.0
65°	19.0	16.2	13.9	11.7	8.7	4.4	0.0
62.5°	20.6	17.5	14.7	12.3	9.5	4.8	0.0
60°	22.2	18.8	15.5	12.9	10.3	5.1	0.0
57.5°	24.8	20.1	16.5	13.5	10.7	5.5	0.0
55°	27.4	21.4	17.5	14.0	11.1	5.9	0.0
52.5°	29.9	22.7	18.4	14.6	11.4	6.3	0.0
50°	32.4	24.8	19.4	15.1	11.8	6.6	0.0
47.5°	35.0	26.8	20.3	15.7	12.1	7.0	0.0
45°	38.9	28.7	21.2	16.3	12.4	7.3	0.0
42.5°	42.7	30.5	22.0	16.9	12.8	7.6	0.0
40°	46.3	32.2	23.1	17.5	13.1	7.9	0.0
37.5°	49.7	33.9	24.4	18.1	13.3	8.2	0.0
35°	52.9	36.2	25.7	18.6	13.6	8.4	0.0
32.5°	58.2	38.7	26.8	19.1	13.9	8.7	0.0
30°	67.9	41.1	27.9	19.6	14.1	8.9	0.0
27.5°	76.9	43.2	28.9	20.0	14.3	9.1	0.0
25°	85.2	45.3	29.9	20.5	14.5	9.3	0.0
22.5°	92.8	47.1	30.7	20.8	14.7	9.5	0.0
20°	99.6	48.8	31.5	21.1	14.9	9.7	0.0
17.5°	105.7	50.2	32.2	21.4	15.0	9.8	0.0
15°	110.9	51.5	32.7	21.7	15.1	9.9	0.0
12.5°	115.4	52.6	33.3	21.9	15.3	10.1	0.0
10°	119.1	53.5	33.7	22.1	15.3	10.1	0.0
7.5°	122.0	54.2	34.0	22.2	15.4	10.2	0.0
5°	124.1	54.7	34.2	22.3	15.5	10.3	0.0
2.5°	125.3	55.0	34.4	22.4	15.5	10.3	0.0
0°	125.7	55.1	34.4	22.4	15.5	10.3	0.0
-2.5°	125.3	55.0	34.4	22.4	15.5	10.3	0.0
-5°	124.1	54.7	34.2	22.3	15.5	10.3	0.0
-7.5°	122.0	54.2	34.0	22.2	15.4	10.2	0.0
-10°	119.1	53.5	33.7	22.1	15.3	10.1	0.0
-12.5°	115.4	52.6	33.3	21.9	15.3	10.1	0.0
-15°	110.9	51.5	32.7	21.7	15.1	9.9	0.0
-17.5°	105.7	50.2	32.2	21.4	15.0	9.8	0.0
-20°	99.6	48.8	31.5	21.1	14.9	9.7	0.0



REPORT NUMBER: P701494 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: EPH-LS-08-0680R-57-80-2S-HEG-S

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	92.8	47.1	30.7	20.8	14.7	9.5	0.0
-25°	85.2	45.3	29.9	20.5	14.5	9.3	0.0
-27.5°	76.9	43.2	28.9	20.0	14.3	9.1	0.0
-30°	67.9	41.1	27.9	19.6	14.1	8.9	0.0
-32.5°	58.2	38.7	26.8	19.1	13.9	8.7	0.0
-35°	52.9	36.2	25.7	18.6	13.6	8.4	0.0
-37.5°	49.7	33.9	24.4	18.1	13.3	8.2	0.0
-40°	46.3	32.2	23.1	17.5	13.1	7.9	0.0
-42.5°	42.7	30.5	22.0	16.9	12.8	7.6	0.0
-45°	38.9	28.7	21.2	16.3	12.4	7.3	0.0
-47.5°	35.0	26.8	20.3	15.7	12.1	7.0	0.0
-50°	32.4	24.8	19.4	15.1	11.8	6.6	0.0
-52.5°	29.9	22.7	18.4	14.6	11.4	6.3	0.0
-55°	27.4	21.4	17.5	14.0	11.1	5.9	0.0
-57.5°	24.8	20.1	16.5	13.5	10.7	5.5	0.0
-60°	22.2	18.8	15.5	12.9	10.3	5.1	0.0
-62.5°	20.6	17.5	14.7	12.3	9.5	4.8	0.0
-65°	19.0	16.2	13.9	11.7	8.7	4.4	0.0
-67.5°	17.4	15.0	13.0	11.1	7.9	3.9	0.0
-70°	15.7	13.9	12.2	10.4	7.0	3.5	0.0
-72.5°	14.4	12.9	11.3	9.3	6.2	3.1	0.0
-75°	13.1	11.8	10.5	8.0	5.3	2.7	0.0
-77.5°	11.8	10.7	8.9	6.7	4.5	2.2	0.0
-80°	10.5	8.9	7.1	5.4	3.6	1.8	0.0
-82.5°	8.0	6.7	5.4	4.0	2.7	1.3	0.0
-85°	5.3	4.5	3.6	2.7	1.8	0.9	0.0
-87.5°	2.7	2.2	1.8	1.3	0.9	0.4	0.0
-90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Horizontal Angle (degrees)



Horizontal Angle (degrees)



Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report

