

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: EPHESUS

Report Number: P575009

Luminaire Tested: **EPH-VN-03-735-U-SL3**

Issue Date: 10/19/2021



**Test Information**

Test Method: LM-79-08  
Report Number: P575009  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 10/19/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: EPHEBUS  
Catalog Number: EPH-VN-03-735-U-SL3  
Description: EPHEBUS LUMAVISION – Middle Tier Light Square Luminaire w/ SL3 distribution lens  
Light Source: (48) 3500K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 26250.7 lumens  
Efficiency: N/A  
Efficacy: 113.1 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 0.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B3 - U0 - G4

Input Watts (W): 232.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

REPORT NUMBER: P575009  
 CATALOG NUMBER: EPH-VN-03-735-U-SL3

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 11.5 fc  
 Type III - Short - N/A

REPORT NUMBER: P575009  
CATALOG NUMBER: EPH-VN-03-735-U-SL3

### Luminous Intensity Polar Plot



— Vertical Plane Through 57-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P575009  
 CATALOG NUMBER: EPH-VN-03-735-U-SL3


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	4025.8	0.0	4025.8
	% Fixture	15.3	0.0	15.3
<b>Street Side</b>	Lumens	22224.9	0.0	22224.9
	% Fixture	84.7	0.0	84.7
<b>Total</b>	Lumens	26250.7	0.0	26250.7
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	604.5	2.3
10°-20°	1301.0	5.0
20°-30°	1682.0	6.4
30°-40°	2263.5	8.6
40°-50°	3609.2	13.7
50°-60°	6374.8	24.3
60°-70°	7013.1	26.7
70°-80°	2933.7	11.2
80°-90°	468.9	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	26250.7	100.0
0°-180°	26250.7	100.0

**Coefficient of Utilization**




REPORT NUMBER: P575009  
 CATALOG NUMBER: EPH-VN-03-735-U-SL3

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2395.3	9.1			
FM (30°-60°)	10579.0	40.3			
FH (60°-80°)	8836.8	33.7			G4/12000
FVH (80°-90°)	413.9	1.6			G3/500
BL (0°-30°)	1192.2	4.5	B3/2500		
BM (30°-60°)	1668.5	6.4	B2/2500		
BH (60°-80°)	1110.0	4.2	B3/2500		G3/2500
BVH (80°-90°)	55.0	0.2			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G4**  
 Type III Short





REPORT NUMBER: P575009  
 CATALOG NUMBER: EPH-VN-03-735-U-SL3

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	57°	65°	75°
0°	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6
2.5°	7413.5	7425.3	7425.3	7448.9	7369.2	7407.6	7401.7	7366.2	7378.1	7316.0
5°	7203.8	7194.9	7242.2	7248.1	7310.1	7327.8	7342.6	7319.0	7324.9	7189.0
7.5°	6666.2	6663.3	6743.0	6811.0	6940.9	7062.0	7141.8	7118.1	7150.6	7065.0
10°	6028.3	6096.2	6178.9	6246.8	6486.1	6639.7	6846.4	6867.1	6991.1	6970.5
12.5°	5549.8	5579.3	5641.3	5836.3	6054.8	6308.9	6604.2	6630.8	6751.9	6811.0
15°	5157.0	5183.5	5263.3	5408.0	5653.2	5954.4	6329.5	6397.5	6639.7	6660.3
17.5°	4870.5	4891.1	4944.3	5089.0	5289.9	5676.8	6031.2	6152.3	6471.3	6571.7
20°	4758.2	4713.9	4743.5	4835.0	5035.9	5334.2	5792.0	5898.3	6305.9	6503.8
22.5°	4708.0	4669.6	4687.3	4681.4	4840.9	5053.6	5535.0	5647.3	6149.4	6424.0
25°	4746.4	4746.4	4728.7	4713.9	4731.6	4870.5	5257.4	5431.6	5939.7	6356.1
27.5°	4953.2	4873.4	4882.3	4820.3	4802.5	4802.5	5133.3	5236.7	5871.7	6317.7
30°	5086.1	5124.5	5127.4	5035.9	4944.3	4778.9	5018.1	5118.6	5815.6	6365.0
32.5°	5425.7	5408.0	5357.8	5340.1	5204.2	5018.1	5074.3	5142.2	5783.1	6471.3
35°	5765.4	5756.5	5759.5	5750.6	5608.9	5334.2	5224.9	5316.5	5842.2	6657.4
37.5°	6116.9	6140.5	6240.9	6240.9	6090.3	5792.0	5647.3	5620.7	6057.8	6961.6
40°	6468.4	6527.4	6654.4	6855.3	6642.6	6365.0	6131.6	6090.3	6317.7	7369.2
42.5°	6805.1	6902.5	7153.6	7451.9	7381.0	7103.4	6793.2	6746.0	6852.3	7974.7
45°	7236.3	7319.0	7714.8	8172.6	8270.0	8024.9	7661.6	7623.2	7617.3	8860.8
47.5°	7892.0	7980.6	8376.4	8837.1	9138.4	9176.8	8769.2	8727.8	8586.1	10057.0
50°	8713.1	8857.8	9191.6	9729.1	10166.2	10576.8	10461.6	10340.5	10062.9	11448.1
52.5°	9312.7	9489.9	9941.8	10630.0	11400.8	12053.6	12467.1	12467.1	11829.1	12975.1
55°	9472.1	9578.5	10148.5	11143.9	12464.1	14115.2	14980.6	14915.6	13932.1	14581.8
57.5°	8837.1	8975.9	9667.1	10709.7	13022.4	16043.9	17476.4	17491.1	16230.0	16448.5
60°	7088.6	7132.9	7948.1	9342.2	12484.8	17597.5	20884.8	20940.9	18843.9	18111.4
62.5°	4900.0	5041.8	5656.1	6878.9	10343.5	17423.2	24172.1	24449.8	20938.0	18988.6
65°	3225.3	3311.0	3638.8	4383.1	7200.8	15101.7	25194.1	26050.6	22538.8	19038.8
67.5°	2339.2	2354.0	2451.5	2835.4	4327.0	10860.3	23448.5	24656.5	23138.4	18619.4
70°	1890.3	1902.1	1937.6	2182.7	2794.1	6796.2	19124.5	21017.7	21339.7	16631.6
72.5°	1535.9	1550.6	1594.9	1825.3	2303.8	3780.6	13985.2	16292.0	17358.2	12304.6
75°	1208.0	1219.8	1326.2	1553.6	2165.0	2596.2	9277.2	11536.7	11681.4	7192.0
77.5°	827.0	847.7	977.6	1317.3	2038.0	2271.3	5783.1	7389.9	6630.8	2814.8
80°	525.7	555.3	632.1	998.3	1801.7	2167.9	3597.5	4412.7	2903.4	962.9
82.5°	310.1	339.7	416.5	646.8	1414.8	2011.4	2534.2	2761.6	1361.6	493.2
85°	171.3	192.0	251.1	389.9	830.0	1786.9	2029.1	1981.9	779.7	262.9
87.5°	56.1	65.0	91.6	156.5	342.6	841.8	1216.9	1143.0	404.6	121.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P575009  
 CATALOG NUMBER: EPH-VN-03-735-U-SL3

**CANDELA DISTRIBUTION (continued):**

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
7218.6	0°	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6	7218.6
7254.0	2.5°	7212.7	7203.8	7070.9	6970.5	6799.2	6657.4	6601.3	6524.5	6521.5	6465.4
7130.0	5°	7038.4	6946.8	6743.0	6548.1	6243.9	6040.1	5854.0	5724.0	5670.9	5555.7
6926.2	7.5°	6813.9	6692.8	6379.7	6013.5	5656.1	5337.1	5047.7	4758.2	4595.8	4539.7
6719.4	10°	6580.6	6367.9	5904.2	5493.7	4994.5	4504.2	4049.4	3641.8	3420.3	3263.7
6592.4	12.5°	6394.5	6111.0	5520.3	4905.9	4247.3	3591.6	3062.9	2634.6	2383.5	2265.4
6427.0	15°	6184.8	5809.7	5100.8	4324.0	3503.0	2758.6	2241.8	1905.1	1804.6	1748.5
6255.7	17.5°	5963.3	5529.1	4646.0	3751.1	2776.4	2076.4	1742.6	1606.8	1562.4	1538.8
6093.2	20°	5756.5	5278.1	4179.3	3113.1	2173.8	1665.8	1509.3	1438.4	1435.4	1447.3
5948.5	22.5°	5464.1	4950.2	3718.6	2522.4	1736.7	1450.2	1349.8	1332.1	1349.8	1364.6
5800.8	25°	5298.7	4681.4	3204.6	2002.5	1435.4	1287.8	1255.3	1249.4	1275.9	1293.7
5679.7	27.5°	5127.4	4403.8	2726.2	1603.8	1258.2	1172.6	1166.7	1172.6	1199.2	1225.7
5608.9	30°	4994.5	4182.3	2277.2	1340.9	1122.4	1089.9	1084.0	1089.9	1104.6	1107.6
5629.5	32.5°	4885.2	3919.4	1896.2	1163.7	1039.7	1013.1	1019.0	1016.0	1019.0	1021.9
5700.4	35°	4820.3	3762.9	1583.1	1054.4	971.7	951.1	948.1	939.2	942.2	945.1
5868.8	37.5°	4959.1	3686.1	1335.0	977.6	924.5	906.8	900.8	894.9	886.1	886.1
6273.4	40°	5168.8	3644.7	1184.4	927.4	889.0	868.4	850.6	844.7	844.7	847.7
6837.5	42.5°	5585.2	3712.7	1081.0	889.0	844.7	821.1	803.4	806.3	815.2	824.1
7614.3	45°	6187.8	3919.4	1033.8	859.5	818.1	785.7	773.8	770.9	779.7	794.5
8751.5	47.5°	6976.4	4241.3	1016.0	832.9	800.4	756.1	741.3	750.2	762.0	782.7
10192.8	50°	8267.1	4965.0	1030.8	809.3	773.8	741.3	723.6	714.8	723.6	738.4
11926.6	52.5°	9953.6	6279.3	1086.9	797.5	756.1	729.5	700.0	685.2	694.1	705.9
13943.9	55°	11970.9	8075.1	1243.5	782.7	726.6	711.8	679.3	649.8	655.7	655.7
15934.6	57.5°	13748.9	9430.8	1429.5	762.0	708.9	688.2	646.8	611.4	605.5	608.4
16947.7	60°	14546.4	9791.1	1518.1	756.1	708.9	658.6	602.5	567.1	558.2	552.3
17107.2	62.5°	14407.6	9167.9	1338.0	729.5	726.6	635.0	561.2	522.8	511.0	499.2
16439.7	65°	13568.8	8278.9	1054.4	694.1	729.5	620.3	519.8	481.4	460.8	446.0
14874.3	67.5°	12035.9	7067.9	835.9	667.5	700.0	593.7	484.4	440.1	422.4	407.6
11979.7	70°	9416.0	5540.9	726.6	632.1	629.1	528.7	443.0	404.6	378.1	360.3
7962.9	72.5°	6105.1	3503.0	623.2	561.2	543.5	443.0	384.0	360.3	339.7	324.9
3727.4	75°	2764.6	1627.4	502.1	469.6	443.0	354.4	324.9	313.1	295.4	280.6
1281.9	77.5°	992.4	694.1	375.1	369.2	330.8	274.7	262.9	254.0	242.2	227.4
617.3	80°	555.3	440.1	280.6	268.8	230.4	203.8	189.0	189.0	183.1	174.3
372.2	82.5°	351.5	286.5	206.8	180.2	150.6	135.9	130.0	127.0	124.1	112.2
233.3	85°	221.5	194.9	135.9	106.3	88.6	67.9	65.0	62.0	56.1	50.2
91.6	87.5°	100.4	112.2	53.2	32.5	23.6	14.8	8.9	3.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O





<u>180°</u>
7218.6
6450.6
5529.1
4477.6
3195.8
2212.2
1739.7
1527.0
1444.3
1370.5
1290.7
1222.8
1107.6
1024.9
942.2
886.1
850.6
818.1
806.3
773.8
744.3
705.9
652.7
611.4
552.3
502.1
443.0
401.7
360.3
324.9
280.6
227.4
171.3
109.3
50.2
0.0
0.0

F REPORT)