

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P488880

Luminaire Tested: **CLM-24-2-INS-A12125-LD4-1STD-27-120-EDD-90**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P488880  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-115-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/11/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: CLM-24-2-INS-A12125-LD4-1STD-27-120-EDD-90  
Description: 2X2 CLM LED LUMINAIRE WITH A12125 LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1480.6 lumens  
Efficiency: N/A  
Efficacy: 89.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.21 / 1.34  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P488880

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1STD-27-120-EDD-90

### Luminous Intensity Polar Plot





TEST NUMBER: P488880

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1STD-27-120-EDD-90

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	48	75	63	54	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39
7	66	52	44	38	64	51	43	37	50	43	37	49	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	45	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1516	1516	1516
5°	1501	1516	1506
10°	1488	1503	1495
15°	1467	1491	1480
20°	1444	1478	1460
25°	1416	1457	1440
30°	1387	1434	1421
35°	1356	1410	1397
40°	1321	1382	1364
45°	1284	1348	1323
50°	1245	1305	1271
55°	1200	1256	1217
60°	1149	1196	1160
65°	1082	1124	1084
70°	996	1036	985
75°	878	917	864
80°	713	744	705
85°	497	528	516



TEST NUMBER: P488880

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1STD-27-120-EDD-90

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.0	3.6
10°-20°	150.3	10.2
20°-30°	224.2	15.1
30°-40°	265.6	17.9
40°-50°	268.8	18.2
50°-60°	234.7	15.9
60°-70°	171.5	11.6
70°-80°	91.3	6.2
80°-90°	21.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.5	28.9
0°-40°	693.2	46.8
0°-60°	1196.7	80.8
0°-90°	1480.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1480.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	563	563	563	563	563	
5°	556	557	561	562	558	53
15°	527	530	535	538	531	148
25°	477	483	491	492	485	220
35°	413	419	429	432	425	258
45°	337	343	354	355	348	260
55°	256	261	268	264	260	229
65°	170	174	177	173	170	168
75°	84	86	88	85	83	90
85°	16	16	17	17	17	20
90°	0	0	0	0	0	



TEST NUMBER: P488880

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1STD-27-120-EDD-90

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	563.2	563.2	563.2	563.2	563.2
2.5°	558.8	560.6	562.5	563.3	558.7
5°	555.8	556.9	561.1	562.3	557.6
7.5°	551.0	552.6	556.7	557.2	552.7
10°	544.5	547.3	550.0	552.9	547.3
12.5°	536.1	539.9	544.5	545.0	540.8
15°	526.6	530.1	535.1	538.3	531.4
17.5°	516.1	519.5	525.9	526.5	522.3
20°	504.3	508.5	516.2	517.6	510.0
22.5°	490.9	496.6	503.0	504.3	498.7
25°	476.9	482.7	490.7	492.5	485.1
27.5°	462.2	467.8	476.8	478.1	471.8
30°	446.5	451.7	461.6	463.8	457.4
32.5°	430.5	435.8	446.7	448.5	442.3
35°	412.8	419.2	429.2	432.1	425.2
37.5°	394.7	401.0	412.3	415.0	407.4
40°	376.0	382.2	393.3	395.5	388.3
42.5°	356.9	363.1	374.9	375.3	369.3
45°	337.3	343.3	354.3	354.6	347.7
47.5°	317.5	323.5	333.4	332.3	325.7
50°	297.4	303.2	311.8	309.6	303.6
52.5°	276.7	282.2	290.4	286.7	281.2
55°	255.8	260.9	267.7	263.9	259.5
57.5°	234.7	239.9	245.1	241.2	237.5
60°	213.5	218.0	222.3	218.3	215.5
62.5°	191.9	195.8	199.5	195.7	193.0
65°	170.0	173.5	176.6	173.0	170.2
67.5°	148.3	151.3	154.1	150.4	147.5
70°	126.6	129.1	131.7	128.0	125.2
72.5°	105.2	107.4	109.7	106.1	103.7
75°	84.4	86.3	88.2	85.0	83.1
77.5°	64.5	66.1	67.4	65.4	63.5
80°	46.0	47.2	48.0	47.2	45.5
82.5°	29.6	30.5	30.9	30.8	29.7
85°	16.1	16.4	17.1	17.3	16.7
87.5°	6.2	6.6	6.8	7.3	6.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)