

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P488903

Luminaire Tested: **CLM-24-2-INS-A12125-LD4-2LO-20-120-EDD**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P488903
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-115-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-24-2-INS-A12125-LD4-2LO-20-120-EDD
Description: 2X2 CLM LED LUMINAIRE WITH A12125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1858.8 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.21 / 1.34
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 23.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P488903

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-2LO-20-120-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P488903

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-2LO-20-120-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	48	75	63	54	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39
7	66	52	44	38	64	51	43	37	50	43	37	49	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	45	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1903	1903	1903
5°	1885	1903	1891
10°	1868	1887	1877
15°	1842	1872	1858
20°	1813	1856	1834
25°	1778	1829	1808
30°	1742	1801	1784
35°	1702	1770	1754
40°	1658	1735	1713
45°	1612	1693	1661
50°	1563	1639	1596
55°	1506	1577	1529
60°	1442	1502	1456
65°	1359	1412	1360
70°	1251	1301	1237
75°	1101	1151	1084
80°	896	934	885
85°	624	664	648



TEST NUMBER: P488903

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-2LO-20-120-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.6	3.6
10°-20°	188.7	10.2
20°-30°	281.4	15.1
30°-40°	333.5	17.9
40°-50°	337.5	18.2
50°-60°	294.7	15.9
60°-70°	215.4	11.6
70°-80°	114.6	6.2
80°-90°	26.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.7	28.9
0°-40°	870.2	46.8
0°-60°	1502.4	80.8
0°-90°	1858.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1858.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	707	707	707	707	707	
5°	698	699	704	706	700	66
15°	661	666	672	676	667	186
25°	599	606	616	618	609	276
35°	518	526	539	542	534	324
45°	424	431	445	445	436	327
55°	321	328	336	331	326	287
65°	214	218	222	217	214	211
75°	106	108	111	107	104	113
85°	20	21	22	22	21	26
90°	0	0	0	0	0	



TEST NUMBER: P488903

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-2LO-20-120-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	707.0	707.0	707.0	707.0	707.0
2.5°	701.5	703.8	706.1	707.2	701.4
5°	697.8	699.1	704.4	706.0	700.0
7.5°	691.8	693.8	698.8	699.6	693.8
10°	683.5	687.1	690.4	694.1	687.1
12.5°	673.0	677.8	683.5	684.2	678.9
15°	661.1	665.5	671.8	675.9	667.1
17.5°	647.9	652.1	660.2	661.0	655.7
20°	633.1	638.4	648.1	649.8	640.3
22.5°	616.3	623.4	631.5	633.1	626.1
25°	598.7	606.0	616.0	618.3	609.0
27.5°	580.2	587.3	598.6	600.2	592.3
30°	560.5	567.1	579.5	582.2	574.2
32.5°	540.5	547.1	560.8	563.1	555.3
35°	518.2	526.3	538.8	542.5	533.8
37.5°	495.5	503.4	517.6	520.9	511.5
40°	472.0	479.8	493.8	496.6	487.5
42.5°	448.0	455.8	470.7	471.2	463.6
45°	423.5	431.0	444.9	445.2	436.5
47.5°	398.6	406.2	418.6	417.2	408.9
50°	373.4	380.6	391.4	388.6	381.2
52.5°	347.3	354.3	364.6	360.0	353.0
55°	321.1	327.6	336.1	331.3	325.8
57.5°	294.7	301.2	307.8	302.8	298.1
60°	268.0	273.7	279.1	274.1	270.5
62.5°	240.9	245.8	250.5	245.7	242.3
65°	213.5	217.8	221.7	217.2	213.6
67.5°	186.2	189.9	193.4	188.9	185.1
70°	159.0	162.1	165.4	160.7	157.2
72.5°	132.1	134.9	137.8	133.2	130.2
75°	105.9	108.4	110.7	106.7	104.3
77.5°	81.0	83.0	84.6	82.1	79.8
80°	57.8	59.3	60.3	59.2	57.1
82.5°	37.1	38.2	38.7	38.7	37.3
85°	20.2	20.6	21.5	21.7	21.0
87.5°	7.8	8.3	8.5	9.2	8.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)