

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P489779

Luminaire Tested: **CLM-24-4-INS-P12125-LD4-1STD-20-120-EDD**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P489779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P387254)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-24-4-INS-P12125-LD4-1STD-20-120-EDD
Description: 2X4 CLM LED LUMINAIRE WITH P12125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2396.7 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.04 / 1.24
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 33.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P489779

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1STD-20-120-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P489779

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1STD-20-120-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70
3	90	80	72	65	88	78	71	65	75	69	64	73	67	62	70	65	61	59
4	83	71	62	55	81	70	61	55	67	60	54	65	59	54	63	57	53	51
5	76	63	54	48	74	62	54	48	60	53	47	58	52	46	56	51	46	44
6	70	57	48	42	68	56	48	42	54	47	41	53	46	41	51	45	40	38
7	65	52	43	37	64	51	43	37	49	42	37	48	41	36	47	41	36	34
8	61	47	39	33	59	47	39	33	45	38	33	44	37	33	43	37	32	30
9	57	43	35	30	55	43	35	30	42	35	30	41	34	29	40	34	29	27
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1388	1388	1388
5°	1333	1324	1324
10°	1241	1229	1239
15°	1177	1175	1187
20°	1134	1142	1151
25°	1102	1120	1126
30°	1075	1102	1108
35°	1057	1088	1099
40°	1038	1080	1089
45°	1016	1070	1082
50°	994	1056	1070
55°	966	1041	1045
60°	932	1012	1010
65°	883	974	967
70°	825	908	897
75°	728	804	796
80°	591	656	623
85°	411	418	401



TEST NUMBER: P489779

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1STD-20-120-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.2	3.8
10°-20°	238.8	10.0
20°-30°	347.3	14.5
30°-40°	413.3	17.2
40°-50°	429.1	17.9
50°-60°	388.8	16.2
60°-70°	293.3	12.2
70°-80°	159.8	6.7
80°-90°	35.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.3	28.3
0°-40°	1090.5	45.5
0°-60°	1908.4	79.6
0°-90°	2396.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2396.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1032	1032	1032	1032	1032	
5°	987	985	980	980	980	92
15°	845	843	844	849	852	239
25°	742	748	754	760	758	342
35°	643	651	662	672	669	402
45°	534	544	562	568	569	413
55°	412	422	444	447	446	368
65°	277	285	306	305	304	274
75°	140	146	155	156	153	149
85°	27	27	27	27	26	34
90°	0	0	0	0	0	



TEST NUMBER: P489779

CATALOG NUMBER: CLM-24-4-INS-P12125-LD4-1STD-20-120-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1031.8	1031.8	1031.8	1031.8	1031.8
2.5°	1022.8	1021.8	1018.4	1017.1	1016.8
5°	987.0	984.6	980.0	979.5	980.0
7.5°	944.2	941.6	936.9	938.7	941.1
10°	908.1	901.6	899.8	902.4	906.8
12.5°	875.8	870.7	869.1	875.8	878.9
15°	845.1	843.1	843.6	849.3	851.8
17.5°	818.6	817.3	820.7	825.0	826.3
20°	792.0	794.6	797.7	802.4	803.9
22.5°	766.0	770.9	776.1	782.2	780.2
25°	742.0	748.2	754.1	760.3	758.5
27.5°	716.5	723.7	732.0	738.7	736.1
30°	692.0	701.0	709.0	717.3	713.4
32.5°	667.8	676.3	685.8	695.9	691.5
35°	643.3	651.0	662.1	672.2	668.8
37.5°	616.2	625.7	638.4	647.1	644.8
40°	590.9	599.7	614.9	620.6	620.1
42.5°	565.4	572.6	588.6	595.1	594.0
45°	534.2	543.8	562.1	568.3	568.8
47.5°	506.6	514.6	534.2	539.1	540.1
50°	474.9	485.0	504.6	510.5	511.3
52.5°	443.7	454.5	474.7	478.8	479.6
55°	412.0	421.8	443.7	446.8	445.5
57.5°	378.7	390.6	410.7	412.3	413.6
60°	346.2	356.6	376.2	378.2	375.4
62.5°	310.9	321.5	341.6	342.1	339.8
65°	277.4	285.4	305.8	305.3	303.7
67.5°	242.3	252.1	267.1	267.6	266.3
70°	209.6	216.3	230.8	231.0	227.9
72.5°	174.3	181.5	193.1	191.6	190.8
75°	140.0	145.7	154.7	155.7	153.1
77.5°	108.5	112.7	119.4	118.6	115.8
80°	76.3	79.7	84.6	83.5	80.4
82.5°	48.7	50.8	53.9	52.6	51.3
85°	26.6	26.8	27.1	26.8	26.0
87.5°	9.8	10.1	10.1	9.8	9.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)