

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P488732

Luminaire Tested: **CLM-12-4-INS-A19156-LD4-3LO-50-120-EDD-90**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P488732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-115-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-12-4-INS-A19156-LD4-3LO-50-120-EDD-90
Description: 1X4 CLM LED LUMINAIRE WITH A19156 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6471.6 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.21 / 1.34
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 70.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P488732

CATALOG NUMBER: CLM-12-4-INS-A19156-LD4-3LO-50-120-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P488732

CATALOG NUMBER: CLM-12-4-INS-A19156-LD4-3LO-50-120-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	48	75	63	54	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39
7	66	52	44	38	64	51	43	37	50	43	37	49	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	45	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6624	6624	6624
5°	6563	6624	6584
10°	6503	6569	6537
15°	6413	6516	6471
20°	6312	6462	6384
25°	6189	6368	6295
30°	6064	6269	6212
35°	5927	6162	6105
40°	5773	6039	5962
45°	5611	5894	5783
50°	5442	5706	5556
55°	5245	5491	5322
60°	5021	5230	5068
65°	4732	4914	4736
70°	4355	4530	4306
75°	3834	4008	3776
80°	3116	3251	3081
85°	2171	2313	2257



TEST NUMBER: P488732

CATALOG NUMBER: CLM-12-4-INS-A19156-LD4-3LO-50-120-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.8	3.6
10°-20°	657.0	10.2
20°-30°	979.8	15.1
30°-40°	1161.1	17.9
40°-50°	1174.9	18.2
50°-60°	1026.1	15.9
60°-70°	749.8	11.6
70°-80°	399.0	6.2
80°-90°	92.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1868.6	28.9
0°-40°	3029.7	46.8
0°-60°	5230.6	80.8
0°-90°	6471.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6471.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2462	2462	2462	2462	2462	
5°	2430	2434	2452	2458	2437	230
15°	2302	2317	2339	2353	2323	649
25°	2084	2110	2145	2153	2120	960
35°	1804	1832	1876	1889	1858	1128
45°	1474	1501	1549	1550	1520	1137
55°	1118	1140	1170	1153	1134	999
65°	743	758	772	756	744	735
75°	369	377	386	371	363	392
85°	70	72	75	76	73	89
90°	0	0	0	0	0	



TEST NUMBER: P488732

CATALOG NUMBER: CLM-12-4-INS-A19156-LD4-3LO-50-120-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2461.6	2461.6	2461.6	2461.6	2461.6
2.5°	2442.3	2450.3	2458.5	2462.1	2442.1
5°	2429.5	2434.1	2452.3	2458.0	2437.2
7.5°	2408.5	2415.4	2433.1	2435.7	2415.7
10°	2379.8	2392.1	2403.9	2416.7	2392.3
12.5°	2343.1	2359.7	2379.8	2382.1	2363.6
15°	2301.8	2317.2	2339.0	2353.1	2322.6
17.5°	2255.6	2270.5	2298.7	2301.3	2282.8
20°	2204.1	2222.5	2256.4	2262.3	2229.2
22.5°	2145.6	2170.5	2198.7	2204.3	2180.0
25°	2084.3	2110.0	2144.8	2152.8	2120.2
27.5°	2020.2	2044.8	2084.0	2089.7	2062.2
30°	1951.5	1974.5	2017.6	2027.1	1999.2
32.5°	1881.7	1904.8	1952.5	1960.4	1933.2
35°	1804.2	1832.5	1875.8	1888.9	1858.4
37.5°	1725.3	1752.7	1801.9	1813.7	1780.9
40°	1643.4	1670.6	1719.1	1728.8	1697.3
42.5°	1559.8	1587.0	1638.8	1640.4	1614.2
45°	1474.4	1500.6	1548.8	1550.1	1519.6
47.5°	1387.7	1414.2	1457.2	1452.4	1423.6
50°	1300.0	1325.2	1362.9	1353.1	1327.2
52.5°	1209.2	1233.6	1269.3	1253.4	1229.0
55°	1117.9	1140.5	1170.3	1153.3	1134.4
57.5°	1025.9	1048.7	1071.5	1054.3	1037.9
60°	933.0	953.0	971.8	954.3	941.7
62.5°	838.6	855.8	872.0	855.3	843.5
65°	743.2	758.4	771.7	756.3	743.8
67.5°	648.3	661.2	673.5	657.6	644.5
70°	553.5	564.5	575.8	559.4	547.3
72.5°	459.8	469.6	479.6	463.7	453.2
75°	368.8	377.3	385.5	371.4	363.2
77.5°	281.9	289.0	294.7	285.7	277.8
80°	201.1	206.5	209.8	206.2	198.8
82.5°	129.3	133.1	134.9	134.6	129.8
85°	70.3	71.6	74.9	75.7	73.1
87.5°	27.2	29.0	29.8	32.1	29.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)