

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P488849

Luminaire Tested: **CLM-12-4-INS-P12125-LD4-3STD-35-120-EDD**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P488849
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P387254)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-12-4-INS-P12125-LD4-3STD-35-120-EDD
Description: 1X4 CLM LED LUMINAIRE WITH P12125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9392.2 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.04 / 1.24
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 99.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P488849

CATALOG NUMBER: CLM-12-4-INS-P12125-LD4-3STD-35-120-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P488849

CATALOG NUMBER: CLM-12-4-INS-P12125-LD4-3STD-35-120-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84					84			
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70					70			
3	90	80	72	65	88	78	71	65	75	69	64	73	67	62	70	65	61	59					59			
4	83	71	62	55	81	70	61	55	67	60	54	65	59	54	63	57	53	51					51			
5	76	63	54	48	74	62	54	48	60	53	47	58	52	46	56	51	46	44					44			
6	70	57	48	42	68	56	48	42	54	47	41	53	46	41	51	45	40	38					38			
7	65	52	43	37	64	51	43	37	49	42	37	48	41	36	47	41	36	34					34			
8	61	47	39	33	59	47	39	33	45	38	33	44	37	33	43	37	32	30					30			
9	57	43	35	30	55	43	35	30	42	35	30	41	34	29	40	34	29	27					27			
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25					25			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10448	10374	10374
10°	9724	9635	9710
15°	9227	9210	9300
20°	8888	8952	9021
25°	8634	8775	8826
30°	8426	8634	8687
35°	8281	8523	8610
40°	8135	8465	8536
45°	7967	8382	8482
50°	7791	8278	8388
55°	7575	8158	8191
60°	7303	7934	7917
65°	6922	7629	7578
70°	6463	7115	7028
75°	5704	6304	6240
80°	4634	5136	4885
85°	3214	3276	3149



TEST NUMBER: P488849

CATALOG NUMBER: CLM-12-4-INS-P12125-LD4-3STD-35-120-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.3	3.8
10°-20°	935.9	10.0
20°-30°	1360.9	14.5
30°-40°	1619.5	17.2
40°-50°	1681.6	17.9
50°-60°	1523.4	16.2
60°-70°	1149.6	12.2
70°-80°	626.4	6.7
80°-90°	137.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2654.1	28.3
0°-40°	4273.6	45.5
0°-60°	7478.7	79.6
0°-90°	9392.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9392.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4044	4044	4044	4044	4044	
5°	3868	3859	3840	3838	3840	359
15°	3312	3304	3306	3328	3338	935
25°	2908	2932	2955	2980	2972	1340
35°	2521	2551	2595	2634	2621	1576
45°	2094	2131	2203	2227	2229	1618
55°	1614	1653	1739	1751	1746	1442
65°	1087	1118	1198	1196	1190	1075
75°	549	571	606	610	600	584
85°	104	105	106	105	102	131
90°	0	0	0	0	0	



TEST NUMBER: P488849

CATALOG NUMBER: CLM-12-4-INS-P12125-LD4-3STD-35-120-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4043.5	4043.5	4043.5	4043.5	4043.5
2.5°	4008.1	4004.1	3990.9	3985.9	3984.8
5°	3867.7	3858.6	3840.4	3838.4	3840.4
7.5°	3700.0	3689.8	3671.7	3678.7	3687.8
10°	3558.5	3533.3	3526.1	3536.3	3553.4
12.5°	3432.2	3412.0	3405.9	3432.2	3444.4
15°	3311.9	3303.9	3305.9	3328.2	3338.2
17.5°	3207.9	3202.9	3216.0	3233.2	3238.2
20°	3103.8	3114.0	3126.1	3144.3	3150.3
22.5°	3001.8	3021.0	3041.2	3065.4	3057.4
25°	2907.9	2932.1	2955.3	2979.6	2972.5
27.5°	2807.8	2836.1	2868.4	2894.7	2884.6
30°	2711.8	2747.2	2778.5	2810.8	2795.7
32.5°	2616.9	2650.2	2687.6	2727.0	2709.8
35°	2520.9	2551.2	2594.6	2634.1	2620.9
37.5°	2414.8	2452.2	2501.6	2536.0	2527.0
40°	2315.8	2350.1	2409.7	2432.0	2429.9
42.5°	2215.7	2244.1	2306.7	2331.9	2327.9
45°	2093.5	2130.9	2202.6	2226.9	2228.9
47.5°	1985.4	2016.7	2093.5	2112.7	2116.7
50°	1861.1	1900.5	1977.3	2000.5	2003.6
52.5°	1738.8	1781.2	1860.1	1876.2	1879.3
55°	1614.5	1652.9	1738.8	1751.0	1745.9
57.5°	1484.2	1530.7	1609.5	1615.6	1620.6
60°	1356.9	1397.3	1474.1	1482.2	1471.1
62.5°	1218.5	1259.9	1338.8	1340.7	1331.6
65°	1087.1	1118.5	1198.2	1196.3	1190.2
67.5°	949.7	988.1	1046.8	1048.7	1043.7
70°	821.4	847.7	904.3	905.3	893.2
72.5°	683.0	711.3	756.7	750.7	747.7
75°	548.6	570.9	606.3	610.3	600.2
77.5°	425.4	441.5	467.8	464.8	453.6
80°	299.0	312.2	331.4	327.4	315.2
82.5°	190.9	199.1	211.2	206.1	201.1
85°	104.1	105.0	106.1	105.0	102.0
87.5°	38.4	39.4	39.4	38.4	35.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)