

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P490188

Luminaire Tested: **CLP-12-4-INS-A12125-LD4-2HI-27-120-EDD-90**

Issue Date: 3/12/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P490188
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-115-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/12/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLP-12-4-INS-A12125-LD4-2HI-27-120-EDD-90
Description: 1X4 CLP LED LUMINAIRE WITH A12125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6824.6 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.21 / 1.34
Luminous Opening: Rectangular (W 1' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 86.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P490188

CATALOG NUMBER: CLP-12-4-INS-A12125-LD4-2HI-27-120-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P490188

CATALOG NUMBER: CLP-12-4-INS-A12125-LD4-2HI-27-120-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	48	75	63	54	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39
7	66	52	44	38	64	51	43	37	50	43	37	49	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	45	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6985	6985	6985
5°	6921	6986	6943
10°	6857	6927	6894
15°	6762	6872	6823
20°	6656	6814	6732
25°	6526	6716	6639
30°	6394	6611	6551
35°	6251	6498	6438
40°	6088	6368	6288
45°	5917	6216	6099
50°	5739	6017	5859
55°	5531	5790	5612
60°	5295	5515	5345
65°	4991	5182	4994
70°	4592	4777	4541
75°	4043	4226	3982
80°	3285	3428	3248
85°	2288	2439	2381



TEST NUMBER: P490188

CATALOG NUMBER: CLP-12-4-INS-A12125-LD4-2HI-27-120-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.5	3.6
10°-20°	692.8	10.2
20°-30°	1033.3	15.1
30°-40°	1224.4	17.9
40°-50°	1238.9	18.2
50°-60°	1082.0	15.9
60°-70°	790.7	11.6
70°-80°	420.7	6.2
80°-90°	97.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	1970.5	28.9
0°-40°	3195.0	46.8
0°-60°	5515.9	80.8
0°-90°	6824.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6824.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2596	2596	2596	2596	2596	
5°	2562	2567	2586	2592	2570	243
15°	2427	2444	2467	2481	2449	684
25°	2198	2225	2262	2270	2236	1013
35°	1903	1932	1978	1992	1960	1190
45°	1555	1582	1633	1635	1602	1200
55°	1179	1203	1234	1216	1196	1054
65°	784	800	814	798	784	776
75°	389	398	406	392	383	413
85°	74	76	79	80	77	94
90°	0	0	0	0	0	



TEST NUMBER: P490188

CATALOG NUMBER: CLP-12-4-INS-A12125-LD4-2HI-27-120-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2595.8	2595.8	2595.8	2595.8	2595.8
2.5°	2575.6	2583.9	2592.6	2596.4	2575.3
5°	2562.0	2566.9	2586.1	2592.0	2570.1
7.5°	2539.9	2547.2	2565.8	2568.5	2547.4
10°	2509.6	2522.5	2535.0	2548.5	2522.8
12.5°	2470.9	2488.5	2509.6	2512.0	2492.5
15°	2427.3	2443.6	2466.6	2481.4	2449.2
17.5°	2378.7	2394.3	2424.1	2426.8	2407.3
20°	2324.3	2343.8	2379.5	2385.7	2350.8
22.5°	2262.6	2288.9	2318.6	2324.6	2298.9
25°	2198.0	2225.0	2261.8	2270.2	2235.9
27.5°	2130.4	2156.3	2197.7	2203.7	2174.7
30°	2057.9	2082.2	2127.7	2137.7	2108.2
32.5°	1984.3	2008.7	2059.0	2067.4	2038.7
35°	1902.7	1932.4	1978.1	1991.9	1959.7
37.5°	1819.4	1848.3	1900.2	1912.7	1878.0
40°	1733.1	1761.7	1812.9	1823.1	1789.9
42.5°	1644.9	1673.6	1728.2	1729.8	1702.2
45°	1554.9	1582.4	1633.3	1634.6	1602.5
47.5°	1463.4	1491.3	1536.7	1531.6	1501.3
50°	1370.9	1397.4	1437.2	1426.9	1399.6
52.5°	1275.2	1300.9	1338.5	1321.7	1296.0
55°	1178.9	1202.7	1234.1	1216.2	1196.2
57.5°	1081.8	1105.9	1130.0	1111.8	1094.5
60°	983.9	1005.0	1024.8	1006.4	993.1
62.5°	884.4	902.5	919.5	902.0	889.5
65°	783.8	799.7	813.8	797.6	784.3
67.5°	683.7	697.2	710.2	693.4	679.7
70°	583.6	595.3	607.2	589.9	577.2
72.5°	484.9	495.2	505.8	489.0	477.9
75°	388.9	397.8	406.5	391.6	383.0
77.5°	297.2	304.8	310.8	301.3	292.9
80°	212.0	217.7	221.2	217.4	209.6
82.5°	136.3	140.4	142.3	142.0	136.9
85°	74.1	75.5	79.0	79.8	77.1
87.5°	28.7	30.6	31.4	33.8	31.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)