

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P488871

Luminaire Tested: **CLM-24-2-INS-A12125-LD4-1LO-30-120-EDD**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P488871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-115-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-24-2-INS-A12125-LD4-1LO-30-120-EDD
Description: 2X2 CLM LED LUMINAIRE WITH A12125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1302.2 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.21 / 1.34
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P488871

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1LO-30-120-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P488871

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1LO-30-120-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	48	75	63	54	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39
7	66	52	44	38	64	51	43	37	50	43	37	49	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	45	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1333	1333	1333
5°	1321	1333	1325
10°	1308	1322	1315
15°	1290	1311	1302
20°	1270	1300	1285
25°	1245	1281	1267
30°	1220	1262	1250
35°	1192	1240	1228
40°	1162	1215	1200
45°	1129	1186	1164
50°	1095	1148	1118
55°	1055	1105	1071
60°	1010	1052	1020
65°	953	989	953
70°	876	912	866
75°	771	807	760
80°	628	654	620
85°	435	466	454



TEST NUMBER: P488871

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1LO-30-120-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.6	3.6
10°-20°	132.2	10.2
20°-30°	197.2	15.1
30°-40°	233.6	17.9
40°-50°	236.4	18.2
50°-60°	206.5	15.9
60°-70°	150.9	11.6
70°-80°	80.3	6.2
80°-90°	18.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.0	28.9
0°-40°	609.6	46.8
0°-60°	1052.5	80.8
0°-90°	1302.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1302.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	495	495	495	495	495	
5°	489	490	494	495	490	46
15°	463	466	471	474	467	131
25°	419	425	432	433	427	193
35°	363	369	377	380	374	227
45°	297	302	312	312	306	229
55°	225	230	236	232	228	201
65°	150	153	155	152	150	148
75°	74	76	78	75	73	79
85°	14	14	15	15	15	18
90°	0	0	0	0	0	



TEST NUMBER: P488871

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1LO-30-120-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	495.3	495.3	495.3	495.3	495.3
2.5°	491.4	493.0	494.7	495.4	491.4
5°	488.9	489.8	493.5	494.6	490.4
7.5°	484.6	486.0	489.6	490.1	486.1
10°	478.8	481.3	483.7	486.3	481.4
12.5°	471.5	474.8	478.8	479.3	475.6
15°	463.2	466.3	470.6	473.5	467.3
17.5°	453.9	456.9	462.5	463.1	459.3
20°	443.5	447.2	454.0	455.2	448.6
22.5°	431.7	436.7	442.4	443.6	438.6
25°	419.4	424.6	431.6	433.2	426.6
27.5°	406.5	411.5	419.3	420.5	415.0
30°	392.7	397.3	406.0	407.9	402.3
32.5°	378.6	383.3	392.9	394.5	389.0
35°	363.0	368.7	377.4	380.1	373.9
37.5°	347.2	352.7	362.6	365.0	358.3
40°	330.7	336.2	345.9	347.9	341.5
42.5°	313.9	319.3	329.8	330.1	324.8
45°	296.7	301.9	311.6	311.9	305.8
47.5°	279.2	284.6	293.2	292.2	286.5
50°	261.6	266.6	274.2	272.3	267.1
52.5°	243.3	248.2	255.4	252.2	247.3
55°	224.9	229.5	235.5	232.1	228.3
57.5°	206.4	211.0	215.6	212.2	208.8
60°	187.7	191.8	195.5	192.0	189.5
62.5°	168.8	172.2	175.5	172.1	169.7
65°	149.6	152.6	155.3	152.2	149.7
67.5°	130.5	133.0	135.5	132.3	129.7
70°	111.4	113.6	115.9	112.6	110.1
72.5°	92.5	94.5	96.5	93.3	91.2
75°	74.2	75.9	77.6	74.7	73.1
77.5°	56.7	58.2	59.3	57.5	55.9
80°	40.5	41.5	42.2	41.5	40.0
82.5°	26.0	26.8	27.1	27.1	26.1
85°	14.1	14.4	15.1	15.2	14.7
87.5°	5.5	5.8	6.0	6.5	5.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)