

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P488877

Luminaire Tested: **CLM-24-2-INS-A12125-LD4-1LO-50-120-EDD**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P488877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-115-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-24-2-INS-A12125-LD4-1LO-50-120-EDD
Description: 2X2 CLM LED LUMINAIRE WITH A12125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1403.8 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.21 / 1.34
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P488877

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1LO-50-120-EDD

Luminous Intensity Polar Plot





TEST NUMBER: P488877

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1LO-50-120-EDD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	48	75	63	54	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39
7	66	52	44	38	64	51	43	37	50	43	37	49	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	45	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1437	1437	1437
5°	1424	1437	1428
10°	1411	1425	1418
15°	1391	1414	1404
20°	1369	1401	1385
25°	1342	1382	1366
30°	1315	1360	1348
35°	1286	1337	1324
40°	1252	1310	1293
45°	1217	1279	1254
50°	1181	1238	1205
55°	1138	1191	1155
60°	1089	1135	1100
65°	1026	1066	1027
70°	945	983	934
75°	832	869	819
80°	676	705	668
85°	469	500	491



TEST NUMBER: P488877

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1LO-50-120-EDD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	3.6
10°-20°	142.5	10.2
20°-30°	212.5	15.1
30°-40°	251.9	17.9
40°-50°	254.8	18.2
50°-60°	222.6	15.9
60°-70°	162.6	11.6
70°-80°	86.5	6.2
80°-90°	20.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.3	28.9
0°-40°	657.2	46.8
0°-60°	1134.6	80.8
0°-90°	1403.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1403.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	534	534	534	534	534	
5°	527	528	532	533	529	50
15°	499	503	507	510	504	141
25°	452	458	465	467	460	208
35°	391	398	407	410	403	245
45°	320	326	336	336	330	247
55°	242	247	254	250	246	217
65°	161	164	167	164	161	160
75°	80	82	84	81	79	85
85°	15	16	16	16	16	19
90°	0	0	0	0	0	



TEST NUMBER: P488877

CATALOG NUMBER: CLM-24-2-INS-A12125-LD4-1LO-50-120-EDD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	534.0	534.0	534.0	534.0	534.0
2.5°	529.8	531.5	533.3	534.1	529.7
5°	527.0	528.0	532.0	533.2	528.7
7.5°	522.4	523.9	527.8	528.3	524.0
10°	516.2	518.9	521.4	524.2	518.9
12.5°	508.3	511.9	516.2	516.7	512.7
15°	499.3	502.6	507.4	510.4	503.8
17.5°	489.3	492.5	498.6	499.2	495.2
20°	478.1	482.1	489.4	490.7	483.6
22.5°	465.4	470.8	476.9	478.2	472.9
25°	452.1	457.7	465.3	467.0	459.9
27.5°	438.2	443.6	452.1	453.3	447.3
30°	423.3	428.3	437.7	439.7	433.7
32.5°	408.2	413.2	423.5	425.3	419.4
35°	391.4	397.5	406.9	409.7	403.1
37.5°	374.2	380.2	390.9	393.4	386.3
40°	356.5	362.4	372.9	375.0	368.2
42.5°	338.4	344.3	355.5	355.8	350.1
45°	319.8	325.5	336.0	336.2	329.6
47.5°	301.0	306.8	316.1	315.0	308.8
50°	282.0	287.5	295.6	293.5	287.9
52.5°	262.3	267.6	275.3	271.9	266.6
55°	242.5	247.4	253.8	250.2	246.1
57.5°	222.5	227.5	232.4	228.7	225.1
60°	202.4	206.7	210.8	207.0	204.3
62.5°	181.9	185.6	189.1	185.5	183.0
65°	161.2	164.5	167.4	164.1	161.3
67.5°	140.6	143.4	146.1	142.6	139.8
70°	120.1	122.4	124.9	121.3	118.7
72.5°	99.7	101.9	104.0	100.6	98.3
75°	80.0	81.8	83.6	80.6	78.8
77.5°	61.1	62.7	63.9	62.0	60.2
80°	43.6	44.8	45.5	44.7	43.1
82.5°	28.0	28.9	29.3	29.2	28.1
85°	15.2	15.5	16.2	16.4	15.9
87.5°	5.9	6.3	6.5	7.0	6.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)