

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P489124

Luminaire Tested: **CLM-24-2-INS-A19156-LD4-3LO-35-120-EDD-90**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P489124
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-115-8)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-24-2-INS-A19156-LD4-3LO-35-120-EDD-90
Description: 2X2 CLM LED LUMINAIRE WITH A19156 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3410.9 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.21 / 1.34
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 35.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P489124

CATALOG NUMBER: CLM-24-2-INS-A19156-LD4-3LO-35-120-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P489124

CATALOG NUMBER: CLM-24-2-INS-A19156-LD4-3LO-35-120-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	48	75	63	54	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39
7	66	52	44	38	64	51	43	37	50	43	37	49	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	45	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3491	3491	3491
5°	3459	3491	3470
10°	3427	3462	3445
15°	3380	3434	3410
20°	3327	3405	3365
25°	3262	3356	3318
30°	3196	3304	3274
35°	3124	3248	3218
40°	3043	3183	3143
45°	2957	3107	3048
50°	2869	3007	2928
55°	2764	2894	2805
60°	2647	2757	2672
65°	2494	2590	2496
70°	2295	2388	2270
75°	2021	2113	1990
80°	1643	1714	1624
85°	1142	1220	1189



TEST NUMBER: P489124

CATALOG NUMBER: CLM-24-2-INS-A19156-LD4-3LO-35-120-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	3.6
10°-20°	346.3	10.2
20°-30°	516.4	15.1
30°-40°	612.0	17.9
40°-50°	619.2	18.2
50°-60°	540.8	15.9
60°-70°	395.2	11.6
70°-80°	210.3	6.2
80°-90°	48.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	984.9	28.9
0°-40°	1596.8	46.8
0°-60°	2756.8	80.8
0°-90°	3410.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3410.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1297	1297	1297	1297	1297	
5°	1280	1283	1292	1296	1284	121
15°	1213	1221	1233	1240	1224	342
25°	1098	1112	1130	1135	1118	506
35°	951	966	989	996	980	595
45°	777	791	816	817	801	600
55°	589	601	617	608	598	527
65°	392	400	407	399	392	388
75°	194	199	203	196	191	207
85°	37	38	40	40	38	47
90°	0	0	0	0	0	



TEST NUMBER: P489124

CATALOG NUMBER: CLM-24-2-INS-A19156-LD4-3LO-35-120-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1297.4	1297.4	1297.4	1297.4	1297.4
2.5°	1287.2	1291.4	1295.8	1297.7	1287.1
5°	1280.5	1282.9	1292.5	1295.5	1284.5
7.5°	1269.4	1273.1	1282.4	1283.7	1273.2
10°	1254.3	1260.8	1267.0	1273.7	1260.9
12.5°	1234.9	1243.7	1254.3	1255.5	1245.7
15°	1213.2	1221.3	1232.8	1240.2	1224.1
17.5°	1188.8	1196.7	1211.6	1212.9	1203.2
20°	1161.7	1171.4	1189.2	1192.4	1174.9
22.5°	1130.9	1144.0	1158.8	1161.8	1149.0
25°	1098.5	1112.1	1130.4	1134.6	1117.5
27.5°	1064.8	1077.7	1098.4	1101.4	1086.9
30°	1028.5	1040.7	1063.4	1068.4	1053.7
32.5°	991.8	1003.9	1029.1	1033.3	1018.9
35°	950.9	965.8	988.7	995.5	979.5
37.5°	909.3	923.8	949.7	955.9	938.6
40°	866.2	880.5	906.1	911.2	894.6
42.5°	822.1	836.4	863.8	864.6	850.8
45°	777.1	790.9	816.3	817.0	800.9
47.5°	731.4	745.3	768.0	765.5	750.3
50°	685.2	698.4	718.3	713.2	699.5
52.5°	637.3	650.2	669.0	660.6	647.7
55°	589.2	601.1	616.8	607.9	597.9
57.5°	540.7	552.7	564.8	555.7	547.0
60°	491.8	502.3	512.2	503.0	496.4
62.5°	442.0	451.1	459.6	450.8	444.6
65°	391.7	399.7	406.7	398.6	392.0
67.5°	341.7	348.5	355.0	346.6	339.7
70°	291.7	297.5	303.5	294.8	288.5
72.5°	242.4	247.5	252.8	244.4	238.8
75°	194.4	198.8	203.2	195.7	191.4
77.5°	148.6	152.3	155.3	150.6	146.4
80°	106.0	108.8	110.6	108.7	104.8
82.5°	68.1	70.2	71.1	71.0	68.4
85°	37.0	37.7	39.5	39.9	38.5
87.5°	14.3	15.3	15.7	16.9	15.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)