

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P489256

Luminaire Tested: **CLM-24-2-INS-P12125-LD4-2HI-35-120-EDD-90**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P489256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P387254)
Test Lab: INNOVATION CENTER
Issue Date: 3/11/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: CLM-24-2-INS-P12125-LD4-2HI-35-120-EDD-90
Description: 2X2 CLM LED LUMINAIRE WITH P12125 LENS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3825.9 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.04 / 1.24
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 43.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P489256

CATALOG NUMBER: CLM-24-2-INS-P12125-LD4-2HI-35-120-EDD-90

Luminous Intensity Polar Plot





TEST NUMBER: P489256

CATALOG NUMBER: CLM-24-2-INS-P12125-LD4-2HI-35-120-EDD-90

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70
3	90	80	72	65	88	78	71	65	75	69	64	73	67	62	70	65	61	59
4	83	71	62	55	81	70	61	55	67	60	54	65	59	54	63	57	53	51
5	76	63	54	48	74	62	54	48	60	53	47	58	52	46	56	51	46	44
6	70	57	48	42	68	56	48	42	54	47	41	53	46	41	51	45	40	38
7	65	52	43	37	64	51	43	37	49	42	37	48	41	36	47	41	36	34
8	61	47	39	33	59	47	39	33	45	38	33	44	37	33	43	37	32	30
9	57	43	35	30	55	43	35	30	42	35	30	41	34	29	40	34	29	27
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4432	4432	4432
5°	4256	4226	4226
10°	3961	3925	3955
15°	3758	3752	3788
20°	3621	3647	3675
25°	3517	3575	3595
30°	3432	3517	3539
35°	3373	3472	3507
40°	3314	3448	3477
45°	3245	3414	3455
50°	3174	3372	3417
55°	3086	3323	3337
60°	2975	3232	3225
65°	2819	3108	3087
70°	2633	2899	2862
75°	2324	2568	2542
80°	1888	2092	1990
85°	1309	1334	1284



TEST NUMBER: P489256

CATALOG NUMBER: CLM-24-2-INS-P12125-LD4-2HI-35-120-EDD-90

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.5	3.8
10°-20°	381.2	10.0
20°-30°	554.4	14.5
30°-40°	659.7	17.2
40°-50°	685.0	17.9
50°-60°	620.6	16.2
60°-70°	468.3	12.2
70°-80°	255.1	6.7
80°-90°	56.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1081.2	28.3
0°-40°	1740.9	45.5
0°-60°	3046.4	79.6
0°-90°	3825.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3825.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1647	1647	1647	1647	1647	
5°	1576	1572	1564	1564	1564	146
15°	1349	1346	1347	1356	1360	381
25°	1184	1194	1204	1214	1211	546
35°	1027	1039	1057	1073	1068	642
45°	853	868	897	907	908	659
55°	658	673	708	713	711	587
65°	443	456	488	487	485	438
75°	224	232	247	249	244	238
85°	42	43	43	43	42	53
90°	0	0	0	0	0	



TEST NUMBER: P489256

CATALOG NUMBER: CLM-24-2-INS-P12125-LD4-2HI-35-120-EDD-90

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1647.1	1647.1	1647.1	1647.1	1647.1
2.5°	1632.7	1631.1	1625.7	1623.6	1623.2
5°	1575.5	1571.8	1564.4	1563.6	1564.4
7.5°	1507.2	1503.0	1495.7	1498.5	1502.2
10°	1449.6	1439.3	1436.4	1440.5	1447.5
12.5°	1398.1	1389.9	1387.4	1398.1	1403.1
15°	1349.1	1345.8	1346.7	1355.7	1359.8
17.5°	1306.7	1304.7	1310.0	1317.0	1319.1
20°	1264.3	1268.5	1273.4	1280.8	1283.3
22.5°	1222.8	1230.6	1238.8	1248.7	1245.4
25°	1184.5	1194.4	1203.9	1213.7	1210.9
27.5°	1143.8	1155.3	1168.5	1179.2	1175.0
30°	1104.6	1119.1	1131.8	1145.0	1138.8
32.5°	1066.0	1079.6	1094.8	1110.8	1103.8
35°	1026.9	1039.2	1056.9	1073.0	1067.6
37.5°	983.7	998.9	1019.0	1033.0	1029.4
40°	943.3	957.3	981.6	990.7	989.8
42.5°	902.6	914.1	939.6	949.9	948.3
45°	852.8	868.0	897.2	907.1	907.9
47.5°	808.7	821.5	852.8	860.6	862.2
50°	758.1	774.2	805.5	814.9	816.2
52.5°	708.3	725.6	757.7	764.3	765.5
55°	657.7	673.3	708.3	713.3	711.2
57.5°	604.6	623.5	655.6	658.1	660.2
60°	552.7	569.2	600.5	603.8	599.3
62.5°	496.4	513.2	545.3	546.1	542.4
65°	442.8	455.6	488.1	487.3	484.8
67.5°	386.9	402.5	426.4	427.2	425.2
70°	334.6	345.3	368.4	368.8	363.8
72.5°	278.2	289.7	308.2	305.8	304.6
75°	223.5	232.5	247.0	248.6	244.5
77.5°	173.3	179.9	190.6	189.3	184.8
80°	121.8	127.2	135.0	133.4	128.4
82.5°	77.8	81.1	86.0	84.0	81.9
85°	42.4	42.8	43.2	42.8	41.6
87.5°	15.6	16.1	16.1	15.6	14.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)