

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P489274

Luminaire Tested: **CLM-24-2-INS-P12125-LD4-2STD-20-120-EDD-90**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P489274  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P387254)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/11/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: CLM-24-2-INS-P12125-LD4-2STD-20-120-EDD-90  
Description: 2X2 CLM LED LUMINAIRE WITH P12125 LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2005.4 lumens  
Efficiency: N/A  
Efficacy: 60.2 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.04 / 1.23  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P489274

CATALOG NUMBER: CLM-24-2-INS-P12125-LD4-2STD-20-120-EDD-90

### Luminous Intensity Polar Plot





TEST NUMBER: P489274

CATALOG NUMBER: CLM-24-2-INS-P12125-LD4-2STD-20-120-EDD-90

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	72	70
3	90	80	72	65	88	78	71	65	75	69	64	73	67	62	70	65	61	59
4	83	71	62	55	81	70	61	55	67	60	54	65	59	54	63	57	53	51
5	76	63	54	48	74	62	54	48	60	53	47	58	52	46	56	51	46	44
6	70	57	48	42	68	56	48	42	54	47	41	53	46	41	51	45	40	38
7	65	52	43	37	64	51	43	37	49	42	37	48	41	36	47	41	36	34
8	61	47	39	33	59	47	39	33	45	38	33	44	37	33	43	37	32	30
9	57	43	35	30	55	43	35	30	42	35	30	41	34	29	40	34	29	27
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2323	2323	2323
5°	2231	2215	2215
10°	2076	2057	2073
15°	1970	1967	1986
20°	1898	1912	1926
25°	1844	1874	1885
30°	1799	1844	1855
35°	1768	1820	1838
40°	1737	1807	1822
45°	1701	1790	1811
50°	1664	1768	1791
55°	1617	1742	1749
60°	1559	1694	1690
65°	1478	1629	1618
70°	1380	1519	1500
75°	1218	1345	1332
80°	990	1097	1043
85°	685	698	673



TEST NUMBER: P489274

CATALOG NUMBER: CLM-24-2-INS-P12125-LD4-2STD-20-120-EDD-90

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.3	3.8
10°-20°	199.8	10.0
20°-30°	290.6	14.5
30°-40°	345.8	17.2
40°-50°	359.1	17.9
50°-60°	325.3	16.2
60°-70°	245.4	12.2
70°-80°	133.7	6.7
80°-90°	29.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	566.7	28.3
0°-40°	912.5	45.5
0°-60°	1596.8	79.6
0°-90°	2005.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2005.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	863	863	863	863	863	
5°	826	824	820	820	820	77
15°	707	705	706	711	713	200
25°	621	626	631	636	635	286
35°	538	545	554	562	560	336
45°	447	455	470	476	476	346
55°	345	353	371	374	373	308
65°	232	239	256	255	254	229
75°	117	122	129	130	128	125
85°	22	22	23	22	22	28
90°	0	0	0	0	0	



TEST NUMBER: P489274

CATALOG NUMBER: CLM-24-2-INS-P12125-LD4-2STD-20-120-EDD-90

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	863.4	863.4	863.4	863.4	863.4
2.5°	855.8	854.9	852.1	851.1	850.8
5°	825.8	823.9	820.0	819.6	820.0
7.5°	790.0	787.8	784.0	785.5	787.4
10°	759.8	754.4	752.9	755.1	758.7
12.5°	732.8	728.5	727.2	732.8	735.4
15°	707.2	705.4	705.9	710.6	712.8
17.5°	684.9	683.9	686.7	690.3	691.4
20°	662.7	664.9	667.5	671.4	672.6
22.5°	640.9	645.0	649.4	654.5	652.8
25°	620.9	626.0	631.0	636.2	634.7
27.5°	599.5	605.5	612.5	618.1	615.9
30°	579.0	586.6	593.3	600.2	596.9
32.5°	558.7	565.9	573.8	582.3	578.6
35°	538.2	544.7	554.0	562.4	559.6
37.5°	515.6	523.6	534.1	541.5	539.5
40°	494.5	501.8	514.5	519.3	518.8
42.5°	473.1	479.1	492.5	497.9	497.0
45°	447.0	455.0	470.3	475.5	475.9
47.5°	423.9	430.6	447.0	451.1	452.0
50°	397.4	405.8	422.2	427.1	427.8
52.5°	371.3	380.3	397.2	400.6	401.3
55°	344.7	352.9	371.3	373.9	372.8
57.5°	316.9	326.8	343.7	345.0	346.0
60°	289.7	298.4	314.7	316.5	314.1
62.5°	260.2	269.0	285.8	286.3	284.3
65°	232.1	238.8	255.8	255.4	254.1
67.5°	202.8	211.0	223.5	223.9	222.9
70°	175.4	181.0	193.1	193.3	190.7
72.5°	145.8	151.9	161.6	160.3	159.6
75°	117.1	121.9	129.4	130.3	128.1
77.5°	90.8	94.3	99.9	99.2	96.9
80°	63.9	66.7	70.8	69.9	67.3
82.5°	40.8	42.5	45.1	44.0	42.9
85°	22.2	22.4	22.6	22.4	21.8
87.5°	8.2	8.4	8.4	8.2	7.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)