

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P489474

Luminaire Tested: **CLM-24-4-INS-A12125-LD4-3HI-40-120-EDD-90**

Issue Date: 3/11/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P489474  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-115-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/11/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: CLM-24-4-INS-A12125-LD4-3HI-40-120-EDD-90  
Description: 2X4 CLM LED LUMINAIRE WITH A12125 LENS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12848.1 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.21 / 1.34  
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 129.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P489474

CATALOG NUMBER: CLM-24-4-INS-A12125-LD4-3HI-40-120-EDD-90

### Luminous Intensity Polar Plot





TEST NUMBER: P489474

CATALOG NUMBER: CLM-24-4-INS-A12125-LD4-3HI-40-120-EDD-90

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	54	51
5	77	64	55	48	75	63	54	48	61	53	48	59	52	47	57	51	47	45
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39
7	66	52	44	38	64	51	43	37	50	43	37	49	42	37	47	41	37	35
8	61	48	39	34	60	47	39	33	46	38	33	45	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	27	52	40	32	27	39	32	27	38	32	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6575	6575	6575
5°	6514	6576	6535
10°	6455	6520	6489
15°	6366	6468	6423
20°	6265	6414	6337
25°	6143	6322	6249
30°	6019	6223	6166
35°	5884	6117	6060
40°	5731	5994	5919
45°	5570	5851	5740
50°	5403	5664	5515
55°	5206	5450	5283
60°	4984	5191	5031
65°	4698	4878	4701
70°	4323	4497	4275
75°	3806	3978	3748
80°	3093	3227	3058
85°	2154	2296	2240



TEST NUMBER: P489474

CATALOG NUMBER: CLM-24-4-INS-A12125-LD4-3HI-40-120-EDD-90

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	460.3	3.6
10°-20°	1304.3	10.2
20°-30°	1945.3	15.1
30°-40°	2305.1	17.9
40°-50°	2332.4	18.2
50°-60°	2037.1	15.9
60°-70°	1488.6	11.6
70°-80°	792.1	6.2
80°-90°	183.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3709.8	28.9
0°-40°	6014.9	46.8
0°-60°	10384.4	80.8
0°-90°	12848.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12848.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4887	4887	4887	4887	4887	
5°	4823	4832	4869	4880	4839	457
15°	4570	4600	4644	4672	4611	1288
25°	4138	4189	4258	4274	4209	1906
35°	3582	3638	3724	3750	3689	2240
45°	2927	2979	3075	3077	3017	2258
55°	2219	2264	2323	2290	2252	1984
65°	1476	1506	1532	1502	1477	1460
75°	732	749	765	737	721	778
85°	140	142	149	150	145	177
90°	0	0	0	0	0	



TEST NUMBER: P489474

CATALOG NUMBER: CLM-24-4-INS-A12125-LD4-3HI-40-120-EDD-90

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4887.0	4887.0	4887.0	4887.0	4887.0
2.5°	4848.8	4864.6	4880.9	4888.0	4848.3
5°	4823.3	4832.5	4868.6	4879.8	4838.6
7.5°	4781.6	4795.3	4830.4	4835.5	4795.8
10°	4724.5	4749.0	4772.4	4797.9	4749.5
12.5°	4651.7	4684.8	4724.5	4729.1	4692.5
15°	4569.8	4600.3	4643.6	4671.6	4611.0
17.5°	4478.1	4507.6	4563.6	4568.7	4532.1
20°	4375.8	4412.4	4479.6	4491.3	4425.7
22.5°	4259.7	4309.1	4365.1	4376.3	4327.9
25°	4138.0	4188.9	4258.1	4273.9	4209.3
27.5°	4010.7	4059.6	4137.5	4148.7	4094.2
30°	3874.2	3920.1	4005.6	4024.4	3968.9
32.5°	3735.7	3781.6	3876.3	3892.1	3838.1
35°	3582.0	3638.0	3724.0	3750.0	3689.4
37.5°	3425.1	3479.6	3577.4	3600.8	3535.6
40°	3262.7	3316.7	3412.9	3432.3	3369.7
42.5°	3096.7	3150.7	3253.6	3256.6	3204.7
45°	2927.2	2979.1	3074.8	3077.4	3016.8
47.5°	2755.1	2807.5	2893.1	2883.4	2826.4
50°	2581.0	2630.9	2705.7	2686.4	2634.9
52.5°	2400.7	2449.1	2519.9	2488.3	2439.9
55°	2219.4	2264.3	2323.3	2289.7	2252.0
57.5°	2036.7	2082.0	2127.3	2093.2	2060.6
60°	1852.3	1892.1	1929.2	1894.6	1869.7
62.5°	1665.0	1699.1	1731.2	1698.1	1674.6
65°	1475.6	1505.6	1532.1	1501.5	1476.6
67.5°	1287.2	1312.6	1337.1	1305.5	1279.5
70°	1098.8	1120.7	1143.1	1110.5	1086.6
72.5°	912.9	932.3	952.1	920.6	899.7
75°	732.2	749.0	765.3	737.3	721.0
77.5°	559.6	573.8	585.0	567.2	551.4
80°	399.2	409.9	416.5	409.4	394.6
82.5°	256.6	264.3	267.8	267.3	257.6
85°	139.5	142.1	148.7	150.2	145.1
87.5°	54.0	57.5	59.1	63.6	58.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)